

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013277

Luminaire Tested: S124RDIP-B1195D365UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013277
REPORT IS A COMBINATION OF REPORTS P999111 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D365UB2750-4F0-XX-W2A-F_3000K
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6301.0 lumens
Efficiency: N/A
Efficacy: 89.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013277

CATALOG NUMBER: S124RDIP-B1195D365UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013277

CATALOG NUMBER: S124RDIP-B1195D365UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	81	81	81
1	104	100	96	92	99	95	92	89	87	84	82	79	77	75	72	70	69
2	95	88	82	76	91	84	78	74	77	72	68	70	67	63	64	61	59
3	87	78	70	64	83	74	67	62	68	63	58	62	58	54	57	53	50
4	80	69	61	55	76	66	59	53	61	55	50	56	51	47	51	47	44
5	74	62	53	47	70	59	52	46	55	48	43	50	45	41	46	42	38
6	68	56	47	41	65	54	46	40	50	43	38	46	40	36	42	38	34
7	63	51	42	37	60	49	41	36	45	39	34	42	36	32	39	34	30
8	59	46	38	33	56	45	37	32	41	35	30	38	33	29	36	31	27
9	55	42	35	29	52	41	34	29	38	32	27	35	30	26	33	28	25
10	52	39	32	27	49	38	31	26	35	29	25	33	28	24	31	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17042	17042	17042
5°	17044	16536	16538
10°	16899	16014	15824
15°	16667	15365	14981
20°	16362	14624	14021
25°	15983	13825	13083
30°	15611	13009	12029
35°	15202	12183	11000
40°	14716	11293	9942
45°	14259	10411	8895
50°	13741	9447	7830
55°	13180	8459	6733
60°	12557	7410	5648
65°	11957	6207	4604
70°	11104	4941	3518
75°	10008	3594	2460
80°	8357	2207	1769
85°	6287	1271	973

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14259 cd/sqm

TEST NUMBER: P1013277

CATALOG NUMBER: S124RDIP-B1195D365UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.5	3.1
10°-20°	547.9	8.7
20°-30°	791.1	12.6
30°-40°	896.6	14.2
40°-50°	865.7	13.7
50°-60°	719.7	11.4
60°-70°	496.8	7.9
70°-80°	251.0	4.0
80°-90°	64.7	1.0
90°-100°	15.8	0.3
100°-110°	103.9	1.6
110°-120°	198.4	3.1
120°-130°	251.9	4.0
130°-140°	269.5	4.3
140°-150°	252.0	4.0
150°-160°	203.2	3.2
160°-170°	131.1	2.1
170°-180°	45.2	0.7
0°-30°	1535.6	24.4
0°-40°	2432.1	38.6
0°-60°	4017.5	63.8
0°-90°	4830.0	76.7
90°-120°	318.1	5.0
90°-150°	1091.6	17.3
90°-180°	1471.0	23.3
0°-180°	6301.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2090	2090	2090	2090	2090	
5°	2087	2080	2061	2077	2074	198
15°	1988	1973	1933	1930	1919	560
25°	1797	1768	1703	1676	1660	828
35°	1554	1503	1423	1368	1339	971
45°	1267	1208	1112	1034	1005	977
55°	960	896	792	709	678	859
65°	653	584	482	413	394	645
75°	347	288	213	176	166	366
85°	86	54	50	46	46	95
90°	1	5	8	10	11	6
95°	20	8	8	10	10	24
105°	107	109	111	114	101	112
115°	200	201	200	201	201	197
125°	281	282	282	283	283	251
135°	348	348	350	350	351	269
145°	402	403	403	403	404	251
155°	440	441	440	441	440	203
165°	465	463	463	466	463	131
175°	475	473	474	477	472	45
180°	475	475	475	475	475	

TEST NUMBER: P1013277

CATALOG NUMBER: S124RDIP-B1195D365UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2089.9	2089.9	2089.9	2089.9	2089.9
2.5°	2096.3	2089.9	2072.3	2089.9	2088.3
5°	2086.7	2080.3	2061.1	2077.1	2073.9
7.5°	2072.3	2065.9	2041.9	2053.1	2048.3
10°	2049.9	2041.9	2013.1	2019.5	2013.1
12.5°	2021.1	2011.5	1976.3	1979.5	1969.9
15°	1987.5	1973.1	1933.1	1929.9	1918.7
17.5°	1949.1	1928.3	1881.9	1873.9	1857.9
20°	1902.7	1881.9	1827.5	1814.7	1793.9
22.5°	1851.5	1827.5	1768.3	1747.5	1731.5
25°	1797.1	1768.3	1702.7	1675.5	1659.5
27.5°	1741.1	1705.9	1637.1	1605.1	1582.6
30°	1681.9	1641.9	1566.6	1526.6	1501.0
32.5°	1619.5	1573.0	1494.6	1446.6	1422.6
35°	1553.8	1502.6	1422.6	1368.2	1339.4
37.5°	1485.0	1432.2	1344.2	1285.0	1256.2
40°	1411.4	1358.6	1267.4	1200.2	1171.4
42.5°	1341.0	1285.0	1189.0	1120.2	1089.8
45°	1267.4	1208.2	1112.2	1033.8	1005.0
47.5°	1192.2	1131.4	1032.2	950.5	918.5
50°	1115.4	1053.0	950.5	870.5	840.1
52.5°	1037.0	976.2	870.5	788.9	756.9
55°	960.2	896.1	792.1	708.9	678.5
57.5°	884.9	817.7	715.3	630.5	608.1
60°	803.3	739.3	636.9	553.7	528.1
62.5°	729.7	662.5	556.9	481.7	462.5
65°	652.9	584.1	481.7	412.9	393.7
67.5°	572.9	507.3	411.3	350.5	328.1
70°	497.7	430.5	339.3	286.4	270.4
72.5°	417.7	358.5	273.6	230.4	216.0
75°	347.3	288.0	212.8	176.0	166.4
77.5°	273.6	222.4	158.4	132.8	129.6
80°	203.2	156.8	108.8	104.0	102.4
82.5°	142.4	100.8	78.4	75.2	73.6
85°	86.4	54.4	49.6	46.4	46.4
87.5°	36.8	24.0	22.4	20.8	22.4
90°	1.1	5.0	7.8	10.0	10.7
92.5°	5.3	4.6	7.5	9.6	9.6
95°	19.6	7.5	7.8	10.0	10.3
97.5°	37.3	45.2	7.8	9.6	10.0
100°	58.3	64.7	15.6	9.6	10.0
102.5°	81.8	86.0	90.3	10.3	10.3
105°	107.0	109.2	110.9	114.1	101.3
107.5°	130.1	131.2	133.7	135.5	136.9
110°	153.6	154.7	156.8	157.5	158.6



TEST NUMBER: P1013277

CATALOG NUMBER: S124RDIP-B1195D365UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	176.4	178.5	179.2	178.8	180.3
115°	199.8	200.9	200.5	201.2	201.2
117.5°	220.8	222.2	223.3	222.9	222.9
120°	242.1	243.6	243.2	243.9	243.2
122.5°	262.1	262.8	263.5	263.8	263.1
125°	280.9	282.3	281.6	282.7	283.0
127.5°	299.0	299.4	301.2	300.8	300.5
130°	316.5	316.8	317.9	318.2	318.2
132.5°	332.5	333.2	334.6	334.9	334.6
135°	348.5	348.1	349.5	350.2	350.9
137.5°	362.7	362.7	364.5	365.2	364.8
140°	376.5	377.3	378.0	379.0	379.4
142.5°	389.0	390.4	390.8	391.5	391.5
145°	401.8	402.9	402.9	403.2	403.9
147.5°	411.7	413.9	413.5	413.9	414.2
150°	422.8	424.2	423.8	423.8	424.2
152.5°	432.0	433.1	432.4	433.1	432.7
155°	440.5	440.9	439.8	441.3	440.2
157.5°	448.0	448.0	446.6	448.4	446.6
160°	454.4	453.3	453.0	455.1	453.0
162.5°	460.1	458.7	458.3	460.5	458.0
165°	464.7	462.9	462.9	465.8	462.6
167.5°	468.6	466.9	466.5	469.7	466.1
170°	471.8	469.7	470.1	472.9	469.3
172.5°	474.0	471.8	472.2	475.0	471.1
175°	475.4	473.3	473.6	476.8	472.5
177.5°	476.5	474.0	474.7	477.5	473.3
180°	475.4	475.4	475.4	475.4	475.4

(END OF REPORT)