

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007475

Luminaire Tested: S123IP-B1025UB2750-4F0-XX-W2A-1_4000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007475
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B1025UB2750-4F0-XX-W2A-1_4000K
Description: Define 3 Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3469.0 lumens
Efficiency: N/A
Efficacy: 121.7 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 28.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007475

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A-1_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1007475

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A-1_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007475

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A-1_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.6	0.1
90°-100°	80.5	2.3
100°-110°	243.7	7.0
110°-120°	415.0	12.0
120°-130°	545.9	15.7
130°-140°	613.6	17.7
140°-150°	603.2	17.4
150°-160°	507.9	14.6
160°-170°	338.1	9.7
170°-180°	118.4	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.6	0.1
90°-120°	739.2	21.3
90°-150°	2502.0	72.1
90°-180°	3466.0	99.9
0°-180°	3469.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	11	24	28	30	4
95°	58	65	73	77	77	64
105°	221	223	232	232	234	237
115°	418	421	419	420	419	413
125°	611	614	612	608	604	545
135°	793	799	798	794	792	611
145°	962	964	967	966	962	601
155°	1102	1102	1103	1107	1100	507
165°	1200	1197	1197	1203	1196	338
175°	1248	1244	1244	1250	1243	119
180°	1251	1251	1251	1251	1251	

TEST NUMBER: P1007475

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.0	10.8	23.6	27.5	29.5
92.5°	29.5	35.4	41.3	44.2	42.3
95°	58.0	64.9	72.7	76.7	76.7
97.5°	95.3	100.2	106.1	111.0	110.1
100°	133.7	139.5	144.5	147.4	149.4
102.5°	177.9	180.8	187.7	190.7	189.7
105°	221.1	223.1	231.9	231.9	233.9
107.5°	272.2	273.2	277.1	280.1	279.1
110°	319.4	321.4	323.3	327.3	325.3

TEST NUMBER: P1007475

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	368.5	369.5	369.5	374.4	374.4
115°	417.7	420.6	418.6	419.6	418.6
117.5°	467.8	468.8	466.8	466.8	463.9
120°	514.0	519.9	515.0	514.0	512.0
122.5°	562.1	566.1	564.1	561.1	558.2
125°	611.3	614.2	612.2	608.3	604.4
127.5°	656.5	662.4	660.4	654.5	650.6
130°	701.7	709.5	706.6	702.7	695.8
132.5°	746.9	754.7	752.8	747.9	742.9
135°	793.1	799.0	798.0	794.1	792.1
137.5°	835.3	840.2	843.2	838.3	835.3
140°	879.5	884.5	885.4	884.5	877.6
142.5°	919.8	924.8	926.7	925.7	920.8
145°	962.1	964.1	967.0	966.0	962.1
147.5°	998.5	1002.4	1005.3	1005.3	999.4
150°	1036.8	1038.8	1040.7	1040.7	1034.8
152.5°	1068.2	1071.2	1072.2	1074.1	1069.2
155°	1101.6	1101.6	1102.6	1106.6	1099.7
157.5°	1130.1	1129.2	1130.1	1134.1	1128.2
160°	1156.7	1154.7	1154.7	1159.6	1155.7
162.5°	1180.3	1177.3	1178.3	1183.2	1176.3
165°	1199.9	1197.0	1197.0	1202.9	1196.0
167.5°	1216.6	1212.7	1213.7	1219.6	1213.7
170°	1230.4	1226.5	1226.5	1233.3	1226.5
172.5°	1241.2	1237.3	1237.3	1243.2	1236.3
175°	1248.1	1244.1	1244.1	1250.0	1243.2
177.5°	1252.0	1248.1	1248.1	1254.0	1247.1
180°	1251.0	1251.0	1251.0	1251.0	1251.0

(END OF REPORT)