

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007482

Luminaire Tested: S123IP-B1025UB2750-4F0-XX-W2A_2700K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007482
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B1025UB2750-4F0-XX-W2A_2700K
Description: Define 3 Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4023.0 lumens
Efficiency: N/A
Efficacy: 141.2 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 28.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007482

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1007482

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007482

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.6	0.1
90°-100°	46.5	1.2
100°-110°	224.8	5.6
110°-120°	551.0	13.7
120°-130°	699.5	17.4
130°-140°	747.2	18.6
140°-150°	698.7	17.4
150°-160°	563.6	14.0
160°-170°	363.7	9.0
170°-180°	125.3	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.6	0.1
90°-120°	822.3	20.4
90°-150°	2967.7	73.8
90°-180°	4020.0	99.9
0°-180°	4023.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	11	24	27	29	3
95°	60	20	30	37	37	71
105°	292	303	215	41	43	310
115°	548	554	562	572	576	541
125°	772	780	784	786	788	690
135°	961	967	971	974	971	740
145°	1109	1116	1118	1120	1120	694
155°	1222	1220	1221	1226	1220	563
165°	1288	1286	1284	1292	1286	364
175°	1319	1314	1315	1322	1314	126
180°	1319	1319	1319	1319	1319	

TEST NUMBER: P1007482

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.0	10.8	23.5	27.4	29.4
92.5°	22.5	16.7	25.5	32.3	33.3
95°	59.8	19.6	30.4	37.2	37.2
97.5°	108.8	81.3	31.4	39.2	40.2
100°	165.6	185.2	32.3	40.2	41.2
102.5°	230.2	243.0	72.5	40.2	42.1
105°	292.0	302.7	214.6	41.2	43.1
107.5°	357.6	366.4	381.1	230.2	101.9
110°	423.3	431.1	441.9	409.5	269.4

TEST NUMBER: P1007482

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	486.0	492.8	503.6	512.4	510.5
115°	547.7	553.6	562.4	572.2	576.1
117.5°	608.4	615.3	620.2	628.0	629.0
120°	664.3	673.1	676.0	683.9	683.9
122.5°	721.1	728.0	731.9	736.8	737.8
125°	772.1	779.9	783.8	785.8	787.7
127.5°	823.0	830.8	835.7	838.7	836.7
130°	870.0	877.9	881.8	885.7	883.7
132.5°	915.1	922.9	925.9	929.8	926.9
135°	961.2	967.0	970.9	973.9	970.9
137.5°	1000.3	1008.2	1010.1	1015.0	1013.1
140°	1039.5	1045.4	1048.3	1052.3	1050.3
142.5°	1075.8	1081.7	1084.6	1087.5	1084.6
145°	1109.1	1116.0	1117.9	1119.9	1119.9
147.5°	1141.4	1146.3	1148.3	1150.2	1145.3
150°	1170.8	1173.8	1175.7	1177.7	1174.7
152.5°	1197.3	1198.3	1199.2	1203.2	1198.3
155°	1221.8	1219.8	1220.8	1225.7	1219.8
157.5°	1241.4	1241.4	1240.4	1246.3	1238.4
160°	1259.0	1258.0	1257.0	1262.9	1256.1
162.5°	1275.7	1272.7	1271.7	1278.6	1272.7
165°	1288.4	1285.5	1284.5	1292.3	1285.5
167.5°	1299.2	1295.3	1295.3	1303.1	1295.3
170°	1308.0	1304.1	1304.1	1311.9	1304.1
172.5°	1313.9	1309.0	1309.9	1317.8	1309.0
175°	1318.8	1313.9	1314.8	1321.7	1313.9
177.5°	1320.7	1315.8	1316.8	1324.6	1314.8
180°	1318.8	1318.8	1318.8	1318.8	1318.8

(END OF REPORT)