

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013299

Luminaire Tested: S124RDIP-B1195D810UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013299
REPORT IS A COMBINATION OF REPORTS P999194 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D810UB2750-4F0-XX-W2A-F_5000K
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7684.0 lumens
Efficiency: N/A
Efficacy: 93.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013299

CATALOG NUMBER: S124RDIP-B1195D810UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013299

CATALOG NUMBER: S124RDIP-B1195D810UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66
1	100	96	92	89	94	90	87	84	79	76	74	68	67	65	59	57	56
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48
3	84	74	67	61	78	70	64	58	61	56	52	54	50	47	46	43	41
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	38	36
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31
6	65	53	45	39	61	50	43	38	45	39	34	39	34	31	34	31	28
7	61	48	40	35	57	46	38	33	41	35	30	36	31	27	31	28	25
8	56	44	36	31	53	42	34	30	37	31	27	33	28	25	29	25	22
9	52	40	33	28	49	38	31	26	34	28	24	30	26	22	27	23	20
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16390	16390	16390
5°	16391	15903	15905
10°	16252	15401	15218
15°	16029	14776	14408
20°	15735	14064	13484
25°	15370	13295	12581
30°	15013	12511	11568
35°	14620	11716	10578
40°	14151	10860	9561
45°	13713	10012	8554
50°	13213	9085	7530
55°	12675	8135	6475
60°	12077	7126	5432
65°	11499	5969	4428
70°	10677	4752	3384
75°	9625	3457	2367
80°	8037	2121	1701
85°	6047	1222	935

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13713 cd/sqm

TEST NUMBER: P1013299

CATALOG NUMBER: S124RDIP-B1195D810UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	2.5
10°-20°	527.0	6.9
20°-30°	760.8	9.9
30°-40°	862.2	11.2
40°-50°	832.5	10.8
50°-60°	692.1	9.0
60°-70°	477.7	6.2
70°-80°	241.4	3.1
80°-90°	63.3	0.8
90°-100°	32.6	0.4
100°-110°	214.6	2.8
110°-120°	409.8	5.3
120°-130°	520.3	6.8
130°-140°	556.6	7.2
140°-150°	520.4	6.8
150°-160°	419.7	5.5
160°-170°	270.7	3.5
170°-180°	93.3	1.2
0°-30°	1476.7	19.2
0°-40°	2339.0	30.4
0°-60°	3863.6	50.3
0°-90°	4646.0	60.5
90°-120°	657.0	8.6
90°-150°	2254.3	29.3
90°-180°	3038.0	39.5
0°-180°	7684.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2010	2010	2010	2010	2010	
5°	2007	2001	1982	1998	1994	190
15°	1911	1898	1859	1856	1845	539
25°	1728	1700	1637	1611	1596	796
35°	1494	1445	1368	1316	1288	934
45°	1219	1162	1070	994	966	940
55°	923	862	762	682	652	826
65°	628	562	463	397	379	620
75°	334	277	205	169	160	352
85°	83	52	48	45	45	91
90°	2	10	16	21	22	7
95°	40	15	16	21	21	50
105°	221	225	229	236	209	231
115°	413	415	414	416	416	406
125°	580	583	582	584	584	518
135°	720	719	722	723	725	554
145°	830	832	832	833	834	518
155°	910	911	908	911	909	420
165°	960	956	956	962	955	271
175°	982	977	978	985	976	93
180°	982	982	982	982	982	



TEST NUMBER: P1013299

CATALOG NUMBER: S124RDIP-B1195D810UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2009.9	2009.9	2009.9	2009.9	2009.9
2.5°	2016.0	2009.9	1992.9	2009.9	2008.3
5°	2006.8	2000.6	1982.2	1997.6	1994.5
7.5°	1992.9	1986.8	1963.7	1974.5	1969.8
10°	1971.4	1963.7	1936.0	1942.1	1936.0
12.5°	1943.7	1934.5	1900.6	1903.7	1894.4
15°	1911.4	1897.5	1859.0	1856.0	1845.2
17.5°	1874.4	1854.4	1809.8	1802.1	1786.7
20°	1829.8	1809.8	1757.5	1745.2	1725.2
22.5°	1780.6	1757.5	1700.5	1680.5	1665.1
25°	1728.2	1700.5	1637.4	1611.3	1595.9
27.5°	1674.4	1640.5	1574.3	1543.6	1522.0
30°	1617.4	1579.0	1506.6	1468.2	1443.5
32.5°	1557.4	1512.8	1437.4	1391.2	1368.1
35°	1494.3	1445.1	1368.1	1315.8	1288.1
37.5°	1428.1	1377.4	1292.7	1235.8	1208.1
40°	1357.3	1306.6	1218.8	1154.2	1126.5
42.5°	1289.6	1235.8	1143.4	1077.3	1048.0
45°	1218.8	1161.9	1069.6	994.2	966.5
47.5°	1146.5	1088.0	992.6	914.1	883.4
50°	1072.6	1012.6	914.1	837.2	807.9
52.5°	997.2	938.8	837.2	758.7	727.9
55°	923.4	861.8	761.8	681.8	652.5
57.5°	851.0	786.4	687.9	606.3	584.8
60°	772.6	711.0	612.5	532.5	507.9
62.5°	701.8	637.1	535.6	463.2	444.8
65°	627.9	561.7	463.2	397.0	378.6
67.5°	550.9	487.8	395.5	337.0	315.5
70°	478.6	414.0	326.3	275.5	260.1
72.5°	401.7	344.7	263.2	221.6	207.8
75°	334.0	277.0	204.7	169.3	160.1
77.5°	263.2	213.9	152.4	127.7	124.7
80°	195.4	150.8	104.6	100.0	98.5
82.5°	137.0	97.0	75.4	72.3	70.8
85°	83.1	52.3	47.7	44.6	44.6
87.5°	35.4	23.1	21.5	20.0	21.5
90°	2.2	10.3	16.2	20.6	22.0
92.5°	11.0	9.5	15.4	19.8	19.8
95°	40.4	15.4	16.2	20.6	21.3
97.5°	77.1	93.3	16.2	19.8	20.6
100°	120.4	133.6	32.3	19.8	20.6
102.5°	168.9	177.7	186.5	21.3	21.3
105°	221.0	225.4	229.1	235.7	209.3
107.5°	268.8	271.0	276.1	279.8	282.7
110°	317.2	319.4	323.8	325.3	327.5

TEST NUMBER: P1013299

CATALOG NUMBER: S124RDIP-B1195D810UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	364.2	368.6	370.1	369.4	372.3
115°	412.7	414.9	414.2	415.6	415.6
117.5°	456.0	458.9	461.2	460.4	460.4
120°	500.1	503.0	502.3	503.7	502.3
122.5°	541.2	542.7	544.1	544.9	543.4
125°	580.1	583.0	581.6	583.8	584.5
127.5°	617.6	618.3	622.0	621.2	620.5
130°	653.5	654.3	656.5	657.2	657.2
132.5°	686.6	688.1	691.0	691.7	691.0
135°	719.6	718.9	721.8	723.3	724.8
137.5°	749.0	749.0	752.7	754.1	753.4
140°	777.6	779.1	780.6	782.8	783.5
142.5°	803.3	806.3	807.0	808.5	808.5
145°	829.8	832.0	832.0	832.7	834.2
147.5°	850.3	854.7	854.0	854.7	855.5
150°	873.1	876.0	875.3	875.3	876.0
152.5°	892.2	894.4	892.9	894.4	893.7
155°	909.8	910.6	908.3	911.3	909.1
157.5°	925.2	925.2	922.3	926.0	922.3
160°	938.5	936.3	935.5	939.9	935.5
162.5°	950.2	947.3	946.5	950.9	945.8
165°	959.8	956.1	956.1	962.0	955.3
167.5°	967.8	964.2	963.4	970.0	962.7
170°	974.4	970.0	970.8	976.6	969.3
172.5°	978.8	974.4	975.2	981.0	973.0
175°	981.8	977.4	978.1	984.7	975.9
177.5°	984.0	978.8	980.3	986.2	977.4
180°	981.8	981.8	981.8	981.8	981.8

(END OF REPORT)