

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007486

Luminaire Tested: S123IP-B1025UB2750-4F0-XX-W2A_5000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007486
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B1025UB2750-4F0-XX-W2A_5000K
Description: Define 3 Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3901.0 lumens
Efficiency: N/A
Efficacy: 136.9 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 28.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007486

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007486

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007486

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.6	0.1
90°-100°	45.1	1.2
100°-110°	218.0	5.6
110°-120°	534.3	13.7
120°-130°	678.2	17.4
130°-140°	724.6	18.6
140°-150°	677.5	17.4
150°-160°	546.5	14.0
160°-170°	352.7	9.0
170°-180°	121.5	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.6	0.1
90°-120°	797.4	20.4
90°-150°	2877.8	73.8
90°-180°	3898.0	99.9
0°-180°	3901.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	10	23	27	28	3
95°	58	19	30	36	36	69
105°	283	294	208	40	42	300
115°	531	537	545	555	559	524
125°	749	756	760	762	764	669
135°	932	938	942	944	942	718
145°	1076	1082	1084	1086	1086	673
155°	1185	1183	1184	1188	1183	546
165°	1249	1246	1246	1253	1246	353
175°	1279	1274	1275	1282	1274	122
180°	1279	1279	1279	1279	1279	

TEST NUMBER: P1007486

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.0	10.5	22.8	26.6	28.5
92.5°	21.9	16.2	24.7	31.4	32.3
95°	58.0	19.0	29.5	36.1	36.1
97.5°	105.5	78.9	30.4	38.0	39.0
100°	160.6	179.6	31.4	39.0	39.9
102.5°	223.3	235.6	70.3	39.0	40.9
105°	283.1	293.6	208.1	39.9	41.8
107.5°	346.8	355.3	369.6	223.3	98.8
110°	410.4	418.0	428.5	397.1	261.3

TEST NUMBER: P1007486

CATALOG NUMBER: S123IP-B1025UB2750-4F0-XX-W2A_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	471.2	477.9	488.3	496.9	495.0
115°	531.1	536.8	545.3	554.8	558.6
117.5°	590.0	596.6	601.4	609.0	609.9
120°	644.1	652.7	655.5	663.1	663.1
122.5°	699.2	705.9	709.7	714.4	715.4
125°	748.6	756.2	760.0	761.9	763.8
127.5°	798.0	805.6	810.4	813.2	811.3
130°	843.6	851.2	855.0	858.8	856.9
132.5°	887.4	895.0	897.8	901.6	898.8
135°	932.0	937.7	941.5	944.4	941.5
137.5°	970.0	977.6	979.5	984.3	982.4
140°	1008.0	1013.7	1016.6	1020.4	1018.5
142.5°	1043.2	1048.9	1051.7	1054.6	1051.7
145°	1075.5	1082.1	1084.0	1085.9	1085.9
147.5°	1106.8	1111.6	1113.5	1115.4	1110.6
150°	1135.3	1138.2	1140.1	1142.0	1139.1
152.5°	1161.0	1161.9	1162.9	1166.7	1161.9
155°	1184.7	1182.8	1183.8	1188.5	1182.8
157.5°	1203.7	1203.7	1202.8	1208.5	1200.9
160°	1220.8	1219.9	1218.9	1224.6	1218.0
162.5°	1237.0	1234.1	1233.2	1239.8	1234.1
165°	1249.3	1246.5	1245.5	1253.1	1246.5
167.5°	1259.8	1256.0	1256.0	1263.6	1256.0
170°	1268.3	1264.5	1264.5	1272.1	1264.5
172.5°	1274.0	1269.3	1270.2	1277.8	1269.3
175°	1278.8	1274.0	1275.0	1281.6	1274.0
177.5°	1280.7	1275.9	1276.9	1284.5	1275.0
180°	1278.8	1278.8	1278.8	1278.8	1278.8

(END OF REPORT)