

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013306

Luminaire Tested: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013306
REPORT IS A COMBINATION OF REPORTS P999231 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_3000K
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5481.0 lumens
Efficiency: N/A
Efficacy: 132.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013306

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013306

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	92	88	85	81	82	79	76	73	61	59	57	45	44	42	30	29	29
2	84	77	71	67	75	69	64	60	54	50	48	39	37	36	26	25	24
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	23	22	21
4	70	60	53	47	62	54	47	43	42	38	34	31	28	26	21	19	18
5	64	53	46	40	57	48	41	36	38	33	29	28	25	22	19	17	16
6	59	48	40	35	53	43	36	31	34	29	25	25	22	20	17	15	14
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12
8	51	39	32	26	45	35	29	24	28	23	20	21	18	15	14	12	11
9	47	35	28	23	42	32	26	21	25	21	18	19	16	14	13	11	10
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4906	4906	4906
5°	4906	4760	4761
10°	4865	4610	4555
15°	4798	4422	4312
20°	4710	4209	4036
25°	4601	3979	3766
30°	4493	3744	3463
35°	4376	3507	3166
40°	4236	3251	2862
45°	4104	2996	2560
50°	3956	2719	2254
55°	3794	2435	1938
60°	3614	2133	1626
65°	3441	1786	1325
70°	3197	1423	1012
75°	2882	1035	708
80°	2406	635	510
85°	1812	366	281

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4104 cd/sqm

TEST NUMBER: P1013306

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.6	1.0
10°-20°	157.7	2.9
20°-30°	227.7	4.2
30°-40°	258.1	4.7
40°-50°	249.2	4.5
50°-60°	207.2	3.8
60°-70°	143.0	2.6
70°-80°	72.3	1.3
80°-90°	21.1	0.4
90°-100°	43.9	0.8
100°-110°	288.8	5.3
110°-120°	551.5	10.1
120°-130°	700.1	12.8
130°-140°	749.0	13.7
140°-150°	700.4	12.8
150°-160°	564.8	10.3
160°-170°	364.2	6.6
170°-180°	125.5	2.3
0°-30°	442.0	8.1
0°-40°	700.1	12.8
0°-60°	1156.4	21.1
0°-90°	1392.7	25.4
90°-120°	884.2	16.1
90°-150°	3033.7	55.3
90°-180°	4088.0	74.6
0°-180°	5481.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	602	602	602	602	602	
5°	601	599	593	598	597	57
15°	572	568	556	556	552	161
25°	517	509	490	482	478	238
35°	447	432	410	394	386	280
45°	365	348	320	298	289	281
55°	276	258	228	204	195	247
65°	188	168	139	119	113	186
75°	100	83	61	51	48	105
85°	25	16	14	13	13	27
90°	3	14	22	28	30	4
95°	54	21	22	28	29	67
105°	297	303	308	317	282	311
115°	555	558	557	559	559	547
125°	781	785	783	786	787	697
135°	968	967	971	973	975	746
145°	1117	1120	1120	1121	1123	698
155°	1224	1225	1222	1226	1223	565
165°	1292	1287	1287	1294	1286	365
175°	1321	1315	1316	1325	1313	126
180°	1321	1321	1321	1321	1321	

TEST NUMBER: P1013306

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	601.6	601.6	601.6	601.6	601.6
2.5°	603.4	601.6	596.5	601.6	601.1
5°	600.7	598.8	593.3	597.9	597.0
7.5°	596.5	594.7	587.8	591.0	589.6
10°	590.1	587.8	579.5	581.3	579.5
12.5°	581.8	579.0	568.9	569.8	567.0
15°	572.1	567.9	556.4	555.5	552.3
17.5°	561.0	555.1	541.7	539.4	534.8
20°	547.7	541.7	526.0	522.3	516.4
22.5°	532.9	526.0	509.0	503.0	498.4
25°	517.3	509.0	490.1	482.3	477.7
27.5°	501.2	491.0	471.2	462.0	455.6
30°	484.1	472.6	450.9	439.4	432.1
32.5°	466.2	452.8	430.2	416.4	409.5
35°	447.3	432.5	409.5	393.8	385.5
37.5°	427.5	412.3	386.9	369.9	361.6
40°	406.3	391.1	364.8	345.5	337.2
42.5°	386.0	369.9	342.2	322.4	313.7
45°	364.8	347.8	320.1	297.6	289.3
47.5°	343.2	325.7	297.1	273.6	264.4
50°	321.1	303.1	273.6	250.6	241.8
52.5°	298.5	281.0	250.6	227.1	217.9
55°	276.4	257.9	228.0	204.1	195.3
57.5°	254.7	235.4	205.9	181.5	175.0
60°	231.2	212.8	183.3	159.4	152.0
62.5°	210.0	190.7	160.3	138.6	133.1
65°	187.9	168.1	138.6	118.8	113.3
67.5°	164.9	146.0	118.4	100.9	94.4
70°	143.3	123.9	97.7	82.5	77.8
72.5°	120.2	103.2	78.8	66.3	62.2
75°	100.0	82.9	61.3	50.7	47.9
77.5°	78.8	64.0	45.6	38.2	37.3
80°	58.5	45.1	31.3	29.9	29.5
82.5°	41.0	29.0	22.6	21.6	21.2
85°	24.9	15.7	14.3	13.4	13.4
87.5°	10.6	6.9	6.4	6.0	6.4
90°	3.0	13.8	21.7	27.7	29.6
92.5°	14.8	12.8	20.8	26.7	26.7
95°	54.4	20.8	21.7	27.7	28.7
97.5°	103.8	125.5	21.7	26.7	27.7
100°	162.1	179.8	43.5	26.7	27.7
102.5°	227.3	239.1	251.0	28.7	28.7
105°	297.4	303.4	308.3	317.2	281.6
107.5°	361.7	364.6	371.6	376.5	380.5
110°	426.9	429.9	435.8	437.8	440.7

TEST NUMBER: P1013306

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	490.1	496.1	498.0	497.1	501.0
115°	555.4	558.3	557.3	559.3	559.3
117.5°	613.7	617.6	620.6	619.6	619.6
120°	673.0	676.9	675.9	677.9	675.9
122.5°	728.3	730.3	732.2	733.2	731.3
125°	780.7	784.6	782.6	785.6	786.6
127.5°	831.1	832.1	837.0	836.0	835.0
130°	879.5	880.5	883.4	884.4	884.4
132.5°	924.0	925.9	929.9	930.9	929.9
135°	968.4	967.4	971.4	973.4	975.3
137.5°	1007.9	1007.9	1012.9	1014.9	1013.9
140°	1046.5	1048.5	1050.4	1053.4	1054.4
142.5°	1081.1	1085.0	1086.0	1088.0	1088.0
145°	1116.6	1119.6	1119.6	1120.6	1122.6
147.5°	1144.3	1150.2	1149.3	1150.2	1151.2
150°	1175.0	1178.9	1177.9	1177.9	1178.9
152.5°	1200.6	1203.6	1201.6	1203.6	1202.6
155°	1224.4	1225.4	1222.4	1226.3	1223.4
157.5°	1245.1	1245.1	1241.2	1246.1	1241.2
160°	1262.9	1259.9	1258.9	1264.9	1258.9
162.5°	1278.7	1274.8	1273.8	1279.7	1272.8
165°	1291.6	1286.6	1286.6	1294.5	1285.6
167.5°	1302.4	1297.5	1296.5	1305.4	1295.5
170°	1311.3	1305.4	1306.4	1314.3	1304.4
172.5°	1317.3	1311.3	1312.3	1320.2	1309.3
175°	1321.2	1315.3	1316.3	1325.2	1313.3
177.5°	1324.2	1317.3	1319.2	1327.1	1315.3
180°	1321.2	1321.2	1321.2	1321.2	1321.2

(END OF REPORT)