

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007502

Luminaire Tested: S123IP-B1195UB2750-4F0-XX-W2A-1_2700K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007502
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B1195UB2750-4F0-XX-W2A-1_2700K
Description: Define 3 Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4064.0 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 35
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007502

CATALOG NUMBER: S123IP-B119SUB2750-4F0-XX-W2A-1_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1007502

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A-1_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007502

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A-1_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.1	0.1
90°-100°	94.3	2.3
100°-110°	285.6	7.0
110°-120°	486.1	12.0
120°-130°	639.5	15.7
130°-140°	718.9	17.7
140°-150°	706.7	17.4
150°-160°	595.0	14.6
160°-170°	396.1	9.7
170°-180°	138.7	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.1	0.1
90°-120°	866.0	21.3
90°-150°	2931.1	72.1
90°-180°	4061.0	99.9
0°-180°	4064.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	13	28	32	34	5
95°	68	76	85	90	90	75
105°	259	261	272	272	274	277
115°	489	493	490	492	490	484
125°	716	720	717	713	708	639
135°	929	936	935	930	928	716
145°	1127	1129	1133	1132	1127	704
155°	1291	1291	1292	1296	1288	594
165°	1406	1402	1402	1409	1401	396
175°	1462	1458	1458	1464	1456	139
180°	1466	1466	1466	1466	1466	

TEST NUMBER: P1007502

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.2	12.7	27.6	32.2	34.5
92.5°	34.5	41.4	48.4	51.8	49.5
95°	67.9	76.0	85.2	89.8	89.8
97.5°	111.7	117.4	124.3	130.1	128.9
100°	156.6	163.5	169.2	172.7	175.0
102.5°	208.4	211.8	219.9	223.4	222.2
105°	259.0	261.3	271.7	271.7	274.0
107.5°	318.9	320.1	324.7	328.1	327.0
110°	374.2	376.5	378.8	383.4	381.1

TEST NUMBER: P1007502

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	431.7	432.9	432.9	438.6	438.6
115°	489.3	492.8	490.5	491.6	490.5
117.5°	548.0	549.2	546.9	546.9	543.4
120°	602.1	609.0	603.3	602.1	599.8
122.5°	658.5	663.1	660.8	657.4	653.9
125°	716.1	719.6	717.3	712.7	708.0
127.5°	769.1	776.0	773.7	766.8	762.2
130°	822.0	831.2	827.8	823.2	815.1
132.5°	875.0	884.2	881.9	876.1	870.4
135°	929.1	936.0	934.9	930.2	927.9
137.5°	978.6	984.4	987.8	982.1	978.6
140°	1030.4	1036.2	1037.3	1036.2	1028.1
142.5°	1077.6	1083.4	1085.7	1084.5	1078.8
145°	1127.1	1129.4	1132.9	1131.7	1127.1
147.5°	1169.7	1174.3	1177.8	1177.8	1170.9
150°	1214.6	1216.9	1219.2	1219.2	1212.3
152.5°	1251.5	1254.9	1256.1	1258.4	1252.6
155°	1290.6	1290.6	1291.8	1296.4	1288.3
157.5°	1324.0	1322.8	1324.0	1328.6	1321.7
160°	1355.1	1352.8	1352.8	1358.5	1353.9
162.5°	1382.7	1379.2	1380.4	1386.2	1378.1
165°	1405.7	1402.3	1402.3	1409.2	1401.1
167.5°	1425.3	1420.7	1421.8	1428.8	1421.8
170°	1441.4	1436.8	1436.8	1444.9	1436.8
172.5°	1454.1	1449.5	1449.5	1456.4	1448.3
175°	1462.1	1457.5	1457.5	1464.4	1456.4
177.5°	1466.7	1462.1	1462.1	1469.1	1461.0
180°	1465.6	1465.6	1465.6	1465.6	1465.6

(END OF REPORT)