

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013307

Luminaire Tested: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013307
REPORT IS A COMBINATION OF REPORTS P999232 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_3500K
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5505.0 lumens
Efficiency: N/A
Efficacy: 132.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013307

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1013307

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	92	88	85	81	82	79	76	73	61	59	57	45	44	42	30	29	29
2	84	77	71	67	75	69	64	60	54	50	48	39	37	36	26	25	24
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	23	22	21
4	70	60	53	47	62	54	47	43	42	38	34	31	28	26	21	19	18
5	64	53	46	40	57	48	41	36	38	33	29	28	25	22	19	17	16
6	59	48	40	35	53	43	36	31	34	29	25	25	22	20	17	15	14
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12
8	51	39	32	26	45	35	29	24	28	23	20	21	18	15	14	12	11
9	47	35	28	23	42	32	26	21	25	21	18	19	16	14	13	11	10
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4927	4927	4927
5°	4927	4780	4781
10°	4885	4630	4575
15°	4819	4441	4331
20°	4730	4228	4053
25°	4620	3996	3782
30°	4513	3761	3477
35°	4395	3522	3180
40°	4254	3265	2874
45°	4122	3010	2571
50°	3972	2731	2264
55°	3811	2446	1946
60°	3630	2142	1633
65°	3456	1794	1331
70°	3210	1429	1017
75°	2893	1039	711
80°	2418	639	511
85°	1819	366	281

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4122 cd/sqm

TEST NUMBER: P1013307

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.8	1.0
10°-20°	158.4	2.9
20°-30°	228.7	4.2
30°-40°	259.2	4.7
40°-50°	250.3	4.5
50°-60°	208.1	3.8
60°-70°	143.6	2.6
70°-80°	72.6	1.3
80°-90°	21.2	0.4
90°-100°	44.0	0.8
100°-110°	290.1	5.3
110°-120°	553.9	10.1
120°-130°	703.2	12.8
130°-140°	752.3	13.7
140°-150°	703.4	12.8
150°-160°	567.3	10.3
160°-170°	365.8	6.6
170°-180°	126.1	2.3
0°-30°	443.9	8.1
0°-40°	703.1	12.8
0°-60°	1161.4	21.1
0°-90°	1398.7	25.4
90°-120°	888.1	16.1
90°-150°	3047.1	55.4
90°-180°	4106.0	74.6
0°-180°	5505.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	604	604	604	604	604	
5°	603	601	596	600	600	57
15°	575	570	559	558	555	162
25°	520	511	492	484	480	239
35°	449	434	411	396	387	281
45°	366	349	322	299	290	283
55°	278	259	229	205	196	248
65°	189	169	139	119	114	186
75°	100	83	62	51	48	106
85°	25	16	14	13	13	27
90°	3	14	22	28	30	4
95°	55	21	22	28	29	67
105°	299	305	310	319	283	313
115°	558	561	560	562	562	549
125°	784	788	786	789	790	700
135°	973	972	976	978	980	750
145°	1122	1124	1124	1126	1128	701
155°	1230	1231	1228	1232	1229	567
165°	1297	1292	1292	1300	1291	367
175°	1327	1321	1322	1331	1319	126
180°	1327	1327	1327	1327	1327	

TEST NUMBER: P1013307

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	604.2	604.2	604.2	604.2	604.2
2.5°	606.0	604.2	599.1	604.2	603.7
5°	603.2	601.4	595.8	600.5	599.5
7.5°	599.1	597.2	590.3	593.5	592.1
10°	592.6	590.3	582.0	583.8	582.0
12.5°	584.3	581.5	571.3	572.3	569.5
15°	574.6	570.4	558.8	557.9	554.7
17.5°	563.5	557.4	544.0	541.7	537.1
20°	550.0	544.0	528.3	524.6	518.6
22.5°	535.2	528.3	511.2	505.2	500.5
25°	519.5	511.2	492.2	484.4	479.7
27.5°	503.3	493.1	473.3	464.0	457.5
30°	486.2	474.6	452.9	441.3	433.9
32.5°	468.2	454.7	432.1	418.2	411.3
35°	449.2	434.4	411.3	395.5	387.2
37.5°	429.3	414.0	388.6	371.5	363.1
40°	408.0	392.8	366.4	347.0	338.6
42.5°	387.7	371.5	343.7	323.8	315.0
45°	366.4	349.3	321.5	298.8	290.5
47.5°	344.6	327.1	298.4	274.8	265.5
50°	322.4	304.4	274.8	251.7	242.9
52.5°	299.8	282.2	251.7	228.1	218.8
55°	277.6	259.1	229.0	204.9	196.1
57.5°	255.8	236.4	206.8	182.3	175.8
60°	232.2	213.7	184.1	160.1	152.7
62.5°	211.0	191.5	161.0	139.2	133.7
65°	188.7	168.9	139.2	119.4	113.8
67.5°	165.6	146.6	118.9	101.3	94.8
70°	143.9	124.4	98.1	82.8	78.2
72.5°	120.7	103.6	79.1	66.6	62.5
75°	100.4	83.3	61.5	50.9	48.1
77.5°	79.1	64.3	45.8	38.4	37.5
80°	58.8	45.3	31.5	30.1	29.6
82.5°	41.2	29.1	22.7	21.7	21.3
85°	25.0	15.7	14.3	13.4	13.4
87.5°	10.6	6.9	6.5	6.0	6.5
90°	3.0	13.9	21.8	27.8	29.8
92.5°	14.9	12.9	20.8	26.8	26.8
95°	54.6	20.8	21.8	27.8	28.8
97.5°	104.2	126.1	21.8	26.8	27.8
100°	162.8	180.6	43.7	26.8	27.8
102.5°	228.3	240.2	252.1	28.8	28.8
105°	298.8	304.7	309.7	318.6	282.9
107.5°	363.3	366.2	373.2	378.2	382.1
110°	428.8	431.8	437.7	439.7	442.7

TEST NUMBER: P1013307

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	492.3	498.3	500.2	499.2	503.2
115°	557.8	560.8	559.8	561.8	561.8
117.5°	616.4	620.3	623.3	622.3	622.3
120°	675.9	679.9	678.9	680.9	678.9
122.5°	731.5	733.5	735.5	736.5	734.5
125°	784.1	788.1	786.1	789.1	790.1
127.5°	834.7	835.7	840.7	839.7	838.7
130°	883.4	884.3	887.3	888.3	888.3
132.5°	928.0	930.0	934.0	935.0	934.0
135°	972.7	971.7	975.7	977.6	979.6
137.5°	1012.4	1012.4	1017.3	1019.3	1018.3
140°	1051.1	1053.1	1055.1	1058.0	1059.0
142.5°	1085.8	1089.8	1090.8	1092.8	1092.8
145°	1121.6	1124.5	1124.5	1125.5	1127.5
147.5°	1149.4	1155.3	1154.3	1155.3	1156.3
150°	1180.1	1184.1	1183.1	1183.1	1184.1
152.5°	1205.9	1208.9	1206.9	1208.9	1207.9
155°	1229.7	1230.7	1227.8	1231.7	1228.8
157.5°	1250.6	1250.6	1246.6	1251.6	1246.6
160°	1268.5	1265.5	1264.5	1270.4	1264.5
162.5°	1284.3	1280.4	1279.4	1285.3	1278.4
165°	1297.2	1292.3	1292.3	1300.2	1291.3
167.5°	1308.2	1303.2	1302.2	1311.1	1301.2
170°	1317.1	1311.1	1312.1	1320.1	1310.1
172.5°	1323.0	1317.1	1318.1	1326.0	1315.1
175°	1327.0	1321.1	1322.1	1331.0	1319.1
177.5°	1330.0	1323.0	1325.0	1333.0	1321.1
180°	1327.0	1327.0	1327.0	1327.0	1327.0

(END OF REPORT)