

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007505

Luminaire Tested: S123IP-B1195UB2750-4F0-XX-W2A-1_4000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007505
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B1195UB2750-4F0-XX-W2A-1_4000K
Description: Define 3 Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4075.0 lumens
Efficiency: N/A
Efficacy: 116.4 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 35
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007505

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A-1_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007505

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A-1_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007505

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A-1_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.1	0.1
90°-100°	94.6	2.3
100°-110°	286.3	7.0
110°-120°	487.4	12.0
120°-130°	641.3	15.7
130°-140°	720.8	17.7
140°-150°	708.6	17.4
150°-160°	596.6	14.6
160°-170°	397.2	9.7
170°-180°	139.1	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.1	0.1
90°-120°	868.4	21.3
90°-150°	2939.0	72.1
90°-180°	4072.0	99.9
0°-180°	4075.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	13	28	32	35	5
95°	68	76	85	90	90	75
105°	260	262	272	272	275	278
115°	491	494	492	493	492	486
125°	718	722	719	715	710	640
135°	932	938	937	933	930	718
145°	1130	1132	1136	1135	1130	706
155°	1294	1294	1295	1300	1292	596
165°	1410	1406	1406	1413	1405	398
175°	1466	1462	1462	1468	1460	139
180°	1470	1470	1470	1470	1470	

TEST NUMBER: P1007505

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.2	12.7	27.7	32.3	34.6
92.5°	34.6	41.6	48.5	51.9	49.6
95°	68.1	76.2	85.4	90.0	90.0
97.5°	112.0	117.7	124.7	130.4	129.3
100°	157.0	163.9	169.7	173.2	175.5
102.5°	208.9	212.4	220.5	224.0	222.8
105°	259.7	262.1	272.4	272.4	274.7
107.5°	319.8	320.9	325.5	329.0	327.9
110°	375.2	377.5	379.8	384.4	382.1

TEST NUMBER: P1007505

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	432.9	434.1	434.1	439.8	439.8
115°	490.6	494.1	491.8	492.9	491.8
117.5°	549.5	550.7	548.3	548.3	544.9
120°	603.8	610.7	604.9	603.8	601.4
122.5°	660.3	664.9	662.6	659.2	655.7
125°	718.0	721.5	719.2	714.6	710.0
127.5°	771.1	778.1	775.8	768.8	764.2
130°	824.2	833.5	830.0	825.4	817.3
132.5°	877.4	886.6	884.3	878.5	872.7
135°	931.6	938.5	937.4	932.8	930.5
137.5°	981.2	987.0	990.5	984.7	981.2
140°	1033.2	1039.0	1040.1	1039.0	1030.9
142.5°	1080.5	1086.3	1088.6	1087.5	1081.7
145°	1130.2	1132.5	1135.9	1134.8	1130.2
147.5°	1172.9	1177.5	1181.0	1181.0	1174.0
150°	1217.9	1220.2	1222.5	1222.5	1215.6
152.5°	1254.8	1258.3	1259.5	1261.8	1256.0
155°	1294.1	1294.1	1295.2	1299.9	1291.8
157.5°	1327.6	1326.4	1327.6	1332.2	1325.3
160°	1358.7	1356.4	1356.4	1362.2	1357.6
162.5°	1386.4	1383.0	1384.1	1389.9	1381.8
165°	1409.5	1406.1	1406.1	1413.0	1404.9
167.5°	1429.2	1424.5	1425.7	1432.6	1425.7
170°	1445.3	1440.7	1440.7	1448.8	1440.7
172.5°	1458.0	1453.4	1453.4	1460.3	1452.2
175°	1466.1	1461.5	1461.5	1468.4	1460.3
177.5°	1470.7	1466.1	1466.1	1473.0	1464.9
180°	1469.6	1469.6	1469.6	1469.6	1469.6

(END OF REPORT)