

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013309

Luminaire Tested: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013309
REPORT IS A COMBINATION OF REPORTS P999234 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_5000K
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5271.0 lumens
Efficiency: N/A
Efficacy: 127.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013309

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013309

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	92	88	85	81	82	79	76	73	61	59	57	45	44	42	30	29	29
2	84	77	71	67	75	69	64	60	54	50	48	39	37	36	26	25	24
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	23	22	21
4	70	60	53	47	62	54	47	43	42	38	34	31	28	26	21	19	18
5	64	53	46	40	57	48	41	36	38	33	29	28	25	22	19	17	16
6	59	48	40	35	53	43	36	31	34	29	25	25	22	20	17	15	14
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12
8	51	39	32	26	45	35	29	24	28	23	20	21	18	15	14	12	11
9	47	35	28	23	42	32	26	21	25	21	18	19	16	14	13	11	10
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4718	4718	4718
5°	4719	4579	4579
10°	4679	4434	4381
15°	4615	4254	4148
20°	4530	4049	3882
25°	4426	3827	3622
30°	4323	3602	3331
35°	4209	3373	3045
40°	4075	3127	2752
45°	3948	2882	2462
50°	3804	2616	2168
55°	3649	2342	1864
60°	3477	2051	1564
65°	3311	1719	1275
70°	3074	1367	974
75°	2769	995	682
80°	2316	610	491
85°	1739	351	268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3948 cd/sqm

TEST NUMBER: P1013309

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.4	1.0
10°-20°	151.7	2.9
20°-30°	219.0	4.2
30°-40°	248.2	4.7
40°-50°	239.7	4.5
50°-60°	199.3	3.8
60°-70°	137.5	2.6
70°-80°	69.5	1.3
80°-90°	20.3	0.4
90°-100°	42.2	0.8
100°-110°	277.7	5.3
110°-120°	530.3	10.1
120°-130°	673.3	12.8
130°-140°	720.3	13.7
140°-150°	673.5	12.8
150°-160°	543.1	10.3
160°-170°	350.3	6.6
170°-180°	120.7	2.3
0°-30°	425.2	8.1
0°-40°	673.4	12.8
0°-60°	1112.3	21.1
0°-90°	1339.6	25.4
90°-120°	850.3	16.1
90°-150°	2917.3	55.3
90°-180°	3931.0	74.6
0°-180°	5271.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	579	579	579	579	579	
5°	578	576	571	575	574	55
15°	550	546	535	534	531	155
25°	498	490	471	464	460	229
35°	430	416	394	379	371	269
45°	351	334	308	286	278	271
55°	266	248	219	196	188	238
65°	181	162	133	114	109	179
75°	96	80	59	49	46	101
85°	24	15	14	13	13	26
90°	3	13	21	27	28	4
95°	52	20	21	27	28	64
105°	286	292	296	305	271	299
115°	534	537	536	538	538	526
125°	751	754	753	756	756	670
135°	931	930	934	936	938	718
145°	1074	1077	1077	1078	1080	671
155°	1177	1178	1176	1179	1176	543
165°	1242	1237	1237	1245	1236	351
175°	1270	1265	1266	1274	1263	121
180°	1270	1270	1270	1270	1270	

TEST NUMBER: P1013309

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	578.6	578.6	578.6	578.6	578.6
2.5°	580.4	578.6	573.8	578.6	578.2
5°	577.7	576.0	570.7	575.1	574.2
7.5°	573.8	572.0	565.3	568.4	567.1
10°	567.6	565.3	557.4	559.1	557.4
12.5°	559.6	556.9	547.2	548.1	545.4
15°	550.3	546.3	535.2	534.3	531.2
17.5°	539.6	533.9	521.0	518.8	514.4
20°	526.8	521.0	506.0	502.4	496.7
22.5°	512.6	506.0	489.6	483.8	479.4
25°	497.6	489.6	471.4	463.9	459.5
27.5°	482.0	472.3	453.3	444.4	438.2
30°	465.7	454.6	433.8	422.7	415.6
32.5°	448.4	435.5	413.8	400.5	393.9
35°	430.2	416.0	393.9	378.8	370.8
37.5°	411.2	396.5	372.2	355.8	347.8
40°	390.8	376.2	350.9	332.3	324.3
42.5°	371.3	355.8	329.2	310.1	301.7
45°	350.9	334.5	307.9	286.2	278.2
47.5°	330.1	313.2	285.8	263.2	254.3
50°	308.8	291.5	263.2	241.0	232.6
52.5°	287.1	270.3	241.0	218.4	209.6
55°	265.8	248.1	219.3	196.3	187.9
57.5°	245.0	226.4	198.0	174.6	168.4
60°	222.4	204.7	176.3	153.3	146.2
62.5°	202.0	183.4	154.2	133.4	128.0
65°	180.8	161.7	133.4	114.3	109.0
67.5°	158.6	140.4	113.9	97.0	90.8
70°	137.8	119.2	93.9	79.3	74.9
72.5°	115.6	99.2	75.8	63.8	59.8
75°	96.1	79.8	58.9	48.7	46.1
77.5°	75.8	61.6	43.9	36.8	35.9
80°	56.3	43.4	30.1	28.8	28.4
82.5°	39.4	27.9	21.7	20.8	20.4
85°	23.9	15.1	13.7	12.8	12.8
87.5°	10.2	6.6	6.2	5.8	6.2
90°	2.9	13.3	20.9	26.6	28.5
92.5°	14.3	12.4	20.0	25.7	25.7
95°	52.3	20.0	20.9	26.6	27.6
97.5°	99.8	120.7	20.9	25.7	26.6
100°	155.8	172.9	41.8	25.7	26.6
102.5°	218.6	230.0	241.4	27.6	27.6
105°	286.0	291.7	296.5	305.0	270.8
107.5°	347.8	350.6	357.3	362.0	365.9
110°	410.5	413.4	419.1	421.0	423.8

TEST NUMBER: P1013309

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	471.3	477.0	478.9	478.0	481.8
115°	534.0	536.9	535.9	537.8	537.8
117.5°	590.1	593.9	596.8	595.8	595.8
120°	647.1	650.9	650.0	651.9	650.0
122.5°	700.3	702.2	704.1	705.1	703.2
125°	750.7	754.5	752.6	755.5	756.4
127.5°	799.2	800.1	804.9	803.9	803.0
130°	845.7	846.7	849.5	850.5	850.5
132.5°	888.5	890.4	894.2	895.1	894.2
135°	931.3	930.3	934.1	936.0	937.9
137.5°	969.3	969.3	974.0	975.9	975.0
140°	1006.3	1008.2	1010.1	1013.0	1013.9
142.5°	1039.6	1043.4	1044.3	1046.2	1046.2
145°	1073.8	1076.6	1076.6	1077.6	1079.5
147.5°	1100.4	1106.1	1105.2	1106.1	1107.1
150°	1129.9	1133.7	1132.7	1132.7	1133.7
152.5°	1154.6	1157.4	1155.5	1157.4	1156.5
155°	1177.4	1178.3	1175.5	1179.3	1176.4
157.5°	1197.3	1197.3	1193.5	1198.3	1193.5
160°	1214.4	1211.6	1210.6	1216.3	1210.6
162.5°	1229.6	1225.8	1224.9	1230.6	1223.9
165°	1242.0	1237.2	1237.2	1244.8	1236.3
167.5°	1252.4	1247.7	1246.7	1255.3	1245.8
170°	1261.0	1255.3	1256.2	1263.8	1254.3
172.5°	1266.7	1261.0	1261.9	1269.6	1259.1
175°	1270.5	1264.8	1265.7	1274.3	1262.9
177.5°	1273.4	1266.7	1268.6	1276.2	1264.8
180°	1270.5	1270.5	1270.5	1270.5	1270.5

(END OF REPORT)