

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013315

Luminaire Tested: S124RDIP-B350D1205UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013315
REPORT IS A COMBINATION OF REPORTS P999270 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D1205UB2750-4F0-XX-W2A-F_2700K
Description: Define 4 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6144.0 lumens
Efficiency: N/A
Efficacy: 128.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013315

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1013315

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31			22
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	27	27	26			19
2	84	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22			16
3	76	67	60	55	67	60	54	50	46	42	39	33	31	29	22	20	19			14
4	70	60	52	46	62	53	47	42	41	37	33	30	27	25	19	18	16			12
5	64	53	45	40	56	47	41	36	37	32	29	27	24	21	17	16	14			10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13			9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	13	11			8
8	50	38	31	26	44	35	28	24	27	22	19	20	17	15	13	11	10			7
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9			7
10	43	32	25	21	38	29	23	19	23	18	15	17	14	12	11	9	8			6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4863	4863	4863
5°	4864	4719	4719
10°	4823	4570	4516
15°	4757	4384	4275
20°	4670	4173	4001
25°	4561	3945	3733
30°	4454	3713	3432
35°	4338	3477	3139
40°	4200	3223	2837
45°	4069	2971	2538
50°	3921	2695	2234
55°	3761	2414	1921
60°	3583	2114	1612
65°	3412	1772	1313
70°	3168	1410	1004
75°	2856	1025	702
80°	2385	631	504
85°	1797	364	277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4069 cd/sqm

TEST NUMBER: P1013315

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.1	0.9
10°-20°	156.4	2.5
20°-30°	225.7	3.7
30°-40°	255.9	4.2
40°-50°	247.0	4.0
50°-60°	205.4	3.3
60°-70°	141.8	2.3
70°-80°	71.6	1.2
80°-90°	21.4	0.3
90°-100°	51.1	0.8
100°-110°	336.5	5.5
110°-120°	642.5	10.5
120°-130°	815.7	13.3
130°-140°	872.6	14.2
140°-150°	815.9	13.3
150°-160°	658.0	10.7
160°-170°	424.3	6.9
170°-180°	146.2	2.4
0°-30°	438.2	7.1
0°-40°	694.0	11.3
0°-60°	1146.4	18.7
0°-90°	1381.2	22.5
90°-120°	1030.1	16.8
90°-150°	3534.3	57.5
90°-180°	4763.0	77.5
0°-180°	6144.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	596	596	596	596	596	
5°	596	594	588	593	592	57
15°	567	563	552	551	548	160
25°	513	505	486	478	474	236
35°	443	429	406	390	382	277
45°	362	345	317	295	287	279
55°	274	256	226	202	194	245
65°	186	167	138	118	112	184
75°	99	82	61	50	48	105
85°	25	16	14	13	13	27
90°	4	16	25	32	34	5
95°	63	24	25	32	33	78
105°	346	353	359	370	328	363
115°	647	650	649	652	652	637
125°	910	914	912	915	916	812
135°	1128	1127	1132	1134	1136	869
145°	1301	1304	1304	1306	1308	813
155°	1426	1428	1424	1429	1425	658
165°	1505	1499	1499	1508	1498	425
175°	1539	1532	1533	1544	1530	147
180°	1539	1539	1539	1539	1539	

TEST NUMBER: P1013315

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	596.4	596.4	596.4	596.4	596.4
2.5°	598.2	596.4	591.4	596.4	595.9
5°	595.5	593.6	588.2	592.7	591.8
7.5°	591.4	589.5	582.7	585.9	584.5
10°	585.0	582.7	574.5	576.3	574.5
12.5°	576.7	574.0	564.0	564.9	562.1
15°	567.2	563.0	551.6	550.7	547.5
17.5°	556.2	550.3	537.0	534.7	530.2
20°	543.0	537.0	521.5	517.8	511.9
22.5°	528.3	521.5	504.6	498.7	494.1
25°	512.8	504.6	485.9	478.1	473.5
27.5°	496.8	486.8	467.1	458.0	451.6
30°	479.9	468.5	447.1	435.6	428.3
32.5°	462.1	448.9	426.5	412.8	406.0
35°	443.4	428.8	406.0	390.4	382.2
37.5°	423.8	408.7	383.6	366.7	358.5
40°	402.8	387.7	361.7	342.5	334.3
42.5°	382.7	366.7	339.3	319.7	311.0
45°	361.7	344.8	317.4	295.0	286.8
47.5°	340.2	322.8	294.5	271.2	262.1
50°	318.3	300.5	271.2	248.4	239.7
52.5°	295.9	278.6	248.4	225.1	216.0
55°	274.0	255.7	226.0	202.3	193.6
57.5°	252.5	233.3	204.1	179.9	173.5
60°	229.2	211.0	181.7	158.0	150.7
62.5°	208.2	189.1	158.9	137.5	132.0
65°	186.3	166.7	137.5	117.8	112.3
67.5°	163.5	144.8	117.4	100.0	93.6
70°	142.0	122.8	96.8	81.7	77.2
72.5°	119.2	102.3	78.1	65.8	61.6
75°	99.1	82.2	60.7	50.2	47.5
77.5°	78.1	63.5	45.2	37.9	37.0
80°	58.0	44.8	31.1	29.7	29.2
82.5°	40.6	28.8	22.4	21.5	21.0
85°	24.7	15.5	14.2	13.2	13.2
87.5°	10.5	6.8	6.4	5.9	6.4
90°	3.5	16.1	25.3	32.2	34.5
92.5°	17.3	15.0	24.2	31.1	31.1
95°	63.3	24.2	25.3	32.2	33.4
97.5°	120.9	146.2	25.3	31.1	32.2
100°	188.8	209.5	50.7	31.1	32.2
102.5°	264.8	278.6	292.4	33.4	33.4
105°	346.5	353.4	359.2	369.5	328.1
107.5°	421.4	424.8	432.9	438.6	443.2
110°	497.3	500.8	507.7	510.0	513.4

TEST NUMBER: P1013315

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	571.0	577.9	580.2	579.1	583.7
115°	647.0	650.4	649.3	651.6	651.6
117.5°	714.9	719.5	723.0	721.8	721.8
120°	784.0	788.6	787.4	789.7	787.4
122.5°	848.5	850.8	853.1	854.2	851.9
125°	909.5	914.1	911.8	915.2	916.4
127.5°	968.2	969.3	975.1	973.9	972.8
130°	1024.6	1025.7	1029.2	1030.4	1030.4
132.5°	1076.4	1078.7	1083.3	1084.5	1083.3
135°	1128.2	1127.1	1131.7	1134.0	1136.3
137.5°	1174.3	1174.3	1180.0	1182.3	1181.2
140°	1219.2	1221.5	1223.8	1227.2	1228.4
142.5°	1259.4	1264.1	1265.2	1267.5	1267.5
145°	1300.9	1304.3	1304.3	1305.5	1307.8
147.5°	1333.1	1340.0	1338.9	1340.0	1341.2
150°	1368.8	1373.4	1372.3	1372.3	1373.4
152.5°	1398.7	1402.2	1399.9	1402.2	1401.1
155°	1426.4	1427.5	1424.1	1428.7	1425.2
157.5°	1450.6	1450.6	1445.9	1451.7	1445.9
160°	1471.3	1467.8	1466.7	1473.6	1466.7
162.5°	1489.7	1485.1	1483.9	1490.8	1482.8
165°	1504.7	1498.9	1498.9	1508.1	1497.8
167.5°	1517.3	1511.6	1510.4	1520.8	1509.3
170°	1527.7	1520.8	1521.9	1531.1	1519.6
172.5°	1534.6	1527.7	1528.8	1538.0	1525.4
175°	1539.2	1532.3	1533.4	1543.8	1530.0
177.5°	1542.7	1534.6	1536.9	1546.1	1532.3
180°	1539.2	1539.2	1539.2	1539.2	1539.2

(END OF REPORT)