

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007515

Luminaire Tested: S123IP-B1195UB2750-4F0-XX-W2A_4000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007515
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B1195UB2750-4F0-XX-W2A_4000K
Description: Define 3 Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4740.0 lumens
Efficiency: N/A
Efficacy: 135.4 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 35
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007515

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007515

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007515

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.1	0.1
90°-100°	54.8	1.2
100°-110°	264.9	5.6
110°-120°	649.2	13.7
120°-130°	824.1	17.4
130°-140°	880.4	18.6
140°-150°	823.3	17.4
150°-160°	664.0	14.0
160°-170°	428.5	9.0
170°-180°	147.7	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.1	0.1
90°-120°	968.9	20.4
90°-150°	3496.7	73.8
90°-180°	4737.0	99.9
0°-180°	4740.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	13	28	32	35	4
95°	70	23	36	44	44	84
105°	344	357	253	48	51	365
115°	645	652	663	674	679	637
125°	910	919	924	926	928	813
135°	1132	1139	1144	1148	1144	872
145°	1307	1315	1317	1320	1320	818
155°	1440	1437	1438	1444	1437	663
165°	1518	1515	1513	1523	1515	429
175°	1554	1548	1549	1557	1548	148
180°	1554	1554	1554	1554	1554	

TEST NUMBER: P1007515

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.2	12.7	27.7	32.3	34.6
92.5°	26.6	19.6	30.0	38.1	39.2
95°	70.4	23.1	35.8	43.9	43.9
97.5°	128.1	95.8	36.9	46.2	47.3
100°	195.1	218.2	38.1	47.3	48.5
102.5°	271.3	286.3	85.4	47.3	49.6
105°	344.0	356.7	252.8	48.5	50.8
107.5°	421.4	431.7	449.1	271.3	120.1
110°	498.7	507.9	520.6	482.5	317.5

TEST NUMBER: P1007515

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	572.6	580.7	593.4	603.7	601.4
115°	645.3	652.2	662.6	674.2	678.8
117.5°	716.9	725.0	730.7	740.0	741.1
120°	782.7	793.1	796.5	805.8	805.8
122.5°	849.6	857.7	862.3	868.1	869.3
125°	909.7	918.9	923.5	925.8	928.1
127.5°	969.7	978.9	984.7	988.2	985.8
130°	1025.1	1034.3	1038.9	1043.6	1041.3
132.5°	1078.2	1087.4	1090.9	1095.5	1092.0
135°	1132.5	1139.4	1144.0	1147.5	1144.0
137.5°	1178.6	1187.9	1190.2	1195.9	1193.6
140°	1224.8	1231.7	1235.2	1239.8	1237.5
142.5°	1267.5	1274.4	1277.9	1281.4	1277.9
145°	1306.8	1314.8	1317.2	1319.5	1319.5
147.5°	1344.9	1350.6	1352.9	1355.2	1349.5
150°	1379.5	1383.0	1385.3	1387.6	1384.1
152.5°	1410.7	1411.8	1413.0	1417.6	1411.8
155°	1439.5	1437.2	1438.4	1444.1	1437.2
157.5°	1462.6	1462.6	1461.5	1468.4	1459.1
160°	1483.4	1482.2	1481.1	1488.0	1479.9
162.5°	1503.0	1499.5	1498.4	1506.5	1499.5
165°	1518.0	1514.6	1513.4	1522.6	1514.6
167.5°	1530.7	1526.1	1526.1	1535.3	1526.1
170°	1541.1	1536.5	1536.5	1545.7	1536.5
172.5°	1548.0	1542.3	1543.4	1552.6	1542.3
175°	1553.8	1548.0	1549.2	1557.3	1548.0
177.5°	1556.1	1550.3	1551.5	1560.7	1549.2
180°	1553.8	1553.8	1553.8	1553.8	1553.8

(END OF REPORT)