

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013324

Luminaire Tested: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013324
REPORT IS A COMBINATION OF REPORTS P999310 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_2700K
Description: Define 4 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2837.0 lumens
Efficiency: N/A
Efficacy: 127.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013324

CATALOG NUMBER: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1013324

CATALOG NUMBER: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49		
1	98	94	90	86	90	86	83	80	73	70	68	60	59	57	49	48	47	41		
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	43	41	40	35		
3	82	72	65	59	75	67	61	56	57	52	48	47	44	41	39	36	34	30		
4	75	64	56	50	69	59	53	47	51	45	41	42	38	35	35	32	30	26		
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23		
6	63	51	43	38	58	48	41	35	41	35	31	34	30	27	28	25	23	20		
7	59	46	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20	18		
8	54	42	35	29	50	39	32	28	34	28	25	29	25	21	24	21	18	16		
9	51	39	31	26	47	36	29	25	31	26	22	27	22	19	22	19	17	15		
10	47	35	28	24	44	33	27	22	29	23	20	25	20	18	21	17	15	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4863	4863	4863
5°	4864	4719	4719
10°	4823	4570	4516
15°	4757	4384	4275
20°	4670	4173	4001
25°	4561	3945	3733
30°	4454	3713	3432
35°	4338	3477	3139
40°	4200	3223	2837
45°	4069	2971	2538
50°	3921	2695	2234
55°	3761	2414	1921
60°	3583	2114	1612
65°	3412	1772	1313
70°	3168	1410	1004
75°	2856	1025	702
80°	2385	631	504
85°	1797	364	277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4069 cd/sqm

TEST NUMBER: P1013324

CATALOG NUMBER: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.1	2.0
10°-20°	156.4	5.5
20°-30°	225.7	8.0
30°-40°	255.9	9.0
40°-50°	247.0	8.7
50°-60°	205.4	7.2
60°-70°	141.8	5.0
70°-80°	71.6	2.5
80°-90°	19.2	0.7
90°-100°	15.7	0.6
100°-110°	103.0	3.6
110°-120°	196.7	6.9
120°-130°	249.7	8.8
130°-140°	267.1	9.4
140°-150°	249.8	8.8
150°-160°	201.4	7.1
160°-170°	129.9	4.6
170°-180°	44.8	1.6
0°-30°	438.2	15.4
0°-40°	694.0	24.5
0°-60°	1146.4	40.4
0°-90°	1379.0	48.6
90°-120°	315.4	11.1
90°-150°	1081.9	38.1
90°-180°	1458.0	51.4
0°-180°	2837.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	596	596	596	596	596	
5°	596	594	588	593	592	57
15°	567	563	552	551	548	160
25°	513	505	486	478	474	236
35°	443	429	406	390	382	277
45°	362	345	317	295	287	279
55°	274	256	226	202	194	245
65°	186	167	138	118	112	184
75°	99	82	61	50	48	105
85°	25	16	14	13	13	27
90°	1	5	8	10	11	2
95°	19	7	8	10	10	24
105°	106	108	110	113	100	111
115°	198	199	199	200	200	195
125°	278	280	279	280	280	249
135°	345	345	346	347	348	266
145°	398	399	399	400	400	249
155°	437	437	436	437	436	201
165°	461	459	459	462	458	130
175°	471	469	469	473	468	45
180°	471	471	471	471	471	

TEST NUMBER: P1013324

CATALOG NUMBER: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	596.4	596.4	596.4	596.4	596.4
2.5°	598.2	596.4	591.4	596.4	595.9
5°	595.5	593.6	588.2	592.7	591.8
7.5°	591.4	589.5	582.7	585.9	584.5
10°	585.0	582.7	574.5	576.3	574.5
12.5°	576.7	574.0	564.0	564.9	562.1
15°	567.2	563.0	551.6	550.7	547.5
17.5°	556.2	550.3	537.0	534.7	530.2
20°	543.0	537.0	521.5	517.8	511.9
22.5°	528.3	521.5	504.6	498.7	494.1
25°	512.8	504.6	485.9	478.1	473.5
27.5°	496.8	486.8	467.1	458.0	451.6
30°	479.9	468.5	447.1	435.6	428.3
32.5°	462.1	448.9	426.5	412.8	406.0
35°	443.4	428.8	406.0	390.4	382.2
37.5°	423.8	408.7	383.6	366.7	358.5
40°	402.8	387.7	361.7	342.5	334.3
42.5°	382.7	366.7	339.3	319.7	311.0
45°	361.7	344.8	317.4	295.0	286.8
47.5°	340.2	322.8	294.5	271.2	262.1
50°	318.3	300.5	271.2	248.4	239.7
52.5°	295.9	278.6	248.4	225.1	216.0
55°	274.0	255.7	226.0	202.3	193.6
57.5°	252.5	233.3	204.1	179.9	173.5
60°	229.2	211.0	181.7	158.0	150.7
62.5°	208.2	189.1	158.9	137.5	132.0
65°	186.3	166.7	137.5	117.8	112.3
67.5°	163.5	144.8	117.4	100.0	93.6
70°	142.0	122.8	96.8	81.7	77.2
72.5°	119.2	102.3	78.1	65.8	61.6
75°	99.1	82.2	60.7	50.2	47.5
77.5°	78.1	63.5	45.2	37.9	37.0
80°	58.0	44.8	31.1	29.7	29.2
82.5°	40.6	28.8	22.4	21.5	21.0
85°	24.7	15.5	14.2	13.2	13.2
87.5°	10.5	6.8	6.4	5.9	6.4
90°	1.1	4.9	7.8	9.9	10.6
92.5°	5.3	4.6	7.4	9.5	9.5
95°	19.4	7.4	7.8	9.9	10.2
97.5°	37.0	44.8	7.8	9.5	9.9
100°	57.8	64.1	15.5	9.5	9.9
102.5°	81.1	85.3	89.5	10.2	10.2
105°	106.1	108.2	110.0	113.1	100.4
107.5°	129.0	130.0	132.5	134.3	135.7
110°	152.2	153.3	155.4	156.1	157.2

TEST NUMBER: P1013324

CATALOG NUMBER: S124RDIP-B350D365UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	174.8	176.9	177.6	177.3	178.7
115°	198.1	199.1	198.8	199.5	199.5
117.5°	218.9	220.3	221.3	221.0	221.0
120°	240.0	241.4	241.1	241.8	241.1
122.5°	259.7	260.4	261.1	261.5	260.8
125°	278.4	279.8	279.1	280.2	280.5
127.5°	296.4	296.7	298.5	298.1	297.8
130°	313.7	314.0	315.1	315.4	315.4
132.5°	329.5	330.2	331.6	332.0	331.6
135°	345.4	345.0	346.4	347.1	347.8
137.5°	359.5	359.5	361.2	361.9	361.6
140°	373.2	373.9	374.6	375.7	376.0
142.5°	385.6	387.0	387.3	388.0	388.0
145°	398.2	399.3	399.3	399.6	400.4
147.5°	408.1	410.2	409.9	410.2	410.6
150°	419.0	420.4	420.1	420.1	420.4
152.5°	428.2	429.3	428.5	429.3	428.9
155°	436.7	437.0	435.9	437.4	436.3
157.5°	444.1	444.1	442.6	444.4	442.6
160°	450.4	449.3	449.0	451.1	449.0
162.5°	456.0	454.6	454.3	456.4	453.9
165°	460.6	458.9	458.9	461.7	458.5
167.5°	464.5	462.7	462.4	465.6	462.0
170°	467.7	465.6	465.9	468.7	465.2
172.5°	469.8	467.7	468.0	470.8	467.0
175°	471.2	469.1	469.4	472.6	468.4
177.5°	472.2	469.8	470.5	473.3	469.1
180°	471.2	471.2	471.2	471.2	471.2

(END OF REPORT)