

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007536

Luminaire Tested: S123IP-B365UB2750-4F0-XX-W2A-1_5000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007536
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B365UB2750-4F0-XX-W2A-1_5000K
Description: Define 3 Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1207.0 lumens
Efficiency: N/A
Efficacy: 129.8 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 9.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007536

CATALOG NUMBER: S123IP-B365UB2750-4F0-XX-W2A-1_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1007536

CATALOG NUMBER: S123IP-B365UB2750-4F0-XX-W2A-1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007536

CATALOG NUMBER: S123IP-B365UB2750-4F0-XX-W2A-1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.9	0.1
90°-100°	28.0	2.3
100°-110°	84.8	7.0
110°-120°	144.4	12.0
120°-130°	189.9	15.7
130°-140°	213.5	17.7
140°-150°	209.9	17.4
150°-160°	176.7	14.6
160°-170°	117.6	9.7
170°-180°	41.2	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	0.9	0.1
90°-120°	257.2	21.3
90°-150°	870.6	72.1
90°-180°	1206.0	99.9
0°-180°	1207.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	4	8	10	10	1
95°	20	23	25	27	27	22
105°	77	78	81	81	81	82
115°	145	146	146	146	146	144
125°	213	214	213	212	210	190
135°	276	278	278	276	276	213
145°	335	335	336	336	335	209
155°	383	383	384	385	383	176
165°	418	416	416	418	416	118
175°	434	433	433	435	432	41
180°	435	435	435	435	435	

TEST NUMBER: P1007536

CATALOG NUMBER: S123IP-B365UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.3	3.8	8.2	9.6	10.3
92.5°	10.3	12.3	14.4	15.4	14.7
95°	20.2	22.6	25.3	26.7	26.7
97.5°	33.2	34.9	36.9	38.6	38.3
100°	46.5	48.6	50.3	51.3	52.0
102.5°	61.9	62.9	65.3	66.3	66.0
105°	76.9	77.6	80.7	80.7	81.4
107.5°	94.7	95.1	96.4	97.5	97.1
110°	111.1	111.8	112.5	113.9	113.2

TEST NUMBER: P1007536

CATALOG NUMBER: S123IP-B365UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	128.2	128.6	128.6	130.3	130.3
115°	145.3	146.3	145.7	146.0	145.7
117.5°	162.8	163.1	162.4	162.4	161.4
120°	178.8	180.9	179.2	178.8	178.1
122.5°	195.6	197.0	196.3	195.2	194.2
125°	212.7	213.7	213.0	211.7	210.3
127.5°	228.4	230.5	229.8	227.7	226.4
130°	244.1	246.9	245.8	244.5	242.1
132.5°	259.9	262.6	261.9	260.2	258.5
135°	275.9	278.0	277.6	276.3	275.6
137.5°	290.6	292.4	293.4	291.7	290.6
140°	306.0	307.7	308.1	307.7	305.3
142.5°	320.0	321.8	322.4	322.1	320.4
145°	334.8	335.4	336.5	336.1	334.8
147.5°	347.4	348.8	349.8	349.8	347.7
150°	360.7	361.4	362.1	362.1	360.1
152.5°	371.7	372.7	373.0	373.7	372.0
155°	383.3	383.3	383.6	385.0	382.6
157.5°	393.2	392.9	393.2	394.6	392.5
160°	402.5	401.8	401.8	403.5	402.1
162.5°	410.7	409.6	410.0	411.7	409.3
165°	417.5	416.5	416.5	418.5	416.1
167.5°	423.3	421.9	422.3	424.3	422.3
170°	428.1	426.7	426.7	429.1	426.7
172.5°	431.9	430.5	430.5	432.5	430.2
175°	434.3	432.9	432.9	434.9	432.5
177.5°	435.6	434.3	434.3	436.3	433.9
180°	435.3	435.3	435.3	435.3	435.3

(END OF REPORT)