

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013337

Luminaire Tested: S124RDIP-B350D590UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013337
REPORT IS A COMBINATION OF REPORTS P999354 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D590UB2750-4F0-XX-W2A-F_5000K
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3612.0 lumens
Efficiency: N/A
Efficacy: 127.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013337

CATALOG NUMBER: S124RDIP-B350D590UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013337

CATALOG NUMBER: S124RDIP-B350D590UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44
1	95	91	87	84	86	83	79	77	67	65	63	53	51	50	39	39	38
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	35	33	32
3	79	70	63	57	72	64	58	53	52	48	44	41	38	36	31	29	27
4	72	62	54	49	65	57	50	45	46	41	38	37	33	31	28	26	24
5	67	55	47	42	60	51	44	39	41	36	33	33	29	27	25	23	21
6	61	50	42	36	55	45	38	33	37	32	28	30	26	23	23	20	18
7	57	45	37	32	51	41	34	29	34	29	25	27	23	21	21	18	16
8	52	41	33	28	48	37	31	26	31	26	22	25	21	18	19	17	15
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4718	4718	4718
5°	4719	4579	4579
10°	4679	4434	4381
15°	4615	4254	4148
20°	4530	4049	3882
25°	4426	3827	3622
30°	4323	3602	3331
35°	4209	3373	3045
40°	4075	3127	2752
45°	3948	2882	2462
50°	3804	2616	2168
55°	3649	2342	1864
60°	3477	2051	1564
65°	3311	1719	1275
70°	3074	1367	974
75°	2769	995	682
80°	2316	610	491
85°	1739	351	268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3948 cd/sqm

TEST NUMBER: P1013337

CATALOG NUMBER: S124RDIP-B350D590UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.4	1.5
10°-20°	151.7	4.2
20°-30°	219.0	6.1
30°-40°	248.2	6.9
40°-50°	239.7	6.6
50°-60°	199.3	5.5
60°-70°	137.5	3.8
70°-80°	69.5	1.9
80°-90°	19.2	0.5
90°-100°	24.4	0.7
100°-110°	160.6	4.4
110°-120°	306.7	8.5
120°-130°	389.4	10.8
130°-140°	416.5	11.5
140°-150°	389.5	10.8
150°-160°	314.1	8.7
160°-170°	202.6	5.6
170°-180°	69.8	1.9
0°-30°	425.2	11.8
0°-40°	673.4	18.6
0°-60°	1112.3	30.8
0°-90°	1338.5	37.1
90°-120°	491.7	13.6
90°-150°	1687.0	46.7
90°-180°	2273.0	62.9
0°-180°	3612.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	579	579	579	579	579	
5°	578	576	571	575	574	55
15°	550	546	535	534	531	155
25°	498	490	471	464	460	229
35°	430	416	394	379	371	269
45°	351	334	308	286	278	271
55°	266	248	219	196	188	238
65°	181	162	133	114	109	179
75°	96	80	59	49	46	101
85°	24	15	14	13	13	26
90°	2	8	12	15	16	3
95°	30	12	12	15	16	37
105°	165	169	172	176	157	173
115°	309	310	310	311	311	304
125°	434	436	435	437	437	388
135°	538	538	540	541	542	415
145°	621	623	623	623	624	388
155°	681	681	680	682	680	314
165°	718	716	716	720	715	203
175°	735	731	732	737	730	70
180°	735	735	735	735	735	

TEST NUMBER: P1013337

CATALOG NUMBER: S124RDIP-B350D590UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	578.6	578.6	578.6	578.6	578.6
2.5°	580.4	578.6	573.8	578.6	578.2
5°	577.7	576.0	570.7	575.1	574.2
7.5°	573.8	572.0	565.3	568.4	567.1
10°	567.6	565.3	557.4	559.1	557.4
12.5°	559.6	556.9	547.2	548.1	545.4
15°	550.3	546.3	535.2	534.3	531.2
17.5°	539.6	533.9	521.0	518.8	514.4
20°	526.8	521.0	506.0	502.4	496.7
22.5°	512.6	506.0	489.6	483.8	479.4
25°	497.6	489.6	471.4	463.9	459.5
27.5°	482.0	472.3	453.3	444.4	438.2
30°	465.7	454.6	433.8	422.7	415.6
32.5°	448.4	435.5	413.8	400.5	393.9
35°	430.2	416.0	393.9	378.8	370.8
37.5°	411.2	396.5	372.2	355.8	347.8
40°	390.8	376.2	350.9	332.3	324.3
42.5°	371.3	355.8	329.2	310.1	301.7
45°	350.9	334.5	307.9	286.2	278.2
47.5°	330.1	313.2	285.8	263.2	254.3
50°	308.8	291.5	263.2	241.0	232.6
52.5°	287.1	270.3	241.0	218.4	209.6
55°	265.8	248.1	219.3	196.3	187.9
57.5°	245.0	226.4	198.0	174.6	168.4
60°	222.4	204.7	176.3	153.3	146.2
62.5°	202.0	183.4	154.2	133.4	128.0
65°	180.8	161.7	133.4	114.3	109.0
67.5°	158.6	140.4	113.9	97.0	90.8
70°	137.8	119.2	93.9	79.3	74.9
72.5°	115.6	99.2	75.8	63.8	59.8
75°	96.1	79.8	58.9	48.7	46.1
77.5°	75.8	61.6	43.9	36.8	35.9
80°	56.3	43.4	30.1	28.8	28.4
82.5°	39.4	27.9	21.7	20.8	20.4
85°	23.9	15.1	13.7	12.8	12.8
87.5°	10.2	6.6	6.2	5.8	6.2
90°	1.6	7.7	12.1	15.4	16.5
92.5°	8.2	7.1	11.5	14.8	14.8
95°	30.2	11.5	12.1	15.4	15.9
97.5°	57.7	69.8	12.1	14.8	15.4
100°	90.1	100.0	24.2	14.8	15.4
102.5°	126.4	133.0	139.6	15.9	15.9
105°	165.4	168.7	171.5	176.4	156.6
107.5°	201.1	202.8	206.6	209.4	211.6
110°	237.4	239.0	242.3	243.4	245.1

TEST NUMBER: P1013337

CATALOG NUMBER: S124RDIP-B350D590UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	272.6	275.9	277.0	276.4	278.6
115°	308.8	310.5	309.9	311.0	311.0
117.5°	341.3	343.5	345.1	344.6	344.6
120°	374.2	376.4	375.9	377.0	375.9
122.5°	405.0	406.1	407.2	407.8	406.7
125°	434.1	436.3	435.2	436.9	437.4
127.5°	462.2	462.7	465.5	464.9	464.4
130°	489.1	489.6	491.3	491.8	491.8
132.5°	513.8	514.9	517.1	517.7	517.1
135°	538.5	538.0	540.2	541.3	542.4
137.5°	560.5	560.5	563.3	564.4	563.8
140°	582.0	583.1	584.1	585.8	586.3
142.5°	601.2	603.4	603.9	605.0	605.0
145°	621.0	622.6	622.6	623.2	624.3
147.5°	636.4	639.7	639.1	639.7	640.2
150°	653.4	655.6	655.0	655.0	655.6
152.5°	667.7	669.3	668.2	669.3	668.8
155°	680.9	681.4	679.8	682.0	680.3
157.5°	692.4	692.4	690.2	693.0	690.2
160°	702.3	700.6	700.1	703.4	700.1
162.5°	711.1	708.9	708.3	711.6	707.8
165°	718.2	715.5	715.5	719.9	714.9
167.5°	724.3	721.5	721.0	725.9	720.4
170°	729.2	725.9	726.5	730.9	725.4
172.5°	732.5	729.2	729.8	734.2	728.1
175°	734.7	731.4	732.0	736.9	730.3
177.5°	736.4	732.5	733.6	738.0	731.4
180°	734.7	734.7	734.7	734.7	734.7

(END OF REPORT)