

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013347

Luminaire Tested: S124RDIP-B350D810UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013347
REPORT IS A COMBINATION OF REPORTS P999394 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D810UB2750-4F0-XX-W2A-F_5000K
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4377.0 lumens
Efficiency: N/A
Efficacy: 128.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013347

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013347

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38
1	94	89	86	82	84	81	77	75	64	62	60	48	47	46	34	33	33
2	85	78	72	68	76	71	66	61	56	53	50	43	40	38	30	29	28
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24
4	71	61	53	48	64	55	49	44	44	39	36	34	31	28	24	22	21
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	22	20	18
6	60	49	41	35	54	44	37	32	35	30	27	27	24	21	20	18	16
7	56	44	36	31	50	40	33	28	32	27	24	25	21	19	18	16	14
8	51	40	32	27	46	36	30	25	29	24	21	23	19	17	17	14	13
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4718	4718	4718
5°	4719	4579	4579
10°	4679	4434	4381
15°	4615	4254	4148
20°	4530	4049	3882
25°	4426	3827	3622
30°	4323	3602	3331
35°	4209	3373	3045
40°	4075	3127	2752
45°	3948	2882	2462
50°	3804	2616	2168
55°	3649	2342	1864
60°	3477	2051	1564
65°	3311	1719	1275
70°	3074	1367	974
75°	2769	995	682
80°	2316	610	491
85°	1739	351	268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3948 cd/sqm

TEST NUMBER: P1013347

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.4	1.2
10°-20°	151.7	3.5
20°-30°	219.0	5.0
30°-40°	248.2	5.7
40°-50°	239.7	5.5
50°-60°	199.3	4.6
60°-70°	137.5	3.1
70°-80°	69.5	1.6
80°-90°	19.7	0.4
90°-100°	32.6	0.7
100°-110°	214.6	4.9
110°-120°	409.8	9.4
120°-130°	520.3	11.9
130°-140°	556.6	12.7
140°-150°	520.4	11.9
150°-160°	419.7	9.6
160°-170°	270.7	6.2
170°-180°	93.3	2.1
0°-30°	425.2	9.7
0°-40°	673.4	15.4
0°-60°	1112.3	25.4
0°-90°	1339.0	30.6
90°-120°	657.0	15.0
90°-150°	2254.3	51.5
90°-180°	3038.0	69.4
0°-180°	4377.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	579	579	579	579	579	
5°	578	576	571	575	574	55
15°	550	546	535	534	531	155
25°	498	490	471	464	460	229
35°	430	416	394	379	371	269
45°	351	334	308	286	278	271
55°	266	248	219	196	188	238
65°	181	162	133	114	109	179
75°	96	80	59	49	46	101
85°	24	15	14	13	13	26
90°	2	10	16	21	22	4
95°	40	15	16	21	21	50
105°	221	225	229	236	209	231
115°	413	415	414	416	416	406
125°	580	583	582	584	584	518
135°	720	719	722	723	725	554
145°	830	832	832	833	834	518
155°	910	911	908	911	909	420
165°	960	956	956	962	955	271
175°	982	977	978	985	976	93
180°	982	982	982	982	982	

TEST NUMBER: P1013347

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	578.6	578.6	578.6	578.6	578.6
2.5°	580.4	578.6	573.8	578.6	578.2
5°	577.7	576.0	570.7	575.1	574.2
7.5°	573.8	572.0	565.3	568.4	567.1
10°	567.6	565.3	557.4	559.1	557.4
12.5°	559.6	556.9	547.2	548.1	545.4
15°	550.3	546.3	535.2	534.3	531.2
17.5°	539.6	533.9	521.0	518.8	514.4
20°	526.8	521.0	506.0	502.4	496.7
22.5°	512.6	506.0	489.6	483.8	479.4
25°	497.6	489.6	471.4	463.9	459.5
27.5°	482.0	472.3	453.3	444.4	438.2
30°	465.7	454.6	433.8	422.7	415.6
32.5°	448.4	435.5	413.8	400.5	393.9
35°	430.2	416.0	393.9	378.8	370.8
37.5°	411.2	396.5	372.2	355.8	347.8
40°	390.8	376.2	350.9	332.3	324.3
42.5°	371.3	355.8	329.2	310.1	301.7
45°	350.9	334.5	307.9	286.2	278.2
47.5°	330.1	313.2	285.8	263.2	254.3
50°	308.8	291.5	263.2	241.0	232.6
52.5°	287.1	270.3	241.0	218.4	209.6
55°	265.8	248.1	219.3	196.3	187.9
57.5°	245.0	226.4	198.0	174.6	168.4
60°	222.4	204.7	176.3	153.3	146.2
62.5°	202.0	183.4	154.2	133.4	128.0
65°	180.8	161.7	133.4	114.3	109.0
67.5°	158.6	140.4	113.9	97.0	90.8
70°	137.8	119.2	93.9	79.3	74.9
72.5°	115.6	99.2	75.8	63.8	59.8
75°	96.1	79.8	58.9	48.7	46.1
77.5°	75.8	61.6	43.9	36.8	35.9
80°	56.3	43.4	30.1	28.8	28.4
82.5°	39.4	27.9	21.7	20.8	20.4
85°	23.9	15.1	13.7	12.8	12.8
87.5°	10.2	6.6	6.2	5.8	6.2
90°	2.2	10.3	16.2	20.6	22.0
92.5°	11.0	9.5	15.4	19.8	19.8
95°	40.4	15.4	16.2	20.6	21.3
97.5°	77.1	93.3	16.2	19.8	20.6
100°	120.4	133.6	32.3	19.8	20.6
102.5°	168.9	177.7	186.5	21.3	21.3
105°	221.0	225.4	229.1	235.7	209.3
107.5°	268.8	271.0	276.1	279.8	282.7
110°	317.2	319.4	323.8	325.3	327.5

TEST NUMBER: P1013347

CATALOG NUMBER: S124RDIP-B350D810UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	364.2	368.6	370.1	369.4	372.3
115°	412.7	414.9	414.2	415.6	415.6
117.5°	456.0	458.9	461.2	460.4	460.4
120°	500.1	503.0	502.3	503.7	502.3
122.5°	541.2	542.7	544.1	544.9	543.4
125°	580.1	583.0	581.6	583.8	584.5
127.5°	617.6	618.3	622.0	621.2	620.5
130°	653.5	654.3	656.5	657.2	657.2
132.5°	686.6	688.1	691.0	691.7	691.0
135°	719.6	718.9	721.8	723.3	724.8
137.5°	749.0	749.0	752.7	754.1	753.4
140°	777.6	779.1	780.6	782.8	783.5
142.5°	803.3	806.3	807.0	808.5	808.5
145°	829.8	832.0	832.0	832.7	834.2
147.5°	850.3	854.7	854.0	854.7	855.5
150°	873.1	876.0	875.3	875.3	876.0
152.5°	892.2	894.4	892.9	894.4	893.7
155°	909.8	910.6	908.3	911.3	909.1
157.5°	925.2	925.2	922.3	926.0	922.3
160°	938.5	936.3	935.5	939.9	935.5
162.5°	950.2	947.3	946.5	950.9	945.8
165°	959.8	956.1	956.1	962.0	955.3
167.5°	967.8	964.2	963.4	970.0	962.7
170°	974.4	970.0	970.8	976.6	969.3
172.5°	978.8	974.4	975.2	981.0	973.0
175°	981.8	977.4	978.1	984.7	975.9
177.5°	984.0	978.8	980.3	986.2	977.4
180°	981.8	981.8	981.8	981.8	981.8

(END OF REPORT)