

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007562

Luminaire Tested: S123IP-B585UB2750-4F0-XX-W2A-1_2700K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007562
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B585UB2750-4F0-XX-W2A-1_2700K
Description: Define 3 Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2000.0 lumens
Efficiency: N/A
Efficacy: 129.9 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 15.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007562

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A-1_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1007562

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A-1_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007562

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A-1_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.5	0.1
90°-100°	46.4	2.3
100°-110°	140.5	7.0
110°-120°	239.2	12.0
120°-130°	314.7	15.7
130°-140°	353.8	17.7
140°-150°	347.8	17.4
150°-160°	292.8	14.6
160°-170°	194.9	9.7
170°-180°	68.3	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.5	0.1
90°-120°	426.2	21.3
90°-150°	1442.5	72.1
90°-180°	1998.0	99.9
0°-180°	2000.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	6	14	16	17	2
95°	33	37	42	44	44	37
105°	128	129	134	134	135	136
115°	241	242	241	242	241	238
125°	352	354	353	351	348	314
135°	457	461	460	458	457	352
145°	555	556	558	557	555	346
155°	635	635	636	638	634	292
165°	692	690	690	694	690	195
175°	720	717	717	721	717	68
180°	721	721	721	721	721	

TEST NUMBER: P1007562

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.6	6.2	13.6	15.9	17.0
92.5°	17.0	20.4	23.8	25.5	24.4
95°	33.4	37.4	41.9	44.2	44.2
97.5°	55.0	57.8	61.2	64.0	63.5
100°	77.1	80.5	83.3	85.0	86.1
102.5°	102.6	104.3	108.2	109.9	109.4
105°	127.5	128.6	133.7	133.7	134.8
107.5°	156.9	157.5	159.8	161.5	160.9
110°	184.1	185.3	186.4	188.7	187.5

TEST NUMBER: P1007562

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	212.5	213.0	213.0	215.9	215.9
115°	240.8	242.5	241.4	241.9	241.4
117.5°	269.7	270.3	269.1	269.1	267.4
120°	296.3	299.7	296.9	296.3	295.2
122.5°	324.1	326.4	325.2	323.5	321.8
125°	352.4	354.1	353.0	350.7	348.4
127.5°	378.5	381.9	380.7	377.3	375.1
130°	404.5	409.1	407.4	405.1	401.1
132.5°	430.6	435.1	434.0	431.2	428.3
135°	457.2	460.6	460.1	457.8	456.7
137.5°	481.6	484.4	486.1	483.3	481.6
140°	507.1	509.9	510.5	509.9	506.0
142.5°	530.3	533.2	534.3	533.7	530.9
145°	554.7	555.8	557.5	556.9	554.7
147.5°	575.6	577.9	579.6	579.6	576.2
150°	597.7	598.9	600.0	600.0	596.6
152.5°	615.9	617.6	618.1	619.3	616.4
155°	635.1	635.1	635.7	638.0	634.0
157.5°	651.6	651.0	651.6	653.8	650.4
160°	666.9	665.7	665.7	668.6	666.3
162.5°	680.5	678.8	679.3	682.2	678.2
165°	691.8	690.1	690.1	693.5	689.5
167.5°	701.4	699.2	699.7	703.1	699.7
170°	709.4	707.1	707.1	711.1	707.1
172.5°	715.6	713.3	713.3	716.7	712.8
175°	719.6	717.3	717.3	720.7	716.7
177.5°	721.8	719.6	719.6	723.0	719.0
180°	721.3	721.3	721.3	721.3	721.3

(END OF REPORT)