

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013353

Luminaire Tested: S124RDIP-B575D1035UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013353
REPORT IS A COMBINATION OF REPORTS P999430 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D1035UB2750-4F0-XX-W2A-F_2700K
Description: Define 4 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6374.0 lumens
Efficiency: N/A
Efficacy: 121.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013353

CATALOG NUMBER: S124RDIP-B575D1035UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1013353

CATALOG NUMBER: S124RDIP-B575D1035UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	91	87	84	86	82	79	76	67	64	63	52	51	49	39	38	37
2	87	79	74	69	78	72	67	63	59	55	52	46	44	42	34	33	32
3	79	70	63	57	71	64	58	53	52	47	44	41	38	35	31	29	27
4	72	62	54	49	65	56	50	45	46	41	37	36	33	30	27	25	23
5	66	55	47	42	60	50	44	38	41	36	32	33	29	26	25	22	21
6	61	49	42	36	55	45	38	33	37	32	28	30	26	23	23	20	18
7	56	45	37	32	51	41	34	29	34	29	25	27	23	20	21	18	16
8	52	40	33	28	47	37	30	26	31	26	22	25	21	18	19	16	15
9	49	37	30	25	44	34	27	23	28	23	20	23	19	16	18	15	13
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8181	8181	8181
5°	8182	7938	7938
10°	8112	7687	7595
15°	8000	7375	7191
20°	7854	7020	6730
25°	7672	6636	6280
30°	7493	6245	5774
35°	7298	5848	5280
40°	7064	5421	4772
45°	6845	4998	4269
50°	6596	4535	3759
55°	6327	4060	3232
60°	6028	3557	2711
65°	5739	2979	2210
70°	5330	2371	1689
75°	4804	1726	1181
80°	4014	1059	850
85°	3020	610	467

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6845 cd/sqm

TEST NUMBER: P1013353

CATALOG NUMBER: S124RDIP-B575D1035UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.3	1.5
10°-20°	263.0	4.1
20°-30°	379.7	6.0
30°-40°	430.4	6.8
40°-50°	415.5	6.5
50°-60°	345.5	5.4
60°-70°	238.4	3.7
70°-80°	120.5	1.9
80°-90°	33.3	0.5
90°-100°	43.5	0.7
100°-110°	286.4	4.5
110°-120°	546.8	8.6
120°-130°	694.2	10.9
130°-140°	742.6	11.7
140°-150°	694.4	10.9
150°-160°	560.0	8.8
160°-170°	361.1	5.7
170°-180°	124.5	2.0
0°-30°	737.1	11.6
0°-40°	1167.5	18.3
0°-60°	1928.5	30.3
0°-90°	2320.7	36.4
90°-120°	876.6	13.8
90°-150°	3007.8	47.2
90°-180°	4053.0	63.6
0°-180°	6374.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1003	1003	1003	1003	1003	
5°	1002	999	989	997	996	95
15°	954	947	928	926	921	269
25°	863	849	817	804	797	397
35°	746	721	683	657	643	466
45°	608	580	534	496	482	469
55°	461	430	380	340	326	412
65°	313	280	231	198	189	309
75°	167	138	102	84	80	176
85°	42	26	24	22	22	46
90°	3	14	22	27	29	5
95°	54	21	22	27	28	66
105°	295	301	306	314	279	309
115°	551	554	553	554	554	542
125°	774	778	776	779	780	691
135°	960	959	963	965	967	740
145°	1107	1110	1110	1111	1113	692
155°	1214	1215	1212	1216	1213	560
165°	1280	1276	1276	1283	1275	362
175°	1310	1304	1305	1314	1302	125
180°	1310	1310	1310	1310	1310	

TEST NUMBER: P1013353

CATALOG NUMBER: S124RDIP-B575D1035UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1003.2	1003.2	1003.2	1003.2	1003.2
2.5°	1006.3	1003.2	994.8	1003.2	1002.4
5°	1001.7	998.6	989.4	997.1	995.5
7.5°	994.8	991.7	980.2	985.5	983.2
10°	984.0	980.2	966.3	969.4	966.3
12.5°	970.2	965.6	948.7	950.2	945.6
15°	954.0	947.1	927.9	926.4	921.0
17.5°	935.6	925.6	903.3	899.5	891.8
20°	913.3	903.3	877.2	871.1	861.1
22.5°	888.7	877.2	848.8	838.8	831.1
25°	862.6	848.8	817.3	804.2	796.6
27.5°	835.7	818.8	785.8	770.5	759.7
30°	807.3	788.1	752.0	732.8	720.5
32.5°	777.4	755.1	717.4	694.4	682.9
35°	745.9	721.3	682.9	656.8	642.9
37.5°	712.8	687.5	645.2	616.8	603.0
40°	677.5	652.2	608.4	576.1	562.3
42.5°	643.7	616.8	570.7	537.7	523.1
45°	608.4	580.0	533.9	496.2	482.4
47.5°	572.3	543.1	495.5	456.3	440.9
50°	535.4	505.4	456.3	417.9	403.3
52.5°	497.8	468.6	417.9	378.7	363.3
55°	460.9	430.2	380.2	340.3	325.7
57.5°	424.8	392.5	343.4	302.6	291.9
60°	385.6	354.9	305.7	265.8	253.5
62.5°	350.3	318.0	267.3	231.2	222.0
65°	313.4	280.4	231.2	198.2	189.0
67.5°	275.0	243.5	197.4	168.2	157.5
70°	238.9	206.6	162.8	137.5	129.8
72.5°	200.5	172.1	131.4	110.6	103.7
75°	166.7	138.3	102.2	84.5	79.9
77.5°	131.4	106.8	76.0	63.8	62.2
80°	97.6	75.3	52.2	49.9	49.2
82.5°	68.4	48.4	37.6	36.1	35.3
85°	41.5	26.1	23.8	22.3	22.3
87.5°	17.7	11.5	10.8	10.0	10.8
90°	2.9	13.7	21.6	27.4	29.4
92.5°	14.7	12.7	20.6	26.5	26.5
95°	53.9	20.6	21.6	27.4	28.4
97.5°	102.9	124.4	21.6	26.5	27.4
100°	160.7	178.3	43.1	26.5	27.4
102.5°	225.3	237.1	248.9	28.4	28.4
105°	294.9	300.8	305.7	314.5	279.2
107.5°	358.6	361.5	368.4	373.3	377.2
110°	423.2	426.2	432.1	434.0	437.0

TEST NUMBER: P1013353

CATALOG NUMBER: S124RDIP-B575D1035UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	485.9	491.8	493.8	492.8	496.7
115°	550.6	553.5	552.6	554.5	554.5
117.5°	608.4	612.3	615.3	614.3	614.3
120°	667.2	671.1	670.1	672.1	670.1
122.5°	722.1	724.0	726.0	727.0	725.0
125°	774.0	777.9	775.9	778.9	779.9
127.5°	824.0	824.9	829.8	828.9	827.9
130°	872.0	872.9	875.9	876.9	876.9
132.5°	916.0	918.0	921.9	922.9	921.9
135°	960.1	959.2	963.1	965.0	967.0
137.5°	999.3	999.3	1004.2	1006.2	1005.2
140°	1037.5	1039.5	1041.5	1044.4	1045.4
142.5°	1071.8	1075.7	1076.7	1078.7	1078.7
145°	1107.1	1110.0	1110.0	1111.0	1113.0
147.5°	1134.5	1140.4	1139.4	1140.4	1141.4
150°	1164.9	1168.8	1167.8	1167.8	1168.8
152.5°	1190.4	1193.3	1191.4	1193.3	1192.3
155°	1213.9	1214.9	1211.9	1215.8	1212.9
157.5°	1234.5	1234.5	1230.5	1235.4	1230.5
160°	1252.1	1249.2	1248.2	1254.1	1248.2
162.5°	1267.8	1263.9	1262.9	1268.8	1261.9
165°	1280.5	1275.6	1275.6	1283.4	1274.6
167.5°	1291.3	1286.4	1285.4	1294.2	1284.4
170°	1300.1	1294.2	1295.2	1303.0	1293.2
172.5°	1306.0	1300.1	1301.1	1308.9	1298.1
175°	1309.9	1304.0	1305.0	1313.8	1302.1
177.5°	1312.8	1306.0	1307.9	1315.8	1304.0
180°	1309.9	1309.9	1309.9	1309.9	1309.9

(END OF REPORT)