

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007563

Luminaire Tested: S123IP-B585UB2750-4F0-XX-W2A-1_3000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007563
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B585UB2750-4F0-XX-W2A-1_3000K
Description: Define 3 Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2018.0 lumens
Efficiency: N/A
Efficacy: 131.0 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 15.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007563

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A-1_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1007563

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A-1_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007563

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A-1_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.5	0.1
90°-100°	46.8	2.3
100°-110°	141.8	7.0
110°-120°	241.4	12.0
120°-130°	317.6	15.7
130°-140°	356.9	17.7
140°-150°	350.9	17.4
150°-160°	295.4	14.6
160°-170°	196.7	9.7
170°-180°	68.9	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.5	0.1
90°-120°	430.0	21.3
90°-150°	1455.5	72.1
90°-180°	2016.0	99.9
0°-180°	2018.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	6	14	16	17	3
95°	34	38	42	45	45	37
105°	129	130	135	135	136	138
115°	243	245	244	244	244	240
125°	356	357	356	354	352	317
135°	461	465	464	462	461	355
145°	560	561	562	562	560	350
155°	641	641	641	644	640	295
165°	698	696	696	700	696	197
175°	726	724	724	727	723	69
180°	728	728	728	728	728	

TEST NUMBER: P1007563

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A-1_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.6	6.3	13.7	16.0	17.2
92.5°	17.2	20.6	24.0	25.7	24.6
95°	33.7	37.7	42.3	44.6	44.6
97.5°	55.5	58.3	61.7	64.6	64.0
100°	77.7	81.2	84.0	85.8	86.9
102.5°	103.5	105.2	109.2	110.9	110.3
105°	128.6	129.8	134.9	134.9	136.1
107.5°	158.4	158.9	161.2	162.9	162.4
110°	185.8	186.9	188.1	190.4	189.2

TEST NUMBER: P1007563

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A-1_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	214.4	215.0	215.0	217.8	217.8
115°	243.0	244.7	243.5	244.1	243.5
117.5°	272.1	272.7	271.5	271.5	269.8
120°	299.0	302.4	299.6	299.0	297.8
122.5°	327.0	329.3	328.1	326.4	324.7
125°	355.6	357.3	356.2	353.9	351.6
127.5°	381.9	385.3	384.2	380.7	378.5
130°	408.2	412.8	411.0	408.8	404.7
132.5°	434.5	439.1	437.9	435.0	432.2
135°	461.3	464.8	464.2	461.9	460.8
137.5°	485.9	488.8	490.5	487.6	485.9
140°	511.7	514.5	515.1	514.5	510.5
142.5°	535.1	538.0	539.1	538.5	535.7
145°	559.7	560.8	562.5	562.0	559.7
147.5°	580.8	583.1	584.8	584.8	581.4
150°	603.1	604.3	605.4	605.4	602.0
152.5°	621.4	623.1	623.7	624.8	622.0
155°	640.9	640.9	641.4	643.7	639.7
157.5°	657.4	656.9	657.4	659.7	656.3
160°	672.9	671.7	671.7	674.6	672.3
162.5°	686.6	684.9	685.4	688.3	684.3
165°	698.0	696.3	696.3	699.7	695.7
167.5°	707.7	705.5	706.0	709.5	706.0
170°	715.7	713.5	713.5	717.5	713.5
172.5°	722.0	719.7	719.7	723.2	719.2
175°	726.0	723.7	723.7	727.2	723.2
177.5°	728.3	726.0	726.0	729.5	725.5
180°	727.7	727.7	727.7	727.7	727.7

(END OF REPORT)