

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013354

Luminaire Tested: S124RDIP-B575D1035UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013354
REPORT IS A COMBINATION OF REPORTS P999431 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B575D1035UB2750-4F0-XX-W2A-F_3000K
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6430.0 lumens
Efficiency: N/A
Efficacy: 122.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013354

CATALOG NUMBER: S124RDIP-B575D1035UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013354

CATALOG NUMBER: S124RDIP-B575D1035UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36		
1	95	91	87	84	86	82	79	76	67	64	63	52	51	49	39	38	37	31		
2	87	79	74	69	78	72	67	63	59	55	52	46	44	42	34	33	32	26		
3	79	70	63	57	71	64	58	53	52	47	44	41	38	35	31	29	27	23		
4	72	62	54	49	65	56	50	45	46	41	37	36	33	30	27	25	23	19		
5	66	55	47	42	60	50	44	38	41	36	32	33	29	26	25	22	21	17		
6	61	49	42	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15		
7	57	45	37	32	51	41	34	29	34	29	25	27	23	20	21	18	16	13		
8	52	40	33	28	47	37	30	26	31	26	22	25	21	18	19	16	15	12		
9	49	37	30	25	44	34	27	23	28	23	20	23	19	16	18	15	13	11		
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8255	8255	8255
5°	8255	8009	8010
10°	8185	7757	7665
15°	8073	7442	7257
20°	7925	7084	6791
25°	7741	6696	6337
30°	7561	6301	5826
35°	7363	5901	5328
40°	7127	5470	4815
45°	6907	5043	4308
50°	6655	4576	3792
55°	6384	4098	3261
60°	6082	3589	2736
65°	5791	3006	2230
70°	5379	2393	1704
75°	4847	1741	1192
80°	4047	1069	857
85°	3049	615	472

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6907 cd/sqm

TEST NUMBER: P1013354

CATALOG NUMBER: S124RDIP-B575D1035UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.2	1.5
10°-20°	265.4	4.1
20°-30°	383.2	6.0
30°-40°	434.3	6.8
40°-50°	419.3	6.5
50°-60°	348.6	5.4
60°-70°	240.6	3.7
70°-80°	121.6	1.9
80°-90°	33.6	0.5
90°-100°	43.9	0.7
100°-110°	288.8	4.5
110°-120°	551.5	8.6
120°-130°	700.1	10.9
130°-140°	749.0	11.6
140°-150°	700.4	10.9
150°-160°	564.8	8.8
160°-170°	364.2	5.7
170°-180°	125.5	2.0
0°-30°	743.8	11.6
0°-40°	1178.0	18.3
0°-60°	1945.9	30.3
0°-90°	2341.7	36.4
90°-120°	884.2	13.8
90°-150°	3033.7	47.2
90°-180°	4088.0	63.6
0°-180°	6430.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1012	1012	1012	1012	1012	
5°	1011	1008	998	1006	1004	96
15°	963	956	936	935	929	271
25°	870	856	825	812	804	401
35°	753	728	689	663	649	470
45°	614	585	539	501	487	473
55°	465	434	384	343	329	416
65°	316	283	233	200	191	312
75°	168	140	103	85	81	177
85°	42	26	24	22	22	46
90°	3	14	22	28	30	5
95°	54	21	22	28	29	67
105°	297	303	308	317	282	311
115°	555	558	557	559	559	547
125°	781	785	783	786	787	697
135°	968	967	971	973	975	746
145°	1117	1120	1120	1121	1123	698
155°	1224	1225	1222	1226	1223	565
165°	1292	1287	1287	1294	1286	365
175°	1321	1315	1316	1325	1313	126
180°	1321	1321	1321	1321	1321	

TEST NUMBER: P1013354

CATALOG NUMBER: S124RDIP-B575D1035UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1012.3	1012.3	1012.3	1012.3	1012.3
2.5°	1015.4	1012.3	1003.8	1012.3	1011.5
5°	1010.7	1007.6	998.3	1006.1	1004.5
7.5°	1003.8	1000.7	989.0	994.5	992.1
10°	992.9	989.0	975.1	978.2	975.1
12.5°	979.0	974.3	957.3	958.8	954.2
15°	962.7	955.7	936.3	934.8	929.4
17.5°	944.1	934.0	911.5	907.6	899.9
20°	921.6	911.5	885.2	879.0	868.9
22.5°	896.8	885.2	856.5	846.4	838.7
25°	870.4	856.5	824.7	811.5	803.8
27.5°	843.3	826.3	792.9	777.4	766.6
30°	814.6	795.3	758.8	739.5	727.0
32.5°	784.4	761.9	723.9	700.7	689.1
35°	752.6	727.8	689.1	662.7	648.8
37.5°	719.3	693.7	651.1	622.4	608.5
40°	683.6	658.1	613.9	581.3	567.4
42.5°	649.5	622.4	575.9	542.6	527.8
45°	613.9	585.2	538.7	500.7	486.8
47.5°	577.5	548.0	499.9	460.4	444.9
50°	540.2	510.0	460.4	421.7	406.9
52.5°	502.3	472.8	421.7	382.1	366.6
55°	465.1	434.1	383.7	343.4	328.6
57.5°	428.6	396.1	346.5	305.4	294.5
60°	389.1	358.1	308.5	268.2	255.8
62.5°	353.4	320.9	269.7	233.3	224.0
65°	316.2	282.9	233.3	200.0	190.7
67.5°	277.5	245.7	199.2	169.7	158.9
70°	241.1	208.5	164.3	138.7	131.0
72.5°	202.3	173.6	132.5	111.6	104.6
75°	168.2	139.5	103.1	85.3	80.6
77.5°	132.5	107.7	76.7	64.3	62.8
80°	98.4	76.0	52.7	50.4	49.6
82.5°	69.0	48.8	38.0	36.4	35.7
85°	41.9	26.4	24.0	22.5	22.5
87.5°	17.8	11.6	10.9	10.1	10.9
90°	3.0	13.8	21.7	27.7	29.6
92.5°	14.8	12.8	20.8	26.7	26.7
95°	54.4	20.8	21.7	27.7	28.7
97.5°	103.8	125.5	21.7	26.7	27.7
100°	162.1	179.8	43.5	26.7	27.7
102.5°	227.3	239.1	251.0	28.7	28.7
105°	297.4	303.4	308.3	317.2	281.6
107.5°	361.7	364.6	371.6	376.5	380.5
110°	426.9	429.9	435.8	437.8	440.7

TEST NUMBER: P1013354

CATALOG NUMBER: S124RDIP-B575D1035UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	490.1	496.1	498.0	497.1	501.0
115°	555.4	558.3	557.3	559.3	559.3
117.5°	613.7	617.6	620.6	619.6	619.6
120°	673.0	676.9	675.9	677.9	675.9
122.5°	728.3	730.3	732.2	733.2	731.3
125°	780.7	784.6	782.6	785.6	786.6
127.5°	831.1	832.1	837.0	836.0	835.0
130°	879.5	880.5	883.4	884.4	884.4
132.5°	924.0	925.9	929.9	930.9	929.9
135°	968.4	967.4	971.4	973.4	975.3
137.5°	1007.9	1007.9	1012.9	1014.9	1013.9
140°	1046.5	1048.5	1050.4	1053.4	1054.4
142.5°	1081.1	1085.0	1086.0	1088.0	1088.0
145°	1116.6	1119.6	1119.6	1120.6	1122.6
147.5°	1144.3	1150.2	1149.3	1150.2	1151.2
150°	1175.0	1178.9	1177.9	1177.9	1178.9
152.5°	1200.6	1203.6	1201.6	1203.6	1202.6
155°	1224.4	1225.4	1222.4	1226.3	1223.4
157.5°	1245.1	1245.1	1241.2	1246.1	1241.2
160°	1262.9	1259.9	1258.9	1264.9	1258.9
162.5°	1278.7	1274.8	1273.8	1279.7	1272.8
165°	1291.6	1286.6	1286.6	1294.5	1285.6
167.5°	1302.4	1297.5	1296.5	1305.4	1295.5
170°	1311.3	1305.4	1306.4	1314.3	1304.4
172.5°	1317.3	1311.3	1312.3	1320.2	1309.3
175°	1321.2	1315.3	1316.3	1325.2	1313.3
177.5°	1324.2	1317.3	1319.2	1327.1	1315.3
180°	1321.2	1321.2	1321.2	1321.2	1321.2

(END OF REPORT)