

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007564

Luminaire Tested: S123IP-B585UB2750-4F0-XX-W2A-1_3500K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007564
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B585UB2750-4F0-XX-W2A-1_3500K
Description: Define 3 Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2026.0 lumens
Efficiency: N/A
Efficacy: 131.6 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 15.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007564

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A-1_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1007564

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A-1_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007564

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A-1_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.5	0.1
90°-100°	47.0	2.3
100°-110°	142.4	7.0
110°-120°	242.3	12.0
120°-130°	318.8	15.7
130°-140°	358.4	17.7
140°-150°	352.3	17.4
150°-160°	296.6	14.6
160°-170°	197.5	9.7
170°-180°	69.1	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.5	0.1
90°-120°	431.8	21.3
90°-150°	1461.2	72.1
90°-180°	2024.0	99.9
0°-180°	2026.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	6	14	16	17	3
95°	34	38	42	45	45	37
105°	129	130	136	136	137	138
115°	244	246	244	245	244	241
125°	357	359	358	355	353	318
135°	463	467	466	464	463	357
145°	562	563	565	564	562	351
155°	643	643	644	646	642	296
165°	701	699	699	702	698	198
175°	729	727	727	730	726	69
180°	731	731	731	731	731	

TEST NUMBER: P1007564

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.6	6.3	13.8	16.1	17.2
92.5°	17.2	20.7	24.1	25.8	24.7
95°	33.9	37.9	42.5	44.8	44.8
97.5°	55.7	58.5	62.0	64.9	64.3
100°	78.1	81.5	84.4	86.1	87.2
102.5°	103.9	105.6	109.6	111.3	110.8
105°	129.1	130.3	135.5	135.5	136.6
107.5°	159.0	159.6	161.9	163.6	163.0
110°	186.5	187.7	188.8	191.1	190.0

TEST NUMBER: P1007564

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	215.2	215.8	215.8	218.7	218.7
115°	243.9	245.6	244.5	245.1	244.5
117.5°	273.2	273.8	272.6	272.6	270.9
120°	300.2	303.6	300.7	300.2	299.0
122.5°	328.3	330.6	329.4	327.7	326.0
125°	357.0	358.7	357.6	355.3	353.0
127.5°	383.4	386.8	385.7	382.2	380.0
130°	409.8	414.4	412.7	410.4	406.4
132.5°	436.2	440.8	439.6	436.8	433.9
135°	463.2	466.6	466.0	463.7	462.6
137.5°	487.9	490.7	492.4	489.6	487.9
140°	513.7	516.6	517.1	516.6	512.5
142.5°	537.2	540.1	541.2	540.7	537.8
145°	561.9	563.0	564.8	564.2	561.9
147.5°	583.1	585.4	587.1	587.1	583.7
150°	605.5	606.7	607.8	607.8	604.4
152.5°	623.9	625.6	626.2	627.3	624.5
155°	643.4	643.4	644.0	646.3	642.2
157.5°	660.0	659.5	660.0	662.3	658.9
160°	675.5	674.4	674.4	677.3	675.0
162.5°	689.3	687.6	688.2	691.0	687.0
165°	700.8	699.1	699.1	702.5	698.5
167.5°	710.5	708.3	708.8	712.3	708.8
170°	718.6	716.3	716.3	720.3	716.3
172.5°	724.9	722.6	722.6	726.0	722.0
175°	728.9	726.6	726.6	730.1	726.0
177.5°	731.2	728.9	728.9	732.4	728.3
180°	730.6	730.6	730.6	730.6	730.6

(END OF REPORT)