

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007572

Luminaire Tested: S123IP-B585UB2750-4F0-XX-W2A_2700K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007572
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B585UB2750-4F0-XX-W2A_2700K
Description: Define 3 Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2327.0 lumens
Efficiency: N/A
Efficacy: 151.1 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 15.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007572

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1007572

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007572

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.5	0.1
90°-100°	26.9	1.2
100°-110°	130.1	5.6
110°-120°	318.7	13.7
120°-130°	404.6	17.4
130°-140°	432.2	18.6
140°-150°	404.2	17.4
150°-160°	326.0	14.0
160°-170°	210.4	9.0
170°-180°	72.5	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.5	0.1
90°-120°	475.6	20.4
90°-150°	1716.6	73.8
90°-180°	2325.0	99.9
0°-180°	2327.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	6	14	16	17	2
95°	35	11	18	22	22	41
105°	169	175	124	24	25	179
115°	317	320	325	331	333	313
125°	447	451	453	454	456	399
135°	556	559	562	563	562	428
145°	642	646	647	648	648	402
155°	707	706	706	709	706	326
165°	745	744	743	748	744	211
175°	763	760	760	764	760	73
180°	763	763	763	763	763	

TEST NUMBER: P1007572

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.6	6.2	13.6	15.9	17.0
92.5°	13.0	9.6	14.7	18.7	19.3
95°	34.6	11.3	17.6	21.5	21.5
97.5°	62.9	47.0	18.1	22.7	23.2
100°	95.8	107.1	18.7	23.2	23.8
102.5°	133.2	140.5	41.9	23.2	24.4
105°	168.9	175.1	124.1	23.8	24.9
107.5°	206.9	212.0	220.5	133.2	58.9
110°	244.8	249.4	255.6	236.9	155.8

TEST NUMBER: P1007572

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	281.1	285.1	291.3	296.4	295.3
115°	316.8	320.2	325.3	331.0	333.2
117.5°	351.9	355.9	358.7	363.3	363.8
120°	384.2	389.3	391.0	395.6	395.6
122.5°	417.1	421.1	423.3	426.2	426.7
125°	446.6	451.1	453.4	454.5	455.6
127.5°	476.0	480.6	483.4	485.1	484.0
130°	503.2	507.8	510.0	512.3	511.2
132.5°	529.3	533.9	535.6	537.8	536.1
135°	556.0	559.4	561.6	563.3	561.6
137.5°	578.6	583.2	584.3	587.1	586.0
140°	601.3	604.7	606.4	608.7	607.5
142.5°	622.3	625.7	627.4	629.1	627.4
145°	641.5	645.5	646.6	647.8	647.8
147.5°	660.2	663.1	664.2	665.3	662.5
150°	677.2	678.9	680.1	681.2	679.5
152.5°	692.5	693.1	693.7	695.9	693.1
155°	706.7	705.6	706.1	709.0	705.6
157.5°	718.0	718.0	717.5	720.9	716.3
160°	728.2	727.7	727.1	730.5	726.5
162.5°	737.9	736.2	735.6	739.6	736.2
165°	745.2	743.5	743.0	747.5	743.5
167.5°	751.5	749.2	749.2	753.7	749.2
170°	756.6	754.3	754.3	758.8	754.3
172.5°	760.0	757.1	757.7	762.2	757.1
175°	762.8	760.0	760.5	764.5	760.0
177.5°	763.9	761.1	761.7	766.2	760.5
180°	762.8	762.8	762.8	762.8	762.8

(END OF REPORT)