

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013398

Luminaire Tested: S124RDIP-B795D1035UB2750-4F0-XX-W2A-A_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013398
REPORT IS A COMBINATION OF REPORTS P999627 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B795D1035UB2750-4F0-XX-W2A-A_3500K
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7478.0 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013398

CATALOG NUMBER: S124RDIP-B795D1035UB2750-4F0-XX-W2A-A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1013398

CATALOG NUMBER: S124RDIP-B795D1035UB2750-4F0-XX-W2A-A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	52	52	52			45
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44			39
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38			33
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	35	33			29
4	74	64	56	51	68	59	52	47	50	45	41	41	38	35	33	31	29			25
5	68	57	49	44	63	53	46	41	45	39	35	37	33	30	30	27	25			22
6	63	51	43	38	58	48	41	36	40	35	31	34	30	27	27	24	22			19
7	58	46	39	33	53	43	36	31	37	31	27	31	27	24	25	22	20			17
8	54	42	35	29	50	39	32	28	33	28	24	28	24	21	23	20	18			15
9	50	39	31	26	46	36	29	25	31	26	22	26	22	19	21	18	16			14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	20	17	15			13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10867	10867	10867	10867
5°	10868	12280	10885	9386
10°	10810	14156	10801	8163
15°	10681	15932	10681	6834
20°	10547	17274	10491	6018
25°	10383	17348	10335	5436
30°	10207	14751	10128	5034
35°	9961	11130	9834	4736
40°	9685	8066	9495	4502
45°	9231	6131	9002	4296
50°	8692	4955	8453	3994
55°	8108	4103	7842	3591
60°	7521	3469	7185	2986
65°	6785	2826	6569	2374
70°	6108	2291	5823	1928
75°	5354	1652	4983	1413
80°	4417	1095	4018	1038
85°	3202	562	2656	562

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 13605 cd/sqm

TEST NUMBER: P1013398

CATALOG NUMBER: S124RDIP-B795D1035UB2750-4F0-XX-W2A-A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.0	1.7
10°-20°	389.7	5.2
20°-30°	610.5	8.2
30°-40°	677.9	9.1
40°-50°	600.7	8.0
50°-60°	468.1	6.3
60°-70°	306.2	4.1
70°-80°	150.3	2.0
80°-90°	39.3	0.5
90°-100°	44.0	0.6
100°-110°	290.1	3.9
110°-120°	553.9	7.4
120°-130°	703.2	9.4
130°-140°	752.3	10.1
140°-150°	703.4	9.4
150°-160°	567.3	7.6
160°-170°	365.8	4.9
170°-180°	126.1	1.7
0°-30°	1129.2	15.1
0°-40°	1807.1	24.2
0°-60°	2875.9	38.5
0°-90°	3371.7	45.1
90°-120°	888.1	11.9
90°-150°	3047.1	40.7
90°-180°	4106.0	54.9
0°-180°	7478.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1333	1333	1333	1333	1333	
5°	1331	1540	1333	1177	1331	126
15°	1274	2040	1274	875	1274	359
25°	1167	2200	1162	690	1167	538
35°	1018	1355	1005	577	1018	636
45°	820	693	800	485	820	633
55°	591	414	571	362	591	528
65°	370	242	359	203	370	370
75°	186	112	173	96	186	197
85°	44	27	36	27	44	50
90°	3	30	3	30	3	6
95°	55	29	55	29	55	67
105°	299	283	299	283	299	313
115°	558	562	558	562	558	549
125°	784	790	784	790	784	700
135°	973	980	973	980	973	750
145°	1122	1128	1122	1128	1122	701
155°	1230	1229	1230	1229	1230	567
165°	1297	1291	1297	1291	1297	367
175°	1327	1319	1327	1319	1327	126
180°	1327	1327	1327	1327	1327	

TEST NUMBER: P1013398

CATALOG NUMBER: S124RDIP-B795D1035UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7
2.5°	1334.9	1346.7	1353.1	1358.5	1369.2	1373.5	1382.1	1384.3	1392.9	1391.8	1388.6
5°	1330.6	1351.0	1366.0	1382.1	1401.5	1412.2	1424.0	1441.2	1449.8	1461.6	1469.1
7.5°	1323.1	1351.0	1375.7	1400.4	1431.5	1448.7	1463.8	1490.6	1513.2	1532.5	1554.0
10°	1311.3	1346.7	1383.2	1416.5	1459.5	1479.9	1502.4	1542.2	1573.3	1600.1	1634.5
12.5°	1293.0	1342.4	1383.2	1428.3	1483.1	1511.0	1541.1	1588.3	1624.8	1668.9	1711.8
15°	1273.7	1328.4	1382.1	1441.2	1503.5	1535.7	1565.8	1629.1	1685.0	1735.5	1782.7
17.5°	1252.2	1312.3	1371.4	1436.9	1512.1	1551.8	1587.3	1663.5	1724.7	1790.2	1837.5
20°	1226.4	1291.9	1359.6	1432.6	1517.5	1561.5	1601.2	1688.2	1755.9	1826.7	1885.8
22.5°	1198.5	1269.4	1343.5	1422.9	1511.0	1559.3	1605.5	1698.9	1777.3	1842.8	1922.3
25°	1167.4	1242.5	1318.8	1402.5	1501.3	1554.0	1601.2	1693.6	1777.3	1863.3	1940.6
27.5°	1135.1	1212.5	1291.9	1380.0	1480.9	1532.5	1586.2	1675.3	1773.0	1866.5	1944.9
30°	1099.7	1174.9	1258.6	1342.4	1449.8	1501.3	1556.1	1652.8	1759.1	1852.5	1937.4
32.5°	1061.0	1138.4	1217.8	1304.8	1410.1	1465.9	1516.4	1625.9	1734.4	1826.7	1906.2
35°	1018.1	1091.1	1166.3	1255.4	1359.6	1410.1	1470.2	1584.0	1693.6	1791.3	1842.8
37.5°	971.9	1041.7	1111.5	1199.6	1299.4	1360.7	1419.7	1534.6	1650.6	1716.1	1743.0
40°	928.9	990.2	1051.4	1136.2	1237.2	1300.5	1360.7	1479.9	1581.9	1632.4	1612.0
42.5°	874.2	937.5	992.3	1070.7	1172.7	1231.8	1293.0	1416.5	1499.2	1519.6	1469.1
45°	820.5	873.1	925.7	1002.0	1109.4	1159.8	1225.3	1340.3	1409.0	1390.7	1316.6
47.5°	767.9	810.8	860.2	934.3	1031.0	1091.1	1152.3	1252.2	1300.5	1274.7	1171.6
50°	705.6	748.5	800.1	864.5	957.9	1015.9	1064.3	1156.6	1193.1	1129.8	1005.2
52.5°	646.5	684.1	728.1	788.3	877.4	930.0	982.6	1062.1	1073.9	1000.9	869.9
55°	590.7	620.7	666.9	715.2	796.8	852.7	889.2	956.9	953.6	862.4	749.6
57.5°	532.7	560.6	591.7	642.2	719.5	761.4	801.1	860.2	829.1	751.7	640.1
60°	481.1	497.2	528.4	576.7	642.2	678.7	709.9	742.1	715.2	631.5	545.6
62.5°	424.2	442.5	465.0	503.7	561.7	596.0	618.6	632.5	604.6	540.2	461.8
65°	370.5	386.6	410.2	444.6	488.6	514.4	526.2	535.9	520.9	447.8	385.5
67.5°	322.2	332.9	354.4	376.9	424.2	430.6	446.8	451.0	421.0	365.1	315.7
70°	273.8	284.6	294.3	321.1	342.6	354.4	357.6	357.6	327.5	291.0	250.2
72.5°	228.7	235.2	244.9	263.1	274.9	283.5	287.8	282.4	254.5	224.4	194.4
75°	185.8	189.0	197.6	209.4	219.1	215.9	214.8	208.3	187.9	166.5	149.3
77.5°	142.8	145.0	154.6	157.9	157.9	161.1	156.8	150.3	133.2	117.1	109.5
80°	107.4	110.6	111.7	113.8	111.7	111.7	108.5	97.7	89.1	81.6	76.2
82.5°	74.1	76.2	77.3	74.1	76.2	73.0	67.7	60.1	54.8	53.7	51.5
85°	44.0	45.1	44.0	44.0	40.8	39.7	35.4	34.4	32.2	32.2	31.1
87.5°	21.5	20.4	18.3	16.1	16.1	15.0	16.1	14.0	16.1	15.0	14.0
90°	3.0	5.4	7.8	10.3	12.7	13.9	14.8	16.5	18.3	20.0	21.8
92.5°	14.9	14.5	14.0	13.6	13.1	12.9	13.8	15.5	17.3	19.0	20.8
95°	54.6	47.1	39.6	32.1	24.6	20.8	20.9	21.1	21.4	21.6	21.8
97.5°	104.2	109.1	113.9	118.8	123.7	126.1	114.5	91.3	68.2	45.0	21.8
100°	162.8	166.8	170.7	174.7	178.6	180.6	165.4	135.0	104.5	74.1	43.7
102.5°	228.3	230.9	233.6	236.2	238.9	240.2	241.5	244.2	246.8	249.5	252.1
105°	298.8	300.1	301.4	302.7	304.0	304.7	305.3	306.4	307.5	308.6	309.7
107.5°	363.3	363.9	364.6	365.2	365.9	366.2	367.0	368.5	370.1	371.6	373.2
110°	428.8	429.5	430.1	430.8	431.5	431.8	432.5	433.8	435.1	436.4	437.7

TEST NUMBER: P1013398

CATALOG NUMBER: S124RDIP-B795D1035UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	492.3	493.6	495.0	496.3	497.6	498.3	498.5	498.9	499.4	499.8	500.2
115°	557.8	558.5	559.1	559.8	560.5	560.8	560.7	560.5	560.2	560.0	559.8
117.5°	616.4	617.3	618.1	619.0	619.9	620.3	620.6	621.3	622.0	622.6	623.3
120°	675.9	676.8	677.7	678.6	679.5	679.9	679.8	679.6	679.3	679.1	678.9
122.5°	731.5	731.9	732.4	732.8	733.3	733.5	733.7	734.2	734.6	735.1	735.5
125°	784.1	785.0	785.9	786.8	787.7	788.1	787.9	787.4	787.0	786.5	786.1
127.5°	834.7	834.9	835.1	835.4	835.6	835.7	836.3	837.4	838.5	839.6	840.7
130°	883.4	883.6	883.8	884.0	884.2	884.3	884.6	885.3	886.0	886.6	887.3
132.5°	928.0	928.4	928.9	929.3	929.8	930.0	930.4	931.3	932.2	933.1	934.0
135°	972.7	972.5	972.3	972.0	971.8	971.7	972.1	973.0	973.9	974.8	975.7
137.5°	1012.4	1012.4	1012.4	1012.4	1012.4	1012.4	1012.9	1014.0	1015.1	1016.2	1017.3
140°	1051.1	1051.5	1052.0	1052.4	1052.9	1053.1	1053.3	1053.8	1054.2	1054.7	1055.1
142.5°	1085.8	1086.7	1087.6	1088.5	1089.4	1089.8	1089.9	1090.1	1090.4	1090.6	1090.8
145°	1121.6	1122.2	1122.9	1123.5	1124.2	1124.5	1124.5	1124.5	1124.5	1124.5	1124.5
147.5°	1149.4	1150.7	1152.0	1153.3	1154.6	1155.3	1155.2	1155.0	1154.7	1154.5	1154.3
150°	1180.1	1181.0	1181.9	1182.8	1183.7	1184.1	1184.0	1183.8	1183.5	1183.3	1183.1
152.5°	1205.9	1206.6	1207.2	1207.9	1208.6	1208.9	1208.7	1208.2	1207.8	1207.3	1206.9
155°	1229.7	1229.9	1230.1	1230.4	1230.6	1230.7	1230.4	1229.7	1229.1	1228.4	1227.8
157.5°	1250.6	1250.6	1250.6	1250.6	1250.6	1250.6	1250.2	1249.3	1248.4	1247.5	1246.6
160°	1268.5	1267.8	1267.2	1266.5	1265.8	1265.5	1265.4	1265.2	1264.9	1264.7	1264.5
162.5°	1284.3	1283.4	1282.6	1281.7	1280.8	1280.4	1280.3	1280.1	1279.8	1279.6	1279.4
165°	1297.2	1296.1	1295.0	1293.9	1292.8	1292.3	1292.3	1292.3	1292.3	1292.3	1292.3
167.5°	1308.2	1307.1	1306.0	1304.9	1303.8	1303.2	1303.1	1302.9	1302.6	1302.4	1302.2
170°	1317.1	1315.8	1314.4	1313.1	1311.8	1311.1	1311.2	1311.4	1311.7	1311.9	1312.1
172.5°	1323.0	1321.7	1320.4	1319.1	1317.8	1317.1	1317.2	1317.4	1317.7	1317.9	1318.1
175°	1327.0	1325.7	1324.4	1323.1	1321.8	1321.1	1321.2	1321.4	1321.7	1321.9	1322.1
177.5°	1330.0	1328.4	1326.9	1325.3	1323.8	1323.0	1323.2	1323.7	1324.1	1324.6	1325.0
180°	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0

TEST NUMBER: P1013398

CATALOG NUMBER: S124RDIP-B795D1035UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7
2.5°	1397.2	1409.0	1410.1	1420.8	1417.6	1412.2	1421.9	1415.4	1428.3	1424.0	1429.4
5°	1478.8	1494.9	1508.9	1517.5	1532.5	1529.3	1545.4	1540.0	1551.8	1540.0	1555.0
7.5°	1574.4	1601.2	1615.2	1637.7	1644.2	1645.2	1664.6	1668.9	1676.4	1668.9	1677.5
10°	1667.8	1700.0	1732.2	1750.5	1762.3	1778.4	1795.6	1803.1	1808.5	1801.0	1806.3
12.5°	1752.6	1803.1	1838.6	1875.1	1883.7	1897.6	1915.9	1913.7	1935.2	1930.9	1940.6
15°	1831.0	1886.9	1929.8	1958.8	1982.5	1994.3	2028.6	2030.8	2029.7	2040.4	2034.0
17.5°	1900.8	1948.1	2009.3	2046.9	2075.9	2075.9	2095.2	2135.0	2131.7	2130.7	2137.1
20°	1957.8	2011.5	2068.4	2131.7	2155.4	2159.7	2186.5	2206.9	2210.1	2210.1	2210.1
22.5°	2000.7	2064.1	2125.3	2170.4	2188.7	2203.7	2227.3	2240.2	2244.5	2242.3	2244.5
25°	2022.2	2082.3	2144.6	2185.4	2196.2	2204.8	2206.9	2214.4	2213.4	2200.5	2208.0
27.5°	2026.5	2084.5	2125.3	2136.0	2130.7	2125.3	2090.9	2094.1	2084.5	2065.1	2072.7
30°	2007.2	2038.3	2037.2	2003.9	1994.3	1971.7	1940.6	1894.4	1856.8	1840.7	1846.1
32.5°	1937.4	1937.4	1898.7	1823.5	1790.2	1749.4	1693.6	1651.7	1602.3	1591.6	1612.0
35°	1840.7	1785.9	1715.1	1616.3	1565.8	1535.7	1439.1	1409.0	1367.1	1355.3	1365.0
37.5°	1690.4	1599.1	1496.0	1403.6	1360.7	1307.0	1222.1	1179.2	1149.1	1128.7	1138.4
40°	1521.7	1411.1	1303.7	1189.9	1142.7	1098.6	1035.3	996.6	948.3	950.4	953.6
42.5°	1360.7	1230.7	1110.4	1005.2	960.1	923.6	879.5	832.3	815.1	809.7	804.4
45°	1189.9	1051.4	938.6	860.2	819.4	785.0	744.2	717.4	697.0	692.7	698.0
47.5°	1028.8	911.8	804.4	731.3	698.0	680.9	648.6	623.9	611.1	600.3	606.8
50°	882.8	773.2	687.3	626.1	602.5	590.7	560.6	547.7	534.8	531.6	530.5
52.5°	762.5	669.1	595.0	545.6	527.3	520.9	498.3	480.0	469.3	472.5	474.7
55°	652.9	573.5	515.5	475.7	460.7	453.2	437.1	424.2	416.7	413.5	415.6
57.5°	556.3	487.6	445.7	413.5	401.6	398.4	381.2	376.9	371.6	368.4	368.4
60°	468.2	419.9	381.2	363.0	350.1	346.9	334.0	328.6	327.5	324.3	322.2
62.5°	394.1	354.4	327.5	308.2	302.8	301.8	293.2	286.7	283.5	281.4	281.4
65°	329.7	300.7	278.1	264.2	259.9	257.7	248.1	245.9	243.8	241.6	240.6
67.5°	274.9	249.1	233.0	223.4	218.0	219.1	213.7	209.4	209.4	208.3	207.3
70°	222.3	206.2	192.2	186.9	184.7	182.6	180.4	177.2	176.1	176.1	176.1
72.5°	175.0	164.3	156.8	153.6	151.4	149.3	147.1	147.1	147.1	146.1	146.1
75°	134.2	129.9	124.6	121.4	121.4	123.5	120.3	117.1	113.8	111.7	112.8
77.5°	100.9	98.8	95.6	90.2	91.3	89.1	89.1	87.0	88.1	88.1	85.9
80°	74.1	70.9	69.8	66.6	67.7	66.6	65.5	65.5	63.4	63.4	63.4
82.5°	51.5	48.3	48.3	47.3	46.2	46.2	45.1	45.1	46.2	44.0	44.0
85°	31.1	30.1	30.1	27.9	27.9	27.9	27.9	29.0	27.9	26.8	26.8
87.5°	14.0	15.0	14.0	12.9	12.9	12.9	11.8	11.8	10.7	11.8	11.8
90°	23.1	24.5	25.8	27.1	27.8	28.0	28.5	28.9	29.4	29.8	29.4
92.5°	22.1	23.5	24.8	26.1	26.8	26.8	26.8	26.8	26.8	26.8	26.8
95°	23.1	24.5	25.8	27.1	27.8	27.9	28.1	28.4	28.6	28.8	28.6
97.5°	22.9	24.0	25.1	26.2	26.8	26.9	27.1	27.4	27.6	27.8	27.6
100°	39.9	36.2	32.4	28.7	26.8	26.9	27.1	27.4	27.6	27.8	27.6
102.5°	202.5	152.9	103.2	53.6	28.8	28.8	28.8	28.8	28.8	28.8	28.8
105°	311.7	313.7	315.6	317.6	318.6	314.6	306.7	298.8	290.8	282.9	290.8
107.5°	374.3	375.4	376.5	377.6	378.2	378.6	379.5	380.4	381.2	382.1	381.2
110°	438.1	438.6	439.0	439.5	439.7	440.0	440.7	441.4	442.0	442.7	442.0

TEST NUMBER: P1013398

CATALOG NUMBER: S124RDIP-B795D1035UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	500.0	499.8	499.5	499.3	499.2	499.6	500.5	501.4	502.3	503.2	502.3
115°	560.2	560.7	561.1	561.6	561.8	561.8	561.8	561.8	561.8	561.8	561.8
117.5°	623.1	622.9	622.6	622.4	622.3	622.3	622.3	622.3	622.3	622.3	622.3
120°	679.3	679.8	680.2	680.7	680.9	680.7	680.2	679.8	679.3	678.9	679.3
122.5°	735.7	735.9	736.2	736.4	736.5	736.3	735.8	735.4	734.9	734.5	734.9
125°	786.8	787.4	788.1	788.8	789.1	789.2	789.4	789.7	789.9	790.1	789.9
127.5°	840.5	840.3	840.0	839.8	839.7	839.6	839.4	839.1	838.9	838.7	838.9
130°	887.5	887.7	888.0	888.2	888.3	888.3	888.3	888.3	888.3	888.3	888.3
132.5°	934.2	934.4	934.7	934.9	935.0	934.9	934.7	934.4	934.2	934.0	934.2
135°	976.1	976.5	977.0	977.4	977.6	977.8	978.3	978.7	979.2	979.6	979.2
137.5°	1017.7	1018.2	1018.6	1019.1	1019.3	1019.2	1019.0	1018.7	1018.5	1018.3	1018.5
140°	1055.7	1056.4	1057.0	1057.7	1058.0	1058.1	1058.3	1058.6	1058.8	1059.0	1058.8
142.5°	1091.2	1091.7	1092.1	1092.6	1092.8	1092.8	1092.8	1092.8	1092.8	1092.8	1092.8
145°	1124.7	1124.9	1125.2	1125.4	1125.5	1125.7	1126.2	1126.6	1127.1	1127.5	1127.1
147.5°	1154.5	1154.7	1155.0	1155.2	1155.3	1155.4	1155.6	1155.9	1156.1	1156.3	1156.1
150°	1183.1	1183.1	1183.1	1183.1	1183.1	1183.2	1183.4	1183.7	1183.9	1184.1	1183.9
152.5°	1207.3	1207.8	1208.2	1208.7	1208.9	1208.8	1208.6	1208.3	1208.1	1207.9	1208.1
155°	1228.7	1229.5	1230.4	1231.3	1231.7	1231.4	1230.7	1230.1	1229.4	1228.8	1229.4
157.5°	1247.7	1248.8	1249.9	1251.0	1251.6	1251.0	1249.9	1248.8	1247.7	1246.6	1247.7
160°	1265.8	1267.1	1268.4	1269.7	1270.4	1269.7	1268.4	1267.1	1265.8	1264.5	1265.8
162.5°	1280.7	1282.0	1283.3	1284.6	1285.3	1284.5	1283.0	1281.5	1279.9	1278.4	1279.9
165°	1294.1	1295.8	1297.6	1299.3	1300.2	1299.2	1297.2	1295.3	1293.3	1291.3	1293.3
167.5°	1304.2	1306.2	1308.1	1310.1	1311.1	1310.0	1307.8	1305.6	1303.4	1301.2	1303.4
170°	1313.9	1315.7	1317.4	1319.2	1320.1	1319.0	1316.8	1314.5	1312.3	1310.1	1312.3
172.5°	1319.9	1321.6	1323.4	1325.1	1326.0	1324.8	1322.4	1319.9	1317.5	1315.1	1317.5
175°	1324.1	1326.1	1328.0	1330.0	1331.0	1329.7	1327.0	1324.4	1321.7	1319.1	1321.7
177.5°	1326.8	1328.6	1330.3	1332.1	1333.0	1331.7	1329.0	1326.4	1323.7	1321.1	1323.7
180°	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0

TEST NUMBER: P1013398

CATALOG NUMBER: S124RDIP-B795D1035UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7
2.5°	1432.6	1425.1	1424.0	1424.0	1412.2	1418.6	1405.8	1391.8	1385.4	1385.4	1373.5
5°	1551.8	1544.3	1536.8	1525.0	1525.0	1518.5	1498.1	1477.7	1462.7	1449.8	1435.8
7.5°	1674.2	1666.7	1645.2	1633.4	1639.9	1627.0	1600.1	1565.8	1540.0	1519.6	1490.6
10°	1807.4	1787.0	1776.3	1769.8	1747.3	1733.3	1702.2	1651.7	1619.5	1592.6	1555.0
12.5°	1915.9	1922.3	1881.5	1884.7	1862.2	1842.8	1794.5	1746.2	1697.9	1660.3	1604.4
15°	2032.9	2013.6	1988.9	1969.6	1962.1	1938.4	1897.6	1833.2	1780.6	1721.5	1658.1
17.5°	2125.3	2110.3	2086.6	2068.4	2052.3	1995.3	1961.0	1904.1	1832.1	1774.1	1696.8
20°	2203.7	2189.7	2156.4	2144.6	2115.6	2074.8	2025.4	1937.4	1872.9	1809.6	1734.4
22.5°	2237.0	2223.0	2194.0	2179.0	2160.7	2121.0	2073.7	1990.0	1910.5	1831.0	1751.6
25°	2209.1	2209.1	2195.1	2189.7	2173.6	2138.2	2089.9	2019.0	1934.1	1848.2	1753.7
27.5°	2073.7	2100.6	2110.3	2115.6	2115.6	2116.7	2083.4	2014.7	1932.0	1848.2	1749.4
30°	1878.3	1923.4	1963.1	1974.9	1995.3	2017.9	2031.9	1998.6	1924.5	1836.4	1737.6
32.5°	1632.4	1690.4	1764.5	1782.7	1810.6	1878.3	1915.9	1929.8	1889.0	1811.7	1706.5
35°	1387.5	1460.5	1505.6	1561.5	1587.3	1687.1	1770.9	1821.4	1811.7	1765.5	1669.9
37.5°	1173.8	1215.7	1270.4	1329.5	1381.1	1476.6	1580.8	1678.5	1718.3	1695.7	1623.8
40°	968.7	1018.1	1083.6	1131.9	1167.4	1262.9	1391.8	1498.1	1585.1	1599.1	1555.0
42.5°	823.7	873.1	912.8	965.5	993.4	1085.7	1199.6	1332.7	1435.8	1490.6	1471.3
45°	712.0	742.1	774.3	804.4	838.7	920.4	1025.6	1171.6	1287.6	1365.0	1372.5
47.5°	614.3	641.1	669.1	697.0	716.3	779.7	876.3	995.5	1122.2	1228.6	1270.4
50°	545.6	558.4	578.8	595.0	617.5	672.3	749.6	852.7	986.9	1101.8	1156.6
52.5°	477.9	494.0	510.1	524.1	539.1	577.8	648.6	737.8	853.8	971.9	1039.6
55°	421.0	433.9	448.9	458.6	467.2	501.5	555.2	623.9	723.8	835.5	919.3
57.5°	374.8	380.2	393.1	398.4	408.1	436.0	474.7	535.9	616.4	724.9	793.6
60°	324.3	335.1	344.7	349.0	356.5	375.9	402.7	459.6	529.4	608.9	687.3
62.5°	283.5	287.8	295.3	300.7	306.1	326.5	349.0	392.0	444.6	511.2	583.1
65°	245.9	248.1	252.4	259.9	263.1	278.1	291.0	322.2	371.6	422.1	494.0
67.5°	207.3	209.4	214.8	219.1	222.3	232.0	245.9	268.5	295.3	351.2	390.9
70°	177.2	177.2	180.4	182.6	185.8	190.1	197.6	214.8	239.5	274.9	311.4
72.5°	148.2	148.2	148.2	151.4	151.4	154.6	158.9	170.8	187.9	215.9	239.5
75°	114.9	116.0	118.1	118.1	119.2	123.5	126.7	129.9	138.5	156.8	178.3
77.5°	87.0	89.1	90.2	88.1	90.2	90.2	94.5	98.8	103.1	108.5	124.6
80°	64.4	65.5	63.4	64.4	64.4	66.6	68.7	67.7	69.8	76.2	80.5
82.5°	43.0	44.0	44.0	44.0	44.0	47.3	47.3	46.2	47.3	48.3	49.4
85°	26.8	25.8	25.8	26.8	25.8	25.8	26.8	27.9	26.8	27.9	29.0
87.5°	11.8	11.8	11.8	11.8	10.7	10.7	11.8	10.7	11.8	10.7	9.7
90°	28.9	28.5	28.0	27.8	27.1	25.8	24.5	23.1	21.8	20.0	18.3
92.5°	26.8	26.8	26.8	26.8	26.1	24.8	23.5	22.1	20.8	19.0	17.3
95°	28.4	28.1	27.9	27.8	27.1	25.8	24.5	23.1	21.8	21.6	21.4
97.5°	27.4	27.1	26.9	26.8	26.2	25.1	24.0	22.9	21.8	45.0	68.2
100°	27.4	27.1	26.9	26.8	28.7	32.4	36.2	39.9	43.7	74.1	104.5
102.5°	28.8	28.8	28.8	28.8	53.6	103.2	152.9	202.5	252.1	249.5	246.8
105°	298.8	306.7	314.6	318.6	317.6	315.6	313.7	311.7	309.7	308.6	307.5
107.5°	380.4	379.5	378.6	378.2	377.6	376.5	375.4	374.3	373.2	371.6	370.1
110°	441.4	440.7	440.0	439.7	439.5	439.0	438.6	438.1	437.7	436.4	435.1

TEST NUMBER: P1013398

CATALOG NUMBER: S124RDIP-B795D1035UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	501.4	500.5	499.6	499.2	499.3	499.5	499.8	500.0	500.2	499.8	499.4
115°	561.8	561.8	561.8	561.8	561.6	561.1	560.7	560.2	559.8	560.0	560.2
117.5°	622.3	622.3	622.3	622.3	622.4	622.6	622.9	623.1	623.3	622.6	622.0
120°	679.8	680.2	680.7	680.9	680.7	680.2	679.8	679.3	678.9	679.1	679.3
122.5°	735.4	735.8	736.3	736.5	736.4	736.2	735.9	735.7	735.5	735.1	734.6
125°	789.7	789.4	789.2	789.1	788.8	788.1	787.4	786.8	786.1	786.5	787.0
127.5°	839.1	839.4	839.6	839.7	839.8	840.0	840.3	840.5	840.7	839.6	838.5
130°	888.3	888.3	888.3	888.3	888.2	888.0	887.7	887.5	887.3	886.6	886.0
132.5°	934.4	934.7	934.9	935.0	934.9	934.7	934.4	934.2	934.0	933.1	932.2
135°	978.7	978.3	977.8	977.6	977.4	977.0	976.5	976.1	975.7	974.8	973.9
137.5°	1018.7	1019.0	1019.2	1019.3	1019.1	1018.6	1018.2	1017.7	1017.3	1016.2	1015.1
140°	1058.6	1058.3	1058.1	1058.0	1057.7	1057.0	1056.4	1055.7	1055.1	1054.7	1054.2
142.5°	1092.8	1092.8	1092.8	1092.8	1092.6	1092.1	1091.7	1091.2	1090.8	1090.6	1090.4
145°	1126.6	1126.2	1125.7	1125.5	1125.4	1125.2	1124.9	1124.7	1124.5	1124.5	1124.5
147.5°	1155.9	1155.6	1155.4	1155.3	1155.2	1155.0	1154.7	1154.5	1154.3	1154.5	1154.7
150°	1183.7	1183.4	1183.2	1183.1	1183.1	1183.1	1183.1	1183.1	1183.1	1183.3	1183.5
152.5°	1208.3	1208.6	1208.8	1208.9	1208.7	1208.2	1207.8	1207.3	1206.9	1207.3	1207.8
155°	1230.1	1230.7	1231.4	1231.7	1231.3	1230.4	1229.5	1228.7	1227.8	1228.4	1229.1
157.5°	1248.8	1249.9	1251.0	1251.6	1251.0	1249.9	1248.8	1247.7	1246.6	1247.5	1248.4
160°	1267.1	1268.4	1269.7	1270.4	1269.7	1268.4	1267.1	1265.8	1264.5	1264.7	1264.9
162.5°	1281.5	1283.0	1284.5	1285.3	1284.6	1283.3	1282.0	1280.7	1279.4	1279.6	1279.8
165°	1295.3	1297.2	1299.2	1300.2	1299.3	1297.6	1295.8	1294.1	1292.3	1292.3	1292.3
167.5°	1305.6	1307.8	1310.0	1311.1	1310.1	1308.1	1306.2	1304.2	1302.2	1302.4	1302.6
170°	1314.5	1316.8	1319.0	1320.1	1319.2	1317.4	1315.7	1313.9	1312.1	1311.9	1311.7
172.5°	1319.9	1322.4	1324.8	1326.0	1325.1	1323.4	1321.6	1319.9	1318.1	1317.9	1317.7
175°	1324.4	1327.0	1329.7	1331.0	1330.0	1328.0	1326.1	1324.1	1322.1	1321.9	1321.7
177.5°	1326.4	1329.0	1331.7	1333.0	1332.1	1330.3	1328.6	1326.8	1325.0	1324.6	1324.1
180°	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0

TEST NUMBER: P1013398

CATALOG NUMBER: S124RDIP-B795D1035UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7
2.5°	1367.1	1361.7	1358.5	1357.4	1347.8	1342.4	1339.2	1337.0	1333.8	1325.2	1317.7
5°	1418.6	1403.6	1396.1	1387.5	1372.5	1355.3	1341.3	1332.7	1322.0	1304.8	1288.7
7.5°	1467.0	1444.4	1429.4	1417.6	1391.8	1363.9	1341.3	1323.1	1302.7	1279.0	1256.5
10°	1517.5	1480.9	1461.6	1443.3	1405.8	1369.2	1337.0	1310.2	1281.2	1250.0	1225.3
12.5°	1557.2	1508.9	1487.4	1461.6	1415.4	1372.5	1331.7	1295.1	1257.6	1224.3	1188.8
15°	1603.4	1543.2	1518.5	1485.2	1421.9	1366.0	1313.4	1273.7	1235.0	1185.6	1148.0
17.5°	1630.2	1560.4	1525.0	1496.0	1427.2	1359.6	1298.4	1249.0	1203.9	1154.5	1114.7
20°	1657.1	1577.6	1537.9	1497.0	1415.4	1343.5	1279.0	1220.0	1172.7	1119.0	1078.2
22.5°	1665.7	1573.3	1531.4	1493.8	1407.9	1327.4	1253.3	1193.1	1138.4	1084.7	1038.5
25°	1665.7	1572.2	1522.8	1474.5	1384.3	1301.6	1227.5	1162.0	1100.8	1047.1	1000.9
27.5°	1648.5	1550.7	1499.2	1455.2	1361.7	1272.6	1196.3	1124.4	1065.3	1011.6	959.0
30°	1627.0	1519.6	1468.0	1415.4	1325.2	1240.4	1157.7	1091.1	1028.8	967.6	920.4
32.5°	1600.1	1486.3	1429.4	1375.7	1280.1	1192.1	1115.8	1050.3	991.2	927.9	875.2
35°	1561.5	1436.9	1373.5	1326.3	1233.9	1142.7	1069.6	1005.2	948.3	882.8	825.8
37.5°	1512.1	1391.8	1327.4	1269.4	1173.8	1090.0	1021.3	959.0	903.2	843.0	779.7
40°	1454.1	1328.4	1272.6	1211.4	1110.4	1031.0	966.5	910.7	854.8	797.9	736.7
42.5°	1388.6	1264.0	1201.7	1142.7	1046.0	967.6	907.5	857.0	805.4	752.8	687.3
45°	1310.2	1193.1	1133.0	1077.1	983.7	903.2	848.4	800.1	756.0	702.3	644.4
47.5°	1222.1	1120.1	1058.9	998.7	907.5	837.7	784.0	743.2	705.6	651.9	599.2
50°	1136.2	1035.3	985.9	924.6	840.9	775.4	720.6	686.2	657.2	604.6	557.4
52.5°	1027.7	951.5	904.2	851.6	771.1	704.5	661.5	631.5	597.1	556.3	514.4
55°	932.2	861.3	823.7	774.3	694.8	635.8	599.2	571.3	544.5	508.0	474.7
57.5°	823.7	779.7	742.1	699.1	620.7	570.3	538.0	514.4	489.7	459.6	432.8
60°	709.9	689.5	652.9	618.6	552.0	508.0	481.1	459.6	436.0	411.3	388.8
62.5°	608.9	597.1	575.6	548.8	486.5	448.9	422.1	405.9	388.8	366.2	344.7
65°	513.3	508.0	487.6	468.2	425.3	392.0	368.4	358.7	339.4	322.2	302.8
67.5°	428.5	422.1	410.2	401.6	365.1	334.0	322.2	309.3	293.2	280.3	264.2
70°	342.6	341.5	334.0	323.3	303.9	281.4	269.6	261.0	244.9	235.2	223.4
72.5°	266.3	271.7	265.3	261.0	248.1	232.0	221.2	215.9	203.0	195.5	186.9
75°	198.7	203.0	206.2	198.7	195.5	187.9	178.3	172.9	166.5	155.7	152.5
77.5°	135.3	145.0	145.0	147.1	148.2	143.9	136.4	132.1	124.6	122.4	118.1
80°	89.1	97.7	98.8	100.9	104.2	104.2	98.8	97.7	90.2	89.1	85.9
82.5°	51.5	59.1	63.4	66.6	65.5	69.8	65.5	64.4	60.1	60.1	58.0
85°	27.9	29.0	31.1	33.3	35.4	37.6	37.6	36.5	35.4	34.4	32.2
87.5°	10.7	10.7	11.8	10.7	11.8	14.0	15.0	15.0	14.0	12.9	10.7
90°	16.5	14.8	13.9	12.7	10.3	7.8	5.4	3.0	5.4	7.8	10.3
92.5°	15.5	13.8	12.9	13.1	13.6	14.0	14.5	14.9	14.5	14.0	13.6
95°	21.1	20.9	20.8	24.6	32.1	39.6	47.1	54.6	47.1	39.6	32.1
97.5°	91.3	114.5	126.1	123.7	118.8	113.9	109.1	104.2	109.1	113.9	118.8
100°	135.0	165.4	180.6	178.6	174.7	170.7	166.8	162.8	166.8	170.7	174.7
102.5°	244.2	241.5	240.2	238.9	236.2	233.6	230.9	228.3	230.9	233.6	236.2
105°	306.4	305.3	304.7	304.0	302.7	301.4	300.1	298.8	300.1	301.4	302.7
107.5°	368.5	367.0	366.2	365.9	365.2	364.6	363.9	363.3	363.9	364.6	365.2
110°	433.8	432.5	431.8	431.5	430.8	430.1	429.5	428.8	429.5	430.1	430.8

TEST NUMBER: P1013398

CATALOG NUMBER: S124RDIP-B795D1035UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	498.9	498.5	498.3	497.6	496.3	495.0	493.6	492.3	493.6	495.0	496.3
115°	560.5	560.7	560.8	560.5	559.8	559.1	558.5	557.8	558.5	559.1	559.8
117.5°	621.3	620.6	620.3	619.9	619.0	618.1	617.3	616.4	617.3	618.1	619.0
120°	679.6	679.8	679.9	679.5	678.6	677.7	676.8	675.9	676.8	677.7	678.6
122.5°	734.2	733.7	733.5	733.3	732.8	732.4	731.9	731.5	731.9	732.4	732.8
125°	787.4	787.9	788.1	787.7	786.8	785.9	785.0	784.1	785.0	785.9	786.8
127.5°	837.4	836.3	835.7	835.6	835.4	835.1	834.9	834.7	834.9	835.1	835.4
130°	885.3	884.6	884.3	884.2	884.0	883.8	883.6	883.4	883.6	883.8	884.0
132.5°	931.3	930.4	930.0	929.8	929.3	928.9	928.4	928.0	928.4	928.9	929.3
135°	973.0	972.1	971.7	971.8	972.0	972.3	972.5	972.7	972.5	972.3	972.0
137.5°	1014.0	1012.9	1012.4	1012.4	1012.4	1012.4	1012.4	1012.4	1012.4	1012.4	1012.4
140°	1053.8	1053.3	1053.1	1052.9	1052.4	1052.0	1051.5	1051.1	1051.5	1052.0	1052.4
142.5°	1090.1	1089.9	1089.8	1089.4	1088.5	1087.6	1086.7	1085.8	1086.7	1087.6	1088.5
145°	1124.5	1124.5	1124.5	1124.2	1123.5	1122.9	1122.2	1121.6	1122.2	1122.9	1123.5
147.5°	1155.0	1155.2	1155.3	1154.6	1153.3	1152.0	1150.7	1149.4	1150.7	1152.0	1153.3
150°	1183.8	1184.0	1184.1	1183.7	1182.8	1181.9	1181.0	1180.1	1181.0	1181.9	1182.8
152.5°	1208.2	1208.7	1208.9	1208.6	1207.9	1207.2	1206.6	1205.9	1206.6	1207.2	1207.9
155°	1229.7	1230.4	1230.7	1230.6	1230.4	1230.1	1229.9	1229.7	1229.9	1230.1	1230.4
157.5°	1249.3	1250.2	1250.6	1250.6	1250.6	1250.6	1250.6	1250.6	1250.6	1250.6	1250.6
160°	1265.2	1265.4	1265.5	1265.8	1266.5	1267.2	1267.8	1268.5	1267.8	1267.2	1266.5
162.5°	1280.1	1280.3	1280.4	1280.8	1281.7	1282.6	1283.4	1284.3	1283.4	1282.6	1281.7
165°	1292.3	1292.3	1292.3	1292.8	1293.9	1295.0	1296.1	1297.2	1296.1	1295.0	1293.9
167.5°	1302.9	1303.1	1303.2	1303.8	1304.9	1306.0	1307.1	1308.2	1307.1	1306.0	1304.9
170°	1311.4	1311.2	1311.1	1311.8	1313.1	1314.4	1315.8	1317.1	1315.8	1314.4	1313.1
172.5°	1317.4	1317.2	1317.1	1317.8	1319.1	1320.4	1321.7	1323.0	1321.7	1320.4	1319.1
175°	1321.4	1321.2	1321.1	1321.8	1323.1	1324.4	1325.7	1327.0	1325.7	1324.4	1323.1
177.5°	1323.7	1323.2	1323.0	1323.8	1325.3	1326.9	1328.4	1330.0	1328.4	1326.9	1325.3
180°	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0

TEST NUMBER: P1013398

CATALOG NUMBER: S124RDIP-B795D1035UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7
2.5°	1311.3	1309.1	1307.0	1298.4	1290.9	1278.0	1267.2	1262.9	1261.9	1262.9	1259.7
5°	1273.7	1272.6	1265.1	1250.0	1236.1	1221.0	1210.3	1199.6	1193.1	1193.1	1185.6
7.5°	1238.2	1230.7	1224.3	1204.9	1188.8	1168.4	1152.3	1142.7	1137.3	1125.5	1125.5
10°	1200.6	1189.9	1181.3	1163.1	1139.4	1119.0	1098.6	1086.8	1077.1	1068.6	1065.3
12.5°	1163.1	1154.5	1138.4	1119.0	1095.4	1069.6	1048.1	1039.6	1017.0	998.7	999.8
15°	1127.6	1108.3	1100.8	1072.8	1044.9	1020.2	989.1	964.4	946.1	934.3	919.3
17.5°	1087.9	1068.6	1054.6	1031.0	994.5	955.8	925.7	892.4	874.2	853.8	844.1
20°	1043.9	1027.7	1017.0	979.4	935.4	889.2	855.9	835.5	815.1	800.1	791.5
22.5°	1006.3	985.9	973.0	922.5	874.2	828.0	802.2	785.0	767.9	755.0	750.7
25°	957.9	946.1	915.0	870.9	811.9	780.7	758.2	735.6	726.0	717.4	707.7
27.5°	918.2	889.2	867.7	809.7	773.2	737.8	715.2	698.0	686.2	677.6	670.1
30°	868.8	842.0	811.9	763.6	730.3	697.0	676.6	662.6	649.7	644.4	637.9
32.5°	817.3	792.6	763.6	724.9	684.1	658.3	642.2	627.2	618.6	613.2	605.7
35°	771.1	739.9	720.6	684.1	650.8	621.8	606.8	593.9	584.2	582.1	581.0
37.5°	721.7	698.0	679.8	642.2	614.3	589.6	575.6	561.7	556.3	555.2	550.9
40°	678.7	658.3	641.1	605.7	575.6	553.1	542.3	533.7	528.4	528.4	527.3
42.5°	641.1	619.7	602.5	570.3	543.4	523.0	511.2	502.6	500.4	501.5	500.4
45°	599.2	581.0	563.8	530.5	508.0	492.9	480.0	475.7	472.5	473.6	474.7
47.5°	559.5	544.5	527.3	500.4	474.7	458.6	451.0	446.8	446.8	446.8	448.9
50°	524.1	506.9	491.9	463.9	440.3	427.4	421.0	415.6	416.7	417.8	418.8
52.5°	482.2	467.2	456.4	428.5	411.3	395.2	387.7	388.8	387.7	387.7	389.8
55°	445.7	430.6	419.9	394.1	376.9	366.2	359.8	356.5	357.6	355.5	359.8
57.5°	404.9	392.0	384.5	359.8	344.7	335.1	329.7	324.3	326.5	325.4	324.3
60°	369.4	354.4	342.6	325.4	312.5	300.7	297.5	292.1	294.3	292.1	291.0
62.5°	328.6	316.8	308.2	291.0	280.3	270.6	263.1	259.9	258.8	255.6	252.4
65°	287.8	281.4	272.8	255.6	244.9	237.3	233.0	229.8	228.7	220.2	210.5
67.5°	250.2	245.9	237.3	224.4	214.8	207.3	200.8	195.5	189.0	182.6	177.2
70°	214.8	208.3	203.0	191.2	182.6	175.0	168.6	162.2	158.9	152.5	150.3
72.5°	180.4	174.0	168.6	157.9	150.3	142.8	140.7	133.2	129.9	128.9	128.9
75°	145.0	139.6	136.4	126.7	120.3	114.9	111.7	109.5	107.4	105.2	102.0
77.5°	110.6	107.4	105.2	98.8	93.4	90.2	89.1	81.6	79.5	77.3	75.2
80°	80.5	79.5	77.3	72.0	69.8	62.3	62.3	60.1	59.1	59.1	59.1
82.5°	54.8	52.6	51.5	46.2	45.1	44.0	43.0	41.9	43.0	41.9	43.0
85°	29.0	27.9	26.8	26.8	26.8	26.8	26.8	26.8	26.8	25.8	26.8
87.5°	10.7	10.7	10.7	10.7	9.7	10.7	10.7	9.7	10.7	10.7	10.7
90°	12.7	13.9	14.8	16.5	18.3	20.0	21.8	23.1	24.5	25.8	27.1
92.5°	13.1	12.9	13.8	15.5	17.3	19.0	20.8	22.1	23.5	24.8	26.1
95°	24.6	20.8	20.9	21.1	21.4	21.6	21.8	23.1	24.5	25.8	27.1
97.5°	123.7	126.1	114.5	91.3	68.2	45.0	21.8	22.9	24.0	25.1	26.2
100°	178.6	180.6	165.4	135.0	104.5	74.1	43.7	39.9	36.2	32.4	28.7
102.5°	238.9	240.2	241.5	244.2	246.8	249.5	252.1	202.5	152.9	103.2	53.6
105°	304.0	304.7	305.3	306.4	307.5	308.6	309.7	311.7	313.7	315.6	317.6
107.5°	365.9	366.2	367.0	368.5	370.1	371.6	373.2	374.3	375.4	376.5	377.6
110°	431.5	431.8	432.5	433.8	435.1	436.4	437.7	438.1	438.6	439.0	439.5

TEST NUMBER: P1013398

CATALOG NUMBER: S124RDIP-B795D1035UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	497.6	498.3	498.5	498.9	499.4	499.8	500.2	500.0	499.8	499.5	499.3
115°	560.5	560.8	560.7	560.5	560.2	560.0	559.8	560.2	560.7	561.1	561.6
117.5°	619.9	620.3	620.6	621.3	622.0	622.6	623.3	623.1	622.9	622.6	622.4
120°	679.5	679.9	679.8	679.6	679.3	679.1	678.9	679.3	679.8	680.2	680.7
122.5°	733.3	733.5	733.7	734.2	734.6	735.1	735.5	735.7	735.9	736.2	736.4
125°	787.7	788.1	787.9	787.4	787.0	786.5	786.1	786.8	787.4	788.1	788.8
127.5°	835.6	835.7	836.3	837.4	838.5	839.6	840.7	840.5	840.3	840.0	839.8
130°	884.2	884.3	884.6	885.3	886.0	886.6	887.3	887.5	887.7	888.0	888.2
132.5°	929.8	930.0	930.4	931.3	932.2	933.1	934.0	934.2	934.4	934.7	934.9
135°	971.8	971.7	972.1	973.0	973.9	974.8	975.7	976.1	976.5	977.0	977.4
137.5°	1012.4	1012.4	1012.9	1014.0	1015.1	1016.2	1017.3	1017.7	1018.2	1018.6	1019.1
140°	1052.9	1053.1	1053.3	1053.8	1054.2	1054.7	1055.1	1055.7	1056.4	1057.0	1057.7
142.5°	1089.4	1089.8	1089.9	1090.1	1090.4	1090.6	1090.8	1091.2	1091.7	1092.1	1092.6
145°	1124.2	1124.5	1124.5	1124.5	1124.5	1124.5	1124.5	1124.7	1124.9	1125.2	1125.4
147.5°	1154.6	1155.3	1155.2	1155.0	1154.7	1154.5	1154.3	1154.5	1154.7	1155.0	1155.2
150°	1183.7	1184.1	1184.0	1183.8	1183.5	1183.3	1183.1	1183.1	1183.1	1183.1	1183.1
152.5°	1208.6	1208.9	1208.7	1208.2	1207.8	1207.3	1206.9	1207.3	1207.8	1208.2	1208.7
155°	1230.6	1230.7	1230.4	1229.7	1229.1	1228.4	1227.8	1228.7	1229.5	1230.4	1231.3
157.5°	1250.6	1250.6	1250.2	1249.3	1248.4	1247.5	1246.6	1247.7	1248.8	1249.9	1251.0
160°	1265.8	1265.5	1265.4	1265.2	1264.9	1264.7	1264.5	1265.8	1267.1	1268.4	1269.7
162.5°	1280.8	1280.4	1280.3	1280.1	1279.8	1279.6	1279.4	1280.7	1282.0	1283.3	1284.6
165°	1292.8	1292.3	1292.3	1292.3	1292.3	1292.3	1292.3	1294.1	1295.8	1297.6	1299.3
167.5°	1303.8	1303.2	1303.1	1302.9	1302.6	1302.4	1302.2	1304.2	1306.2	1308.1	1310.1
170°	1311.8	1311.1	1311.2	1311.4	1311.7	1311.9	1312.1	1313.9	1315.7	1317.4	1319.2
172.5°	1317.8	1317.1	1317.2	1317.4	1317.7	1317.9	1318.1	1319.9	1321.6	1323.4	1325.1
175°	1321.8	1321.1	1321.2	1321.4	1321.7	1321.9	1322.1	1324.1	1326.1	1328.0	1330.0
177.5°	1323.8	1323.0	1323.2	1323.7	1324.1	1324.6	1325.0	1326.8	1328.6	1330.3	1332.1
180°	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0

TEST NUMBER: P1013398

CATALOG NUMBER: S124RDIP-B795D1035UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7
2.5°	1259.7	1264.0	1258.6	1261.9	1254.3	1253.3	1254.3	1254.3	1255.4	1256.5	1257.6
5°	1188.8	1187.8	1181.3	1177.0	1173.8	1177.0	1179.2	1181.3	1179.2	1181.3	1182.4
7.5°	1122.2	1119.0	1115.8	1108.3	1110.4	1108.3	1114.7	1111.5	1111.5	1116.9	1121.2
10°	1063.2	1056.7	1054.6	1046.0	1039.6	1038.5	1046.0	1049.2	1052.4	1054.6	1063.2
12.5°	986.9	977.3	969.8	973.0	954.7	962.2	964.4	960.1	973.0	988.0	979.4
15°	905.3	906.4	891.4	886.0	870.9	875.2	876.3	887.1	897.8	896.7	909.6
17.5°	845.2	838.7	825.8	824.8	818.3	821.5	820.5	829.1	825.8	831.2	842.0
20°	789.3	785.0	774.3	770.0	772.1	770.0	771.1	772.1	775.4	787.2	785.0
22.5°	745.3	739.9	739.9	734.6	728.1	726.0	731.3	734.6	738.9	741.0	746.4
25°	706.6	702.3	697.0	693.8	688.4	689.5	692.7	697.0	700.2	704.5	708.8
27.5°	666.9	666.9	661.5	660.5	658.3	657.2	661.5	663.7	663.7	666.9	671.2
30°	635.8	635.8	630.4	629.3	628.2	628.2	631.5	632.5	633.6	636.8	639.0
32.5°	605.7	604.6	602.5	603.5	602.5	603.5	603.5	604.6	606.8	607.8	612.1
35°	577.8	578.8	576.7	576.7	575.6	576.7	578.8	579.9	581.0	583.1	583.1
37.5°	550.9	553.1	552.0	555.2	555.2	555.2	555.2	557.4	557.4	557.4	556.3
40°	527.3	527.3	526.2	528.4	530.5	530.5	531.6	531.6	532.7	532.7	531.6
42.5°	500.4	502.6	505.8	506.9	509.0	508.0	511.2	510.1	511.2	509.0	506.9
45°	475.7	475.7	480.0	484.3	485.4	485.4	485.4	487.6	485.4	482.2	481.1
47.5°	448.9	451.0	453.2	458.6	459.6	459.6	459.6	459.6	457.5	457.5	457.5
50°	422.1	423.1	424.2	426.3	429.6	428.5	428.5	428.5	432.8	428.5	429.6
52.5°	389.8	390.9	392.0	396.3	395.2	395.2	396.3	396.3	399.5	398.4	396.3
55°	357.6	357.6	359.8	359.8	359.8	361.9	363.0	365.1	364.1	365.1	366.2
57.5°	325.4	323.3	322.2	322.2	325.4	324.3	325.4	325.4	329.7	331.8	332.9
60°	287.8	287.8	286.7	280.3	280.3	279.2	282.4	284.6	286.7	296.4	295.3
62.5°	249.1	244.9	240.6	241.6	235.2	238.4	236.3	238.4	244.9	252.4	253.4
65°	210.5	207.3	203.0	201.9	199.7	203.0	201.9	203.0	206.2	210.5	215.9
67.5°	176.1	175.0	172.9	171.8	171.8	171.8	174.0	174.0	175.0	178.3	181.5
70°	150.3	149.3	150.3	148.2	149.3	148.2	149.3	150.3	151.4	152.5	155.7
72.5°	126.7	126.7	126.7	124.6	126.7	125.6	125.6	126.7	127.8	128.9	131.0
75°	100.9	98.8	96.7	94.5	93.4	95.6	96.7	95.6	98.8	103.1	103.1
77.5°	76.2	75.2	75.2	75.2	76.2	75.2	77.3	76.2	77.3	77.3	79.5
80°	59.1	58.0	59.1	59.1	58.0	60.1	59.1	59.1	60.1	61.2	60.1
82.5°	43.0	44.0	43.0	43.0	43.0	45.1	43.0	43.0	43.0	44.0	44.0
85°	26.8	26.8	26.8	26.8	27.9	26.8	27.9	26.8	29.0	27.9	27.9
87.5°	9.7	10.7	11.8	11.8	11.8	11.8	10.7	11.8	12.9	11.8	12.9
90°	27.8	28.0	28.5	28.9	29.4	29.8	29.4	28.9	28.5	28.0	27.8
92.5°	26.8	26.8	26.8	26.8	26.8	26.8	26.8	26.8	26.8	26.8	26.8
95°	27.8	27.9	28.1	28.4	28.6	28.8	28.6	28.4	28.1	27.9	27.8
97.5°	26.8	26.9	27.1	27.4	27.6	27.8	27.6	27.4	27.1	26.9	26.8
100°	26.8	26.9	27.1	27.4	27.6	27.8	27.6	27.4	27.1	26.9	26.8
102.5°	28.8	28.8	28.8	28.8	28.8	28.8	28.8	28.8	28.8	28.8	28.8
105°	318.6	314.6	306.7	298.8	290.8	282.9	290.8	298.8	306.7	314.6	318.6
107.5°	378.2	378.6	379.5	380.4	381.2	382.1	381.2	380.4	379.5	378.6	378.2
110°	439.7	440.0	440.7	441.4	442.0	442.7	442.0	441.4	440.7	440.0	439.7

TEST NUMBER: P1013398

CATALOG NUMBER: S124RDIP-B795D1035UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	499.2	499.6	500.5	501.4	502.3	503.2	502.3	501.4	500.5	499.6	499.2
115°	561.8	561.8	561.8	561.8	561.8	561.8	561.8	561.8	561.8	561.8	561.8
117.5°	622.3	622.3	622.3	622.3	622.3	622.3	622.3	622.3	622.3	622.3	622.3
120°	680.9	680.7	680.2	679.8	679.3	678.9	679.3	679.8	680.2	680.7	680.9
122.5°	736.5	736.3	735.8	735.4	734.9	734.5	734.9	735.4	735.8	736.3	736.5
125°	789.1	789.2	789.4	789.7	789.9	790.1	789.9	789.7	789.4	789.2	789.1
127.5°	839.7	839.6	839.4	839.1	838.9	838.7	838.9	839.1	839.4	839.6	839.7
130°	888.3	888.3	888.3	888.3	888.3	888.3	888.3	888.3	888.3	888.3	888.3
132.5°	935.0	934.9	934.7	934.4	934.2	934.0	934.2	934.4	934.7	934.9	935.0
135°	977.6	977.8	978.3	978.7	979.2	979.6	979.2	978.7	978.3	977.8	977.6
137.5°	1019.3	1019.2	1019.0	1018.7	1018.5	1018.3	1018.5	1018.7	1019.0	1019.2	1019.3
140°	1058.0	1058.1	1058.3	1058.6	1058.8	1059.0	1058.8	1058.6	1058.3	1058.1	1058.0
142.5°	1092.8	1092.8	1092.8	1092.8	1092.8	1092.8	1092.8	1092.8	1092.8	1092.8	1092.8
145°	1125.5	1125.7	1126.2	1126.6	1127.1	1127.5	1127.1	1126.6	1126.2	1125.7	1125.5
147.5°	1155.3	1155.4	1155.6	1155.9	1156.1	1156.3	1156.1	1155.9	1155.6	1155.4	1155.3
150°	1183.1	1183.2	1183.4	1183.7	1183.9	1184.1	1183.9	1183.7	1183.4	1183.2	1183.1
152.5°	1208.9	1208.8	1208.6	1208.3	1208.1	1207.9	1208.1	1208.3	1208.6	1208.8	1208.9
155°	1231.7	1231.4	1230.7	1230.1	1229.4	1228.8	1229.4	1230.1	1230.7	1231.4	1231.7
157.5°	1251.6	1251.0	1249.9	1248.8	1247.7	1246.6	1247.7	1248.8	1249.9	1251.0	1251.6
160°	1270.4	1269.7	1268.4	1267.1	1265.8	1264.5	1265.8	1267.1	1268.4	1269.7	1270.4
162.5°	1285.3	1284.5	1283.0	1281.5	1279.9	1278.4	1279.9	1281.5	1283.0	1284.5	1285.3
165°	1300.2	1299.2	1297.2	1295.3	1293.3	1291.3	1293.3	1295.3	1297.2	1299.2	1300.2
167.5°	1311.1	1310.0	1307.8	1305.6	1303.4	1301.2	1303.4	1305.6	1307.8	1310.0	1311.1
170°	1320.1	1319.0	1316.8	1314.5	1312.3	1310.1	1312.3	1314.5	1316.8	1319.0	1320.1
172.5°	1326.0	1324.8	1322.4	1319.9	1317.5	1315.1	1317.5	1319.9	1322.4	1324.8	1326.0
175°	1331.0	1329.7	1327.0	1324.4	1321.7	1319.1	1321.7	1324.4	1327.0	1329.7	1331.0
177.5°	1333.0	1331.7	1329.0	1326.4	1323.7	1321.1	1323.7	1326.4	1329.0	1331.7	1333.0
180°	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0

TEST NUMBER: P1013398

CATALOG NUMBER: S124RDIP-B795D1035UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7
2.5°	1261.9	1267.2	1265.1	1257.6	1260.8	1267.2	1273.7	1282.3	1287.6	1291.9	1294.1
5°	1187.8	1197.4	1195.3	1195.3	1199.6	1210.3	1221.0	1239.3	1245.7	1253.3	1264.0
7.5°	1122.2	1129.8	1136.2	1138.4	1144.8	1158.8	1172.7	1193.1	1209.2	1217.8	1224.3
10°	1064.3	1069.6	1079.3	1084.7	1091.1	1108.3	1128.7	1150.2	1166.3	1181.3	1189.9
12.5°	990.2	1011.6	1024.5	1033.1	1041.7	1067.5	1083.6	1107.2	1126.5	1140.5	1153.4
15°	907.5	933.2	940.8	974.0	995.5	1015.9	1040.6	1068.6	1086.8	1102.9	1120.1
17.5°	837.7	855.9	864.5	899.9	918.2	950.4	985.9	1021.3	1049.2	1061.0	1078.2
20°	793.6	803.3	820.5	832.3	851.6	889.2	927.9	970.8	1012.7	1024.5	1041.7
22.5°	748.5	761.4	773.2	789.3	804.4	830.1	868.8	916.1	961.2	982.6	1003.0
25°	707.7	720.6	728.1	745.3	759.3	785.0	811.9	860.2	913.9	932.2	964.4
27.5°	675.5	683.0	695.9	703.4	719.5	743.2	767.9	804.4	857.0	888.1	919.3
30°	643.3	648.6	659.4	670.1	681.9	698.0	726.0	761.4	809.7	836.6	867.7
32.5°	611.1	619.7	626.1	633.6	646.5	665.8	685.2	719.5	758.2	788.3	819.4
35°	584.2	587.4	596.0	604.6	613.2	630.4	650.8	684.1	718.5	742.1	770.0
37.5°	555.2	560.6	567.0	570.3	584.2	595.0	616.4	642.2	683.0	698.0	726.0
40°	532.7	531.6	538.0	543.4	549.8	567.0	579.9	607.8	640.1	663.7	680.9
42.5°	504.7	504.7	506.9	513.3	521.9	532.7	547.7	571.3	604.6	621.8	642.2
45°	482.2	479.0	480.0	484.3	489.7	500.4	515.5	535.9	569.2	583.1	604.6
47.5°	455.3	452.1	452.1	456.4	460.7	468.2	480.0	503.7	530.5	548.8	564.9
50°	425.3	426.3	425.3	428.5	430.6	438.2	451.0	470.4	495.1	510.1	528.4
52.5°	397.4	395.2	394.1	396.3	400.6	405.9	419.9	437.1	460.7	475.7	491.9
55°	363.0	365.1	365.1	365.1	371.6	373.7	384.5	401.6	425.3	437.1	452.1
57.5°	331.8	330.8	332.9	331.8	337.2	344.7	353.3	366.2	389.8	401.6	415.6
60°	297.5	298.6	299.6	299.6	303.9	311.4	321.1	332.9	352.2	364.1	376.9
62.5°	255.6	261.0	266.3	268.5	274.9	280.3	286.7	299.6	316.8	325.4	337.2
65°	215.9	223.4	230.9	236.3	240.6	245.9	254.5	266.3	280.3	288.9	300.7
67.5°	181.5	186.9	196.5	201.9	210.5	216.9	222.3	232.0	249.1	252.4	262.0
70°	156.8	158.9	163.2	167.5	177.2	182.6	189.0	198.7	211.6	219.1	224.4
72.5°	132.1	133.2	135.3	139.6	143.9	150.3	157.9	166.5	178.3	181.5	189.0
75°	105.2	111.7	111.7	114.9	118.1	121.4	127.8	136.4	143.9	149.3	153.6
77.5°	78.4	81.6	83.8	89.1	93.4	96.7	100.9	107.4	111.7	116.0	119.2
80°	61.2	62.3	63.4	63.4	65.5	69.8	74.1	78.4	83.8	85.9	89.1
82.5°	45.1	45.1	45.1	47.3	48.3	49.4	49.4	51.5	56.9	59.1	62.3
85°	29.0	29.0	29.0	29.0	30.1	31.1	32.2	33.3	33.3	33.3	35.4
87.5°	11.8	14.0	12.9	14.0	14.0	14.0	14.0	15.0	15.0	16.1	16.1
90°	27.1	25.8	24.5	23.1	21.8	20.0	18.3	16.5	14.8	13.9	12.7
92.5°	26.1	24.8	23.5	22.1	20.8	19.0	17.3	15.5	13.8	12.9	13.1
95°	27.1	25.8	24.5	23.1	21.8	21.6	21.4	21.1	20.9	20.8	24.6
97.5°	26.2	25.1	24.0	22.9	21.8	45.0	68.2	91.3	114.5	126.1	123.7
100°	28.7	32.4	36.2	39.9	43.7	74.1	104.5	135.0	165.4	180.6	178.6
102.5°	53.6	103.2	152.9	202.5	252.1	249.5	246.8	244.2	241.5	240.2	238.9
105°	317.6	315.6	313.7	311.7	309.7	308.6	307.5	306.4	305.3	304.7	304.0
107.5°	377.6	376.5	375.4	374.3	373.2	371.6	370.1	368.5	367.0	366.2	365.9
110°	439.5	439.0	438.6	438.1	437.7	436.4	435.1	433.8	432.5	431.8	431.5

TEST NUMBER: P1013398

CATALOG NUMBER: S124RDIP-B795D1035UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	499.3	499.5	499.8	500.0	500.2	499.8	499.4	498.9	498.5	498.3	497.6
115°	561.6	561.1	560.7	560.2	559.8	560.0	560.2	560.5	560.7	560.8	560.5
117.5°	622.4	622.6	622.9	623.1	623.3	622.6	622.0	621.3	620.6	620.3	619.9
120°	680.7	680.2	679.8	679.3	678.9	679.1	679.3	679.6	679.8	679.9	679.5
122.5°	736.4	736.2	735.9	735.7	735.5	735.1	734.6	734.2	733.7	733.5	733.3
125°	788.8	788.1	787.4	786.8	786.1	786.5	787.0	787.4	787.9	788.1	787.7
127.5°	839.8	840.0	840.3	840.5	840.7	839.6	838.5	837.4	836.3	835.7	835.6
130°	888.2	888.0	887.7	887.5	887.3	886.6	886.0	885.3	884.6	884.3	884.2
132.5°	934.9	934.7	934.4	934.2	934.0	933.1	932.2	931.3	930.4	930.0	929.8
135°	977.4	977.0	976.5	976.1	975.7	974.8	973.9	973.0	972.1	971.7	971.8
137.5°	1019.1	1018.6	1018.2	1017.7	1017.3	1016.2	1015.1	1014.0	1012.9	1012.4	1012.4
140°	1057.7	1057.0	1056.4	1055.7	1055.1	1054.7	1054.2	1053.8	1053.3	1053.1	1052.9
142.5°	1092.6	1092.1	1091.7	1091.2	1090.8	1090.6	1090.4	1090.1	1089.9	1089.8	1089.4
145°	1125.4	1125.2	1124.9	1124.7	1124.5	1124.5	1124.5	1124.5	1124.5	1124.5	1124.2
147.5°	1155.2	1155.0	1154.7	1154.5	1154.3	1154.5	1154.7	1155.0	1155.2	1155.3	1154.6
150°	1183.1	1183.1	1183.1	1183.1	1183.1	1183.3	1183.5	1183.8	1184.0	1184.1	1183.7
152.5°	1208.7	1208.2	1207.8	1207.3	1206.9	1207.3	1207.8	1208.2	1208.7	1208.9	1208.6
155°	1231.3	1230.4	1229.5	1228.7	1227.8	1228.4	1229.1	1229.7	1230.4	1230.7	1230.6
157.5°	1251.0	1249.9	1248.8	1247.7	1246.6	1247.5	1248.4	1249.3	1250.2	1250.6	1250.6
160°	1269.7	1268.4	1267.1	1265.8	1264.5	1264.7	1264.9	1265.2	1265.4	1265.5	1265.8
162.5°	1284.6	1283.3	1282.0	1280.7	1279.4	1279.6	1279.8	1280.1	1280.3	1280.4	1280.8
165°	1299.3	1297.6	1295.8	1294.1	1292.3	1292.3	1292.3	1292.3	1292.3	1292.3	1292.8
167.5°	1310.1	1308.1	1306.2	1304.2	1302.2	1302.4	1302.6	1302.9	1303.1	1303.2	1303.8
170°	1319.2	1317.4	1315.7	1313.9	1312.1	1311.9	1311.7	1311.4	1311.2	1311.1	1311.8
172.5°	1325.1	1323.4	1321.6	1319.9	1318.1	1317.9	1317.7	1317.4	1317.2	1317.1	1317.8
175°	1330.0	1328.0	1326.1	1324.1	1322.1	1321.9	1321.7	1321.4	1321.2	1321.1	1321.8
177.5°	1332.1	1330.3	1328.6	1326.8	1325.0	1324.6	1324.1	1323.7	1323.2	1323.0	1323.8
180°	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0	1327.0

TEST NUMBER: P1013398

CATALOG NUMBER: S124RDIP-B795D1035UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1332.7	1332.7	1332.7	1332.7
2.5°	1302.7	1309.1	1319.8	1334.9
5°	1272.6	1290.9	1308.0	1330.6
7.5°	1245.7	1267.2	1290.9	1323.1
10°	1214.6	1241.5	1271.5	1311.3
12.5°	1178.1	1215.7	1250.0	1293.0
15°	1151.2	1179.2	1223.2	1273.7
17.5°	1113.7	1151.2	1195.3	1252.2
20°	1078.2	1118.0	1167.4	1226.4
22.5°	1040.6	1085.7	1135.1	1198.5
25°	1002.0	1050.3	1099.7	1167.4
27.5°	966.5	1010.6	1066.4	1135.1
30°	923.6	974.0	1027.7	1099.7
32.5°	881.7	934.3	989.1	1061.0
35°	836.6	889.2	949.3	1018.1
37.5°	792.6	850.5	905.3	971.9
40°	744.2	804.4	861.3	928.9
42.5°	697.0	759.3	816.2	874.2
45°	652.9	714.2	765.7	820.5
47.5°	611.1	665.8	718.5	767.9
50°	570.3	616.4	664.8	705.6
52.5°	527.3	571.3	610.0	646.5
55°	488.6	523.0	557.4	590.7
57.5°	442.5	476.8	506.9	532.7
60°	403.8	425.3	454.3	481.1
62.5°	359.8	384.5	407.0	424.2
65°	316.8	338.3	355.5	370.5
67.5°	280.3	293.2	306.1	322.2
70°	236.3	247.0	262.0	273.8
72.5°	198.7	207.3	214.8	228.7
75°	161.1	168.6	172.9	185.8
77.5°	124.6	132.1	135.3	142.8
80°	95.6	96.7	100.9	107.4
82.5°	65.5	67.7	68.7	74.1
85°	37.6	43.0	41.9	44.0
87.5°	16.1	17.2	19.3	21.5
90°	10.3	7.8	5.4	3.0
92.5°	13.6	14.0	14.5	14.9
95°	32.1	39.6	47.1	54.6
97.5°	118.8	113.9	109.1	104.2
100°	174.7	170.7	166.8	162.8
102.5°	236.2	233.6	230.9	228.3
105°	302.7	301.4	300.1	298.8
107.5°	365.2	364.6	363.9	363.3
110°	430.8	430.1	429.5	428.8

TEST NUMBER: P1013398

CATALOG NUMBER: S124RDIP-B795D1035UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	496.3	495.0	493.6	492.3
115°	559.8	559.1	558.5	557.8
117.5°	619.0	618.1	617.3	616.4
120°	678.6	677.7	676.8	675.9
122.5°	732.8	732.4	731.9	731.5
125°	786.8	785.9	785.0	784.1
127.5°	835.4	835.1	834.9	834.7
130°	884.0	883.8	883.6	883.4
132.5°	929.3	928.9	928.4	928.0
135°	972.0	972.3	972.5	972.7
137.5°	1012.4	1012.4	1012.4	1012.4
140°	1052.4	1052.0	1051.5	1051.1
142.5°	1088.5	1087.6	1086.7	1085.8
145°	1123.5	1122.9	1122.2	1121.6
147.5°	1153.3	1152.0	1150.7	1149.4
150°	1182.8	1181.9	1181.0	1180.1
152.5°	1207.9	1207.2	1206.6	1205.9
155°	1230.4	1230.1	1229.9	1229.7
157.5°	1250.6	1250.6	1250.6	1250.6
160°	1266.5	1267.2	1267.8	1268.5
162.5°	1281.7	1282.6	1283.4	1284.3
165°	1293.9	1295.0	1296.1	1297.2
167.5°	1304.9	1306.0	1307.1	1308.2
170°	1313.1	1314.4	1315.8	1317.1
172.5°	1319.1	1320.4	1321.7	1323.0
175°	1323.1	1324.4	1325.7	1327.0
177.5°	1325.3	1326.9	1328.4	1330.0
180°	1327.0	1327.0	1327.0	1327.0

(END OF REPORT)