

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007583

Luminaire Tested: S123IP-B585UB40-4F0-XX-W2A-1

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007583
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B585UB40-4F0-XX-W2A-1
Description: Define 3 Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2006.0 lumens
Efficiency: N/A
Efficacy: 130.3 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 15.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007583

CATALOG NUMBER: S123IP-B585UB40-4F0-XX-W2A-1

Luminous Intensity Polar Plot



TEST NUMBER: P1007583

CATALOG NUMBER: S123IP-B585UB40-4F0-XX-W2A-1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007583

CATALOG NUMBER: S123IP-B585UB40-4F0-XX-W2A-1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.5	0.1
90°-100°	46.6	2.3
100°-110°	141.0	7.0
110°-120°	240.0	12.0
120°-130°	315.7	15.7
130°-140°	354.8	17.7
140°-150°	348.8	17.4
150°-160°	293.7	14.6
160°-170°	195.5	9.7
170°-180°	68.5	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.5	0.1
90°-120°	427.5	21.3
90°-150°	1446.8	72.1
90°-180°	2004.0	99.9
0°-180°	2006.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	6	14	16	17	2
95°	34	38	42	44	44	37
105°	128	129	134	134	135	137
115°	242	243	242	243	242	239
125°	354	355	354	352	350	315
135°	459	462	461	459	458	353
145°	556	558	559	559	556	347
155°	637	637	638	640	636	293
165°	694	692	692	696	692	196
175°	722	719	719	723	719	69
180°	723	723	723	723	723	

TEST NUMBER: P1007583

CATALOG NUMBER: S123IP-B585UB40-4F0-XX-W2A-1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.6	6.3	13.6	15.9	17.0
92.5°	17.0	20.5	23.9	25.6	24.4
95°	33.5	37.5	42.1	44.3	44.3
97.5°	55.1	58.0	61.4	64.2	63.6
100°	77.3	80.7	83.5	85.2	86.4
102.5°	102.9	104.6	108.5	110.2	109.7
105°	127.9	129.0	134.1	134.1	135.3
107.5°	157.4	158.0	160.3	162.0	161.4
110°	184.7	185.8	187.0	189.2	188.1

TEST NUMBER: P1007583

CATALOG NUMBER: S123IP-B585UB40-4F0-XX-W2A-1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	213.1	213.7	213.7	216.5	216.5
115°	241.5	243.2	242.1	242.7	242.1
117.5°	270.5	271.1	269.9	269.9	268.2
120°	297.2	300.6	297.8	297.2	296.1
122.5°	325.1	327.3	326.2	324.5	322.8
125°	353.5	355.2	354.0	351.8	349.5
127.5°	379.6	383.0	381.9	378.5	376.2
130°	405.8	410.3	408.6	406.3	402.3
132.5°	431.9	436.4	435.3	432.5	429.6
135°	458.6	462.0	461.4	459.2	458.0
137.5°	483.0	485.9	487.6	484.7	483.0
140°	508.6	511.5	512.0	511.5	507.5
142.5°	531.9	534.8	535.9	535.3	532.5
145°	556.3	557.5	559.2	558.6	556.3
147.5°	577.4	579.6	581.4	581.4	577.9
150°	599.5	600.7	601.8	601.8	598.4
152.5°	617.7	619.4	620.0	621.1	618.3
155°	637.0	637.0	637.6	639.9	635.9
157.5°	653.5	653.0	653.5	655.8	652.4
160°	668.9	667.7	667.7	670.6	668.3
162.5°	682.5	680.8	681.4	684.2	680.2
165°	693.9	692.2	692.2	695.6	691.6
167.5°	703.5	701.3	701.8	705.2	701.8
170°	711.5	709.2	709.2	713.2	709.2
172.5°	717.7	715.5	715.5	718.9	714.9
175°	721.7	719.4	719.4	722.9	718.9
177.5°	724.0	721.7	721.7	725.1	721.1
180°	723.4	723.4	723.4	723.4	723.4

(END OF REPORT)