

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013415

Luminaire Tested: S124RDIP-B795D1205UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013415
REPORT IS A COMBINATION OF REPORTS P999674 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B795D1205UB2750-4F0-XX-W2A-F_5000K
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7725.0 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013415

CATALOG NUMBER: S124RDIP-B795D1205UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013415

CATALOG NUMBER: S124RDIP-B795D1205UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47			40
1	96	92	88	85	87	84	80	78	69	66	64	55	53	52	42	41	40			34
2	87	80	74	69	79	73	68	64	60	57	54	48	46	44	37	36	34			29
3	80	71	64	58	72	65	59	54	53	49	45	43	40	37	33	31	29			25
4	73	63	55	49	66	57	51	46	47	43	39	38	35	32	30	27	25			21
5	67	56	48	42	61	51	44	39	43	37	33	34	31	28	27	24	22			19
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	22	20			17
7	57	45	37	32	52	42	35	30	35	30	26	28	24	22	22	20	18			15
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16			13
9	49	37	30	25	45	35	28	24	29	24	20	24	20	17	19	16	14			12
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	18	15	13			11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10951	10951	10951
5°	10952	10625	10627
10°	10859	10290	10168
15°	10710	9873	9627
20°	10514	9397	9009
25°	10271	8883	8406
30°	10031	8360	7729
35°	9769	7828	7068
40°	9456	7257	6388
45°	9163	6690	5716
50°	8829	6071	5031
55°	8469	5436	4326
60°	8069	4762	3629
65°	7682	3988	2959
70°	7135	3175	2261
75°	6429	2310	1581
80°	5371	1418	1137
85°	4039	817	625

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9163 cd/sqm

TEST NUMBER: P1013415

CATALOG NUMBER: S124RDIP-B795D1205UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	1.6
10°-20°	352.1	4.6
20°-30°	508.3	6.6
30°-40°	576.1	7.5
40°-50°	556.3	7.2
50°-60°	462.5	6.0
60°-70°	319.2	4.1
70°-80°	161.3	2.1
80°-90°	44.0	0.6
90°-100°	49.5	0.6
100°-110°	326.3	4.2
110°-120°	623.1	8.1
120°-130°	791.0	10.2
130°-140°	846.2	11.0
140°-150°	791.3	10.2
150°-160°	638.1	8.3
160°-170°	411.5	5.3
170°-180°	141.8	1.8
0°-30°	986.7	12.8
0°-40°	1562.8	20.2
0°-60°	2581.6	33.4
0°-90°	3106.1	40.2
90°-120°	999.0	12.9
90°-150°	3427.5	44.4
90°-180°	4619.0	59.8
0°-180°	7725.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1343	1343	1343	1343	1343	
5°	1341	1337	1324	1335	1333	127
15°	1277	1268	1242	1240	1233	360
25°	1155	1136	1094	1077	1066	532
35°	998	966	914	879	861	624
45°	814	776	715	664	646	628
55°	617	576	509	456	436	552
65°	420	375	310	265	253	414
75°	223	185	137	113	107	235
85°	56	35	32	30	30	61
90°	3	16	25	31	34	6
95°	61	23	25	31	32	76
105°	336	343	348	358	318	352
115°	627	631	630	632	632	618
125°	882	886	884	888	889	788
135°	1094	1093	1098	1100	1102	843
145°	1262	1265	1265	1266	1268	788
155°	1383	1384	1381	1386	1382	638
165°	1459	1454	1454	1462	1452	412
175°	1493	1486	1487	1497	1484	142
180°	1493	1493	1493	1493	1493	

TEST NUMBER: P1013415

CATALOG NUMBER: S124RDIP-B795D1205UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1342.9	1342.9	1342.9	1342.9	1342.9
2.5°	1347.1	1342.9	1331.6	1342.9	1341.9
5°	1340.9	1336.8	1324.4	1334.7	1332.7
7.5°	1331.6	1327.5	1312.1	1319.3	1316.2
10°	1317.2	1312.1	1293.6	1297.7	1293.6
12.5°	1298.7	1292.6	1269.9	1272.0	1265.8
15°	1277.1	1267.9	1242.2	1240.1	1232.9
17.5°	1252.4	1239.1	1209.3	1204.1	1193.8
20°	1222.6	1209.3	1174.3	1166.1	1152.7
22.5°	1189.7	1174.3	1136.3	1122.9	1112.6
25°	1154.8	1136.3	1094.1	1076.6	1066.3
27.5°	1118.8	1096.1	1051.9	1031.4	1017.0
30°	1080.7	1055.0	1006.7	981.0	964.5
32.5°	1040.6	1010.8	960.4	929.6	914.1
35°	998.5	965.6	914.1	879.2	860.7
37.5°	954.2	920.3	863.8	825.7	807.2
40°	906.9	873.0	814.4	771.2	752.7
42.5°	861.7	825.7	764.0	719.8	700.3
45°	814.4	776.4	714.7	664.3	645.8
47.5°	766.1	727.0	663.2	610.8	590.2
50°	716.7	676.6	610.8	559.4	539.8
52.5°	666.3	627.3	559.4	506.9	486.4
55°	617.0	575.8	509.0	455.5	436.0
57.5°	568.6	525.5	459.6	405.1	390.7
60°	516.2	475.1	409.3	355.8	339.3
62.5°	468.9	425.7	357.8	309.5	297.2
65°	419.5	375.3	309.5	265.3	253.0
67.5°	368.1	326.0	264.3	225.2	210.8
70°	319.8	276.6	218.0	184.1	173.8
72.5°	268.4	230.3	175.8	148.1	138.8
75°	223.1	185.1	136.8	113.1	106.9
77.5°	175.8	142.9	101.8	85.3	83.3
80°	130.6	100.8	69.9	66.8	65.8
82.5°	91.5	64.8	50.4	48.3	47.3
85°	55.5	35.0	31.9	29.8	29.8
87.5°	23.7	15.4	14.4	13.4	14.4
90°	3.3	15.6	24.6	31.3	33.5
92.5°	16.7	14.5	23.4	30.1	30.1
95°	61.4	23.4	24.6	31.3	32.4
97.5°	117.2	141.8	24.6	30.1	31.3
100°	183.1	203.2	49.1	30.1	31.3
102.5°	256.8	270.2	283.6	32.4	32.4
105°	336.1	342.7	348.3	358.4	318.2
107.5°	408.6	412.0	419.8	425.4	429.8
110°	482.3	485.7	492.4	494.6	497.9

TEST NUMBER: P1013415

CATALOG NUMBER: S124RDIP-B795D1205UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	553.8	560.5	562.7	561.6	566.0
115°	627.4	630.8	629.7	631.9	631.9
117.5°	693.3	697.8	701.1	700.0	700.0
120°	760.3	764.8	763.7	765.9	763.7
122.5°	822.8	825.1	827.3	828.4	826.2
125°	882.0	886.5	884.2	887.6	888.7
127.5°	938.9	940.1	945.6	944.5	943.4
130°	993.6	994.8	998.1	999.2	999.2
132.5°	1043.9	1046.1	1050.6	1051.7	1050.6
135°	1094.1	1093.0	1097.5	1099.7	1101.9
137.5°	1138.8	1138.8	1144.4	1146.6	1145.5
140°	1182.3	1184.6	1186.8	1190.1	1191.3
142.5°	1221.4	1225.9	1227.0	1229.2	1229.2
145°	1261.6	1264.9	1264.9	1266.1	1268.3
147.5°	1292.8	1299.5	1298.4	1299.5	1300.7
150°	1327.5	1331.9	1330.8	1330.8	1331.9
152.5°	1356.5	1359.8	1357.6	1359.8	1358.7
155°	1383.3	1384.4	1381.0	1385.5	1382.2
157.5°	1406.7	1406.7	1402.3	1407.8	1402.3
160°	1426.8	1423.5	1422.4	1429.1	1422.4
162.5°	1444.7	1440.2	1439.1	1445.8	1438.0
165°	1459.2	1453.6	1453.6	1462.5	1452.5
167.5°	1471.5	1465.9	1464.8	1474.8	1463.7
170°	1481.5	1474.8	1475.9	1484.9	1473.7
172.5°	1488.2	1481.5	1482.6	1491.6	1479.3
175°	1492.7	1486.0	1487.1	1497.2	1483.8
177.5°	1496.0	1488.2	1490.5	1499.4	1486.0
180°	1492.7	1492.7	1492.7	1492.7	1492.7

(END OF REPORT)