

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013431

Luminaire Tested: S124RDIP-B795D590UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013431
REPORT IS A COMBINATION OF REPORTS P999752 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B795D590UB2750-4F0-XX-W2A-F_3500K
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5618.0 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013431

CATALOG NUMBER: S124RDIP-B795D590UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1013431

CATALOG NUMBER: S124RDIP-B795D590UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	63	63	63
1	100	96	92	88	93	89	86	83	77	75	73	66	65	63	56	55	54
2	91	84	78	73	85	78	73	69	68	64	61	59	56	53	50	48	46
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	45	42	39
4	76	66	58	52	71	62	55	49	54	48	44	47	42	39	40	37	34
5	70	59	51	45	65	55	48	42	48	43	38	42	38	34	36	33	30
6	65	53	45	39	60	50	42	37	44	38	34	38	34	30	33	29	27
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	26	24
8	56	43	36	30	52	41	34	29	36	31	26	32	27	24	28	24	21
9	52	40	32	27	49	38	31	26	33	28	24	29	25	22	26	22	19
10	49	37	29	25	45	35	28	24	31	25	22	27	23	20	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11438	11438	11438
5°	11439	11098	11099
10°	11342	10748	10620
15°	11186	10312	10055
20°	10982	9815	9410
25°	10727	9279	8781
30°	10478	8732	8073
35°	10203	8177	7382
40°	9877	7579	6672
45°	9570	6987	5970
50°	9222	6341	5256
55°	8846	5677	4519
60°	8429	4974	3790
65°	8025	4166	3090
70°	7451	3316	2361
75°	6717	2412	1652
80°	5610	1481	1187
85°	4221	853	652

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9570 cd/sqm

TEST NUMBER: P1013431

CATALOG NUMBER: S124RDIP-B795D590UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.9	2.3
10°-20°	367.8	6.5
20°-30°	530.9	9.5
30°-40°	601.7	10.7
40°-50°	581.0	10.3
50°-60°	483.0	8.6
60°-70°	333.4	5.9
70°-80°	168.5	3.0
80°-90°	44.4	0.8
90°-100°	25.5	0.5
100°-110°	167.8	3.0
110°-120°	320.5	5.7
120°-130°	406.8	7.2
130°-140°	435.2	7.7
140°-150°	406.9	7.2
150°-160°	328.2	5.8
160°-170°	211.6	3.8
170°-180°	72.9	1.3
0°-30°	1030.6	18.3
0°-40°	1632.3	29.1
0°-60°	2696.4	48.0
0°-90°	3242.6	57.7
90°-120°	513.8	9.1
90°-150°	1762.7	31.4
90°-180°	2375.0	42.3
0°-180°	5618.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1403	1403	1403	1403	1403	
5°	1400	1396	1383	1394	1392	133
15°	1334	1324	1297	1295	1288	376
25°	1206	1187	1143	1124	1114	556
35°	1043	1008	955	918	899	652
45°	851	811	746	694	674	656
55°	644	601	532	476	455	576
65°	438	392	323	277	264	433
75°	233	193	143	118	112	246
85°	58	36	33	31	31	64
90°	2	8	13	16	17	5
95°	32	12	13	16	17	39
105°	173	176	179	184	164	181
115°	323	324	324	325	325	318
125°	454	456	455	456	457	405
135°	563	562	564	566	567	434
145°	649	650	650	651	652	405
155°	711	712	710	712	711	328
165°	750	748	748	752	747	212
175°	768	764	765	770	763	73
180°	768	768	768	768	768	

TEST NUMBER: P1013431

CATALOG NUMBER: S124RDIP-B795D590UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1402.7	1402.7	1402.7	1402.7	1402.7
2.5°	1407.0	1402.7	1390.8	1402.7	1401.6
5°	1400.5	1396.2	1383.3	1394.1	1391.9
7.5°	1390.8	1386.6	1370.4	1378.0	1374.7
10°	1375.8	1370.4	1351.1	1355.4	1351.1
12.5°	1356.5	1350.0	1326.4	1328.6	1322.1
15°	1333.9	1324.3	1297.4	1295.3	1287.7
17.5°	1308.1	1294.2	1263.0	1257.7	1246.9
20°	1277.0	1263.0	1226.5	1217.9	1204.0
22.5°	1242.6	1226.5	1186.8	1172.8	1162.1
25°	1206.1	1186.8	1142.8	1124.5	1113.8
27.5°	1168.5	1144.9	1098.7	1077.2	1062.2
30°	1128.8	1101.9	1051.5	1024.6	1007.4
32.5°	1086.9	1055.8	1003.1	970.9	954.8
35°	1042.9	1008.5	954.8	918.3	898.9
37.5°	996.7	961.2	902.2	862.4	843.1
40°	947.3	911.8	850.6	805.5	786.2
42.5°	900.0	862.4	798.0	751.8	731.4
45°	850.6	810.9	746.4	693.8	674.5
47.5°	800.1	759.3	692.7	638.0	616.5
50°	748.6	706.7	638.0	584.3	563.9
52.5°	696.0	655.1	584.3	529.5	508.0
55°	644.4	601.4	531.6	475.8	455.4
57.5°	593.9	548.8	480.1	423.2	408.1
60°	539.2	496.2	427.5	371.6	354.4
62.5°	489.8	444.6	373.8	323.3	310.4
65°	438.2	392.0	323.3	277.1	264.2
67.5°	384.5	340.5	276.0	235.2	220.2
70°	334.0	288.9	227.7	192.2	181.5
72.5°	280.3	240.6	183.7	154.7	145.0
75°	233.1	193.3	142.8	118.1	111.7
77.5°	183.7	149.3	106.3	89.1	87.0
80°	136.4	105.3	73.0	69.8	68.7
82.5°	95.6	67.7	52.6	50.5	49.4
85°	58.0	36.5	33.3	31.1	31.1
87.5°	24.7	16.1	15.0	14.0	15.0
90°	1.7	8.0	12.6	16.1	17.2
92.5°	8.6	7.5	12.1	15.5	15.5
95°	31.6	12.1	12.6	16.1	16.7
97.5°	60.3	72.9	12.6	15.5	16.1
100°	94.2	104.5	25.3	15.5	16.1
102.5°	132.1	138.9	145.8	16.7	16.7
105°	172.8	176.3	179.1	184.3	163.6
107.5°	210.1	211.9	215.9	218.8	221.1
110°	248.0	249.8	253.2	254.4	256.1

TEST NUMBER: P1013431

CATALOG NUMBER: S124RDIP-B795D590UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	284.8	288.2	289.4	288.8	291.1
115°	322.7	324.4	323.8	325.0	325.0
117.5°	356.6	358.9	360.6	360.0	360.0
120°	391.0	393.3	392.7	393.9	392.7
122.5°	423.2	424.3	425.5	426.0	424.9
125°	453.6	455.9	454.7	456.5	457.0
127.5°	482.9	483.4	486.3	485.7	485.2
130°	511.0	511.6	513.3	513.9	513.9
132.5°	536.8	538.0	540.3	540.9	540.3
135°	562.7	562.1	564.4	565.6	566.7
137.5°	585.7	585.7	588.5	589.7	589.1
140°	608.0	609.2	610.3	612.1	612.6
142.5°	628.1	630.4	631.0	632.2	632.2
145°	648.8	650.5	650.5	651.1	652.3
147.5°	664.9	668.3	667.8	668.3	668.9
150°	682.7	685.0	684.4	684.4	685.0
152.5°	697.6	699.3	698.2	699.3	698.8
155°	711.4	712.0	710.2	712.5	710.8
157.5°	723.5	723.5	721.2	724.0	721.2
160°	733.8	732.1	731.5	734.9	731.5
162.5°	743.0	740.7	740.1	743.5	739.5
165°	750.4	747.6	747.6	752.2	747.0
167.5°	756.8	753.9	753.3	758.5	752.7
170°	761.9	758.5	759.0	763.6	757.9
172.5°	765.4	761.9	762.5	767.1	760.8
175°	767.7	764.2	764.8	770.0	763.1
177.5°	769.4	765.4	766.5	771.1	764.2
180°	767.7	767.7	767.7	767.7	767.7

(END OF REPORT)