

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1024860

Luminaire Tested: S124DIP-B1020D1205UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1024860
REPORT IS A COMBINATION OF REPORTS P995205 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B1020D1205UB30-4F0-XX-W2A-A4
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8884.0 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1024860

CATALOG NUMBER: S124DIP-B1020D1205UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1024860

CATALOG NUMBER: S124DIP-B1020D1205UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	58	58	58
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	51	50	49	49	49	44
2	90	82	76	71	83	76	71	67	65	61	58	55	52	50	45	43	42	42	42	37
3	82	73	65	60	76	68	61	56	58	53	49	49	45	42	40	38	36	36	36	32
4	75	64	57	51	69	60	53	48	51	46	42	44	40	36	36	33	31	31	31	27
5	69	58	50	44	64	54	46	41	46	41	36	39	35	32	33	30	27	27	27	24
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24	24	24	21
7	59	47	39	33	54	44	37	32	38	32	28	32	28	25	27	24	21	21	21	19
8	55	42	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19	19	19	17
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	17	17	15
10	48	36	28	24	44	33	27	23	29	24	20	25	21	18	21	18	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13526	13526	13526	13526
5°	13492	15517	13570	11660
10°	13391	18104	13493	10229
15°	13230	20870	13322	9153
20°	13058	22631	13153	8206
25°	12809	22372	12931	7507
30°	12564	18491	12717	7148
35°	12222	13779	12356	6930
40°	11820	10380	11935	6823
45°	11209	8331	11349	6677
50°	10479	7019	10631	6609
55°	9620	6108	9771	6531
60°	8787	5380	9043	6423
65°	8003	4629	8078	6155
70°	7081	3808	7235	5667
75°	6179	2926	6138	4816
80°	4861	1923	4804	3655
85°	3202	864	2998	2132

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 17489 cd/sqm

TEST NUMBER: P1024860

CATALOG NUMBER: S124DIP-B1020D1205UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.4	1.8
10°-20°	498.3	5.6
20°-30°	791.6	8.9
30°-40°	879.6	9.9
40°-50°	799.9	9.0
50°-60°	653.6	7.4
60°-70°	466.6	5.3
70°-80°	256.7	2.9
80°-90°	71.7	0.8
90°-100°	428.4	4.8
100°-110°	894.3	10.1
110°-120°	795.0	8.9
120°-130°	669.2	7.5
130°-140°	558.3	6.3
140°-150°	426.3	4.8
150°-160°	299.7	3.4
160°-170°	176.3	2.0
170°-180°	57.3	0.6
0°-30°	1451.2	16.3
0°-40°	2330.8	26.2
0°-60°	3784.3	42.6
0°-90°	4579.3	51.5
90°-120°	2117.6	23.8
90°-150°	3771.4	42.5
90°-180°	4305.0	48.5
0°-180°	8884.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1659	1659	1659	1659	1659	
5°	1652	1946	1661	1462	1652	157
15°	1578	2673	1589	1172	1578	445
25°	1440	2838	1454	952	1440	664
35°	1249	1678	1263	844	1249	780
45°	996	941	1009	754	996	768
55°	701	616	712	658	701	630
65°	437	396	441	526	437	432
75°	214	198	213	326	214	225
85°	44	41	41	102	44	51
90°	1	24	1	24	1	5
95°	38	283	38	283	38	42
105°	136	1634	136	1634	136	145
115°	239	1569	239	1569	239	237
125°	333	1252	333	1252	333	297
135°	396	1119	396	1119	396	306
145°	456	914	456	914	456	286
155°	519	765	519	765	519	239
165°	566	668	566	668	566	160
175°	590	602	590	602	590	56
180°	591	591	591	591	591	

TEST NUMBER: P1024860

CATALOG NUMBER: S124DIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7
2.5°	1658.7	1675.2	1682.0	1687.5	1705.4	1710.9	1712.3	1720.5	1727.4	1728.8	1728.8
5°	1651.8	1677.9	1698.5	1717.8	1746.6	1759.0	1774.1	1790.6	1812.6	1826.3	1833.2
7.5°	1640.8	1679.3	1710.9	1743.9	1783.7	1808.5	1822.2	1866.2	1896.4	1921.2	1951.4
10°	1624.3	1673.8	1719.1	1767.2	1823.6	1853.8	1884.0	1937.6	1980.2	2028.3	2066.8
12.5°	1599.6	1664.2	1719.1	1786.5	1856.6	1892.3	1928.0	2021.5	2070.9	2113.5	2182.3
15°	1577.6	1642.2	1720.5	1789.2	1875.8	1929.4	1981.6	2042.1	2120.4	2212.5	2278.4
17.5°	1552.9	1633.9	1706.8	1803.0	1899.2	1950.0	1992.6	2086.1	2196.0	2286.7	2347.2
20°	1518.5	1601.0	1697.2	1798.8	1912.9	1952.8	2009.1	2134.2	2233.1	2322.4	2421.4
22.5°	1478.7	1574.9	1676.5	1774.1	1892.3	1976.1	2038.0	2147.9	2267.5	2370.5	2481.8
25°	1440.2	1544.6	1633.9	1767.2	1892.3	1948.6	2018.7	2149.3	2279.8	2404.9	2518.9
27.5°	1399.0	1496.5	1617.5	1723.3	1864.8	1926.6	2002.2	2145.1	2283.9	2409.0	2531.3
30°	1353.6	1458.0	1558.4	1683.4	1820.8	1900.5	1970.6	2125.9	2267.5	2398.0	2512.1
32.5°	1302.8	1401.7	1508.9	1627.1	1771.4	1852.4	1940.4	2099.8	2251.0	2363.6	2451.6
35°	1249.2	1349.5	1442.9	1563.9	1712.3	1793.4	1878.6	2054.5	2204.2	2296.3	2347.2
37.5°	1190.1	1284.9	1377.0	1496.5	1644.9	1731.5	1818.1	1988.5	2130.0	2207.0	2193.2
40°	1133.7	1218.9	1304.1	1416.8	1572.1	1664.2	1739.8	1911.5	2035.2	2068.2	2022.8
42.5°	1069.1	1142.0	1224.4	1339.9	1491.0	1577.6	1672.4	1829.1	1921.2	1907.4	1830.5
45°	996.3	1060.9	1143.3	1251.9	1405.8	1495.1	1574.9	1723.3	1790.6	1756.2	1616.1
47.5°	926.2	989.4	1056.8	1165.3	1315.1	1390.7	1471.8	1605.1	1643.6	1570.7	1430.6
50°	850.6	902.9	972.9	1076.0	1216.2	1295.9	1363.2	1470.4	1484.2	1394.8	1249.2
52.5°	777.8	821.8	889.1	990.8	1121.4	1184.6	1250.5	1345.4	1334.4	1242.3	1102.1
55°	700.8	742.1	803.9	897.4	1012.8	1073.3	1129.6	1213.4	1190.1	1095.2	972.9
57.5°	636.3	665.1	725.6	812.2	907.0	972.9	1021.0	1087.0	1051.3	956.5	842.4
60°	562.1	597.8	648.6	718.7	812.2	856.1	898.7	942.7	918.0	827.3	725.6
62.5°	494.7	522.2	566.2	633.5	706.3	746.2	791.5	819.0	794.3	710.5	625.3
65°	437.0	459.0	493.3	548.3	618.4	651.4	677.5	703.6	683.0	604.7	542.8
67.5°	373.8	393.0	421.9	465.9	525.0	548.3	573.0	590.9	567.6	515.3	454.9
70°	317.4	331.2	358.7	391.7	432.9	454.9	475.5	493.3	472.7	428.8	383.4
72.5°	259.7	270.7	295.5	318.8	355.9	371.0	386.2	399.9	393.0	351.8	314.7
75°	214.4	218.5	235.0	254.2	277.6	294.1	305.1	313.3	307.8	274.8	251.5
77.5°	162.2	167.7	180.0	195.1	215.8	225.4	232.2	240.5	233.6	207.5	191.0
80°	118.2	119.6	126.4	140.2	153.9	155.3	162.2	173.2	169.0	151.2	138.8
82.5°	75.6	79.7	82.5	90.7	100.3	103.1	107.2	109.9	108.6	97.6	93.4
85°	44.0	44.0	46.7	52.2	55.0	59.1	60.5	61.8	64.6	57.7	53.6
87.5°	19.2	20.6	20.6	22.0	24.7	24.7	26.1	27.5	28.9	27.5	23.4
90°	1.2	3.5	7.0	8.1	9.3	9.3	9.3	16.3	16.3	18.6	20.9
92.5°	16.3	23.2	36.0	53.4	74.3	89.4	104.5	176.5	289.1	398.3	455.2
95°	38.3	41.8	53.4	68.5	96.4	120.8	145.1	246.2	436.6	714.1	946.4
97.5°	63.9	63.9	74.3	88.2	112.6	133.5	154.4	234.6	398.3	683.9	1012.5
100°	88.2	88.2	96.4	110.3	132.4	151.0	169.5	238.0	369.3	606.1	933.6
102.5°	111.5	113.8	120.8	133.5	154.4	171.9	189.3	249.7	361.1	553.9	834.9
105°	135.9	139.3	145.1	159.1	180.0	196.8	213.7	269.4	365.8	528.3	761.7
107.5°	162.6	164.9	170.7	185.8	205.5	222.4	239.2	290.3	379.7	521.4	714.1
110°	189.3	191.6	197.4	211.3	232.2	247.9	263.6	314.7	396.0	523.7	692.1



TEST NUMBER: P1024860

CATALOG NUMBER: S124DIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	214.8	217.1	224.1	236.9	257.8	273.5	289.1	337.9	413.4	530.7	681.6
115°	239.2	242.7	250.8	262.4	284.5	300.2	315.8	362.3	432.0	539.9	679.3
117.5°	264.7	268.2	275.2	288.0	308.9	325.2	341.4	385.5	450.5	549.2	678.1
120°	290.3	292.6	300.7	313.5	333.3	349.6	365.8	409.9	470.3	559.7	678.1
122.5°	313.5	315.8	324.0	335.6	357.6	373.3	389.0	433.1	488.9	570.1	677.0
125°	333.3	337.9	344.9	357.6	379.7	396.0	412.2	454.0	507.4	580.6	675.8
127.5°	351.8	355.3	363.4	377.4	400.6	416.8	433.1	473.8	523.7	588.7	673.5
130°	366.9	371.6	380.9	398.3	420.3	437.2	454.0	493.5	538.8	598.0	672.3
132.5°	382.0	385.5	398.3	414.5	438.9	454.6	470.3	509.8	553.9	606.1	671.2
135°	396.0	400.6	412.2	432.0	456.3	471.4	486.5	524.9	566.7	614.3	670.0
137.5°	409.9	414.5	427.3	445.9	471.4	486.0	500.5	536.5	575.9	618.9	670.0
140°	425.0	428.5	441.2	461.0	485.4	499.3	513.2	548.1	585.2	624.7	668.8
142.5°	441.2	444.7	456.3	474.9	498.1	511.5	524.9	558.5	592.2	629.4	668.8
145°	456.3	459.8	471.4	487.7	509.8	522.6	535.3	565.5	596.8	630.5	666.5
147.5°	473.8	474.9	485.4	502.8	521.4	533.0	544.6	573.6	601.5	631.7	663.0
150°	490.0	491.2	500.5	514.4	531.8	542.8	553.9	579.4	605.0	631.7	659.5
152.5°	505.1	505.1	514.4	527.2	542.3	552.2	562.0	584.1	607.3	629.4	653.7
155°	519.0	520.2	527.2	538.8	551.6	560.3	569.0	588.7	608.5	627.0	647.9
157.5°	533.0	533.0	539.9	549.2	560.8	567.8	574.8	592.2	608.5	624.7	642.1
160°	545.8	545.8	550.4	558.5	567.8	574.2	580.6	594.5	608.5	621.2	635.2
162.5°	557.4	556.2	559.7	566.7	574.8	579.4	584.1	596.8	608.5	617.7	628.2
165°	565.5	565.5	567.8	573.6	579.4	582.9	586.4	596.8	606.1	613.1	621.2
167.5°	574.8	573.6	574.8	579.4	582.9	585.8	588.7	596.8	603.8	608.5	614.3
170°	580.6	579.4	580.6	584.1	586.4	588.2	589.9	595.7	601.5	603.8	607.3
172.5°	586.4	585.2	585.2	587.6	588.7	589.8	591.0	594.5	599.2	599.2	600.3
175°	589.9	588.7	588.7	589.9	591.0	591.0	591.0	593.4	596.8	595.7	595.7
177.5°	592.2	591.0	589.9	591.0	591.0	591.0	591.0	592.2	594.5	592.2	592.2
180°	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0

TEST NUMBER: P1024860

CATALOG NUMBER: S124DIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7
2.5°	1732.9	1757.6	1768.6	1771.4	1786.5	1776.9	1781.0	1779.6	1790.6	1792.0	1792.0
5°	1859.3	1888.2	1897.8	1911.5	1932.1	1937.6	1933.5	1941.8	1956.9	1945.9	1962.4
7.5°	1992.6	2024.2	2046.2	2076.4	2083.3	2101.2	2112.2	2121.8	2124.5	2125.9	2128.7
10°	2116.3	2156.1	2186.4	2237.2	2248.2	2257.8	2305.9	2286.7	2311.4	2303.2	2305.9
12.5°	2216.6	2294.9	2319.7	2404.9	2413.1	2446.1	2443.4	2473.6	2479.1	2490.1	2479.1
15°	2348.5	2439.2	2479.1	2527.2	2554.7	2593.1	2600.0	2641.2	2657.7	2672.8	2657.7
17.5°	2469.5	2517.6	2619.3	2657.7	2675.6	2696.2	2748.4	2763.5	2788.3	2778.7	2806.1
20°	2529.9	2598.6	2705.8	2771.8	2799.3	2818.5	2862.5	2885.9	2895.5	2895.5	2898.2
22.5°	2583.5	2682.5	2762.2	2837.8	2862.5	2876.2	2902.3	2920.2	2924.3	2927.1	2929.8
25°	2631.6	2720.9	2785.5	2828.1	2837.8	2837.8	2852.9	2841.9	2824.0	2837.8	2846.0
27.5°	2631.6	2694.8	2723.7	2738.8	2738.8	2701.7	2679.7	2634.4	2595.9	2584.9	2609.6
30°	2587.6	2616.5	2576.7	2539.5	2510.7	2486.0	2399.4	2330.7	2316.9	2307.3	2344.4
32.5°	2486.0	2448.9	2370.5	2263.3	2220.7	2164.4	2097.1	2044.8	2013.2	2002.2	1994.0
35°	2305.9	2209.7	2108.0	1963.8	1933.5	1862.1	1770.0	1731.5	1679.3	1677.9	1695.8
37.5°	2109.4	1961.0	1851.1	1713.6	1671.0	1595.5	1508.9	1469.0	1433.3	1405.8	1438.8
40°	1879.9	1750.7	1583.1	1470.4	1409.9	1370.1	1297.3	1253.3	1236.8	1223.1	1243.7
42.5°	1665.5	1524.0	1393.5	1278.0	1228.5	1183.2	1135.1	1092.5	1080.1	1078.8	1093.9
45°	1452.5	1313.7	1192.8	1093.9	1062.3	1034.8	988.1	975.7	955.1	941.3	948.2
47.5°	1282.1	1139.2	1038.9	963.3	935.8	912.5	882.2	861.6	843.8	838.3	846.5
50°	1114.5	1018.3	915.2	852.0	831.4	809.4	786.1	766.8	758.6	753.1	758.6
52.5°	979.8	876.7	806.7	755.8	735.2	718.7	702.2	694.0	683.0	685.7	691.2
55°	858.9	768.2	709.1	672.0	659.6	652.8	632.1	622.5	618.4	615.6	618.4
57.5°	744.8	678.9	634.9	603.3	586.8	582.7	566.2	566.2	562.1	557.9	559.3
60°	654.1	597.8	555.2	530.4	527.7	520.8	509.8	508.5	498.8	503.0	504.3
62.5°	562.1	516.7	487.8	472.7	463.1	460.4	453.5	452.1	448.0	449.4	446.6
65°	489.2	452.1	423.3	410.9	406.8	405.4	399.9	395.8	393.0	395.8	393.0
67.5°	416.4	391.7	369.7	357.3	351.8	350.4	346.3	343.6	344.9	340.8	343.6
70°	347.7	322.9	309.2	302.3	299.6	295.5	295.5	295.5	295.5	292.7	291.3
72.5°	292.7	268.0	258.4	254.2	251.5	250.1	246.0	247.4	246.0	244.6	250.1
75°	232.2	217.1	207.5	203.4	206.1	202.0	197.9	200.6	196.5	197.9	203.4
77.5°	175.9	169.0	163.5	160.8	158.0	155.3	155.3	152.5	152.5	152.5	152.5
80°	127.8	126.4	116.8	115.4	115.4	112.7	112.7	112.7	112.7	111.3	112.7
82.5°	85.2	83.8	81.1	79.7	77.0	78.3	78.3	75.6	75.6	74.2	75.6
85°	49.5	49.5	46.7	45.3	44.0	45.3	42.6	41.2	42.6	41.2	42.6
87.5°	23.4	20.6	22.0	20.6	17.9	19.2	16.5	17.9	16.5	15.1	17.9
90°	19.7	20.9	22.1	23.2	23.2	23.2	24.4	25.5	24.4	24.4	24.4
92.5°	378.5	279.8	209.0	164.9	150.4	135.9	118.4	110.3	105.7	105.7	105.7
95°	973.1	860.4	680.4	524.9	468.6	412.2	355.3	319.3	298.4	283.3	298.4
97.5°	1220.4	1239.0	1149.6	1021.8	956.8	891.8	812.8	743.2	708.3	680.4	708.3
100°	1230.8	1400.4	1423.6	1366.7	1323.8	1280.8	1179.8	1108.9	1074.1	1064.8	1074.1
102.5°	1143.8	1392.2	1530.4	1565.3	1553.6	1542.0	1489.8	1443.3	1406.2	1399.2	1406.2
105°	1034.6	1300.5	1501.4	1616.4	1640.2	1664.0	1666.3	1657.0	1640.7	1633.8	1640.7
107.5°	945.2	1187.9	1405.0	1565.3	1614.0	1662.8	1713.9	1734.8	1744.1	1745.2	1744.1
110°	881.3	1088.0	1288.9	1457.3	1521.2	1585.0	1667.4	1716.2	1737.1	1747.6	1737.1

TEST NUMBER: P1024860

CATALOG NUMBER: S124DIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	845.3	1014.9	1186.7	1343.5	1407.4	1471.2	1567.6	1629.1	1660.5	1679.1	1660.5
115°	825.6	970.7	1113.6	1249.4	1305.2	1360.9	1452.6	1522.3	1559.5	1568.7	1559.5
117.5°	815.1	945.2	1066.0	1176.3	1225.0	1273.8	1355.1	1415.5	1455.0	1460.8	1455.0
120°	807.0	928.9	1036.9	1129.8	1171.0	1212.3	1278.5	1329.5	1359.7	1372.5	1359.7
122.5°	797.7	915.0	1018.3	1100.8	1135.6	1170.5	1223.9	1265.7	1290.1	1302.8	1290.1
125°	787.3	898.7	998.6	1078.7	1110.6	1142.6	1189.0	1222.7	1244.8	1251.7	1244.8
127.5°	773.3	880.2	976.5	1056.7	1086.8	1117.0	1163.5	1193.7	1212.3	1219.2	1212.3
130°	760.6	856.9	948.7	1027.6	1058.4	1089.2	1136.8	1165.8	1184.4	1191.4	1184.4
132.5°	749.0	832.6	917.3	994.0	1024.8	1055.5	1102.0	1135.6	1153.0	1160.0	1153.0
135°	737.3	810.5	886.0	956.8	985.8	1014.9	1061.3	1093.8	1112.4	1119.4	1112.4
137.5°	726.9	789.6	855.8	917.3	944.0	970.7	1014.9	1048.5	1063.6	1071.8	1063.6
140°	718.8	772.2	826.8	879.0	903.4	927.8	968.4	994.0	1010.2	1019.5	1010.2
142.5°	711.8	755.9	802.4	845.3	865.6	886.0	920.8	944.0	958.0	963.8	958.0
145°	703.7	740.8	780.3	815.1	831.4	847.7	876.7	896.4	908.0	913.8	908.0
147.5°	696.7	728.1	760.6	789.6	803.0	816.3	838.4	855.8	865.1	867.4	865.1
150°	688.6	716.4	743.2	766.4	776.8	787.3	805.9	820.9	827.9	829.1	827.9
152.5°	679.3	703.7	725.7	746.6	754.8	762.9	778.0	789.6	793.1	794.2	793.1
155°	670.0	690.9	709.5	726.9	733.8	740.8	752.4	761.7	765.2	765.2	765.2
157.5°	660.7	677.0	693.2	708.3	714.1	719.9	729.2	736.2	738.5	738.5	738.5
160°	650.3	664.2	677.0	689.7	694.4	699.0	706.0	713.0	714.1	714.1	714.1
162.5°	641.0	651.4	661.9	671.2	675.2	679.3	683.9	690.9	692.1	690.9	692.1
165°	630.5	639.8	646.8	654.9	657.8	660.7	665.4	670.0	668.8	667.7	668.8
167.5°	621.2	628.2	634.0	641.0	642.8	644.5	646.8	650.3	650.3	649.1	650.3
170°	611.9	617.7	621.2	625.9	627.6	629.4	631.7	632.8	631.7	631.7	631.7
172.5°	603.8	608.5	610.8	613.1	614.2	615.4	616.6	617.7	616.6	614.3	616.6
175°	598.0	600.3	601.5	603.8	603.8	603.8	603.8	606.1	603.8	601.5	603.8
177.5°	593.4	594.5	595.7	595.7	596.2	596.8	595.7	596.8	594.5	592.2	594.5
180°	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0

TEST NUMBER: P1024860

CATALOG NUMBER: S124DIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7
2.5°	1789.2	1785.1	1779.6	1779.6	1772.7	1772.7	1761.7	1742.5	1726.0	1720.5	1723.3
5°	1941.8	1943.1	1934.9	1928.0	1915.7	1906.0	1888.2	1853.8	1842.8	1820.8	1805.7
7.5°	2116.3	2110.8	2095.7	2084.7	2081.9	2059.9	2021.5	1980.2	1947.3	1925.3	1893.7
10°	2312.8	2290.8	2268.8	2262.0	2245.5	2208.4	2164.4	2119.0	2073.7	2025.6	1972.0
12.5°	2477.7	2435.1	2433.7	2417.2	2385.6	2365.0	2312.8	2248.2	2169.9	2116.3	2055.8
15°	2655.0	2615.1	2582.1	2551.9	2536.8	2476.3	2432.4	2351.3	2257.8	2200.1	2158.9
17.5°	2781.4	2763.5	2707.2	2693.5	2672.8	2602.8	2532.7	2453.0	2371.9	2290.8	2179.5
20°	2883.1	2872.1	2835.0	2815.8	2782.8	2727.8	2642.6	2550.5	2457.1	2341.7	2237.2
22.5°	2927.1	2913.3	2883.1	2866.6	2846.0	2799.3	2726.4	2622.0	2499.7	2396.6	2285.3
25°	2840.5	2865.2	2857.0	2850.1	2841.9	2814.4	2759.4	2667.4	2547.8	2431.0	2292.2
27.5°	2645.4	2688.0	2729.2	2734.7	2748.4	2759.4	2737.4	2671.5	2571.2	2447.5	2294.9
30°	2382.9	2402.1	2486.0	2510.7	2529.9	2600.0	2641.2	2624.8	2547.8	2436.5	2296.3
32.5°	2046.2	2097.1	2182.3	2241.3	2293.6	2371.9	2479.1	2521.7	2494.2	2403.5	2264.7
35°	1727.4	1787.9	1886.8	1962.4	2014.6	2125.9	2252.3	2344.4	2378.8	2333.4	2209.7
37.5°	1466.3	1539.1	1627.1	1655.9	1716.4	1853.8	2028.3	2156.1	2240.0	2244.1	2147.9
40°	1269.8	1306.9	1377.0	1420.9	1480.0	1595.5	1765.9	1934.9	2061.3	2103.9	2053.1
42.5°	1103.5	1132.4	1184.6	1238.2	1291.8	1379.7	1536.4	1694.4	1864.8	1950.0	1948.6
45°	971.6	1001.8	1037.5	1081.5	1118.6	1213.4	1337.1	1499.3	1646.3	1778.2	1811.2
47.5°	856.1	882.2	926.2	945.5	970.2	1059.5	1166.7	1317.9	1470.4	1621.6	1660.1
50°	770.9	792.9	823.2	835.5	863.0	929.0	1016.9	1139.2	1308.3	1447.0	1518.5
52.5°	694.0	710.5	733.8	743.5	762.7	812.2	891.9	988.1	1128.2	1271.1	1371.5
55°	628.0	639.0	655.5	666.5	680.2	724.2	783.3	869.9	990.8	1114.5	1212.1
57.5°	566.2	574.4	590.9	596.4	607.4	641.8	683.0	755.8	867.1	977.1	1071.9
60°	508.5	514.0	523.6	535.9	544.2	567.6	606.0	666.5	755.8	856.1	933.1
62.5°	453.5	461.7	464.5	470.0	476.9	498.8	529.1	573.0	651.4	733.8	814.9
65°	397.1	404.0	409.5	410.9	417.8	434.3	461.7	500.2	551.1	622.5	698.1
67.5°	344.9	349.1	351.8	357.3	364.2	372.4	394.4	423.3	470.0	527.7	588.2
70°	296.8	296.8	301.0	302.3	310.6	320.2	329.8	357.3	398.5	445.2	486.5
72.5°	244.6	251.5	250.1	257.0	255.6	262.5	274.8	292.7	322.9	360.0	399.9
75°	199.3	203.4	203.4	203.4	206.1	211.6	218.5	235.0	258.4	288.6	311.9
77.5°	155.3	158.0	158.0	158.0	159.4	164.9	171.8	182.8	199.3	217.1	230.9
80°	111.3	114.1	114.1	116.8	116.8	118.2	125.1	130.6	138.8	152.5	166.3
82.5°	75.6	77.0	79.7	79.7	78.3	81.1	82.5	87.9	96.2	98.9	108.6
85°	41.2	42.6	44.0	44.0	45.3	48.1	46.7	52.2	52.2	57.7	60.5
87.5°	16.5	19.2	19.2	17.9	19.2	19.2	19.2	22.0	23.4	24.7	23.4
90°	25.5	24.4	23.2	23.2	23.2	22.1	20.9	19.7	20.9	18.6	16.3
92.5°	110.3	118.4	135.9	150.4	164.9	209.0	279.8	378.5	455.2	398.3	289.1
95°	319.3	355.3	412.2	468.6	524.9	680.4	860.4	973.1	946.4	714.1	436.6
97.5°	743.2	812.8	891.8	956.8	1021.8	1149.6	1239.0	1220.4	1012.5	683.9	398.3
100°	1108.9	1179.8	1280.8	1323.8	1366.7	1423.6	1400.4	1230.8	933.6	606.1	369.3
102.5°	1443.3	1489.8	1542.0	1553.6	1565.3	1530.4	1392.2	1143.8	834.9	553.9	361.1
105°	1657.0	1666.3	1664.0	1640.2	1616.4	1501.4	1300.5	1034.6	761.7	528.3	365.8
107.5°	1734.8	1713.9	1662.8	1614.0	1565.3	1405.0	1187.9	945.2	714.1	521.4	379.7
110°	1716.2	1667.4	1585.0	1521.2	1457.3	1288.9	1088.0	881.3	692.1	523.7	396.0

TEST NUMBER: P1024860

CATALOG NUMBER: S124DIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1629.1	1567.6	1471.2	1407.4	1343.5	1186.7	1014.9	845.3	681.6	530.7	413.4
115°	1522.3	1452.6	1360.9	1305.2	1249.4	1113.6	970.7	825.6	679.3	539.9	432.0
117.5°	1415.5	1355.1	1273.8	1225.0	1176.3	1066.0	945.2	815.1	678.1	549.2	450.5
120°	1329.5	1278.5	1212.3	1171.0	1129.8	1036.9	928.9	807.0	678.1	559.7	470.3
122.5°	1265.7	1223.9	1170.5	1135.6	1100.8	1018.3	915.0	797.7	677.0	570.1	488.9
125°	1222.7	1189.0	1142.6	1110.6	1078.7	998.6	898.7	787.3	675.8	580.6	507.4
127.5°	1193.7	1163.5	1117.0	1086.8	1056.7	976.5	880.2	773.3	673.5	588.7	523.7
130°	1165.8	1136.8	1089.2	1058.4	1027.6	948.7	856.9	760.6	672.3	598.0	538.8
132.5°	1135.6	1102.0	1055.5	1024.8	994.0	917.3	832.6	749.0	671.2	606.1	553.9
135°	1093.8	1061.3	1014.9	985.8	956.8	886.0	810.5	737.3	670.0	614.3	566.7
137.5°	1048.5	1014.9	970.7	944.0	917.3	855.8	789.6	726.9	670.0	618.9	575.9
140°	994.0	968.4	927.8	903.4	879.0	826.8	772.2	718.8	668.8	624.7	585.2
142.5°	944.0	920.8	886.0	865.6	845.3	802.4	755.9	711.8	668.8	629.4	592.2
145°	896.4	876.7	847.7	831.4	815.1	780.3	740.8	703.7	666.5	630.5	596.8
147.5°	855.8	838.4	816.3	803.0	789.6	760.6	728.1	696.7	663.0	631.7	601.5
150°	820.9	805.9	787.3	776.8	766.4	743.2	716.4	688.6	659.5	631.7	605.0
152.5°	789.6	778.0	762.9	754.8	746.6	725.7	703.7	679.3	653.7	629.4	607.3
155°	761.7	752.4	740.8	733.8	726.9	709.5	690.9	670.0	647.9	627.0	608.5
157.5°	736.2	729.2	719.9	714.1	708.3	693.2	677.0	660.7	642.1	624.7	608.5
160°	713.0	706.0	699.0	694.4	689.7	677.0	664.2	650.3	635.2	621.2	608.5
162.5°	690.9	683.9	679.3	675.2	671.2	661.9	651.4	641.0	628.2	617.7	608.5
165°	670.0	665.4	660.7	657.8	654.9	646.8	639.8	630.5	621.2	613.1	606.1
167.5°	650.3	646.8	644.5	642.8	641.0	634.0	628.2	621.2	614.3	608.5	603.8
170°	632.8	631.7	629.4	627.6	625.9	621.2	617.7	611.9	607.3	603.8	601.5
172.5°	617.7	616.6	615.4	614.2	613.1	610.8	608.5	603.8	600.3	599.2	599.2
175°	606.1	603.8	603.8	603.8	603.8	601.5	600.3	598.0	595.7	595.7	596.8
177.5°	596.8	595.7	596.8	596.2	595.7	595.7	594.5	593.4	592.2	592.2	594.5
180°	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0

TEST NUMBER: P1024860

CATALOG NUMBER: S124DIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7
2.5°	1710.9	1705.4	1701.3	1701.3	1688.9	1676.5	1669.7	1666.9	1664.2	1653.2	1638.1
5°	1781.0	1763.1	1750.7	1738.4	1717.8	1695.8	1673.8	1661.4	1643.6	1618.8	1601.0
7.5°	1859.3	1816.7	1803.0	1787.9	1746.6	1709.5	1679.3	1653.2	1624.3	1592.7	1561.1
10°	1925.3	1879.9	1849.7	1823.6	1770.0	1720.5	1675.2	1636.7	1599.6	1558.4	1519.9
12.5°	1988.5	1923.9	1892.3	1853.8	1797.5	1726.0	1666.9	1618.8	1563.9	1521.3	1474.5
15°	2076.4	1967.9	1915.7	1890.9	1815.3	1731.5	1660.1	1588.6	1543.2	1478.7	1437.4
17.5°	2090.2	2002.2	1967.9	1904.7	1814.0	1719.1	1636.7	1565.2	1496.5	1438.8	1385.2
20°	2138.3	2022.8	1967.9	1928.0	1808.5	1712.3	1621.6	1529.5	1463.5	1401.7	1341.2
22.5°	2168.5	2038.0	1980.2	1917.0	1803.0	1687.5	1580.3	1500.6	1419.6	1356.3	1308.3
25°	2160.3	2029.7	1965.1	1906.0	1767.2	1651.8	1555.6	1453.9	1378.3	1309.6	1246.4
27.5°	2156.1	2009.1	1940.4	1874.4	1743.9	1622.9	1502.0	1419.6	1335.7	1256.0	1209.3
30°	2145.1	1983.0	1903.3	1831.8	1695.8	1569.4	1466.3	1370.1	1286.3	1213.4	1151.6
32.5°	2108.0	1939.0	1862.1	1785.1	1643.6	1517.1	1412.7	1323.4	1239.5	1164.0	1104.9
35°	2058.6	1886.8	1803.0	1721.9	1580.3	1452.5	1356.3	1262.9	1184.6	1111.7	1055.4
37.5°	2009.1	1826.3	1748.0	1654.6	1524.0	1390.7	1291.8	1207.9	1135.1	1059.5	997.7
40°	1937.6	1754.9	1668.3	1588.6	1436.1	1311.0	1220.3	1144.7	1073.3	1001.8	949.6
42.5°	1840.1	1676.5	1587.2	1499.3	1356.3	1232.7	1144.7	1077.4	1010.0	951.0	893.2
45°	1741.1	1581.7	1502.0	1423.7	1268.4	1151.6	1070.5	1008.7	952.3	887.7	841.0
47.5°	1621.6	1486.9	1407.2	1330.2	1183.2	1066.4	992.2	934.5	882.2	828.7	784.7
50°	1499.3	1382.5	1309.6	1229.9	1089.8	983.9	911.1	863.0	820.4	769.6	733.8
52.5°	1367.3	1265.7	1203.8	1126.9	1003.2	905.6	831.4	783.3	747.6	710.5	678.9
55°	1227.2	1153.0	1087.0	1025.2	908.4	820.4	754.4	711.8	687.1	652.8	625.3
57.5°	1100.7	1029.3	989.4	919.3	817.7	731.1	678.9	643.1	614.3	593.7	571.7
60°	968.8	911.1	867.1	816.3	727.0	654.1	599.2	578.5	548.3	533.2	523.6
62.5°	842.4	801.2	759.9	721.5	641.8	573.0	531.8	505.7	487.8	472.7	464.5
65°	722.8	684.4	655.5	621.1	555.2	500.2	461.7	441.1	423.3	419.1	409.5
67.5°	606.0	589.5	557.9	530.4	474.1	431.5	402.6	376.5	366.9	362.8	354.5
70°	507.1	487.8	463.1	439.7	397.1	360.0	333.9	324.3	310.6	309.2	299.6
72.5°	417.8	394.4	376.5	358.7	327.1	294.1	280.3	266.6	259.7	254.2	250.1
75°	331.2	314.7	302.3	287.2	259.7	237.7	218.5	213.0	208.9	207.5	204.8
77.5°	247.4	236.4	230.9	215.8	196.5	177.3	169.0	160.8	160.8	158.0	159.4
80°	175.9	169.0	162.2	153.9	137.4	129.2	122.3	116.8	114.1	112.7	114.1
82.5°	111.3	107.2	105.8	100.3	89.3	85.2	79.7	75.6	75.6	75.6	75.6
85°	61.8	61.8	61.8	53.6	49.5	45.3	42.6	41.2	41.2	41.2	42.6
87.5°	26.1	26.1	22.0	22.0	20.6	17.9	16.5	16.5	17.9	17.9	19.2
90°	16.3	9.3	9.3	9.3	8.1	7.0	3.5	1.2	3.5	7.0	8.1
92.5°	176.5	104.5	89.4	74.3	53.4	36.0	23.2	16.3	23.2	36.0	53.4
95°	246.2	145.1	120.8	96.4	68.5	53.4	41.8	38.3	41.8	53.4	68.5
97.5°	234.6	154.4	133.5	112.6	88.2	74.3	63.9	63.9	63.9	74.3	88.2
100°	238.0	169.5	151.0	132.4	110.3	96.4	88.2	88.2	88.2	96.4	110.3
102.5°	249.7	189.3	171.9	154.4	133.5	120.8	113.8	111.5	113.8	120.8	133.5
105°	269.4	213.7	196.8	180.0	159.1	145.1	139.3	135.9	139.3	145.1	159.1
107.5°	290.3	239.2	222.4	205.5	185.8	170.7	164.9	162.6	164.9	170.7	185.8
110°	314.7	263.6	247.9	232.2	211.3	197.4	191.6	189.3	191.6	197.4	211.3

TEST NUMBER: P1024860

CATALOG NUMBER: S124DIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	337.9	289.1	273.5	257.8	236.9	224.1	217.1	214.8	217.1	224.1	236.9
115°	362.3	315.8	300.2	284.5	262.4	250.8	242.7	239.2	242.7	250.8	262.4
117.5°	385.5	341.4	325.2	308.9	288.0	275.2	268.2	264.7	268.2	275.2	288.0
120°	409.9	365.8	349.6	333.3	313.5	300.7	292.6	290.3	292.6	300.7	313.5
122.5°	433.1	389.0	373.3	357.6	335.6	324.0	315.8	313.5	315.8	324.0	335.6
125°	454.0	412.2	396.0	379.7	357.6	344.9	337.9	333.3	337.9	344.9	357.6
127.5°	473.8	433.1	416.8	400.6	377.4	363.4	355.3	351.8	355.3	363.4	377.4
130°	493.5	454.0	437.2	420.3	398.3	380.9	371.6	366.9	371.6	380.9	398.3
132.5°	509.8	470.3	454.6	438.9	414.5	398.3	385.5	382.0	385.5	398.3	414.5
135°	524.9	486.5	471.4	456.3	432.0	412.2	400.6	396.0	400.6	412.2	432.0
137.5°	536.5	500.5	486.0	471.4	445.9	427.3	414.5	409.9	414.5	427.3	445.9
140°	548.1	513.2	499.3	485.4	461.0	441.2	428.5	425.0	428.5	441.2	461.0
142.5°	558.5	524.9	511.5	498.1	474.9	456.3	444.7	441.2	444.7	456.3	474.9
145°	565.5	535.3	522.6	509.8	487.7	471.4	459.8	456.3	459.8	471.4	487.7
147.5°	573.6	544.6	533.0	521.4	502.8	485.4	474.9	473.8	474.9	485.4	502.8
150°	579.4	553.9	542.8	531.8	514.4	500.5	491.2	490.0	491.2	500.5	514.4
152.5°	584.1	562.0	552.2	542.3	527.2	514.4	505.1	505.1	505.1	514.4	527.2
155°	588.7	569.0	560.3	551.6	538.8	527.2	520.2	519.0	520.2	527.2	538.8
157.5°	592.2	574.8	567.8	560.8	549.2	539.9	533.0	533.0	533.0	539.9	549.2
160°	594.5	580.6	574.2	567.8	558.5	550.4	545.8	545.8	545.8	550.4	558.5
162.5°	596.8	584.1	579.4	574.8	566.7	559.7	556.2	557.4	556.2	559.7	566.7
165°	596.8	586.4	582.9	579.4	573.6	567.8	565.5	565.5	565.5	567.8	573.6
167.5°	596.8	588.7	585.8	582.9	579.4	574.8	573.6	574.8	573.6	574.8	579.4
170°	595.7	589.9	588.2	586.4	584.1	580.6	579.4	580.6	579.4	580.6	584.1
172.5°	594.5	591.0	589.8	588.7	587.6	585.2	585.2	586.4	585.2	585.2	587.6
175°	593.4	591.0	591.0	591.0	589.9	588.7	588.7	589.9	588.7	588.7	589.9
177.5°	592.2	591.0	591.0	591.0	591.0	589.9	591.0	592.2	591.0	589.9	591.0
180°	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0

TEST NUMBER: P1024860

CATALOG NUMBER: S124DIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7
2.5°	1633.9	1628.4	1631.2	1617.5	1605.1	1587.2	1572.1	1569.4	1566.6	1574.9	1569.4
5°	1587.2	1580.3	1573.5	1557.0	1532.2	1517.1	1495.1	1493.8	1485.5	1473.2	1475.9
7.5°	1536.4	1532.2	1522.6	1496.5	1474.5	1448.4	1430.6	1415.4	1408.6	1397.6	1393.5
10°	1495.1	1480.0	1471.8	1442.9	1416.8	1389.3	1366.0	1355.0	1342.6	1333.0	1326.1
12.5°	1438.8	1434.7	1411.3	1388.0	1366.0	1334.4	1316.5	1284.9	1268.4	1276.6	1273.9
15°	1401.7	1382.5	1377.0	1344.0	1306.9	1286.3	1253.3	1232.7	1225.8	1213.4	1198.3
17.5°	1352.2	1339.9	1320.6	1290.4	1247.8	1218.9	1195.6	1176.3	1168.1	1151.6	1139.2
20°	1305.5	1284.9	1269.8	1242.3	1201.1	1164.0	1135.1	1122.7	1102.1	1088.4	1081.5
22.5°	1262.9	1247.8	1225.8	1184.6	1148.8	1113.1	1078.8	1060.9	1041.7	1033.4	1022.4
25°	1210.7	1185.9	1170.8	1125.5	1087.0	1058.1	1026.5	1003.2	992.2	978.4	975.7
27.5°	1159.8	1136.5	1118.6	1078.8	1032.0	994.9	975.7	959.2	940.0	940.0	933.1
30°	1109.0	1092.5	1065.0	1026.5	982.6	946.8	924.8	909.7	902.9	897.4	896.0
32.5°	1058.1	1036.2	1019.7	967.4	934.5	901.5	885.0	872.6	864.4	863.0	864.4
35°	1005.9	981.2	964.7	918.0	885.0	854.8	847.9	836.9	832.8	831.4	838.3
37.5°	951.0	931.7	911.1	872.6	835.5	817.7	803.9	799.8	798.4	806.7	809.4
40°	900.1	883.6	864.4	823.2	795.7	776.4	769.6	765.4	770.9	779.2	783.3
42.5°	852.0	828.7	813.5	776.4	751.7	740.7	732.5	732.5	738.0	747.6	754.4
45°	801.2	783.3	768.2	735.2	713.2	700.8	699.5	700.8	707.7	714.6	722.8
47.5°	751.7	733.8	717.3	689.9	670.6	663.7	662.4	663.7	674.7	684.4	694.0
50°	706.3	687.1	672.0	645.9	630.8	622.5	623.9	630.8	639.0	652.8	665.1
52.5°	652.8	639.0	625.3	601.9	588.2	582.7	586.8	592.3	607.4	617.0	632.1
55°	600.5	588.2	577.2	559.3	548.3	544.2	546.9	555.2	567.6	584.0	601.9
57.5°	552.4	538.7	527.7	515.3	503.0	504.3	505.7	516.7	531.8	546.9	567.6
60°	498.8	490.6	481.0	465.9	460.4	460.4	464.5	476.9	490.6	515.3	533.2
62.5°	450.7	439.7	432.9	423.3	415.0	416.4	426.0	437.0	453.5	474.1	497.5
65°	401.3	388.9	383.4	375.2	372.4	373.8	380.7	397.1	415.0	432.9	454.9
67.5°	346.3	342.2	336.7	328.4	331.2	332.6	339.4	353.2	372.4	390.3	415.0
70°	299.6	291.3	290.0	283.1	283.1	287.2	301.0	310.6	328.4	347.7	373.8
72.5°	250.1	243.2	243.2	237.7	241.9	246.0	252.9	266.6	283.1	302.3	324.3
75°	199.3	196.5	199.3	196.5	196.5	203.4	211.6	222.6	240.5	261.1	279.0
77.5°	153.9	153.9	152.5	156.7	156.7	160.8	171.8	182.8	196.5	213.0	232.2
80°	112.7	112.7	112.7	116.8	120.9	120.9	127.8	141.5	153.9	164.9	182.8
82.5°	77.0	77.0	77.0	79.7	85.2	85.2	93.4	101.7	115.4	125.1	133.3
85°	46.7	46.7	45.3	48.1	49.5	53.6	60.5	66.0	72.8	81.1	89.3
87.5°	20.6	20.6	22.0	23.4	24.7	27.5	30.2	33.0	39.9	42.6	46.7
90°	9.3	9.3	9.3	16.3	16.3	18.6	20.9	19.7	20.9	22.1	23.2
92.5°	74.3	89.4	104.5	176.5	289.1	398.3	455.2	378.5	279.8	209.0	164.9
95°	96.4	120.8	145.1	246.2	436.6	714.1	946.4	973.1	860.4	680.4	524.9
97.5°	112.6	133.5	154.4	234.6	398.3	683.9	1012.5	1220.4	1239.0	1149.6	1021.8
100°	132.4	151.0	169.5	238.0	369.3	606.1	933.6	1230.8	1400.4	1423.6	1366.7
102.5°	154.4	171.9	189.3	249.7	361.1	553.9	834.9	1143.8	1392.2	1530.4	1565.3
105°	180.0	196.8	213.7	269.4	365.8	528.3	761.7	1034.6	1300.5	1501.4	1616.4
107.5°	205.5	222.4	239.2	290.3	379.7	521.4	714.1	945.2	1187.9	1405.0	1565.3
110°	232.2	247.9	263.6	314.7	396.0	523.7	692.1	881.3	1088.0	1288.9	1457.3

TEST NUMBER: P1024860

CATALOG NUMBER: S124DIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	257.8	273.5	289.1	337.9	413.4	530.7	681.6	845.3	1014.9	1186.7	1343.5
115°	284.5	300.2	315.8	362.3	432.0	539.9	679.3	825.6	970.7	1113.6	1249.4
117.5°	308.9	325.2	341.4	385.5	450.5	549.2	678.1	815.1	945.2	1066.0	1176.3
120°	333.3	349.6	365.8	409.9	470.3	559.7	678.1	807.0	928.9	1036.9	1129.8
122.5°	357.6	373.3	389.0	433.1	488.9	570.1	677.0	797.7	915.0	1018.3	1100.8
125°	379.7	396.0	412.2	454.0	507.4	580.6	675.8	787.3	898.7	998.6	1078.7
127.5°	400.6	416.8	433.1	473.8	523.7	588.7	673.5	773.3	880.2	976.5	1056.7
130°	420.3	437.2	454.0	493.5	538.8	598.0	672.3	760.6	856.9	948.7	1027.6
132.5°	438.9	454.6	470.3	509.8	553.9	606.1	671.2	749.0	832.6	917.3	994.0
135°	456.3	471.4	486.5	524.9	566.7	614.3	670.0	737.3	810.5	886.0	956.8
137.5°	471.4	486.0	500.5	536.5	575.9	618.9	670.0	726.9	789.6	855.8	917.3
140°	485.4	499.3	513.2	548.1	585.2	624.7	668.8	718.8	772.2	826.8	879.0
142.5°	498.1	511.5	524.9	558.5	592.2	629.4	668.8	711.8	755.9	802.4	845.3
145°	509.8	522.6	535.3	565.5	596.8	630.5	666.5	703.7	740.8	780.3	815.1
147.5°	521.4	533.0	544.6	573.6	601.5	631.7	663.0	696.7	728.1	760.6	789.6
150°	531.8	542.8	553.9	579.4	605.0	631.7	659.5	688.6	716.4	743.2	766.4
152.5°	542.3	552.2	562.0	584.1	607.3	629.4	653.7	679.3	703.7	725.7	746.6
155°	551.6	560.3	569.0	588.7	608.5	627.0	647.9	670.0	690.9	709.5	726.9
157.5°	560.8	567.8	574.8	592.2	608.5	624.7	642.1	660.7	677.0	693.2	708.3
160°	567.8	574.2	580.6	594.5	608.5	621.2	635.2	650.3	664.2	677.0	689.7
162.5°	574.8	579.4	584.1	596.8	608.5	617.7	628.2	641.0	651.4	661.9	671.2
165°	579.4	582.9	586.4	596.8	606.1	613.1	621.2	630.5	639.8	646.8	654.9
167.5°	582.9	585.8	588.7	596.8	603.8	608.5	614.3	621.2	628.2	634.0	641.0
170°	586.4	588.2	589.9	595.7	601.5	603.8	607.3	611.9	617.7	621.2	625.9
172.5°	588.7	589.8	591.0	594.5	599.2	599.2	600.3	603.8	608.5	610.8	613.1
175°	591.0	591.0	591.0	593.4	596.8	595.7	595.7	598.0	600.3	601.5	603.8
177.5°	591.0	591.0	591.0	592.2	594.5	592.2	592.2	593.4	594.5	595.7	595.7
180°	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0

TEST NUMBER: P1024860

CATALOG NUMBER: S124DIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7
2.5°	1565.2	1563.9	1557.0	1559.7	1551.5	1554.2	1558.4	1559.7	1565.2	1561.1	1559.7
5°	1469.0	1466.3	1462.2	1458.0	1456.7	1462.2	1452.5	1455.3	1458.0	1462.2	1467.7
7.5°	1390.7	1389.3	1385.2	1378.3	1375.6	1372.8	1374.2	1383.8	1382.5	1381.1	1390.7
10°	1319.2	1320.6	1312.4	1311.0	1302.8	1301.4	1302.8	1305.5	1309.6	1315.1	1316.5
12.5°	1245.0	1262.9	1247.8	1242.3	1229.9	1236.8	1239.5	1227.2	1234.0	1238.2	1258.8
15°	1198.3	1190.1	1180.5	1180.5	1175.0	1172.2	1165.3	1175.0	1180.5	1188.7	1185.9
17.5°	1133.7	1120.0	1114.5	1109.0	1110.4	1115.9	1100.7	1122.7	1122.7	1126.9	1120.0
20°	1077.4	1066.4	1059.5	1056.8	1052.6	1049.9	1048.5	1054.0	1062.3	1065.0	1071.9
22.5°	1018.3	1018.3	1007.3	1003.2	1000.4	996.3	1003.2	999.1	1004.6	1010.0	1021.0
25°	968.8	968.8	964.7	959.2	955.1	952.3	956.5	955.1	959.2	966.1	968.8
27.5°	929.0	924.8	923.5	922.1	920.7	922.1	920.7	924.8	929.0	930.3	927.6
30°	894.6	890.5	891.9	891.9	893.2	891.9	890.5	894.6	896.0	893.2	894.6
32.5°	863.0	863.0	865.8	867.1	867.1	868.5	869.9	867.1	868.5	864.4	865.8
35°	836.9	839.6	842.4	843.8	845.1	843.8	846.5	845.1	842.4	839.6	838.3
37.5°	810.8	813.5	819.0	820.4	824.5	825.9	823.2	823.2	821.8	816.3	813.5
40°	783.3	786.1	792.9	797.0	799.8	803.9	801.2	801.2	795.7	790.2	786.1
42.5°	757.2	762.7	769.6	773.7	779.2	779.2	779.2	776.4	769.6	764.1	759.9
45°	731.1	732.5	742.1	748.9	754.4	754.4	754.4	750.3	746.2	735.2	729.7
47.5°	702.2	706.3	717.3	724.2	729.7	731.1	731.1	727.0	718.7	709.1	702.2
50°	670.6	677.5	689.9	699.5	706.3	709.1	705.0	702.2	692.6	681.6	673.4
52.5°	640.4	648.6	663.7	672.0	681.6	683.0	681.6	677.5	666.5	651.4	644.5
55°	610.2	617.0	633.5	647.3	655.5	658.2	655.5	648.6	634.9	619.8	612.9
57.5°	577.2	586.8	604.7	618.4	628.0	629.4	626.6	619.8	608.8	589.5	579.9
60°	542.8	555.2	573.0	586.8	599.2	600.5	597.8	588.2	574.4	555.2	546.9
62.5°	508.5	518.1	538.7	553.8	563.4	570.3	564.8	555.2	541.4	522.2	509.8
65°	468.6	482.3	500.2	514.0	525.0	526.3	523.6	515.3	500.2	479.6	470.0
67.5°	430.1	439.7	457.6	475.5	479.6	483.7	479.6	471.4	459.0	441.1	427.4
70°	383.4	391.7	413.6	426.0	431.5	435.6	432.9	424.6	413.6	397.1	386.2
72.5°	336.7	343.6	364.2	373.8	384.8	383.4	382.0	376.5	361.4	350.4	343.6
75°	287.2	295.5	309.2	321.6	325.7	325.7	325.7	321.6	311.9	294.1	287.2
77.5°	241.9	246.0	257.0	263.8	268.0	269.3	268.0	261.1	255.6	243.2	239.1
80°	185.5	196.5	204.8	206.1	211.6	211.6	211.6	208.9	203.4	191.0	189.6
82.5°	140.2	142.9	151.2	155.3	158.0	156.7	156.7	151.2	149.8	142.9	140.2
85°	94.8	98.9	97.6	103.1	104.4	101.7	101.7	104.4	97.6	98.9	94.8
87.5°	52.2	52.2	55.0	53.6	59.1	59.1	56.3	57.7	55.0	53.6	52.2
90°	23.2	23.2	24.4	25.5	24.4	24.4	24.4	25.5	24.4	23.2	23.2
92.5°	150.4	135.9	118.4	110.3	105.7	105.7	105.7	110.3	118.4	135.9	150.4
95°	468.6	412.2	355.3	319.3	298.4	283.3	298.4	319.3	355.3	412.2	468.6
97.5°	956.8	891.8	812.8	743.2	708.3	680.4	708.3	743.2	812.8	891.8	956.8
100°	1323.8	1280.8	1179.8	1108.9	1074.1	1064.8	1074.1	1108.9	1179.8	1280.8	1323.8
102.5°	1553.6	1542.0	1489.8	1443.3	1406.2	1399.2	1406.2	1443.3	1489.8	1542.0	1553.6
105°	1640.2	1664.0	1666.3	1657.0	1640.7	1633.8	1640.7	1657.0	1666.3	1664.0	1640.2
107.5°	1614.0	1662.8	1713.9	1734.8	1744.1	1745.2	1744.1	1734.8	1713.9	1662.8	1614.0
110°	1521.2	1585.0	1667.4	1716.2	1737.1	1747.6	1737.1	1716.2	1667.4	1585.0	1521.2

TEST NUMBER: P1024860

CATALOG NUMBER: S124DIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1407.4	1471.2	1567.6	1629.1	1660.5	1679.1	1660.5	1629.1	1567.6	1471.2	1407.4
115°	1305.2	1360.9	1452.6	1522.3	1559.5	1568.7	1559.5	1522.3	1452.6	1360.9	1305.2
117.5°	1225.0	1273.8	1355.1	1415.5	1455.0	1460.8	1455.0	1415.5	1355.1	1273.8	1225.0
120°	1171.0	1212.3	1278.5	1329.5	1359.7	1372.5	1359.7	1329.5	1278.5	1212.3	1171.0
122.5°	1135.6	1170.5	1223.9	1265.7	1290.1	1302.8	1290.1	1265.7	1223.9	1170.5	1135.6
125°	1110.6	1142.6	1189.0	1222.7	1244.8	1251.7	1244.8	1222.7	1189.0	1142.6	1110.6
127.5°	1086.8	1117.0	1163.5	1193.7	1212.3	1219.2	1212.3	1193.7	1163.5	1117.0	1086.8
130°	1058.4	1089.2	1136.8	1165.8	1184.4	1191.4	1184.4	1165.8	1136.8	1089.2	1058.4
132.5°	1024.8	1055.5	1102.0	1135.6	1153.0	1160.0	1153.0	1135.6	1102.0	1055.5	1024.8
135°	985.8	1014.9	1061.3	1093.8	1112.4	1119.4	1112.4	1093.8	1061.3	1014.9	985.8
137.5°	944.0	970.7	1014.9	1048.5	1063.6	1071.8	1063.6	1048.5	1014.9	970.7	944.0
140°	903.4	927.8	968.4	994.0	1010.2	1019.5	1010.2	994.0	968.4	927.8	903.4
142.5°	865.6	886.0	920.8	944.0	958.0	963.8	958.0	944.0	920.8	886.0	865.6
145°	831.4	847.7	876.7	896.4	908.0	913.8	908.0	896.4	876.7	847.7	831.4
147.5°	803.0	816.3	838.4	855.8	865.1	867.4	865.1	855.8	838.4	816.3	803.0
150°	776.8	787.3	805.9	820.9	827.9	829.1	827.9	820.9	805.9	787.3	776.8
152.5°	754.8	762.9	778.0	789.6	793.1	794.2	793.1	789.6	778.0	762.9	754.8
155°	733.8	740.8	752.4	761.7	765.2	765.2	765.2	761.7	752.4	740.8	733.8
157.5°	714.1	719.9	729.2	736.2	738.5	738.5	738.5	736.2	729.2	719.9	714.1
160°	694.4	699.0	706.0	713.0	714.1	714.1	714.1	713.0	706.0	699.0	694.4
162.5°	675.2	679.3	683.9	690.9	692.1	690.9	692.1	690.9	683.9	679.3	675.2
165°	657.8	660.7	665.4	670.0	668.8	667.7	668.8	670.0	665.4	660.7	657.8
167.5°	642.8	644.5	646.8	650.3	650.3	649.1	650.3	650.3	646.8	644.5	642.8
170°	627.6	629.4	631.7	632.8	631.7	631.7	631.7	632.8	631.7	629.4	627.6
172.5°	614.2	615.4	616.6	617.7	616.6	614.3	616.6	617.7	616.6	615.4	614.2
175°	603.8	603.8	603.8	606.1	603.8	601.5	603.8	606.1	603.8	603.8	603.8
177.5°	596.2	596.8	595.7	596.8	594.5	592.2	594.5	596.8	595.7	596.8	596.2
180°	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0

TEST NUMBER: P1024860

CATALOG NUMBER: S124DIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7	1658.7
2.5°	1559.7	1568.0	1559.7	1565.2	1568.0	1574.9	1577.6	1590.0	1594.1	1603.7	1603.7
5°	1466.3	1470.4	1471.8	1477.3	1482.8	1496.5	1506.1	1524.0	1544.6	1547.4	1559.7
7.5°	1390.7	1397.6	1408.6	1404.4	1414.1	1434.7	1447.0	1469.0	1489.6	1500.6	1515.8
10°	1323.4	1331.6	1335.7	1339.9	1357.7	1375.6	1394.8	1409.9	1437.4	1453.9	1466.3
12.5°	1268.4	1261.5	1269.8	1284.9	1305.5	1316.5	1342.6	1366.0	1386.6	1404.4	1415.4
15°	1196.9	1202.4	1210.7	1236.8	1242.3	1269.8	1279.4	1305.5	1344.0	1360.5	1374.2
17.5°	1128.2	1146.1	1162.6	1172.2	1188.7	1210.7	1238.2	1267.0	1291.8	1311.0	1327.5
20°	1073.3	1091.1	1100.7	1107.6	1124.1	1154.3	1180.5	1216.2	1247.8	1262.9	1284.9
22.5°	1029.3	1029.3	1043.0	1063.6	1073.3	1102.1	1124.1	1162.6	1196.9	1216.2	1236.8
25°	974.3	982.6	993.6	1011.4	1025.2	1048.5	1080.1	1113.1	1150.2	1166.7	1192.8
27.5°	929.0	938.6	953.7	957.8	971.6	992.2	1025.2	1060.9	1099.4	1117.2	1139.2
30°	894.6	900.1	905.6	913.9	926.2	944.1	971.6	1003.2	1049.9	1063.6	1091.1
32.5°	864.4	867.1	869.9	876.7	883.6	901.5	923.5	957.8	996.3	1016.9	1041.7
35°	836.9	834.1	835.5	839.6	846.5	853.4	876.7	905.6	941.3	966.1	985.3
37.5°	810.8	805.3	803.9	803.9	806.7	814.9	832.8	857.5	896.0	916.6	935.8
40°	781.9	776.4	773.7	772.3	770.9	776.4	790.2	814.9	845.1	864.4	886.4
42.5°	754.4	748.9	742.1	740.7	738.0	740.7	750.3	773.7	799.8	819.0	836.9
45°	727.0	717.3	709.1	703.6	705.0	700.8	707.7	725.6	755.8	768.2	786.1
47.5°	696.7	685.7	674.7	669.2	663.7	666.5	669.2	684.4	710.5	722.8	740.7
50°	667.9	652.8	640.4	633.5	629.4	626.6	629.4	644.5	663.7	674.7	689.9
52.5°	634.9	619.8	607.4	596.4	590.9	586.8	588.2	601.9	619.8	630.8	645.9
55°	604.7	585.4	568.9	555.2	551.1	549.7	548.3	557.9	573.0	584.0	596.4
57.5°	570.3	551.1	533.2	516.7	508.5	507.1	507.1	509.8	529.1	537.3	544.2
60°	535.9	515.3	496.1	481.0	468.6	464.5	463.1	468.6	478.2	486.5	496.1
62.5°	497.5	476.9	453.5	439.7	427.4	416.4	420.5	421.9	435.6	439.7	448.0
65°	460.4	437.0	417.8	395.8	382.0	375.2	372.4	375.2	386.2	387.5	393.0
67.5°	417.8	395.8	372.4	357.3	344.9	332.6	329.8	329.8	335.3	339.4	346.3
70°	376.5	354.5	328.4	311.9	299.6	288.6	284.5	283.1	287.2	290.0	296.8
72.5°	328.4	306.4	287.2	269.3	254.2	246.0	241.9	239.1	243.2	246.0	247.4
75°	277.6	259.7	240.5	222.6	213.0	204.8	199.3	195.1	197.9	197.9	197.9
77.5°	229.5	211.6	196.5	184.1	171.8	162.2	158.0	153.9	155.3	155.3	158.0
80°	178.6	166.3	153.9	142.9	131.9	123.7	120.9	116.8	114.1	112.7	112.7
82.5°	131.9	122.3	111.3	101.7	96.2	87.9	85.2	79.7	79.7	78.3	78.3
85°	87.9	82.5	71.5	64.6	60.5	56.3	53.6	50.8	46.7	46.7	45.3
87.5°	46.7	44.0	41.2	33.0	33.0	28.9	27.5	26.1	22.0	23.4	23.4
90°	23.2	22.1	20.9	19.7	20.9	18.6	16.3	16.3	9.3	9.3	9.3
92.5°	164.9	209.0	279.8	378.5	455.2	398.3	289.1	176.5	104.5	89.4	74.3
95°	524.9	680.4	860.4	973.1	946.4	714.1	436.6	246.2	145.1	120.8	96.4
97.5°	1021.8	1149.6	1239.0	1220.4	1012.5	683.9	398.3	234.6	154.4	133.5	112.6
100°	1366.7	1423.6	1400.4	1230.8	933.6	606.1	369.3	238.0	169.5	151.0	132.4
102.5°	1565.3	1530.4	1392.2	1143.8	834.9	553.9	361.1	249.7	189.3	171.9	154.4
105°	1616.4	1501.4	1300.5	1034.6	761.7	528.3	365.8	269.4	213.7	196.8	180.0
107.5°	1565.3	1405.0	1187.9	945.2	714.1	521.4	379.7	290.3	239.2	222.4	205.5
110°	1457.3	1288.9	1088.0	881.3	692.1	523.7	396.0	314.7	263.6	247.9	232.2

TEST NUMBER: P1024860

CATALOG NUMBER: S124DIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1343.5	1186.7	1014.9	845.3	681.6	530.7	413.4	337.9	289.1	273.5	257.8
115°	1249.4	1113.6	970.7	825.6	679.3	539.9	432.0	362.3	315.8	300.2	284.5
117.5°	1176.3	1066.0	945.2	815.1	678.1	549.2	450.5	385.5	341.4	325.2	308.9
120°	1129.8	1036.9	928.9	807.0	678.1	559.7	470.3	409.9	365.8	349.6	333.3
122.5°	1100.8	1018.3	915.0	797.7	677.0	570.1	488.9	433.1	389.0	373.3	357.6
125°	1078.7	998.6	898.7	787.3	675.8	580.6	507.4	454.0	412.2	396.0	379.7
127.5°	1056.7	976.5	880.2	773.3	673.5	588.7	523.7	473.8	433.1	416.8	400.6
130°	1027.6	948.7	856.9	760.6	672.3	598.0	538.8	493.5	454.0	437.2	420.3
132.5°	994.0	917.3	832.6	749.0	671.2	606.1	553.9	509.8	470.3	454.6	438.9
135°	956.8	886.0	810.5	737.3	670.0	614.3	566.7	524.9	486.5	471.4	456.3
137.5°	917.3	855.8	789.6	726.9	670.0	618.9	575.9	536.5	500.5	486.0	471.4
140°	879.0	826.8	772.2	718.8	668.8	624.7	585.2	548.1	513.2	499.3	485.4
142.5°	845.3	802.4	755.9	711.8	668.8	629.4	592.2	558.5	524.9	511.5	498.1
145°	815.1	780.3	740.8	703.7	666.5	630.5	596.8	565.5	535.3	522.6	509.8
147.5°	789.6	760.6	728.1	696.7	663.0	631.7	601.5	573.6	544.6	533.0	521.4
150°	766.4	743.2	716.4	688.6	659.5	631.7	605.0	579.4	553.9	542.8	531.8
152.5°	746.6	725.7	703.7	679.3	653.7	629.4	607.3	584.1	562.0	552.2	542.3
155°	726.9	709.5	690.9	670.0	647.9	627.0	608.5	588.7	569.0	560.3	551.6
157.5°	708.3	693.2	677.0	660.7	642.1	624.7	608.5	592.2	574.8	567.8	560.8
160°	689.7	677.0	664.2	650.3	635.2	621.2	608.5	594.5	580.6	574.2	567.8
162.5°	671.2	661.9	651.4	641.0	628.2	617.7	608.5	596.8	584.1	579.4	574.8
165°	654.9	646.8	639.8	630.5	621.2	613.1	606.1	596.8	586.4	582.9	579.4
167.5°	641.0	634.0	628.2	621.2	614.3	608.5	603.8	596.8	588.7	585.8	582.9
170°	625.9	621.2	617.7	611.9	607.3	603.8	601.5	595.7	589.9	588.2	586.4
172.5°	613.1	610.8	608.5	603.8	600.3	599.2	599.2	594.5	591.0	589.8	588.7
175°	603.8	601.5	600.3	598.0	595.7	595.7	596.8	593.4	591.0	591.0	591.0
177.5°	595.7	595.7	594.5	593.4	592.2	592.2	594.5	592.2	591.0	591.0	591.0
180°	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0	591.0

TEST NUMBER: P1024860

CATALOG NUMBER: S124DIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1658.7	1658.7	1658.7	1658.7
2.5°	1613.3	1627.1	1639.4	1658.7
5°	1577.6	1596.8	1622.9	1651.8
7.5°	1536.4	1566.6	1601.0	1640.8
10°	1497.9	1532.2	1576.2	1624.3
12.5°	1458.0	1499.3	1547.4	1599.6
15°	1412.7	1453.9	1507.5	1577.6
17.5°	1371.5	1420.9	1478.7	1552.9
20°	1323.4	1370.1	1433.3	1518.5
22.5°	1280.8	1334.4	1404.4	1478.7
25°	1234.0	1280.8	1350.9	1440.2
27.5°	1187.3	1245.0	1312.4	1399.0
30°	1142.0	1190.1	1262.9	1353.6
32.5°	1092.5	1150.2	1217.6	1302.8
35°	1038.9	1093.9	1157.1	1249.2
37.5°	990.8	1044.4	1109.0	1190.1
40°	937.2	993.6	1052.6	1133.7
42.5°	885.0	935.8	994.9	1069.1
45°	834.1	878.1	931.7	996.3
47.5°	781.9	819.0	868.5	926.2
50°	725.6	765.4	802.5	850.6
52.5°	673.4	707.7	738.0	777.8
55°	622.5	645.9	670.6	700.8
57.5°	568.9	586.8	604.7	636.3
60°	515.3	531.8	541.4	562.1
62.5°	463.1	470.0	482.3	494.7
65°	405.4	415.0	421.9	437.0
67.5°	353.2	357.3	364.2	373.8
70°	298.2	307.8	310.6	317.4
72.5°	251.5	255.6	258.4	259.7
75°	199.3	203.4	206.1	214.4
77.5°	156.7	155.3	160.8	162.2
80°	115.4	111.3	112.7	118.2
82.5°	75.6	77.0	75.6	75.6
85°	46.7	45.3	42.6	44.0
87.5°	20.6	20.6	19.2	19.2
90°	8.1	7.0	3.5	1.2
92.5°	53.4	36.0	23.2	16.3
95°	68.5	53.4	41.8	38.3
97.5°	88.2	74.3	63.9	63.9
100°	110.3	96.4	88.2	88.2
102.5°	133.5	120.8	113.8	111.5
105°	159.1	145.1	139.3	135.9
107.5°	185.8	170.7	164.9	162.6
110°	211.3	197.4	191.6	189.3

TEST NUMBER: P1024860

CATALOG NUMBER: S124DIP-B1020D1205UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	236.9	224.1	217.1	214.8
115°	262.4	250.8	242.7	239.2
117.5°	288.0	275.2	268.2	264.7
120°	313.5	300.7	292.6	290.3
122.5°	335.6	324.0	315.8	313.5
125°	357.6	344.9	337.9	333.3
127.5°	377.4	363.4	355.3	351.8
130°	398.3	380.9	371.6	366.9
132.5°	414.5	398.3	385.5	382.0
135°	432.0	412.2	400.6	396.0
137.5°	445.9	427.3	414.5	409.9
140°	461.0	441.2	428.5	425.0
142.5°	474.9	456.3	444.7	441.2
145°	487.7	471.4	459.8	456.3
147.5°	502.8	485.4	474.9	473.8
150°	514.4	500.5	491.2	490.0
152.5°	527.2	514.4	505.1	505.1
155°	538.8	527.2	520.2	519.0
157.5°	549.2	539.9	533.0	533.0
160°	558.5	550.4	545.8	545.8
162.5°	566.7	559.7	556.2	557.4
165°	573.6	567.8	565.5	565.5
167.5°	579.4	574.8	573.6	574.8
170°	584.1	580.6	579.4	580.6
172.5°	587.6	585.2	585.2	586.4
175°	589.9	588.7	588.7	589.9
177.5°	591.0	589.9	591.0	592.2
180°	591.0	591.0	591.0	591.0

(END OF REPORT)