

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012943

Luminaire Tested: S124DIP-B1195D1205UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012943
REPORT IS A COMBINATION OF REPORTS P995500 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B1195D1205UB2750-4F0-XX-W2A-F_3500K
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9976.0 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012943

CATALOG NUMBER: S124DIP-B1195D1205UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1012943

CATALOG NUMBER: S124DIP-B1195D1205UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	58	58	58
1	98	94	90	86	91	87	83	80	74	71	69	62	60	59	51	50	49	49	49	49
2	89	82	76	70	82	76	71	66	65	61	57	54	51	49	45	43	41	41	41	41
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	40	37	35	35	35	35
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	30	30	30
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	26	26	26
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	23	23	23
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	26	23	20	20	20	20
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	18	18	18
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	22	19	17	17	17	17
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	17	15	15	15	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16355	16355	16355
5°	16369	15885	15904
10°	16230	15444	15336
15°	15998	14919	14694
20°	15700	14353	14031
25°	15366	13753	13316
30°	14962	13105	12531
35°	14544	12442	11773
40°	14109	11728	10966
45°	13652	11012	10212
50°	13146	10318	9377
55°	12597	9508	8547
60°	12034	8620	7684
65°	11391	7704	6709
70°	10648	6599	5666
75°	9542	5320	4539
80°	8131	3845	3192
85°	6316	2142	1719

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13652 cd/sqm

TEST NUMBER: P1012943

CATALOG NUMBER: S124DIP-B1195D1205UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	1.9
10°-20°	532.6	5.3
20°-30°	783.8	7.9
30°-40°	911.2	9.1
40°-50°	911.1	9.1
50°-60°	796.9	8.0
60°-70°	591.6	5.9
70°-80°	335.7	3.4
80°-90°	99.4	1.0
90°-100°	51.8	0.5
100°-110°	340.8	3.4
110°-120°	650.9	6.5
120°-130°	826.3	8.3
130°-140°	883.9	8.9
140°-150°	826.5	8.3
150°-160°	666.5	6.7
160°-170°	429.9	4.3
170°-180°	148.2	1.5
0°-30°	1505.5	15.1
0°-40°	2416.7	24.2
0°-60°	4124.6	41.3
0°-90°	5151.2	51.6
90°-120°	1043.5	10.5
90°-150°	3580.2	35.9
90°-180°	4825.0	48.4
0°-180°	9976.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2006	2006	2006	2006	2006	
5°	2004	1998	1980	1998	1994	190
15°	1908	1901	1877	1887	1882	538
25°	1728	1716	1694	1696	1689	795
35°	1487	1475	1453	1442	1434	930
45°	1213	1202	1176	1159	1154	935
55°	918	913	890	871	861	822
65°	622	614	598	582	574	616
75°	331	323	315	309	307	351
85°	87	87	84	84	82	93
90°	4	16	26	33	35	9
95°	64	24	26	33	34	79
105°	351	358	364	374	332	367
115°	655	659	658	660	660	645
125°	921	926	924	927	928	823
135°	1143	1142	1146	1149	1151	881
145°	1318	1321	1321	1322	1325	823
155°	1445	1446	1443	1447	1444	666
165°	1524	1518	1518	1528	1517	431
175°	1559	1552	1553	1564	1550	148
180°	1559	1559	1559	1559	1559	

TEST NUMBER: P1012943

CATALOG NUMBER: S124DIP-B1195D1205UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2005.7	2005.7	2005.7	2005.7	2005.7
2.5°	2012.1	2007.3	1989.6	2005.7	2004.1
5°	2004.1	1997.7	1980.0	1997.7	1994.4
7.5°	1989.6	1983.2	1963.9	1978.4	1976.8
10°	1968.7	1962.3	1941.4	1954.3	1951.1
12.5°	1941.4	1935.0	1912.5	1926.9	1922.1
15°	1907.7	1901.2	1877.1	1886.8	1881.9
17.5°	1869.1	1861.1	1838.6	1845.0	1841.8
20°	1825.7	1817.7	1793.6	1798.4	1795.2
22.5°	1779.1	1767.8	1743.7	1753.4	1746.9
25°	1727.7	1716.4	1693.9	1695.5	1689.1
27.5°	1669.8	1658.6	1637.7	1634.4	1626.4
30°	1611.9	1599.1	1578.2	1571.8	1563.7
32.5°	1550.9	1539.6	1517.1	1509.1	1501.1
35°	1486.6	1475.3	1452.8	1441.6	1433.6
37.5°	1419.1	1409.4	1385.3	1374.1	1362.8
40°	1353.2	1340.3	1316.2	1300.2	1292.1
42.5°	1282.5	1276.1	1248.7	1229.5	1224.6
45°	1213.4	1202.1	1176.4	1158.7	1153.9
47.5°	1141.1	1133.0	1108.9	1089.6	1076.8
50°	1067.1	1060.7	1038.2	1015.7	1006.1
52.5°	994.8	986.8	962.7	943.4	930.5
55°	917.7	912.8	890.3	871.1	861.4
57.5°	845.3	840.5	818.0	798.7	789.1
60°	769.8	761.8	740.9	726.4	718.4
62.5°	695.9	689.5	667.0	654.1	646.1
65°	622.0	613.9	597.9	581.8	573.7
67.5°	546.4	540.0	523.9	507.9	506.2
70°	477.3	466.1	453.2	440.4	435.5
72.5°	403.4	392.1	382.5	372.9	368.0
75°	331.1	323.0	315.0	308.6	307.0
77.5°	260.4	257.1	249.1	247.5	242.7
80°	197.7	192.9	189.6	186.4	184.8
82.5°	136.6	135.0	135.0	133.4	131.8
85°	86.8	86.8	83.6	83.6	82.0
87.5°	41.8	40.2	38.6	38.6	38.6
90°	3.5	16.3	25.7	32.7	35.0
92.5°	17.5	15.2	24.5	31.5	31.5
95°	64.1	24.5	25.7	32.7	33.8
97.5°	122.5	148.1	25.7	31.5	32.7
100°	191.3	212.2	51.3	31.5	32.7
102.5°	268.2	282.2	296.2	33.8	33.8
105°	351.0	358.0	363.9	374.4	332.4
107.5°	426.8	430.3	438.5	444.3	449.0
110°	503.8	507.3	514.3	516.6	520.1



TEST NUMBER: P1012943

CATALOG NUMBER: S124DIP-B1195D1205UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	578.4	585.4	587.8	586.6	591.3
115°	655.4	658.9	657.7	660.1	660.1
117.5°	724.2	728.9	732.4	731.2	731.2
120°	794.2	798.9	797.7	800.0	797.7
122.5°	859.5	861.8	864.2	865.3	863.0
125°	921.3	926.0	923.6	927.1	928.3
127.5°	980.8	981.9	987.8	986.6	985.4
130°	1037.9	1039.1	1042.6	1043.8	1043.8
132.5°	1090.4	1092.7	1097.4	1098.6	1097.4
135°	1142.9	1141.7	1146.4	1148.7	1151.0
137.5°	1189.5	1189.5	1195.4	1197.7	1196.5
140°	1235.0	1237.3	1239.7	1243.2	1244.3
142.5°	1275.8	1280.5	1281.7	1284.0	1284.0
145°	1317.8	1321.3	1321.3	1322.5	1324.8
147.5°	1350.5	1357.5	1356.3	1357.5	1358.6
150°	1386.6	1391.3	1390.1	1390.1	1391.3
152.5°	1416.9	1420.4	1418.1	1420.4	1419.3
155°	1444.9	1446.1	1442.6	1447.3	1443.8
157.5°	1469.4	1469.4	1464.8	1470.6	1464.8
160°	1490.4	1486.9	1485.7	1492.7	1485.7
162.5°	1509.1	1504.4	1503.2	1510.2	1502.1
165°	1524.2	1518.4	1518.4	1527.7	1517.2
167.5°	1537.1	1531.2	1530.1	1540.6	1528.9
170°	1547.6	1540.6	1541.7	1551.1	1539.4
172.5°	1554.6	1547.6	1548.7	1558.1	1545.2
175°	1559.2	1552.2	1553.4	1563.9	1549.9
177.5°	1562.7	1554.6	1556.9	1566.2	1552.2
180°	1559.2	1559.2	1559.2	1559.2	1559.2

(END OF REPORT)