

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012978

Luminaire Tested: S124DIP-B1195D810UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012978
REPORT IS A COMBINATION OF REPORTS P995673 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B1195D810UB2750-4F0-XX-W2A-D_2700K
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7965.0 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012978

CATALOG NUMBER: S124DIP-B1195D810UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1012978

CATALOG NUMBER: S124DIP-B1195D810UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	98	93	89	85	91	87	83	79	74	72	69	63	61	59	53	51	50
2	89	81	74	68	82	75	69	64	65	60	56	55	51	48	46	43	41
3	81	71	63	56	75	66	59	53	57	51	47	48	44	40	40	37	34
4	74	62	54	47	68	58	50	45	50	44	39	43	38	34	36	32	29
5	68	55	47	40	62	52	44	38	45	38	34	38	33	30	32	28	25
6	62	49	41	35	57	46	39	33	40	34	29	34	29	26	29	25	22
7	57	45	36	30	53	42	34	29	36	30	26	31	26	23	26	23	20
8	53	40	32	27	49	38	31	26	33	27	23	28	24	20	24	20	17
9	50	37	29	24	46	35	28	23	30	24	20	26	21	18	22	19	16
10	46	34	26	21	43	32	25	20	28	22	18	24	20	16	21	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11555	11555	11555
5°	11586	11254	11274
10°	11511	11032	11000
15°	11403	10783	10692
20°	11244	10513	10393
25°	11064	10216	10070
30°	10869	9922	9740
35°	10649	9621	9447
40°	10472	9331	9144
45°	10211	9060	8875
50°	9988	8752	8592
55°	9758	8456	8266
60°	9401	8086	7959
65°	9008	7688	7590
70°	8531	7233	7163
75°	7864	6726	6757
80°	7115	6210	6331
85°	6120	5691	5986

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10211 cd/sqm

TEST NUMBER: P1012978

CATALOG NUMBER: S124DIP-B1195D810UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.3	1.7
10°-20°	384.7	4.8
20°-30°	581.6	7.3
30°-40°	703.7	8.8
40°-50°	743.9	9.3
50°-60°	700.1	8.8
60°-70°	581.0	7.3
70°-80°	407.7	5.1
80°-90°	231.9	2.9
90°-100°	170.4	2.1
100°-110°	322.6	4.1
110°-120°	490.5	6.2
120°-130°	574.7	7.2
130°-140°	590.4	7.4
140°-150°	539.8	6.8
150°-160°	432.7	5.4
160°-170°	279.0	3.5
170°-180°	96.2	1.2
0°-30°	1100.6	13.8
0°-40°	1804.2	22.7
0°-60°	3248.2	40.8
0°-90°	4468.8	56.1
90°-120°	983.5	12.3
90°-150°	2688.3	33.8
90°-180°	3496.0	43.9
0°-180°	7965.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1417	1417	1417	1417	1417	
5°	1418	1414	1403	1415	1414	135
15°	1360	1361	1357	1371	1369	383
25°	1244	1254	1258	1276	1277	573
35°	1088	1108	1123	1146	1150	682
45°	908	938	968	995	1003	701
55°	711	744	792	824	833	633
65°	492	543	597	636	649	488
75°	273	332	398	443	457	290
85°	84	151	222	270	286	88
90°	28	100	174	224	238	20
95°	62	89	155	202	217	68
105°	242	278	341	387	373	255
115°	435	452	502	538	549	429
125°	604	606	644	676	687	540
135°	745	744	758	785	796	575
145°	857	858	858	868	876	536
155°	938	939	936	940	937	433
165°	989	986	986	992	985	280
175°	1012	1008	1008	1015	1006	96
180°	1012	1012	1012	1012	1012	

TEST NUMBER: P1012978

CATALOG NUMBER: S124DIP-B1195D810UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1417.0	1417.0	1417.0	1417.0	1417.0
2.5°	1423.3	1418.5	1405.9	1417.0	1415.4
5°	1418.5	1413.8	1402.7	1415.4	1413.8
7.5°	1409.0	1405.9	1396.3	1410.6	1409.0
10°	1396.3	1394.7	1386.8	1401.1	1399.5
12.5°	1378.9	1378.9	1374.1	1386.8	1386.8
15°	1359.8	1361.4	1356.7	1370.9	1369.4
17.5°	1334.5	1339.2	1337.6	1351.9	1350.3
20°	1307.5	1312.2	1313.8	1329.7	1329.7
22.5°	1277.3	1283.7	1286.8	1302.7	1305.9
25°	1244.0	1253.5	1258.3	1275.7	1277.3
27.5°	1207.5	1221.8	1228.1	1244.0	1245.6
30°	1171.0	1183.7	1194.8	1212.3	1215.4
32.5°	1131.3	1147.2	1159.9	1180.5	1183.7
35°	1088.5	1107.5	1123.4	1145.6	1150.4
37.5°	1045.7	1067.9	1086.9	1109.1	1113.9
40°	1004.4	1025.0	1047.2	1071.1	1077.4
42.5°	956.8	980.6	1007.6	1034.6	1039.3
45°	907.6	937.8	967.9	994.9	1002.8
47.5°	861.6	891.7	926.7	953.6	963.2
50°	810.8	845.7	880.6	912.4	921.9
52.5°	760.0	795.0	836.2	867.9	877.5
55°	710.9	744.2	791.8	823.5	833.0
57.5°	655.3	696.6	742.6	780.7	788.6
60°	601.4	642.6	695.0	731.5	744.2
62.5°	549.0	595.0	647.4	683.9	696.6
65°	491.9	542.7	596.6	636.3	649.0
67.5°	437.9	491.9	549.0	588.7	601.4
70°	382.4	436.4	496.7	539.5	550.6
72.5°	328.5	384.0	449.0	490.3	503.0
75°	272.9	331.6	398.3	442.7	457.0
77.5°	220.6	282.4	352.3	396.7	412.6
80°	173.0	236.4	306.2	353.8	366.5
82.5°	125.4	192.0	261.8	311.0	325.3
85°	84.1	150.7	222.1	269.7	285.6
87.5°	52.4	117.4	187.2	233.3	247.5
90°	27.7	99.5	173.8	224.3	238.5
92.5°	35.2	89.1	163.5	212.4	225.1
95°	62.2	88.9	154.7	202.1	217.2
97.5°	98.5	161.2	146.8	191.8	206.8
100°	141.7	196.5	153.9	183.8	195.7
102.5°	191.6	235.6	305.0	175.9	188.6
105°	242.2	278.4	340.9	387.4	372.9
107.5°	291.4	320.6	381.4	424.9	439.1
110°	339.7	364.2	424.2	462.3	477.2



TEST NUMBER: P1012978

CATALOG NUMBER: S124DIP-B1195D810UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	386.6	410.1	464.0	498.2	513.9
115°	434.9	451.5	501.6	538.0	549.1
117.5°	479.6	492.1	542.0	574.7	587.4
120°	523.4	531.3	576.5	609.7	620.9
122.5°	565.8	567.3	611.8	644.2	653.8
125°	604.3	605.9	644.0	676.4	686.7
127.5°	643.0	642.2	677.7	705.5	715.9
130°	678.5	677.7	705.4	734.6	744.1
132.5°	712.6	712.5	734.6	762.3	771.1
135°	745.1	744.3	758.5	785.4	796.4
137.5°	775.4	773.8	783.8	809.2	816.4
140°	804.9	804.8	807.9	830.8	839.4
142.5°	829.8	832.8	832.0	851.0	857.3
145°	857.0	857.7	857.7	868.0	875.9
147.5°	878.2	881.2	880.4	882.8	889.8
150°	901.7	903.1	902.4	902.4	903.1
152.5°	919.8	922.1	920.5	922.1	921.3
155°	937.9	938.7	936.4	939.5	937.2
157.5°	953.8	953.8	950.8	954.6	950.8
160°	967.5	965.2	964.4	969.0	964.4
162.5°	979.6	976.6	975.8	980.3	975.0
165°	989.4	985.6	985.6	991.7	984.9
167.5°	997.8	994.0	993.2	1000.0	992.5
170°	1004.6	1000.0	1000.8	1006.8	999.3
172.5°	1009.1	1004.6	1005.3	1011.4	1003.1
175°	1012.1	1007.6	1008.4	1015.2	1006.1
177.5°	1014.4	1009.1	1010.6	1016.7	1007.6
180°	1012.1	1012.1	1012.1	1012.1	1012.1

(END OF REPORT)