

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013001

Luminaire Tested: S124DIP-B350D1035UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013001
REPORT IS A COMBINATION OF REPORTS P995741 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B350D1035UB2750-4F0-XX-W2A-F_4000K
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5536.0 lumens
Efficiency: N/A
Efficacy: 133.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013001

CATALOG NUMBER: S124DIP-B350D1035UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013001

CATALOG NUMBER: S124DIP-B350D1035UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27			
1	93	88	85	81	82	79	76	73	61	59	57	45	44	43	30	30	29	22			
2	84	77	71	66	75	69	64	60	54	50	47	40	38	36	27	26	24	19			
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21	16			
4	70	60	52	46	62	54	47	42	42	37	34	31	28	26	21	19	18	14			
5	64	53	45	40	57	48	41	36	37	33	29	28	25	22	19	17	16	12			
6	59	47	40	34	52	43	36	31	34	29	25	25	22	19	17	15	14	10			
7	54	43	35	30	48	38	32	27	30	26	22	23	20	17	16	14	12	9			
8	50	39	31	26	45	35	28	24	28	23	19	21	18	15	14	12	11	8			
9	47	35	28	23	42	32	25	21	25	21	17	19	16	13	13	11	10	7			
10	44	32	25	20	39	29	23	19	23	19	15	18	14	12	12	10	9	7			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4664	4664	4664
5°	4668	4530	4535
10°	4628	4404	4373
15°	4562	4255	4191
20°	4477	4092	4001
25°	4382	3922	3797
30°	4267	3737	3573
35°	4147	3548	3357
40°	4023	3344	3127
45°	3893	3141	2912
50°	3749	2943	2674
55°	3592	2711	2437
60°	3431	2458	2191
65°	3249	2197	1913
70°	3036	1881	1616
75°	2720	1517	1294
80°	2320	1097	910
85°	1797	610	490

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3893 cd/sqm

TEST NUMBER: P1013001

CATALOG NUMBER: S124DIP-B350D1035UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	1.0
10°-20°	151.9	2.7
20°-30°	223.5	4.0
30°-40°	259.8	4.7
40°-50°	259.8	4.7
50°-60°	227.2	4.1
60°-70°	168.7	3.0
70°-80°	95.7	1.7
80°-90°	30.1	0.5
90°-100°	43.6	0.8
100°-110°	287.2	5.2
110°-120°	548.4	9.9
120°-130°	696.2	12.6
130°-140°	744.8	13.5
140°-150°	696.4	12.6
150°-160°	561.6	10.1
160°-170°	362.2	6.5
170°-180°	124.8	2.3
0°-30°	429.3	7.8
0°-40°	689.1	12.4
0°-60°	1176.2	21.2
0°-90°	1470.7	26.6
90°-120°	879.2	15.9
90°-150°	3016.6	54.5
90°-180°	4065.0	73.4
0°-180°	5536.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	572	572	572	572	572	
5°	572	570	565	570	569	54
15°	544	542	535	538	537	153
25°	493	490	483	484	482	227
35°	424	421	414	411	409	265
45°	346	343	336	330	329	267
55°	262	260	254	248	246	234
65°	177	175	170	166	164	176
75°	94	92	90	88	88	100
85°	25	25	24	24	23	27
90°	3	14	22	28	30	4
95°	54	21	22	28	28	67
105°	296	302	307	315	280	310
115°	552	555	554	556	556	544
125°	776	780	778	781	782	693
135°	963	962	966	968	970	742
145°	1110	1113	1113	1114	1116	694
155°	1218	1218	1216	1219	1216	561
165°	1284	1279	1279	1287	1278	363
175°	1314	1308	1309	1318	1306	125
180°	1314	1314	1314	1314	1314	

TEST NUMBER: P1013001

CATALOG NUMBER: S124DIP-B350D1035UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	571.9	571.9	571.9	571.9	571.9
2.5°	573.8	572.4	567.4	571.9	571.5
5°	571.5	569.7	564.6	569.7	568.7
7.5°	567.4	565.5	560.0	564.2	563.7
10°	561.4	559.6	553.6	557.3	556.4
12.5°	553.6	551.8	545.4	549.5	548.1
15°	544.0	542.2	535.3	538.0	536.7
17.5°	533.0	530.7	524.3	526.1	525.2
20°	520.6	518.3	511.4	512.8	511.9
22.5°	507.3	504.1	497.2	500.0	498.2
25°	492.7	489.5	483.0	483.5	481.7
27.5°	476.2	473.0	467.0	466.1	463.8
30°	459.7	456.0	450.0	448.2	445.9
32.5°	442.2	439.0	432.6	430.3	428.0
35°	423.9	420.7	414.3	411.1	408.8
37.5°	404.7	401.9	395.0	391.8	388.6
40°	385.9	382.2	375.3	370.8	368.5
42.5°	365.7	363.9	356.1	350.6	349.2
45°	346.0	342.8	335.5	330.4	329.0
47.5°	325.4	323.1	316.2	310.7	307.1
50°	304.3	302.5	296.1	289.6	286.9
52.5°	283.7	281.4	274.5	269.0	265.3
55°	261.7	260.3	253.9	248.4	245.6
57.5°	241.1	239.7	233.3	227.8	225.0
60°	219.5	217.2	211.3	207.1	204.9
62.5°	198.4	196.6	190.2	186.5	184.2
65°	177.4	175.1	170.5	165.9	163.6
67.5°	155.8	154.0	149.4	144.8	144.4
70°	136.1	132.9	129.2	125.6	124.2
72.5°	115.0	111.8	109.1	106.3	104.9
75°	94.4	92.1	89.8	88.0	87.5
77.5°	74.2	73.3	71.0	70.6	69.2
80°	56.4	55.0	54.1	53.2	52.7
82.5°	39.0	38.5	38.5	38.0	37.6
85°	24.7	24.7	23.8	23.8	23.4
87.5°	11.9	11.5	11.0	11.0	11.0
90°	2.9	13.8	21.6	27.5	29.5
92.5°	14.7	12.8	20.6	26.5	26.5
95°	54.0	20.6	21.6	27.5	28.5
97.5°	103.2	124.8	21.6	26.5	27.5
100°	161.2	178.8	43.2	26.5	27.5
102.5°	226.0	237.8	249.6	28.5	28.5
105°	295.8	301.7	306.6	315.4	280.0
107.5°	359.6	362.6	369.5	374.4	378.3
110°	424.5	427.4	433.3	435.3	438.3

TEST NUMBER: P1013001

CATALOG NUMBER: S124DIP-B350D1035UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	487.4	493.3	495.2	494.3	498.2
115°	552.2	555.2	554.2	556.2	556.2
117.5°	610.2	614.1	617.1	616.1	616.1
120°	669.2	673.1	672.1	674.1	672.1
122.5°	724.2	726.2	728.1	729.1	727.1
125°	776.3	780.2	778.2	781.2	782.2
127.5°	826.4	827.4	832.3	831.3	830.3
130°	874.5	875.5	878.5	879.5	879.5
132.5°	918.8	920.7	924.7	925.6	924.7
135°	963.0	962.0	965.9	967.9	969.9
137.5°	1002.3	1002.3	1007.2	1009.2	1008.2
140°	1040.6	1042.6	1044.5	1047.5	1048.5
142.5°	1075.0	1078.9	1079.9	1081.9	1081.9
145°	1110.4	1113.3	1113.3	1114.3	1116.3
147.5°	1137.9	1143.8	1142.8	1143.8	1144.8
150°	1168.3	1172.3	1171.3	1171.3	1172.3
152.5°	1193.9	1196.8	1194.9	1196.8	1195.9
155°	1217.5	1218.5	1215.5	1219.4	1216.5
157.5°	1238.1	1238.1	1234.2	1239.1	1234.2
160°	1255.8	1252.9	1251.9	1257.8	1251.9
162.5°	1271.5	1267.6	1266.6	1272.5	1265.6
165°	1284.3	1279.4	1279.4	1287.2	1278.4
167.5°	1295.1	1290.2	1289.2	1298.1	1288.2
170°	1303.9	1298.1	1299.0	1306.9	1297.1
172.5°	1309.8	1303.9	1304.9	1312.8	1302.0
175°	1313.8	1307.9	1308.9	1317.7	1305.9
177.5°	1316.7	1309.8	1311.8	1319.7	1307.9
180°	1313.8	1313.8	1313.8	1313.8	1313.8

(END OF REPORT)