

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1025081

Luminaire Tested: S124DIP-B1195D1205UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1025081
REPORT IS A COMBINATION OF REPORTS P995486 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B1195D1205UB27-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9215.0 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1025081

CATALOG NUMBER: S124DIP-B1195D1205UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1025081

CATALOG NUMBER: S124DIP-B1195D1205UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	87	92	88	85	81	76	73	71	64	62	61	54	53	51
2	90	83	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37
4	75	64	56	50	70	60	53	47	52	46	42	44	40	37	37	34	32
5	69	57	49	43	64	54	46	41	46	41	36	40	35	32	34	30	28
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	24	22
8	55	42	34	29	51	40	33	28	35	29	25	30	25	22	26	22	19
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16146	16146	16146
5°	16159	15681	15700
10°	16022	15246	15139
15°	15792	14729	14506
20°	15499	14169	13850
25°	15168	13577	13145
30°	14770	12938	12371
35°	14357	12282	11622
40°	13928	11578	10826
45°	13476	10871	10081
50°	12977	10186	9257
55°	12435	9386	8438
60°	11879	8510	7585
65°	11244	7605	6624
70°	10512	6515	5593
75°	9418	5252	4480
80°	8024	3797	3151
85°	6236	2114	1696

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13476 cd/sqm

TEST NUMBER: P1025081

CATALOG NUMBER: S124DIP-B1195D1205UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.6	2.0
10°-20°	525.8	5.7
20°-30°	773.8	8.4
30°-40°	899.5	9.8
40°-50°	899.4	9.8
50°-60°	786.6	8.5
60°-70°	584.0	6.3
70°-80°	331.4	3.6
80°-90°	98.1	1.1
90°-100°	97.0	1.1
100°-110°	290.6	3.2
110°-120°	493.7	5.4
120°-130°	651.1	7.1
130°-140°	731.2	7.9
140°-150°	718.7	7.8
150°-160°	604.5	6.6
160°-170°	402.2	4.4
170°-180°	140.8	1.5
0°-30°	1486.2	16.1
0°-40°	2385.7	25.9
0°-60°	4071.7	44.2
0°-90°	5085.2	55.2
90°-120°	881.3	9.6
90°-150°	2982.3	32.4
90°-180°	4130.0	44.8
0°-180°	9215.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1980	1980	1980	1980	1980	
5°	1978	1972	1955	1972	1969	188
15°	1883	1877	1853	1863	1858	531
25°	1706	1694	1672	1674	1667	785
35°	1468	1456	1434	1423	1415	918
45°	1198	1187	1161	1144	1139	923
55°	906	901	879	860	850	811
65°	614	606	590	574	566	608
75°	327	319	311	305	303	347
85°	86	86	82	82	81	92
90°	4	16	25	32	34	11
95°	69	79	88	91	91	75
105°	268	269	274	277	281	284
115°	502	502	500	498	497	495
125°	731	731	730	728	725	652
135°	943	950	950	947	944	729
145°	1145	1150	1151	1150	1146	717
155°	1312	1312	1311	1316	1311	604
165°	1429	1425	1423	1430	1425	403
175°	1486	1480	1479	1487	1479	141
180°	1488	1488	1488	1488	1488	

TEST NUMBER: P1025081

CATALOG NUMBER: S124DIP-B1195D1205UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1980.0	1980.0	1980.0	1980.0	1980.0
2.5°	1986.3	1981.6	1964.1	1980.0	1978.4
5°	1978.4	1972.0	1954.6	1972.0	1968.9
7.5°	1964.1	1957.8	1938.7	1953.0	1951.4
10°	1943.5	1937.1	1916.5	1929.2	1926.0
12.5°	1916.5	1910.2	1888.0	1902.2	1897.5
15°	1883.2	1876.9	1853.1	1862.6	1857.8
17.5°	1845.1	1837.2	1815.0	1821.3	1818.2
20°	1802.3	1794.4	1770.6	1775.3	1772.1
22.5°	1756.3	1745.2	1721.4	1730.9	1724.5
25°	1705.5	1694.4	1672.2	1673.8	1667.4
27.5°	1648.4	1637.3	1616.7	1613.5	1605.6
30°	1591.3	1578.6	1558.0	1551.6	1543.7
32.5°	1531.0	1519.9	1497.7	1489.7	1481.8
35°	1467.5	1456.4	1434.2	1423.1	1415.2
37.5°	1400.9	1391.4	1367.6	1356.5	1345.4
40°	1335.9	1323.2	1299.4	1283.5	1275.6
42.5°	1266.0	1259.7	1232.7	1213.7	1208.9
45°	1197.8	1186.7	1161.3	1143.9	1139.1
47.5°	1126.4	1118.5	1094.7	1075.7	1063.0
50°	1053.4	1047.1	1024.9	1002.7	993.2
52.5°	982.1	974.1	950.3	931.3	918.6
55°	905.9	901.1	878.9	859.9	850.4
57.5°	834.5	829.8	807.5	788.5	779.0
60°	759.9	752.0	731.4	717.1	709.2
62.5°	687.0	680.6	658.4	645.7	637.8
65°	614.0	606.1	590.2	574.3	566.4
67.5°	539.4	533.1	517.2	501.3	499.8
70°	471.2	460.1	447.4	434.7	429.9
72.5°	398.2	387.1	377.6	368.1	363.3
75°	326.8	318.9	311.0	304.6	303.0
77.5°	257.0	253.8	245.9	244.3	239.6
80°	195.1	190.4	187.2	184.0	182.4
82.5°	134.9	133.3	133.3	131.7	130.1
85°	85.7	85.7	82.5	82.5	80.9
87.5°	41.2	39.7	38.1	38.1	38.1
90°	3.5	16.1	25.3	32.2	34.5
92.5°	29.9	44.9	50.7	54.1	55.3
95°	69.1	79.4	87.5	90.9	90.9
97.5°	110.5	119.7	128.9	133.5	133.5
100°	161.2	165.8	176.1	178.4	178.4
102.5°	214.1	215.3	224.5	227.9	229.1
105°	268.2	269.4	274.0	277.4	280.9
107.5°	324.6	325.8	326.9	331.5	330.4
110°	382.2	384.5	383.3	381.0	384.5

TEST NUMBER: P1025081

CATALOG NUMBER: S124DIP-B1195D1205UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	442.0	442.0	439.7	439.7	439.7
115°	501.9	501.9	499.6	498.4	497.3
117.5°	558.3	558.3	557.2	553.7	550.2
120°	614.7	619.3	615.9	610.1	612.4
122.5°	673.4	674.6	673.4	670.0	664.2
125°	731.0	731.0	729.8	727.5	725.2
127.5°	782.8	786.2	783.9	781.6	780.5
130°	838.0	841.5	841.5	839.2	834.6
132.5°	894.4	896.7	895.6	893.3	892.1
135°	942.8	949.7	949.7	947.4	943.9
137.5°	996.9	1000.3	1002.6	999.2	1000.3
140°	1051.0	1053.3	1053.3	1052.1	1051.0
142.5°	1100.5	1102.8	1101.6	1101.6	1101.6
145°	1145.4	1150.0	1151.1	1150.0	1146.5
147.5°	1191.4	1197.2	1196.0	1194.9	1193.7
150°	1232.9	1237.5	1237.5	1237.5	1236.3
152.5°	1272.0	1274.3	1275.5	1278.9	1275.5
155°	1312.3	1312.3	1311.1	1315.7	1311.1
157.5°	1346.8	1344.5	1344.5	1348.0	1344.5
160°	1376.8	1375.6	1374.5	1377.9	1372.2
162.5°	1404.4	1400.9	1399.8	1406.7	1400.9
165°	1428.6	1425.1	1422.8	1429.7	1425.1
167.5°	1448.1	1443.5	1443.5	1450.4	1443.5
170°	1464.2	1458.5	1459.6	1466.5	1458.5
172.5°	1475.8	1471.2	1471.2	1479.2	1471.2
175°	1486.1	1480.4	1479.2	1487.3	1479.2
177.5°	1490.7	1485.0	1485.0	1493.0	1483.8
180°	1488.4	1488.4	1488.4	1488.4	1488.4

(END OF REPORT)