

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1025120

Luminaire Tested: S124DIP-B1195D365UB27-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1025120
REPORT IS A COMBINATION OF REPORTS P995540 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B1195D365UB27-4F0-XX-W2A-A1
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6549.0 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1025120

CATALOG NUMBER: S124DIP-B1195D365UB27-4F0-XX-W2A-A1

Luminous Intensity Polar Plot





TEST NUMBER: P1025120

CATALOG NUMBER: S124DIP-B1195D365UB27-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	114	114	114	114	110	110	110	110	100	100	100	92	92	92	84	84	84	81			
1	105	101	97	93	100	96	93	90	89	86	83	82	80	78	75	74	72	69			
2	96	88	82	77	92	85	79	74	78	74	70	72	69	65	67	64	61	58			
3	88	78	71	65	84	75	68	63	69	64	59	64	60	56	59	56	53	50			
4	81	70	61	55	77	67	59	54	62	56	51	58	52	48	53	49	46	43			
5	74	62	54	48	71	60	52	47	56	49	44	52	46	42	48	44	40	38			
6	69	56	48	42	66	54	46	41	51	44	39	47	41	37	44	39	35	33			
7	64	51	43	37	61	49	42	36	46	39	35	43	37	33	40	35	32	29			
8	59	47	39	33	57	45	38	32	42	36	31	40	34	30	37	32	28	26			
9	55	43	35	30	53	41	34	29	39	32	28	36	31	27	34	29	26	24			
10	52	39	32	27	50	38	31	26	36	30	25	34	28	24	32	27	23	22			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15615	15615	15615	15615
5°	15576	17914	15667	13460
10°	15459	20900	15577	11809
15°	15273	24094	15380	10567
20°	15076	26126	15185	9474
25°	14787	25827	14928	8667
30°	14505	21347	14681	8251
35°	14109	15908	14264	8000
40°	13647	11984	13778	7877
45°	12941	9618	13102	7709
50°	12097	8103	12274	7630
55°	11106	7052	11281	7540
60°	10144	6211	10441	7415
65°	9239	5343	9327	7106
70°	8177	4396	8353	6543
75°	7132	3378	7086	5559
80°	5610	2220	5548	4220
85°	3697	998	3464	2461

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 20191 cd/sqm

TEST NUMBER: P1025120

CATALOG NUMBER: S124DIP-B1195D365UB27-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.4	2.8
10°-20°	575.2	8.8
20°-30°	913.8	14.0
30°-40°	1015.4	15.5
40°-50°	923.4	14.1
50°-60°	754.6	11.5
60°-70°	538.6	8.2
70°-80°	296.4	4.5
80°-90°	81.1	1.2
90°-100°	29.7	0.5
100°-110°	89.0	1.4
110°-120°	151.1	2.3
120°-130°	199.3	3.0
130°-140°	223.8	3.4
140°-150°	220.0	3.4
150°-160°	185.0	2.8
160°-170°	123.1	1.9
170°-180°	43.1	0.7
0°-30°	1675.4	25.6
0°-40°	2690.8	41.1
0°-60°	4368.8	66.7
0°-90°	5285.0	80.7
90°-120°	269.7	4.1
90°-150°	912.8	13.9
90°-180°	1264.0	19.3
0°-180°	6549.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1915	1915	1915	1915	1915	
5°	1907	2246	1918	1688	1907	181
15°	1821	3086	1834	1353	1821	514
25°	1663	3276	1678	1099	1663	766
35°	1442	1937	1458	974	1442	901
45°	1150	1087	1164	871	1150	887
55°	809	711	822	760	809	728
65°	504	457	509	608	504	498
75°	248	228	246	376	248	260
85°	51	48	48	117	51	59
90°	1	11	1	11	1	5
95°	21	28	21	28	21	23
105°	82	86	82	86	82	87
115°	154	152	154	152	154	152
125°	224	222	224	222	224	199
135°	289	289	289	289	289	223
145°	351	351	351	351	351	219
155°	402	401	402	401	402	185
165°	437	436	437	436	437	123
175°	455	453	455	453	455	43
180°	456	456	456	456	456	

TEST NUMBER: P1025120

CATALOG NUMBER: S124DIP-B1195D365UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9
2.5°	1914.9	1933.9	1941.9	1948.2	1968.8	1975.2	1976.8	1986.3	1994.2	1995.8	1995.8
5°	1907.0	1937.1	1960.9	1983.1	2016.4	2030.7	2048.2	2067.2	2092.6	2108.4	2116.4
7.5°	1894.3	1938.7	1975.2	2013.3	2059.3	2087.8	2103.7	2154.4	2189.4	2217.9	2252.8
10°	1875.2	1932.3	1984.7	2040.2	2105.3	2140.2	2175.1	2236.9	2286.1	2341.7	2386.1
12.5°	1846.7	1921.2	1984.7	2062.4	2143.3	2184.6	2225.8	2333.7	2390.8	2440.0	2519.3
15°	1821.3	1895.9	1986.3	2065.6	2165.6	2227.4	2287.7	2357.5	2447.9	2554.2	2630.4
17.5°	1792.7	1886.3	1970.4	2081.5	2192.5	2251.2	2300.4	2408.3	2535.2	2639.9	2709.7
20°	1753.1	1848.3	1959.3	2076.7	2208.4	2254.4	2319.4	2463.8	2578.0	2681.2	2795.4
22.5°	1707.1	1818.1	1935.5	2048.2	2184.6	2281.4	2352.8	2479.7	2617.7	2736.7	2865.2
25°	1662.6	1783.2	1886.3	2040.2	2184.6	2249.6	2330.5	2481.3	2632.0	2776.4	2908.0
27.5°	1615.0	1727.7	1867.3	1989.5	2152.9	2224.3	2311.5	2476.5	2636.7	2781.1	2922.3
30°	1562.7	1683.3	1799.1	1943.4	2102.1	2194.1	2275.0	2454.3	2617.7	2768.4	2900.1
32.5°	1504.0	1618.2	1742.0	1878.4	2045.0	2138.6	2240.1	2424.2	2598.7	2728.8	2830.3
35°	1442.1	1557.9	1665.8	1805.4	1976.8	2070.4	2168.7	2371.8	2544.7	2651.0	2709.7
37.5°	1373.9	1483.4	1589.7	1727.7	1899.0	1999.0	2098.9	2295.6	2459.1	2547.9	2532.0
40°	1308.9	1407.2	1505.6	1635.7	1814.9	1921.2	2008.5	2206.8	2349.6	2387.7	2335.3
42.5°	1234.3	1318.4	1413.6	1546.8	1721.3	1821.3	1930.8	2111.6	2217.9	2202.0	2113.2
45°	1150.2	1224.8	1320.0	1445.3	1623.0	1726.1	1818.1	1989.5	2067.2	2027.5	1865.7
47.5°	1069.3	1142.3	1220.0	1345.3	1518.3	1605.5	1699.1	1853.0	1897.4	1813.4	1651.5
50°	982.0	1042.3	1123.2	1242.2	1404.0	1496.1	1573.8	1697.5	1713.4	1610.3	1442.1
52.5°	898.0	948.7	1026.5	1143.9	1294.6	1367.6	1443.7	1553.2	1540.5	1434.2	1272.4
55°	809.1	856.7	928.1	1036.0	1169.2	1239.0	1304.1	1400.9	1373.9	1264.4	1123.2
57.5°	734.5	767.9	837.7	937.6	1047.1	1123.2	1178.8	1254.9	1213.7	1104.2	972.5
60°	648.9	690.1	748.8	829.7	937.6	988.4	1037.6	1088.3	1059.8	955.1	837.7
62.5°	571.1	602.9	653.6	731.4	815.5	861.5	913.8	945.5	917.0	820.2	721.9
65°	504.5	529.9	569.5	633.0	713.9	752.0	782.1	812.3	788.5	698.1	626.7
67.5°	431.5	453.7	487.1	537.8	606.0	633.0	661.6	682.2	655.2	594.9	525.1
70°	366.5	382.3	414.1	452.1	499.7	525.1	548.9	569.5	545.8	495.0	442.6
72.5°	299.8	312.5	341.1	368.1	410.9	428.4	445.8	461.7	453.7	406.1	363.3
75°	247.5	252.3	271.3	293.5	320.5	339.5	352.2	361.7	355.4	317.3	290.3
77.5°	187.2	193.6	207.8	225.3	249.1	260.2	268.1	277.6	269.7	239.6	220.5
80°	136.4	138.0	146.0	161.8	177.7	179.3	187.2	199.9	195.1	174.5	160.2
82.5°	87.3	92.0	95.2	104.7	115.8	119.0	123.7	126.9	125.3	112.6	107.9
85°	50.8	50.8	53.9	60.3	63.5	68.2	69.8	71.4	74.6	66.6	61.9
87.5°	22.2	23.8	23.8	25.4	28.6	28.6	30.1	31.7	33.3	31.7	27.0
90°	1.1	1.9	2.8	3.6	4.5	4.9	5.2	5.9	6.5	7.2	7.8
92.5°	9.2	10.2	11.2	12.2	13.2	13.7	13.9	14.3	14.7	15.1	15.5
95°	21.1	21.8	22.5	23.2	23.9	24.3	24.6	25.1	25.7	26.2	26.8
97.5°	33.8	34.4	35.0	35.7	36.3	36.6	36.9	37.6	38.2	38.9	39.5
100°	49.3	49.6	49.9	50.2	50.5	50.7	51.1	51.8	52.5	53.2	53.9
102.5°	65.5	65.6	65.7	65.8	65.9	65.9	66.2	66.8	67.5	68.1	68.7
105°	82.1	82.2	82.2	82.3	82.4	82.4	82.6	82.9	83.2	83.6	83.9
107.5°	99.4	99.5	99.5	99.6	99.7	99.7	99.7	99.8	99.9	100.0	100.1
110°	117.0	117.2	117.3	117.5	117.6	117.7	117.7	117.6	117.5	117.4	117.3

TEST NUMBER: P1025120

CATALOG NUMBER: S124DIP-B1195D365UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	135.3	135.3	135.3	135.3	135.3	135.3	135.2	135.1	134.9	134.8	134.6
115°	153.6	153.6	153.6	153.6	153.6	153.6	153.5	153.4	153.2	153.1	152.9
117.5°	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.8	170.7	170.6	170.5
120°	188.1	188.4	188.8	189.1	189.4	189.6	189.5	189.2	189.0	188.7	188.5
122.5°	206.1	206.2	206.3	206.4	206.5	206.5	206.5	206.4	206.3	206.2	206.1
125°	223.7	223.7	223.7	223.7	223.7	223.7	223.7	223.6	223.5	223.5	223.4
127.5°	239.6	239.8	240.0	240.3	240.5	240.6	240.5	240.4	240.2	240.1	239.9
130°	256.5	256.7	257.0	257.2	257.5	257.6	257.6	257.6	257.6	257.6	257.6
132.5°	273.8	274.0	274.1	274.3	274.4	274.5	274.5	274.4	274.3	274.2	274.1
135°	288.6	289.1	289.5	290.0	290.5	290.7	290.7	290.7	290.7	290.7	290.7
137.5°	305.1	305.3	305.6	305.8	306.1	306.2	306.3	306.4	306.6	306.7	306.9
140°	321.7	321.9	322.0	322.2	322.3	322.4	322.4	322.4	322.4	322.4	322.4
142.5°	336.8	337.0	337.1	337.3	337.4	337.5	337.5	337.4	337.3	337.3	337.2
145°	350.6	350.9	351.2	351.5	351.8	352.0	352.0	352.1	352.2	352.2	352.3
147.5°	364.7	365.1	365.5	365.8	366.2	366.4	366.4	366.3	366.2	366.2	366.1
150°	377.3	377.6	378.0	378.3	378.6	378.8	378.8	378.8	378.8	378.8	378.8
152.5°	389.3	389.5	389.6	389.8	389.9	390.0	390.0	390.1	390.2	390.3	390.4
155°	401.7	401.7	401.7	401.7	401.7	401.7	401.7	401.6	401.5	401.4	401.3
157.5°	412.2	412.0	411.9	411.7	411.6	411.5	411.5	411.5	411.5	411.5	411.5
160°	421.4	421.3	421.2	421.1	421.0	421.0	421.0	420.9	420.8	420.8	420.7
162.5°	429.8	429.6	429.4	429.1	428.9	428.8	428.8	428.7	428.6	428.5	428.4
165°	437.2	437.0	436.8	436.5	436.3	436.2	436.1	436.0	435.8	435.7	435.5
167.5°	443.2	442.9	442.6	442.3	442.0	441.8	441.8	441.8	441.8	441.8	441.8
170°	448.2	447.8	447.4	447.0	446.6	446.4	446.4	446.5	446.6	446.7	446.8
172.5°	451.7	451.4	451.1	450.8	450.5	450.3	450.3	450.3	450.3	450.3	450.3
175°	454.9	454.5	454.1	453.7	453.3	453.1	453.1	453.0	452.9	452.8	452.7
177.5°	456.3	455.9	455.5	455.1	454.7	454.5	454.5	454.5	454.5	454.5	454.5
180°	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6

TEST NUMBER: P1025120

CATALOG NUMBER: S124DIP-B1195D365UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9
2.5°	2000.6	2029.1	2041.8	2045.0	2062.4	2051.3	2056.1	2054.5	2067.2	2068.8	2068.8
5°	2146.5	2179.8	2190.9	2206.8	2230.6	2236.9	2232.2	2241.7	2259.2	2246.5	2265.5
7.5°	2300.4	2336.9	2362.3	2397.2	2405.1	2425.7	2438.4	2449.5	2452.7	2454.3	2457.5
10°	2443.2	2489.2	2524.1	2582.8	2595.5	2606.6	2662.1	2639.9	2668.5	2659.0	2662.1
12.5°	2559.0	2649.4	2678.0	2776.4	2785.9	2823.9	2820.8	2855.7	2862.0	2874.7	2862.0
15°	2711.3	2816.0	2862.0	2917.5	2949.3	2993.7	3001.6	3049.2	3068.3	3085.7	3068.3
17.5°	2850.9	2906.4	3023.8	3068.3	3088.9	3112.7	3173.0	3190.4	3219.0	3207.9	3239.6
20°	2920.7	3000.0	3123.8	3199.9	3231.7	3253.9	3304.7	3331.6	3342.7	3342.7	3345.9
22.5°	2982.6	3096.8	3188.8	3276.1	3304.7	3320.5	3350.7	3371.3	3376.0	3379.2	3382.4
25°	3038.1	3141.2	3215.8	3265.0	3276.1	3276.1	3293.5	3280.9	3260.2	3276.1	3285.6
27.5°	3038.1	3111.1	3144.4	3161.9	3161.9	3119.0	3093.6	3041.3	2996.9	2984.2	3012.7
30°	2987.4	3020.7	2974.7	2931.8	2898.5	2870.0	2770.0	2690.7	2674.8	2663.7	2706.5
32.5°	2870.0	2827.1	2736.7	2612.9	2563.8	2498.7	2421.0	2360.7	2324.2	2311.5	2302.0
35°	2662.1	2551.1	2433.7	2267.1	2232.2	2149.7	2043.4	1999.0	1938.7	1937.1	1957.7
37.5°	2435.3	2263.9	2137.0	1978.3	1929.2	1841.9	1742.0	1696.0	1654.7	1623.0	1661.1
40°	2170.3	2021.2	1827.6	1697.5	1627.7	1581.7	1497.6	1446.9	1427.8	1412.0	1435.8
42.5°	1922.8	1759.4	1608.7	1475.4	1418.3	1366.0	1310.4	1261.3	1247.0	1245.4	1262.8
45°	1676.9	1516.7	1377.1	1262.8	1226.4	1194.6	1140.7	1126.4	1102.6	1086.7	1094.7
47.5°	1480.2	1315.2	1199.4	1112.1	1080.4	1053.4	1018.5	994.7	974.1	967.8	977.3
50°	1286.6	1175.6	1056.6	983.6	959.8	934.4	907.5	885.3	875.7	869.4	875.7
52.5°	1131.2	1012.2	931.3	872.6	848.8	829.7	810.7	801.2	788.5	791.7	798.0
55°	991.6	886.8	818.6	775.8	761.5	753.6	729.8	718.7	713.9	710.7	713.9
57.5°	859.9	783.7	733.0	696.5	677.4	672.7	653.6	653.6	648.9	644.1	645.7
60°	755.2	690.1	640.9	612.4	609.2	601.3	588.6	587.0	575.9	580.7	582.2
62.5°	648.9	596.5	563.2	545.8	534.6	531.5	523.5	522.0	517.2	518.8	515.6
65°	564.8	522.0	488.6	474.4	469.6	468.0	461.7	456.9	453.7	456.9	453.7
67.5°	480.7	452.1	426.8	412.5	406.1	404.6	399.8	396.6	398.2	393.4	396.6
70°	401.4	372.8	357.0	349.0	345.9	341.1	341.1	341.1	341.1	337.9	336.3
72.5°	337.9	309.4	298.3	293.5	290.3	288.7	284.0	285.6	284.0	282.4	288.7
75°	268.1	250.7	239.6	234.8	238.0	233.2	228.5	231.6	226.9	228.5	234.8
77.5°	203.1	195.1	188.8	185.6	182.4	179.3	179.3	176.1	176.1	176.1	176.1
80°	147.5	146.0	134.9	133.3	133.3	130.1	130.1	130.1	130.1	128.5	130.1
82.5°	98.4	96.8	93.6	92.0	88.8	90.4	90.4	87.3	87.3	85.7	87.3
85°	57.1	57.1	53.9	52.4	50.8	52.4	49.2	47.6	49.2	47.6	49.2
87.5°	27.0	23.8	25.4	23.8	20.6	22.2	19.0	20.6	19.0	17.5	20.6
90°	8.3	8.7	9.2	9.7	9.9	10.0	10.1	10.3	10.4	10.6	10.4
92.5°	15.7	16.0	16.2	16.5	16.6	16.6	16.7	16.8	16.8	16.9	16.8
95°	27.0	27.2	27.5	27.7	27.8	27.8	27.8	27.8	27.8	27.8	27.8
97.5°	39.8	40.1	40.4	40.7	40.9	40.9	40.9	40.9	40.9	40.9	40.9
100°	54.1	54.2	54.4	54.5	54.6	54.6	54.6	54.6	54.6	54.6	54.6
102.5°	68.9	69.2	69.4	69.7	69.8	69.8	69.9	70.0	70.0	70.1	70.0
105°	84.1	84.3	84.6	84.8	84.9	85.0	85.3	85.5	85.8	86.0	85.8
107.5°	100.4	100.7	101.0	101.3	101.5	101.5	101.4	101.3	101.2	101.1	101.2
110°	117.1	117.0	116.8	116.7	116.6	116.7	117.0	117.2	117.5	117.7	117.5

TEST NUMBER: P1025120

CATALOG NUMBER: S124DIP-B1195D365UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	134.6	134.6	134.6	134.6	134.6	134.6	134.6	134.6	134.6	134.6	134.6
115°	152.8	152.8	152.7	152.6	152.6	152.6	152.5	152.4	152.3	152.2	152.3
117.5°	170.3	170.1	169.8	169.6	169.5	169.4	169.1	168.9	168.6	168.4	168.6
120°	188.1	187.7	187.3	186.9	186.7	186.8	186.9	187.1	187.2	187.4	187.2
122.5°	205.9	205.7	205.4	205.2	205.1	204.9	204.5	204.1	203.7	203.3	203.7
125°	223.2	223.1	222.9	222.8	222.7	222.6	222.5	222.3	222.2	222.0	222.2
127.5°	239.7	239.6	239.4	239.3	239.2	239.2	239.1	239.0	239.0	238.9	239.0
130°	257.4	257.3	257.1	257.0	256.9	256.7	256.4	256.1	255.7	255.4	255.7
132.5°	273.9	273.8	273.6	273.5	273.4	273.4	273.3	273.2	273.2	273.1	273.2
135°	290.5	290.4	290.2	290.1	290.0	289.9	289.6	289.4	289.1	288.9	289.1
137.5°	306.7	306.4	306.2	305.9	305.8	305.8	305.9	306.0	306.1	306.2	306.1
140°	322.3	322.2	322.1	322.0	322.0	322.0	321.9	321.8	321.8	321.7	321.8
142.5°	337.2	337.2	337.2	337.2	337.2	337.2	337.2	337.2	337.2	337.2	337.2
145°	352.2	352.2	352.1	352.0	352.0	351.9	351.6	351.4	351.1	350.9	351.1
147.5°	366.0	365.9	365.8	365.7	365.7	365.7	365.6	365.5	365.5	365.4	365.5
150°	378.8	378.8	378.8	378.8	378.8	378.8	378.7	378.6	378.5	378.4	378.5
152.5°	390.6	390.8	391.1	391.3	391.4	391.3	391.1	390.8	390.6	390.4	390.6
155°	401.6	401.9	402.2	402.5	402.7	402.5	402.2	401.9	401.6	401.3	401.6
157.5°	411.7	412.0	412.2	412.5	412.6	412.5	412.2	412.0	411.7	411.5	411.7
160°	420.9	421.1	421.4	421.6	421.7	421.5	421.1	420.8	420.4	420.0	420.4
162.5°	428.9	429.3	429.8	430.3	430.5	430.3	429.9	429.6	429.2	428.8	429.2
165°	436.0	436.4	436.9	437.4	437.6	437.4	437.1	436.8	436.5	436.2	436.5
167.5°	442.3	442.7	443.2	443.7	443.9	443.7	443.2	442.7	442.3	441.8	442.3
170°	447.3	447.7	448.2	448.7	448.9	448.6	448.1	447.5	447.0	446.4	447.0
172.5°	450.8	451.4	451.9	452.4	452.7	452.4	451.9	451.4	450.8	450.3	450.8
175°	453.3	453.8	454.4	454.9	455.2	454.9	454.4	453.8	453.3	452.7	453.3
177.5°	455.1	455.6	456.2	456.7	457.0	456.7	456.1	455.4	454.8	454.2	454.8
180°	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6

TEST NUMBER: P1025120

CATALOG NUMBER: S124DIP-B1195D365UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9
2.5°	2065.6	2060.8	2054.5	2054.5	2046.6	2046.6	2033.9	2011.7	1992.6	1986.3	1989.5
5°	2241.7	2243.3	2233.8	2225.8	2211.6	2200.5	2179.8	2140.2	2127.5	2102.1	2084.6
7.5°	2443.2	2436.8	2419.4	2406.7	2403.5	2378.1	2333.7	2286.1	2248.1	2222.7	2186.2
10°	2670.1	2644.7	2619.3	2611.4	2592.3	2549.5	2498.7	2446.4	2394.0	2338.5	2276.6
12.5°	2860.4	2811.3	2809.7	2790.6	2754.1	2730.3	2670.1	2595.5	2505.1	2443.2	2373.4
15°	3065.1	3019.1	2981.0	2946.1	2928.7	2858.8	2808.1	2714.5	2606.6	2540.0	2492.4
17.5°	3211.0	3190.4	3125.4	3109.5	3085.7	3004.8	2923.9	2831.9	2738.3	2644.7	2516.2
20°	3328.4	3315.8	3272.9	3250.7	3212.6	3149.2	3050.8	2944.5	2836.6	2703.4	2582.8
22.5°	3379.2	3363.4	3328.4	3309.4	3285.6	3231.7	3147.6	3027.0	2885.8	2766.8	2638.3
25°	3279.3	3307.8	3298.3	3290.4	3280.9	3249.1	3185.7	3079.4	2941.3	2806.5	2646.3
27.5°	3054.0	3103.2	3150.8	3157.1	3173.0	3185.7	3160.3	3084.1	2968.3	2825.5	2649.4
30°	2751.0	2773.2	2870.0	2898.5	2920.7	3001.6	3049.2	3030.2	2941.3	2812.8	2651.0
32.5°	2362.3	2421.0	2519.3	2587.6	2647.8	2738.3	2862.0	2911.2	2879.5	2774.8	2614.5
35°	1994.2	2064.0	2178.2	2265.5	2325.8	2454.3	2600.3	2706.5	2746.2	2693.9	2551.1
37.5°	1692.8	1776.9	1878.4	1911.7	1981.5	2140.2	2341.7	2489.2	2586.0	2590.7	2479.7
40°	1465.9	1508.7	1589.7	1640.4	1708.6	1841.9	2038.6	2233.8	2379.7	2428.9	2370.2
42.5°	1273.9	1307.3	1367.6	1429.4	1491.3	1592.8	1773.7	1956.1	2152.9	2251.2	2249.6
45°	1121.6	1156.5	1197.8	1248.6	1291.4	1400.9	1543.7	1730.9	1900.6	2052.9	2091.0
47.5°	988.4	1018.5	1069.3	1091.5	1120.1	1223.2	1346.9	1521.4	1697.5	1872.1	1916.5
50°	890.0	915.4	950.3	964.6	996.3	1072.5	1174.0	1315.2	1510.3	1670.6	1753.1
52.5°	801.2	820.2	847.2	858.3	880.5	937.6	1029.6	1140.7	1302.5	1467.5	1583.3
55°	725.0	737.7	756.8	769.4	785.3	836.1	904.3	1004.2	1143.9	1286.6	1399.3
57.5°	653.6	663.2	682.2	688.5	701.2	740.9	788.5	872.6	1001.1	1128.0	1237.5
60°	587.0	593.3	604.5	618.7	628.2	655.2	699.6	769.4	872.6	988.4	1077.2
62.5°	523.5	533.1	536.2	542.6	550.5	575.9	610.8	661.6	752.0	847.2	940.8
65°	458.5	466.4	472.8	474.4	482.3	501.3	533.1	577.5	636.2	718.7	805.9
67.5°	398.2	403.0	406.1	412.5	420.4	429.9	455.3	488.6	542.6	609.2	679.0
70°	342.7	342.7	347.4	349.0	358.5	369.7	380.8	412.5	460.1	514.0	561.6
72.5°	282.4	290.3	288.7	296.7	295.1	303.0	317.3	337.9	372.8	415.7	461.7
75°	230.0	234.8	234.8	234.8	238.0	244.3	252.3	271.3	298.3	333.2	360.1
77.5°	179.3	182.4	182.4	182.4	184.0	190.4	198.3	211.0	230.0	250.7	266.5
80°	128.5	131.7	131.7	134.9	134.9	136.4	144.4	150.7	160.2	176.1	192.0
82.5°	87.3	88.8	92.0	92.0	90.4	93.6	95.2	101.5	111.1	114.2	125.3
85°	47.6	49.2	50.8	50.8	52.4	55.5	53.9	60.3	60.3	66.6	69.8
87.5°	19.0	22.2	22.2	20.6	22.2	22.2	22.2	25.4	27.0	28.6	27.0
90°	10.3	10.1	10.0	9.9	9.7	9.2	8.7	8.3	7.8	7.2	6.5
92.5°	16.8	16.7	16.6	16.6	16.5	16.2	16.0	15.7	15.5	15.1	14.7
95°	27.8	27.8	27.8	27.8	27.7	27.5	27.2	27.0	26.8	26.2	25.7
97.5°	40.9	40.9	40.9	40.9	40.7	40.4	40.1	39.8	39.5	38.9	38.2
100°	54.6	54.6	54.6	54.6	54.5	54.4	54.2	54.1	53.9	53.2	52.5
102.5°	70.0	69.9	69.8	69.8	69.7	69.4	69.2	68.9	68.7	68.1	67.5
105°	85.5	85.3	85.0	84.9	84.8	84.6	84.3	84.1	83.9	83.6	83.2
107.5°	101.3	101.4	101.5	101.5	101.3	101.0	100.7	100.4	100.1	100.0	99.9
110°	117.2	117.0	116.7	116.6	116.7	116.8	117.0	117.1	117.3	117.4	117.5

TEST NUMBER: P1025120

CATALOG NUMBER: S124DIP-B1195D365UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	134.6	134.6	134.6	134.6	134.6	134.6	134.6	134.6	134.6	134.8	134.9
115°	152.4	152.5	152.6	152.6	152.6	152.7	152.8	152.8	152.9	153.1	153.2
117.5°	168.9	169.1	169.4	169.5	169.6	169.8	170.1	170.3	170.5	170.6	170.7
120°	187.1	186.9	186.8	186.7	186.9	187.3	187.7	188.1	188.5	188.7	189.0
122.5°	204.1	204.5	204.9	205.1	205.2	205.4	205.7	205.9	206.1	206.2	206.3
125°	222.3	222.5	222.6	222.7	222.8	222.9	223.1	223.2	223.4	223.5	223.5
127.5°	239.0	239.1	239.2	239.2	239.3	239.4	239.6	239.7	239.9	240.1	240.2
130°	256.1	256.4	256.7	256.9	257.0	257.1	257.3	257.4	257.6	257.6	257.6
132.5°	273.2	273.3	273.4	273.4	273.5	273.6	273.8	273.9	274.1	274.2	274.3
135°	289.4	289.6	289.9	290.0	290.1	290.2	290.4	290.5	290.7	290.7	290.7
137.5°	306.0	305.9	305.8	305.8	305.9	306.2	306.4	306.7	306.9	306.7	306.6
140°	321.8	321.9	322.0	322.0	322.0	322.1	322.2	322.3	322.4	322.4	322.4
142.5°	337.2	337.2	337.2	337.2	337.2	337.2	337.2	337.2	337.2	337.3	337.3
145°	351.4	351.6	351.9	352.0	352.0	352.1	352.2	352.2	352.3	352.2	352.2
147.5°	365.5	365.6	365.7	365.7	365.7	365.8	365.9	366.0	366.1	366.2	366.2
150°	378.6	378.7	378.8	378.8	378.8	378.8	378.8	378.8	378.8	378.8	378.8
152.5°	390.8	391.1	391.3	391.4	391.3	391.1	390.8	390.6	390.4	390.3	390.2
155°	401.9	402.2	402.5	402.7	402.5	402.2	401.9	401.6	401.3	401.4	401.5
157.5°	412.0	412.2	412.5	412.6	412.5	412.2	412.0	411.7	411.5	411.5	411.5
160°	420.8	421.1	421.5	421.7	421.6	421.4	421.1	420.9	420.7	420.8	420.8
162.5°	429.6	429.9	430.3	430.5	430.3	429.8	429.3	428.9	428.4	428.5	428.6
165°	436.8	437.1	437.4	437.6	437.4	436.9	436.4	436.0	435.5	435.7	435.8
167.5°	442.7	443.2	443.7	443.9	443.7	443.2	442.7	442.3	441.8	441.8	441.8
170°	447.5	448.1	448.6	448.9	448.7	448.2	447.7	447.3	446.8	446.7	446.6
172.5°	451.4	451.9	452.4	452.7	452.4	451.9	451.4	450.8	450.3	450.3	450.3
175°	453.8	454.4	454.9	455.2	454.9	454.4	453.8	453.3	452.7	452.8	452.9
177.5°	455.4	456.1	456.7	457.0	456.7	456.2	455.6	455.1	454.5	454.5	454.5
180°	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6

TEST NUMBER: P1025120

CATALOG NUMBER: S124DIP-B1195D365UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9
2.5°	1975.2	1968.8	1964.1	1964.1	1949.8	1935.5	1927.6	1924.4	1921.2	1908.5	1891.1
5°	2056.1	2035.5	2021.2	2006.9	1983.1	1957.7	1932.3	1918.1	1897.4	1868.9	1848.3
7.5°	2146.5	2097.3	2081.5	2064.0	2016.4	1973.6	1938.7	1908.5	1875.2	1838.7	1802.2
10°	2222.7	2170.3	2135.4	2105.3	2043.4	1986.3	1933.9	1889.5	1846.7	1799.1	1754.7
12.5°	2295.6	2221.1	2184.6	2140.2	2075.1	1992.6	1924.4	1868.9	1805.4	1756.2	1702.3
15°	2397.2	2271.8	2211.6	2183.0	2095.7	1999.0	1916.5	1834.0	1781.6	1707.1	1659.5
17.5°	2413.0	2311.5	2271.8	2198.9	2094.2	1984.7	1889.5	1807.0	1727.7	1661.1	1599.2
20°	2468.6	2335.3	2271.8	2225.8	2087.8	1976.8	1872.1	1765.8	1689.6	1618.2	1548.4
22.5°	2503.5	2352.8	2286.1	2213.1	2081.5	1948.2	1824.5	1732.4	1638.8	1565.9	1510.3
25°	2494.0	2343.2	2268.7	2200.5	2040.2	1907.0	1795.9	1678.5	1591.2	1511.9	1438.9
27.5°	2489.2	2319.4	2240.1	2164.0	2013.3	1873.6	1734.0	1638.8	1542.1	1450.0	1396.1
30°	2476.5	2289.3	2197.3	2114.8	1957.7	1811.8	1692.8	1581.7	1485.0	1400.9	1329.5
32.5°	2433.7	2238.5	2149.7	2060.8	1897.4	1751.5	1630.9	1527.8	1431.0	1343.8	1275.5
35°	2376.6	2178.2	2081.5	1987.9	1824.5	1676.9	1565.9	1458.0	1367.6	1283.5	1218.4
37.5°	2319.4	2108.4	2018.0	1910.1	1759.4	1605.5	1491.3	1394.5	1310.4	1223.2	1151.8
40°	2236.9	2025.9	1926.0	1834.0	1657.9	1513.5	1408.8	1321.5	1239.0	1156.5	1096.3
42.5°	2124.3	1935.5	1832.4	1730.9	1565.9	1423.1	1321.5	1243.8	1166.1	1097.8	1031.2
45°	2010.1	1826.0	1734.0	1643.6	1464.3	1329.5	1235.9	1164.5	1099.4	1024.9	970.9
47.5°	1872.1	1716.6	1624.6	1535.7	1366.0	1231.1	1145.4	1078.8	1018.5	956.7	905.9
50°	1730.9	1596.0	1511.9	1419.9	1258.1	1135.9	1051.8	996.3	947.1	888.4	847.2
52.5°	1578.6	1461.2	1389.8	1300.9	1158.1	1045.5	959.8	904.3	863.0	820.2	783.7
55°	1416.7	1331.1	1254.9	1183.5	1048.7	947.1	871.0	821.8	793.2	753.6	721.9
57.5°	1270.8	1188.3	1142.3	1061.4	944.0	844.0	783.7	742.5	709.2	685.4	660.0
60°	1118.5	1051.8	1001.1	942.4	839.3	755.2	691.7	667.9	633.0	615.6	604.5
62.5°	972.5	924.9	877.3	832.9	740.9	661.6	614.0	583.8	563.2	545.8	536.2
65°	834.5	790.1	756.8	717.1	640.9	577.5	533.1	509.3	488.6	483.9	472.8
67.5°	699.6	680.6	644.1	612.4	547.3	498.2	464.8	434.7	423.6	418.8	409.3
70°	585.4	563.2	534.6	507.7	458.5	415.7	385.5	374.4	358.5	357.0	345.9
72.5°	482.3	455.3	434.7	414.1	377.6	339.5	323.6	307.8	299.8	293.5	288.7
75°	382.3	363.3	349.0	331.6	299.8	274.5	252.3	245.9	241.1	239.6	236.4
77.5°	285.6	272.9	266.5	249.1	226.9	204.7	195.1	185.6	185.6	182.4	184.0
80°	203.1	195.1	187.2	177.7	158.6	149.1	141.2	134.9	131.7	130.1	131.7
82.5°	128.5	123.7	122.2	115.8	103.1	98.4	92.0	87.3	87.3	87.3	87.3
85°	71.4	71.4	71.4	61.9	57.1	52.4	49.2	47.6	47.6	47.6	49.2
87.5°	30.1	30.1	25.4	25.4	23.8	20.6	19.0	19.0	20.6	20.6	22.2
90°	5.9	5.2	4.9	4.5	3.6	2.8	1.9	1.1	1.9	2.8	3.6
92.5°	14.3	13.9	13.7	13.2	12.2	11.2	10.2	9.2	10.2	11.2	12.2
95°	25.1	24.6	24.3	23.9	23.2	22.5	21.8	21.1	21.8	22.5	23.2
97.5°	37.6	36.9	36.6	36.3	35.7	35.0	34.4	33.8	34.4	35.0	35.7
100°	51.8	51.1	50.7	50.5	50.2	49.9	49.6	49.3	49.6	49.9	50.2
102.5°	66.8	66.2	65.9	65.9	65.8	65.7	65.6	65.5	65.6	65.7	65.8
105°	82.9	82.6	82.4	82.4	82.3	82.2	82.2	82.1	82.2	82.2	82.3
107.5°	99.8	99.7	99.7	99.7	99.6	99.5	99.5	99.4	99.5	99.5	99.6
110°	117.6	117.7	117.7	117.6	117.5	117.3	117.2	117.0	117.2	117.3	117.5

TEST NUMBER: P1025120

CATALOG NUMBER: S124DIP-B1195D365UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	135.1	135.2	135.3	135.3	135.3	135.3	135.3	135.3	135.3	135.3	135.3
115°	153.4	153.5	153.6	153.6	153.6	153.6	153.6	153.6	153.6	153.6	153.6
117.5°	170.8	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9	170.9
120°	189.2	189.5	189.6	189.4	189.1	188.8	188.4	188.1	188.4	188.8	189.1
122.5°	206.4	206.5	206.5	206.5	206.4	206.3	206.2	206.1	206.2	206.3	206.4
125°	223.6	223.7	223.7	223.7	223.7	223.7	223.7	223.7	223.7	223.7	223.7
127.5°	240.4	240.5	240.6	240.5	240.3	240.0	239.8	239.6	239.8	240.0	240.3
130°	257.6	257.6	257.6	257.5	257.2	257.0	256.7	256.5	256.7	257.0	257.2
132.5°	274.4	274.5	274.5	274.4	274.3	274.1	274.0	273.8	274.0	274.1	274.3
135°	290.7	290.7	290.7	290.5	290.0	289.5	289.1	288.6	289.1	289.5	290.0
137.5°	306.4	306.3	306.2	306.1	305.8	305.6	305.3	305.1	305.3	305.6	305.8
140°	322.4	322.4	322.4	322.3	322.2	322.0	321.9	321.7	321.9	322.0	322.2
142.5°	337.4	337.5	337.5	337.4	337.3	337.1	337.0	336.8	337.0	337.1	337.3
145°	352.1	352.0	352.0	351.8	351.5	351.2	350.9	350.6	350.9	351.2	351.5
147.5°	366.3	366.4	366.4	366.2	365.8	365.5	365.1	364.7	365.1	365.5	365.8
150°	378.8	378.8	378.8	378.6	378.3	378.0	377.6	377.3	377.6	378.0	378.3
152.5°	390.1	390.0	390.0	389.9	389.8	389.6	389.5	389.3	389.5	389.6	389.8
155°	401.6	401.7	401.7	401.7	401.7	401.7	401.7	401.7	401.7	401.7	401.7
157.5°	411.5	411.5	411.5	411.6	411.7	411.9	412.0	412.2	412.0	411.9	411.7
160°	420.9	421.0	421.0	421.0	421.1	421.2	421.3	421.4	421.3	421.2	421.1
162.5°	428.7	428.8	428.8	428.9	429.1	429.4	429.6	429.8	429.6	429.4	429.1
165°	436.0	436.1	436.2	436.3	436.5	436.8	437.0	437.2	437.0	436.8	436.5
167.5°	441.8	441.8	441.8	442.0	442.3	442.6	442.9	443.2	442.9	442.6	442.3
170°	446.5	446.4	446.4	446.6	447.0	447.4	447.8	448.2	447.8	447.4	447.0
172.5°	450.3	450.3	450.3	450.5	450.8	451.1	451.4	451.7	451.4	451.1	450.8
175°	453.0	453.1	453.1	453.3	453.7	454.1	454.5	454.9	454.5	454.1	453.7
177.5°	454.5	454.5	454.5	454.7	455.1	455.5	455.9	456.3	455.9	455.5	455.1
180°	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6

TEST NUMBER: P1025120

CATALOG NUMBER: S124DIP-B1195D365UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9
2.5°	1886.3	1880.0	1883.2	1867.3	1853.0	1832.4	1814.9	1811.8	1808.6	1818.1	1811.8
5°	1832.4	1824.5	1816.5	1797.5	1768.9	1751.5	1726.1	1724.5	1715.0	1700.7	1703.9
7.5°	1773.7	1768.9	1757.8	1727.7	1702.3	1672.2	1651.5	1634.1	1626.1	1613.5	1608.7
10°	1726.1	1708.6	1699.1	1665.8	1635.7	1603.9	1577.0	1564.3	1550.0	1538.9	1531.0
12.5°	1661.1	1656.3	1629.3	1602.4	1577.0	1540.5	1519.9	1483.4	1464.3	1473.8	1470.7
15°	1618.2	1596.0	1589.7	1551.6	1508.7	1485.0	1446.9	1423.1	1415.1	1400.9	1383.4
17.5°	1561.1	1546.8	1524.6	1489.7	1440.5	1407.2	1380.2	1358.0	1348.5	1329.5	1315.2
20°	1507.2	1483.4	1465.9	1434.2	1386.6	1343.8	1310.4	1296.2	1272.4	1256.5	1248.6
22.5°	1458.0	1440.5	1415.1	1367.6	1326.3	1285.1	1245.4	1224.8	1202.6	1193.0	1180.3
25°	1397.7	1369.1	1351.7	1299.3	1254.9	1221.6	1185.1	1158.1	1145.4	1129.6	1126.4
27.5°	1339.0	1312.0	1291.4	1245.4	1191.5	1148.6	1126.4	1107.4	1085.2	1085.2	1077.2
30°	1280.3	1261.3	1229.5	1185.1	1134.3	1093.1	1067.7	1050.3	1042.3	1036.0	1034.4
32.5°	1221.6	1196.2	1177.2	1116.9	1078.8	1040.7	1021.7	1007.4	997.9	996.3	997.9
35°	1161.3	1132.8	1113.7	1059.8	1021.7	986.8	978.9	966.2	961.4	959.8	967.8
37.5°	1097.8	1075.6	1051.8	1007.4	964.6	944.0	928.1	923.3	921.7	931.3	934.4
40°	1039.1	1020.1	997.9	950.3	918.6	896.4	888.4	883.7	890.0	899.5	904.3
42.5°	983.6	956.7	939.2	896.4	867.8	855.1	845.6	845.6	851.9	863.0	871.0
45°	924.9	904.3	886.8	848.8	823.4	809.1	807.5	809.1	817.0	825.0	834.5
47.5°	867.8	847.2	828.1	796.4	774.2	766.3	764.7	766.3	779.0	790.1	801.2
50°	815.5	793.2	775.8	745.6	728.2	718.7	720.3	728.2	737.7	753.6	767.9
52.5°	753.6	737.7	721.9	694.9	679.0	672.7	677.4	683.8	701.2	712.3	729.8
55°	693.3	679.0	666.3	645.7	633.0	628.2	631.4	640.9	655.2	674.3	694.9
57.5°	637.8	621.9	609.2	594.9	580.7	582.2	583.8	596.5	614.0	631.4	655.2
60°	575.9	566.4	555.3	537.8	531.5	531.5	536.2	550.5	566.4	594.9	615.6
62.5°	520.4	507.7	499.7	488.6	479.1	480.7	491.8	504.5	523.5	547.3	574.3
65°	463.3	449.0	442.6	433.1	429.9	431.5	439.5	458.5	479.1	499.7	525.1
67.5°	399.8	395.0	388.7	379.2	382.3	383.9	391.9	407.7	429.9	450.6	479.1
70°	345.9	336.3	334.7	326.8	326.8	331.6	347.4	358.5	379.2	401.4	431.5
72.5°	288.7	280.8	280.8	274.5	279.2	284.0	291.9	307.8	326.8	349.0	374.4
75°	230.0	226.9	230.0	226.9	226.9	234.8	244.3	257.0	277.6	301.4	322.1
77.5°	177.7	177.7	176.1	180.9	180.9	185.6	198.3	211.0	226.9	245.9	268.1
80°	130.1	130.1	130.1	134.9	139.6	139.6	147.5	163.4	177.7	190.4	211.0
82.5°	88.8	88.8	88.8	92.0	98.4	98.4	107.9	117.4	133.3	144.4	153.9
85°	53.9	53.9	52.4	55.5	57.1	61.9	69.8	76.2	84.1	93.6	103.1
87.5°	23.8	23.8	25.4	27.0	28.6	31.7	34.9	38.1	46.0	49.2	53.9
90°	4.5	4.9	5.2	5.9	6.5	7.2	7.8	8.3	8.7	9.2	9.7
92.5°	13.2	13.7	13.9	14.3	14.7	15.1	15.5	15.7	16.0	16.2	16.5
95°	23.9	24.3	24.6	25.1	25.7	26.2	26.8	27.0	27.2	27.5	27.7
97.5°	36.3	36.6	36.9	37.6	38.2	38.9	39.5	39.8	40.1	40.4	40.7
100°	50.5	50.7	51.1	51.8	52.5	53.2	53.9	54.1	54.2	54.4	54.5
102.5°	65.9	65.9	66.2	66.8	67.5	68.1	68.7	68.9	69.2	69.4	69.7
105°	82.4	82.4	82.6	82.9	83.2	83.6	83.9	84.1	84.3	84.6	84.8
107.5°	99.7	99.7	99.7	99.8	99.9	100.0	100.1	100.4	100.7	101.0	101.3
110°	117.6	117.7	117.7	117.6	117.5	117.4	117.3	117.1	117.0	116.8	116.7



TEST NUMBER: P1025120

CATALOG NUMBER: S124DIP-B1195D365UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	135.3	135.3	135.2	135.1	134.9	134.8	134.6	134.6	134.6	134.6	134.6
115°	153.6	153.6	153.5	153.4	153.2	153.1	152.9	152.8	152.8	152.7	152.6
117.5°	170.9	170.9	170.9	170.8	170.7	170.6	170.5	170.3	170.1	169.8	169.6
120°	189.4	189.6	189.5	189.2	189.0	188.7	188.5	188.1	187.7	187.3	186.9
122.5°	206.5	206.5	206.5	206.4	206.3	206.2	206.1	205.9	205.7	205.4	205.2
125°	223.7	223.7	223.7	223.6	223.5	223.5	223.4	223.2	223.1	222.9	222.8
127.5°	240.5	240.6	240.5	240.4	240.2	240.1	239.9	239.7	239.6	239.4	239.3
130°	257.5	257.6	257.6	257.6	257.6	257.6	257.6	257.4	257.3	257.1	257.0
132.5°	274.4	274.5	274.5	274.4	274.3	274.2	274.1	273.9	273.8	273.6	273.5
135°	290.5	290.7	290.7	290.7	290.7	290.7	290.7	290.5	290.4	290.2	290.1
137.5°	306.1	306.2	306.3	306.4	306.6	306.7	306.9	306.7	306.4	306.2	305.9
140°	322.3	322.4	322.4	322.4	322.4	322.4	322.4	322.3	322.2	322.1	322.0
142.5°	337.4	337.5	337.5	337.4	337.3	337.3	337.2	337.2	337.2	337.2	337.2
145°	351.8	352.0	352.0	352.1	352.2	352.2	352.3	352.2	352.2	352.1	352.0
147.5°	366.2	366.4	366.4	366.3	366.2	366.2	366.1	366.0	365.9	365.8	365.7
150°	378.6	378.8	378.8	378.8	378.8	378.8	378.8	378.8	378.8	378.8	378.8
152.5°	389.9	390.0	390.0	390.1	390.2	390.3	390.4	390.6	390.8	391.1	391.3
155°	401.7	401.7	401.7	401.6	401.5	401.4	401.3	401.6	401.9	402.2	402.5
157.5°	411.6	411.5	411.5	411.5	411.5	411.5	411.5	411.7	412.0	412.2	412.5
160°	421.0	421.0	421.0	420.9	420.8	420.8	420.7	420.9	421.1	421.4	421.6
162.5°	428.9	428.8	428.8	428.7	428.6	428.5	428.4	428.9	429.3	429.8	430.3
165°	436.3	436.2	436.1	436.0	435.8	435.7	435.5	436.0	436.4	436.9	437.4
167.5°	442.0	441.8	441.8	441.8	441.8	441.8	441.8	442.3	442.7	443.2	443.7
170°	446.6	446.4	446.4	446.5	446.6	446.7	446.8	447.3	447.7	448.2	448.7
172.5°	450.5	450.3	450.3	450.3	450.3	450.3	450.3	450.8	451.4	451.9	452.4
175°	453.3	453.1	453.1	453.0	452.9	452.8	452.7	453.3	453.8	454.4	454.9
177.5°	454.7	454.5	454.5	454.5	454.5	454.5	454.5	455.1	455.6	456.2	456.7
180°	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6

TEST NUMBER: P1025120

CATALOG NUMBER: S124DIP-B1195D365UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9
2.5°	1807.0	1805.4	1797.5	1800.7	1791.1	1794.3	1799.1	1800.7	1807.0	1802.2	1800.7
5°	1696.0	1692.8	1688.0	1683.3	1681.7	1688.0	1676.9	1680.1	1683.3	1688.0	1694.4
7.5°	1605.5	1603.9	1599.2	1591.2	1588.1	1584.9	1586.5	1597.6	1596.0	1594.4	1605.5
10°	1523.0	1524.6	1515.1	1513.5	1504.0	1502.4	1504.0	1507.2	1511.9	1518.3	1519.9
12.5°	1437.4	1458.0	1440.5	1434.2	1419.9	1427.8	1431.0	1416.7	1424.7	1429.4	1453.2
15°	1383.4	1373.9	1362.8	1362.8	1356.4	1353.3	1345.3	1356.4	1362.8	1372.3	1369.1
17.5°	1308.9	1293.0	1286.6	1280.3	1281.9	1288.2	1270.8	1296.2	1296.2	1300.9	1293.0
20°	1243.8	1231.1	1223.2	1220.0	1215.2	1212.1	1210.5	1216.8	1226.4	1229.5	1237.5
22.5°	1175.6	1175.6	1162.9	1158.1	1155.0	1150.2	1158.1	1153.4	1159.7	1166.1	1178.8
25°	1118.5	1118.5	1113.7	1107.4	1102.6	1099.4	1104.2	1102.6	1107.4	1115.3	1118.5
27.5°	1072.5	1067.7	1066.1	1064.5	1062.9	1064.5	1062.9	1067.7	1072.5	1074.1	1070.9
30°	1032.8	1028.0	1029.6	1029.6	1031.2	1029.6	1028.0	1032.8	1034.4	1031.2	1032.8
32.5°	996.3	996.3	999.5	1001.1	1001.1	1002.7	1004.2	1001.1	1002.7	997.9	999.5
35°	966.2	969.3	972.5	974.1	975.7	974.1	977.3	975.7	972.5	969.3	967.8
37.5°	936.0	939.2	945.5	947.1	951.9	953.5	950.3	950.3	948.7	942.4	939.2
40°	904.3	907.5	915.4	920.2	923.3	928.1	924.9	924.9	918.6	912.2	907.5
42.5°	874.2	880.5	888.4	893.2	899.5	899.5	899.5	896.4	888.4	882.1	877.3
45°	844.0	845.6	856.7	864.6	871.0	871.0	871.0	866.2	861.5	848.8	842.4
47.5°	810.7	815.5	828.1	836.1	842.4	844.0	844.0	839.3	829.7	818.6	810.7
50°	774.2	782.1	796.4	807.5	815.5	818.6	813.9	810.7	799.6	786.9	777.4
52.5°	739.3	748.8	766.3	775.8	786.9	788.5	786.9	782.1	769.4	752.0	744.1
55°	704.4	712.3	731.4	747.2	756.8	759.9	756.8	748.8	733.0	715.5	707.6
57.5°	666.3	677.4	698.1	713.9	725.0	726.6	723.4	715.5	702.8	680.6	669.5
60°	626.7	640.9	661.6	677.4	691.7	693.3	690.1	679.0	663.2	640.9	631.4
62.5°	587.0	598.1	621.9	639.4	650.5	658.4	652.0	640.9	625.1	602.9	588.6
65°	541.0	556.9	577.5	593.3	606.0	607.6	604.5	594.9	577.5	553.7	542.6
67.5°	496.6	507.7	528.3	548.9	553.7	558.4	553.7	544.2	529.9	509.3	493.4
70°	442.6	452.1	477.5	491.8	498.2	502.9	499.7	490.2	477.5	458.5	445.8
72.5°	388.7	396.6	420.4	431.5	444.2	442.6	441.0	434.7	417.2	404.6	396.6
75°	331.6	341.1	357.0	371.2	376.0	376.0	376.0	371.2	360.1	339.5	331.6
77.5°	279.2	284.0	296.7	304.6	309.4	311.0	309.4	301.4	295.1	280.8	276.0
80°	214.2	226.9	236.4	238.0	244.3	244.3	244.3	241.1	234.8	220.5	218.9
82.5°	161.8	165.0	174.5	179.3	182.4	180.9	180.9	174.5	172.9	165.0	161.8
85°	109.5	114.2	112.6	119.0	120.6	117.4	117.4	120.6	112.6	114.2	109.5
87.5°	60.3	60.3	63.5	61.9	68.2	68.2	65.0	66.6	63.5	61.9	60.3
90°	9.9	10.0	10.1	10.3	10.4	10.6	10.4	10.3	10.1	10.0	9.9
92.5°	16.6	16.6	16.7	16.8	16.8	16.9	16.8	16.8	16.7	16.6	16.6
95°	27.8	27.8	27.8	27.8	27.8	27.8	27.8	27.8	27.8	27.8	27.8
97.5°	40.9	40.9	40.9	40.9	40.9	40.9	40.9	40.9	40.9	40.9	40.9
100°	54.6	54.6	54.6	54.6	54.6	54.6	54.6	54.6	54.6	54.6	54.6
102.5°	69.8	69.8	69.9	70.0	70.0	70.1	70.0	70.0	69.9	69.8	69.8
105°	84.9	85.0	85.3	85.5	85.8	86.0	85.8	85.5	85.3	85.0	84.9
107.5°	101.5	101.5	101.4	101.3	101.2	101.1	101.2	101.3	101.4	101.5	101.5
110°	116.6	116.7	117.0	117.2	117.5	117.7	117.5	117.2	117.0	116.7	116.6

TEST NUMBER: P1025120

CATALOG NUMBER: S124DIP-B1195D365UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	134.6	134.6	134.6	134.6	134.6	134.6	134.6	134.6	134.6	134.6	134.6
115°	152.6	152.6	152.5	152.4	152.3	152.2	152.3	152.4	152.5	152.6	152.6
117.5°	169.5	169.4	169.1	168.9	168.6	168.4	168.6	168.9	169.1	169.4	169.5
120°	186.7	186.8	186.9	187.1	187.2	187.4	187.2	187.1	186.9	186.8	186.7
122.5°	205.1	204.9	204.5	204.1	203.7	203.3	203.7	204.1	204.5	204.9	205.1
125°	222.7	222.6	222.5	222.3	222.2	222.0	222.2	222.3	222.5	222.6	222.7
127.5°	239.2	239.2	239.1	239.0	239.0	238.9	239.0	239.0	239.1	239.2	239.2
130°	256.9	256.7	256.4	256.1	255.7	255.4	255.7	256.1	256.4	256.7	256.9
132.5°	273.4	273.4	273.3	273.2	273.2	273.1	273.2	273.2	273.3	273.4	273.4
135°	290.0	289.9	289.6	289.4	289.1	288.9	289.1	289.4	289.6	289.9	290.0
137.5°	305.8	305.8	305.9	306.0	306.1	306.2	306.1	306.0	305.9	305.8	305.8
140°	322.0	322.0	321.9	321.8	321.8	321.7	321.8	321.8	321.9	322.0	322.0
142.5°	337.2	337.2	337.2	337.2	337.2	337.2	337.2	337.2	337.2	337.2	337.2
145°	352.0	351.9	351.6	351.4	351.1	350.9	351.1	351.4	351.6	351.9	352.0
147.5°	365.7	365.7	365.6	365.5	365.5	365.4	365.5	365.5	365.6	365.7	365.7
150°	378.8	378.8	378.7	378.6	378.5	378.4	378.5	378.6	378.7	378.8	378.8
152.5°	391.4	391.3	391.1	390.8	390.6	390.4	390.6	390.8	391.1	391.3	391.4
155°	402.7	402.5	402.2	401.9	401.6	401.3	401.6	401.9	402.2	402.5	402.7
157.5°	412.6	412.5	412.2	412.0	411.7	411.5	411.7	412.0	412.2	412.5	412.6
160°	421.7	421.5	421.1	420.8	420.4	420.0	420.4	420.8	421.1	421.5	421.7
162.5°	430.5	430.3	429.9	429.6	429.2	428.8	429.2	429.6	429.9	430.3	430.5
165°	437.6	437.4	437.1	436.8	436.5	436.2	436.5	436.8	437.1	437.4	437.6
167.5°	443.9	443.7	443.2	442.7	442.3	441.8	442.3	442.7	443.2	443.7	443.9
170°	448.9	448.6	448.1	447.5	447.0	446.4	447.0	447.5	448.1	448.6	448.9
172.5°	452.7	452.4	451.9	451.4	450.8	450.3	450.8	451.4	451.9	452.4	452.7
175°	455.2	454.9	454.4	453.8	453.3	452.7	453.3	453.8	454.4	454.9	455.2
177.5°	457.0	456.7	456.1	455.4	454.8	454.2	454.8	455.4	456.1	456.7	457.0
180°	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6

TEST NUMBER: P1025120

CATALOG NUMBER: S124DIP-B1195D365UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9	1914.9
2.5°	1800.7	1810.2	1800.7	1807.0	1810.2	1818.1	1821.3	1835.6	1840.3	1851.4	1851.4
5°	1692.8	1697.5	1699.1	1705.5	1711.8	1727.7	1738.8	1759.4	1783.2	1786.4	1800.7
7.5°	1605.5	1613.5	1626.1	1621.4	1632.5	1656.3	1670.6	1696.0	1719.8	1732.4	1749.9
10°	1527.8	1537.3	1542.1	1546.8	1567.4	1588.1	1610.3	1627.7	1659.5	1678.5	1692.8
12.5°	1464.3	1456.4	1465.9	1483.4	1507.2	1519.9	1550.0	1577.0	1600.8	1621.4	1634.1
15°	1381.8	1388.2	1397.7	1427.8	1434.2	1465.9	1477.0	1507.2	1551.6	1570.6	1586.5
17.5°	1302.5	1323.1	1342.2	1353.3	1372.3	1397.7	1429.4	1462.7	1491.3	1513.5	1532.5
20°	1239.0	1259.7	1270.8	1278.7	1297.7	1332.6	1362.8	1404.0	1440.5	1458.0	1483.4
22.5°	1188.3	1188.3	1204.1	1227.9	1239.0	1272.4	1297.7	1342.2	1381.8	1404.0	1427.8
25°	1124.8	1134.3	1147.0	1167.7	1183.5	1210.5	1247.0	1285.1	1327.9	1346.9	1377.1
27.5°	1072.5	1083.6	1101.0	1105.8	1121.6	1145.4	1183.5	1224.8	1269.2	1289.8	1315.2
30°	1032.8	1039.1	1045.5	1055.0	1069.3	1089.9	1121.6	1158.1	1212.1	1227.9	1259.7
32.5°	997.9	1001.1	1004.2	1012.2	1020.1	1040.7	1066.1	1105.8	1150.2	1174.0	1202.6
35°	966.2	963.0	964.6	969.3	977.3	985.2	1012.2	1045.5	1086.7	1115.3	1137.5
37.5°	936.0	929.7	928.1	928.1	931.3	940.8	961.4	990.0	1034.4	1058.2	1080.4
40°	902.7	896.4	893.2	891.6	890.0	896.4	912.2	940.8	975.7	997.9	1023.3
42.5°	871.0	864.6	856.7	855.1	851.9	855.1	866.2	893.2	923.3	945.5	966.2
45°	839.3	828.1	818.6	812.3	813.9	809.1	817.0	837.7	872.6	886.8	907.5
47.5°	804.3	791.7	779.0	772.6	766.3	769.4	772.6	790.1	820.2	834.5	855.1
50°	771.0	753.6	739.3	731.4	726.6	723.4	726.6	744.1	766.3	779.0	796.4
52.5°	733.0	715.5	701.2	688.5	682.2	677.4	679.0	694.9	715.5	728.2	745.6
55°	698.1	675.8	656.8	640.9	636.2	634.6	633.0	644.1	661.6	674.3	688.5
57.5°	658.4	636.2	615.6	596.5	587.0	585.4	585.4	588.6	610.8	620.3	628.2
60°	618.7	594.9	572.7	555.3	541.0	536.2	534.6	541.0	552.1	561.6	572.7
62.5°	574.3	550.5	523.5	507.7	493.4	480.7	485.5	487.1	502.9	507.7	517.2
65°	531.5	504.5	482.3	456.9	441.0	433.1	429.9	433.1	445.8	447.4	453.7
67.5°	482.3	456.9	429.9	412.5	398.2	383.9	380.8	380.8	387.1	391.9	399.8
70°	434.7	409.3	379.2	360.1	345.9	333.2	328.4	326.8	331.6	334.7	342.7
72.5°	379.2	353.8	331.6	311.0	293.5	284.0	279.2	276.0	280.8	284.0	285.6
75°	320.5	299.8	277.6	257.0	245.9	236.4	230.0	225.3	228.5	228.5	228.5
77.5°	264.9	244.3	226.9	212.6	198.3	187.2	182.4	177.7	179.3	179.3	182.4
80°	206.2	192.0	177.7	165.0	152.3	142.8	139.6	134.9	131.7	130.1	130.1
82.5°	152.3	141.2	128.5	117.4	111.1	101.5	98.4	92.0	92.0	90.4	90.4
85°	101.5	95.2	82.5	74.6	69.8	65.0	61.9	58.7	53.9	53.9	52.4
87.5°	53.9	50.8	47.6	38.1	38.1	33.3	31.7	30.1	25.4	27.0	27.0
90°	9.7	9.2	8.7	8.3	7.8	7.2	6.5	5.9	5.2	4.9	4.5
92.5°	16.5	16.2	16.0	15.7	15.5	15.1	14.7	14.3	13.9	13.7	13.2
95°	27.7	27.5	27.2	27.0	26.8	26.2	25.7	25.1	24.6	24.3	23.9
97.5°	40.7	40.4	40.1	39.8	39.5	38.9	38.2	37.6	36.9	36.6	36.3
100°	54.5	54.4	54.2	54.1	53.9	53.2	52.5	51.8	51.1	50.7	50.5
102.5°	69.7	69.4	69.2	68.9	68.7	68.1	67.5	66.8	66.2	65.9	65.9
105°	84.8	84.6	84.3	84.1	83.9	83.6	83.2	82.9	82.6	82.4	82.4
107.5°	101.3	101.0	100.7	100.4	100.1	100.0	99.9	99.8	99.7	99.7	99.7
110°	116.7	116.8	117.0	117.1	117.3	117.4	117.5	117.6	117.7	117.7	117.6

TEST NUMBER: P1025120

CATALOG NUMBER: S124DIP-B1195D365UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	134.6	134.6	134.6	134.6	134.6	134.8	134.9	135.1	135.2	135.3	135.3
115°	152.6	152.7	152.8	152.8	152.9	153.1	153.2	153.4	153.5	153.6	153.6
117.5°	169.6	169.8	170.1	170.3	170.5	170.6	170.7	170.8	170.9	170.9	170.9
120°	186.9	187.3	187.7	188.1	188.5	188.7	189.0	189.2	189.5	189.6	189.4
122.5°	205.2	205.4	205.7	205.9	206.1	206.2	206.3	206.4	206.5	206.5	206.5
125°	222.8	222.9	223.1	223.2	223.4	223.5	223.5	223.6	223.7	223.7	223.7
127.5°	239.3	239.4	239.6	239.7	239.9	240.1	240.2	240.4	240.5	240.6	240.5
130°	257.0	257.1	257.3	257.4	257.6	257.6	257.6	257.6	257.6	257.6	257.5
132.5°	273.5	273.6	273.8	273.9	274.1	274.2	274.3	274.4	274.5	274.5	274.4
135°	290.1	290.2	290.4	290.5	290.7	290.7	290.7	290.7	290.7	290.7	290.5
137.5°	305.9	306.2	306.4	306.7	306.9	306.7	306.6	306.4	306.3	306.2	306.1
140°	322.0	322.1	322.2	322.3	322.4	322.4	322.4	322.4	322.4	322.4	322.3
142.5°	337.2	337.2	337.2	337.2	337.2	337.3	337.3	337.4	337.5	337.5	337.4
145°	352.0	352.1	352.2	352.2	352.3	352.2	352.2	352.1	352.0	352.0	351.8
147.5°	365.7	365.8	365.9	366.0	366.1	366.2	366.2	366.3	366.4	366.4	366.2
150°	378.8	378.8	378.8	378.8	378.8	378.8	378.8	378.8	378.8	378.8	378.6
152.5°	391.3	391.1	390.8	390.6	390.4	390.3	390.2	390.1	390.0	390.0	389.9
155°	402.5	402.2	401.9	401.6	401.3	401.4	401.5	401.6	401.7	401.7	401.7
157.5°	412.5	412.2	412.0	411.7	411.5	411.5	411.5	411.5	411.5	411.5	411.6
160°	421.6	421.4	421.1	420.9	420.7	420.8	420.8	420.9	421.0	421.0	421.0
162.5°	430.3	429.8	429.3	428.9	428.4	428.5	428.6	428.7	428.8	428.8	428.9
165°	437.4	436.9	436.4	436.0	435.5	435.7	435.8	436.0	436.1	436.2	436.3
167.5°	443.7	443.2	442.7	442.3	441.8	441.8	441.8	441.8	441.8	441.8	442.0
170°	448.7	448.2	447.7	447.3	446.8	446.7	446.6	446.5	446.4	446.4	446.6
172.5°	452.4	451.9	451.4	450.8	450.3	450.3	450.3	450.3	450.3	450.3	450.5
175°	454.9	454.4	453.8	453.3	452.7	452.8	452.9	453.0	453.1	453.1	453.3
177.5°	456.7	456.2	455.6	455.1	454.5	454.5	454.5	454.5	454.5	454.5	454.7
180°	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6	455.6

TEST NUMBER: P1025120

CATALOG NUMBER: S124DIP-B1195D365UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1914.9	1914.9	1914.9	1914.9
2.5°	1862.5	1878.4	1892.7	1914.9
5°	1821.3	1843.5	1873.6	1907.0
7.5°	1773.7	1808.6	1848.3	1894.3
10°	1729.3	1768.9	1819.7	1875.2
12.5°	1683.3	1730.9	1786.4	1846.7
15°	1630.9	1678.5	1740.4	1821.3
17.5°	1583.3	1640.4	1707.1	1792.7
20°	1527.8	1581.7	1654.7	1753.1
22.5°	1478.6	1540.5	1621.4	1707.1
25°	1424.7	1478.6	1559.5	1662.6
27.5°	1370.7	1437.4	1515.1	1615.0
30°	1318.4	1373.9	1458.0	1562.7
32.5°	1261.3	1327.9	1405.6	1504.0
35°	1199.4	1262.8	1335.8	1442.1
37.5°	1143.9	1205.7	1280.3	1373.9
40°	1082.0	1147.0	1215.2	1308.9
42.5°	1021.7	1080.4	1148.6	1234.3
45°	963.0	1013.8	1075.6	1150.2
47.5°	902.7	945.5	1002.7	1069.3
50°	837.7	883.7	926.5	982.0
52.5°	777.4	817.0	851.9	898.0
55°	718.7	745.6	774.2	809.1
57.5°	656.8	677.4	698.1	734.5
60°	594.9	614.0	625.1	648.9
62.5°	534.6	542.6	556.9	571.1
65°	468.0	479.1	487.1	504.5
67.5°	407.7	412.5	420.4	431.5
70°	344.3	355.4	358.5	366.5
72.5°	290.3	295.1	298.3	299.8
75°	230.0	234.8	238.0	247.5
77.5°	180.9	179.3	185.6	187.2
80°	133.3	128.5	130.1	136.4
82.5°	87.3	88.8	87.3	87.3
85°	53.9	52.4	49.2	50.8
87.5°	23.8	23.8	22.2	22.2
90°	3.6	2.8	1.9	1.1
92.5°	12.2	11.2	10.2	9.2
95°	23.2	22.5	21.8	21.1
97.5°	35.7	35.0	34.4	33.8
100°	50.2	49.9	49.6	49.3
102.5°	65.8	65.7	65.6	65.5
105°	82.3	82.2	82.2	82.1
107.5°	99.6	99.5	99.5	99.4
110°	117.5	117.3	117.2	117.0

TEST NUMBER: P1025120

CATALOG NUMBER: S124DIP-B1195D365UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	135.3	135.3	135.3	135.3
115°	153.6	153.6	153.6	153.6
117.5°	170.9	170.9	170.9	170.9
120°	189.1	188.8	188.4	188.1
122.5°	206.4	206.3	206.2	206.1
125°	223.7	223.7	223.7	223.7
127.5°	240.3	240.0	239.8	239.6
130°	257.2	257.0	256.7	256.5
132.5°	274.3	274.1	274.0	273.8
135°	290.0	289.5	289.1	288.6
137.5°	305.8	305.6	305.3	305.1
140°	322.2	322.0	321.9	321.7
142.5°	337.3	337.1	337.0	336.8
145°	351.5	351.2	350.9	350.6
147.5°	365.8	365.5	365.1	364.7
150°	378.3	378.0	377.6	377.3
152.5°	389.8	389.6	389.5	389.3
155°	401.7	401.7	401.7	401.7
157.5°	411.7	411.9	412.0	412.2
160°	421.1	421.2	421.3	421.4
162.5°	429.1	429.4	429.6	429.8
165°	436.5	436.8	437.0	437.2
167.5°	442.3	442.6	442.9	443.2
170°	447.0	447.4	447.8	448.2
172.5°	450.8	451.1	451.4	451.7
175°	453.7	454.1	454.5	454.9
177.5°	455.1	455.5	455.9	456.3
180°	455.6	455.6	455.6	455.6

(END OF REPORT)