

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013066

Luminaire Tested: S124DIP-B575D1035UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013066
REPORT IS A COMBINATION OF REPORTS P996034 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B575D1035UB2750-4F0-XX-W2A-D_3000K
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6450.0 lumens
Efficiency: N/A
Efficacy: 122.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013066

CATALOG NUMBER: S124DIP-B575D1035UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013066

CATALOG NUMBER: S124DIP-B575D1035UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34		
1	93	89	85	81	84	80	77	74	64	62	59	49	48	46	35	34	33	27		
2	85	77	71	66	76	70	64	60	56	52	49	43	40	38	31	29	28	22		
3	77	68	60	54	69	61	55	50	49	44	40	37	34	32	27	25	23	18		
4	70	60	52	46	63	54	47	42	43	38	34	33	30	27	24	22	20	16		
5	64	53	45	39	58	48	41	36	38	33	29	30	26	23	21	19	17	13		
6	59	47	39	33	53	43	36	31	34	29	25	27	23	20	19	17	15	12		
7	55	42	35	29	49	39	32	27	31	26	22	24	20	18	18	15	13	10		
8	51	38	31	25	45	35	28	23	28	23	19	22	18	16	16	14	12	9		
9	47	35	28	23	42	32	25	21	26	21	17	20	17	14	15	12	10	8		
10	44	32	25	20	39	29	23	18	24	19	15	19	15	12	14	11	9	7		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5642	5642	5642
5°	5658	5495	5505
10°	5621	5387	5372
15°	5568	5266	5221
20°	5490	5133	5075
25°	5403	4988	4917
30°	5307	4845	4756
35°	5200	4698	4613
40°	5114	4557	4465
45°	4986	4424	4334
50°	4877	4274	4196
55°	4765	4129	4037
60°	4591	3949	3887
65°	4399	3754	3706
70°	4165	3531	3498
75°	3841	3285	3299
80°	3475	3032	3092
85°	2991	2780	2924

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 90°

Luminance: 5023 cd/sqm

TEST NUMBER: P1013066

CATALOG NUMBER: S124DIP-B575D1035UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.6	1.0
10°-20°	187.8	2.9
20°-30°	284.0	4.4
30°-40°	343.6	5.3
40°-50°	363.2	5.6
50°-60°	341.9	5.3
60°-70°	283.7	4.4
70°-80°	199.1	3.1
80°-90°	115.0	1.8
90°-100°	110.7	1.7
100°-110°	338.3	5.2
110°-120°	584.7	9.1
120°-130°	718.8	11.1
130°-140°	757.1	11.7
140°-150°	702.0	10.9
150°-160°	564.8	8.8
160°-170°	364.2	5.6
170°-180°	125.5	1.9
0°-30°	537.4	8.3
0°-40°	881.0	13.7
0°-60°	1586.1	24.6
0°-90°	2183.8	33.9
90°-120°	1033.7	16.0
90°-150°	3211.6	49.8
90°-180°	4266.0	66.1
0°-180°	6450.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	692	692	692	692	692	
5°	693	690	685	691	690	66
15°	664	665	662	669	669	187
25°	608	612	614	623	624	280
35°	532	541	549	559	562	333
45°	443	458	473	486	490	343
55°	347	363	387	402	407	309
65°	240	265	291	311	317	238
75°	133	162	194	216	223	142
85°	41	74	108	132	140	43
90°	15	57	98	127	135	11
95°	64	56	89	116	124	75
105°	304	326	359	388	358	319
115°	560	570	594	613	618	552
125°	784	787	804	822	828	700
135°	970	969	978	993	999	748
145°	1117	1120	1120	1125	1130	698
155°	1224	1225	1222	1226	1223	565
165°	1292	1287	1287	1294	1286	365
175°	1321	1315	1316	1325	1313	126
180°	1321	1321	1321	1321	1321	

TEST NUMBER: P1013066

CATALOG NUMBER: S124DIP-B575D1035UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	691.9	691.9	691.9	691.9	691.9
2.5°	695.0	692.7	686.5	691.9	691.1
5°	692.7	690.4	684.9	691.1	690.4
7.5°	688.0	686.5	681.8	688.8	688.0
10°	681.8	681.1	677.2	684.2	683.4
12.5°	673.3	673.3	671.0	677.2	677.2
15°	664.0	664.8	662.5	669.4	668.7
17.5°	651.6	653.9	653.2	660.1	659.4
20°	638.4	640.8	641.5	649.3	649.3
22.5°	623.7	626.8	628.4	636.1	637.7
25°	607.5	612.1	614.4	623.0	623.7
27.5°	589.6	596.6	599.7	607.5	608.2
30°	571.8	578.0	583.4	592.0	593.5
32.5°	552.4	560.2	566.4	576.5	578.0
35°	531.5	540.8	548.6	559.4	561.7
37.5°	510.6	521.4	530.7	541.6	543.9
40°	490.5	500.5	511.4	523.0	526.1
42.5°	467.2	478.8	492.0	505.2	507.5
45°	443.2	457.9	472.6	485.8	489.7
47.5°	420.7	435.4	452.5	465.7	470.3
50°	395.9	413.0	430.0	445.5	450.2
52.5°	371.1	388.2	408.3	423.8	428.5
55°	347.1	363.4	386.6	402.1	406.8
57.5°	320.0	340.1	362.6	381.2	385.1
60°	293.7	313.8	339.4	357.2	363.4
62.5°	268.1	290.6	316.1	333.9	340.1
65°	240.2	265.0	291.3	310.7	316.9
67.5°	213.8	240.2	268.1	287.5	293.7
70°	186.7	213.1	242.5	263.4	268.9
72.5°	160.4	187.5	219.3	239.4	245.6
75°	133.3	161.9	194.5	216.2	223.1
77.5°	107.7	137.9	172.0	193.7	201.5
80°	84.5	115.4	149.5	172.8	179.0
82.5°	61.2	93.8	127.8	151.9	158.8
85°	41.1	73.6	108.5	131.7	139.5
87.5°	25.6	57.3	91.4	113.9	120.9
90°	15.4	57.2	98.4	126.9	135.0
92.5°	26.4	51.5	92.9	120.5	126.7
95°	64.5	56.4	89.1	116.0	124.0
97.5°	113.1	157.3	85.2	110.4	118.4
100°	170.6	208.5	102.4	106.5	112.9
102.5°	235.8	264.7	306.0	103.9	110.1
105°	304.4	325.9	359.4	387.7	358.3
107.5°	368.7	384.7	418.9	443.1	452.6
110°	433.1	446.9	480.0	499.8	508.9

TEST NUMBER: P1013066

CATALOG NUMBER: S124DIP-B575D1035UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	495.5	510.8	538.3	554.4	564.5
115°	560.0	569.9	593.7	612.8	618.2
117.5°	618.3	626.9	653.1	668.4	674.6
120°	676.9	683.1	704.6	722.1	726.3
122.5°	732.2	734.2	757.0	773.5	777.0
125°	783.8	786.9	804.3	822.0	827.7
127.5°	834.2	834.4	854.8	867.8	872.2
130°	881.8	882.0	897.3	912.3	916.9
132.5°	926.3	927.4	940.7	954.9	958.6
135°	969.9	968.9	978.4	992.8	999.3
137.5°	1009.4	1008.7	1016.8	1030.4	1033.3
140°	1048.0	1049.3	1051.9	1065.0	1069.9
142.5°	1081.9	1085.8	1086.0	1096.5	1099.6
145°	1117.4	1119.6	1119.6	1125.2	1130.3
147.5°	1145.1	1150.2	1149.3	1151.0	1155.1
150°	1175.8	1178.9	1177.9	1177.9	1178.9
152.5°	1200.6	1203.6	1201.6	1203.6	1202.6
155°	1224.4	1225.4	1222.4	1226.3	1223.4
157.5°	1245.1	1245.1	1241.2	1246.1	1241.2
160°	1262.9	1259.9	1258.9	1264.9	1258.9
162.5°	1278.7	1274.8	1273.8	1279.7	1272.8
165°	1291.6	1286.6	1286.6	1294.5	1285.6
167.5°	1302.4	1297.5	1296.5	1305.4	1295.5
170°	1311.3	1305.4	1306.4	1314.3	1304.4
172.5°	1317.3	1311.3	1312.3	1320.2	1309.3
175°	1321.2	1315.3	1316.3	1325.2	1313.3
177.5°	1324.2	1317.3	1319.2	1327.1	1315.3
180°	1321.2	1321.2	1321.2	1321.2	1321.2

(END OF REPORT)