

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013085

Luminaire Tested: S124DIP-B575D1205UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013085
REPORT IS A COMBINATION OF REPORTS P996098 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B575D1205UB2750-4F0-XX-W2A-F_2700K
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7227.0 lumens
Efficiency: N/A
Efficacy: 122.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013085

CATALOG NUMBER: S124DIP-B575D1205UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1013085

CATALOG NUMBER: S124DIP-B575D1205UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	42	42	42			34
1	94	90	86	83	85	81	78	75	65	63	61	50	49	48	37	36	35			29
2	86	79	73	67	77	71	66	62	57	53	50	44	42	40	32	31	29			24
3	78	69	62	56	70	62	56	51	50	46	42	39	36	34	29	27	25			20
4	71	61	53	47	64	55	49	44	45	40	36	35	31	29	25	23	22			17
5	65	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19			15
6	60	48	41	35	54	44	37	32	36	31	27	28	24	22	21	18	16			13
7	56	44	36	30	50	40	33	28	32	27	24	25	22	19	19	16	15			12
8	52	40	32	27	46	36	29	25	29	24	21	23	20	17	17	15	13			11
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	14	12			10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	12	11			9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7819	7819	7819
5°	7826	7594	7603
10°	7759	7383	7331
15°	7648	7133	7025
20°	7506	6861	6708
25°	7345	6575	6366
30°	7153	6265	5990
35°	6953	5948	5628
40°	6745	5607	5242
45°	6527	5265	4882
50°	6284	4933	4482
55°	6022	4545	4086
60°	5753	4121	3673
65°	5445	3683	3208
70°	5091	3156	2709
75°	4562	2543	2169
80°	3887	1839	1527
85°	3020	1025	822

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6527 cd/sqm

TEST NUMBER: P1013085

CATALOG NUMBER: S124DIP-B575D1205UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.4	1.3
10°-20°	254.6	3.5
20°-30°	374.7	5.2
30°-40°	435.6	6.0
40°-50°	435.5	6.0
50°-60°	380.9	5.3
60°-70°	282.8	3.9
70°-80°	160.5	2.2
80°-90°	49.1	0.7
90°-100°	51.1	0.7
100°-110°	336.5	4.7
110°-120°	642.5	8.9
120°-130°	815.7	11.3
130°-140°	872.6	12.1
140°-150°	815.9	11.3
150°-160°	658.0	9.1
160°-170°	424.3	5.9
170°-180°	146.2	2.0
0°-30°	719.7	10.0
0°-40°	1155.3	16.0
0°-60°	1971.8	27.3
0°-90°	2464.2	34.1
90°-120°	1030.1	14.3
90°-150°	3534.3	48.9
90°-180°	4763.0	65.9
0°-180°	7227.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	959	959	959	959	959	
5°	958	955	946	955	953	91
15°	912	909	897	902	900	257
25°	826	820	810	810	808	380
35°	711	705	694	689	685	444
45°	580	575	562	554	552	447
55°	439	436	426	416	412	393
65°	297	294	286	278	274	294
75°	158	154	151	148	147	168
85°	42	42	40	40	39	45
90°	4	16	25	32	34	6
95°	63	24	25	32	33	78
105°	346	353	359	370	328	363
115°	647	650	649	652	652	637
125°	910	914	912	915	916	812
135°	1128	1127	1132	1134	1136	869
145°	1301	1304	1304	1306	1308	813
155°	1426	1428	1424	1429	1425	658
165°	1505	1499	1499	1508	1498	425
175°	1539	1532	1533	1544	1530	147
180°	1539	1539	1539	1539	1539	

TEST NUMBER: P1013085

CATALOG NUMBER: S124DIP-B575D1205UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	958.8	958.8	958.8	958.8	958.8
2.5°	961.9	959.6	951.1	958.8	958.1
5°	958.1	955.0	946.5	955.0	953.4
7.5°	951.1	948.1	938.8	945.8	945.0
10°	941.2	938.1	928.1	934.2	932.7
12.5°	928.1	925.0	914.3	921.2	918.9
15°	912.0	908.9	897.4	902.0	899.7
17.5°	893.5	889.7	878.9	882.0	880.5
20°	872.8	868.9	857.4	859.7	858.2
22.5°	850.5	845.1	833.6	838.2	835.1
25°	825.9	820.5	809.8	810.5	807.5
27.5°	798.2	792.9	782.9	781.3	777.5
30°	770.6	764.4	754.5	751.4	747.5
32.5°	741.4	736.0	725.3	721.4	717.6
35°	710.7	705.3	694.5	689.2	685.3
37.5°	678.4	673.8	662.3	656.9	651.5
40°	646.9	640.8	629.2	621.5	617.7
42.5°	613.1	610.0	597.0	587.7	585.4
45°	580.1	574.7	562.4	553.9	551.6
47.5°	545.5	541.6	530.1	520.9	514.8
50°	510.1	507.1	496.3	485.6	480.9
52.5°	475.6	471.7	460.2	451.0	444.8
55°	438.7	436.4	425.6	416.4	411.8
57.5°	404.1	401.8	391.1	381.8	377.2
60°	368.0	364.2	354.2	347.3	343.4
62.5°	332.7	329.6	318.8	312.7	308.9
65°	297.3	293.5	285.8	278.1	274.3
67.5°	261.2	258.1	250.5	242.8	242.0
70°	228.2	222.8	216.7	210.5	208.2
72.5°	192.8	187.5	182.9	178.2	175.9
75°	158.3	154.4	150.6	147.5	146.7
77.5°	124.5	122.9	119.1	118.3	116.0
80°	94.5	92.2	90.7	89.1	88.4
82.5°	65.3	64.5	64.5	63.8	63.0
85°	41.5	41.5	40.0	40.0	39.2
87.5°	20.0	19.2	18.4	18.4	18.4
90°	3.5	16.1	25.3	32.2	34.5
92.5°	17.3	15.0	24.2	31.1	31.1
95°	63.3	24.2	25.3	32.2	33.4
97.5°	120.9	146.2	25.3	31.1	32.2
100°	188.8	209.5	50.7	31.1	32.2
102.5°	264.8	278.6	292.4	33.4	33.4
105°	346.5	353.4	359.2	369.5	328.1
107.5°	421.4	424.8	432.9	438.6	443.2
110°	497.3	500.8	507.7	510.0	513.4

TEST NUMBER: P1013085

CATALOG NUMBER: S124DIP-B575D1205UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	571.0	577.9	580.2	579.1	583.7
115°	647.0	650.4	649.3	651.6	651.6
117.5°	714.9	719.5	723.0	721.8	721.8
120°	784.0	788.6	787.4	789.7	787.4
122.5°	848.5	850.8	853.1	854.2	851.9
125°	909.5	914.1	911.8	915.2	916.4
127.5°	968.2	969.3	975.1	973.9	972.8
130°	1024.6	1025.7	1029.2	1030.4	1030.4
132.5°	1076.4	1078.7	1083.3	1084.5	1083.3
135°	1128.2	1127.1	1131.7	1134.0	1136.3
137.5°	1174.3	1174.3	1180.0	1182.3	1181.2
140°	1219.2	1221.5	1223.8	1227.2	1228.4
142.5°	1259.4	1264.1	1265.2	1267.5	1267.5
145°	1300.9	1304.3	1304.3	1305.5	1307.8
147.5°	1333.1	1340.0	1338.9	1340.0	1341.2
150°	1368.8	1373.4	1372.3	1372.3	1373.4
152.5°	1398.7	1402.2	1399.9	1402.2	1401.1
155°	1426.4	1427.5	1424.1	1428.7	1425.2
157.5°	1450.6	1450.6	1445.9	1451.7	1445.9
160°	1471.3	1467.8	1466.7	1473.6	1466.7
162.5°	1489.7	1485.1	1483.9	1490.8	1482.8
165°	1504.7	1498.9	1498.9	1508.1	1497.8
167.5°	1517.3	1511.6	1510.4	1520.8	1509.3
170°	1527.7	1520.8	1521.9	1531.1	1519.6
172.5°	1534.6	1527.7	1528.8	1538.0	1525.4
175°	1539.2	1532.3	1533.4	1543.8	1530.0
177.5°	1542.7	1534.6	1536.9	1546.1	1532.3
180°	1539.2	1539.2	1539.2	1539.2	1539.2

(END OF REPORT)