

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1025220

Luminaire Tested: S124DIP-B1195D810UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1025220
REPORT IS A COMBINATION OF REPORTS P995685 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B1195D810UB30-4F0-XX-W2A-A4
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8163.0 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1025220

CATALOG NUMBER: S124DIP-B1195D810UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1025220

CATALOG NUMBER: S124DIP-B1195D810UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70
1	102	97	93	90	95	92	88	85	81	79	76	71	70	68	63	61	60
2	93	85	79	74	87	80	75	70	71	67	64	63	60	57	55	53	51
3	85	75	68	62	79	71	65	59	63	58	54	56	52	49	49	46	44
4	78	67	59	53	73	63	56	51	56	51	46	50	46	42	44	41	38
5	72	60	52	46	67	57	49	44	51	45	40	45	40	37	40	36	33
6	66	54	46	40	62	51	44	38	46	40	35	41	36	32	36	32	29
7	61	49	41	35	57	46	39	34	42	36	31	37	32	29	33	29	26
8	57	44	37	31	53	42	35	30	38	32	28	34	29	26	31	27	24
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	28	24	21
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15751	15751	15751	15751
5°	15712	18070	15803	13578
10°	15594	21082	15713	11912
15°	15406	24304	15513	10659
20°	15207	26353	15317	9556
25°	14916	26052	15058	8743
30°	14631	21533	14809	8323
35°	14232	16047	14389	8069
40°	13765	12088	13898	7945
45°	13053	9702	13215	7776
50°	12203	8174	12381	7697
55°	11204	7114	11380	7606
60°	10231	6264	10531	7479
65°	9320	5390	9408	7168
70°	8248	4435	8426	6600
75°	7193	3407	7147	5608
80°	5659	2239	5593	4256
85°	3726	1006	3493	2482

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 20367 cd/sqm

TEST NUMBER: P1025220

CATALOG NUMBER: S124DIP-B1195D810UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.0	2.3
10°-20°	580.2	7.1
20°-30°	921.8	11.3
30°-40°	1024.3	12.5
40°-50°	931.5	11.4
50°-60°	761.2	9.3
60°-70°	543.3	6.7
70°-80°	299.0	3.7
80°-90°	82.3	1.0
90°-100°	281.8	3.5
100°-110°	588.2	7.2
110°-120°	522.9	6.4
120°-130°	440.2	5.4
130°-140°	367.2	4.5
140°-150°	280.4	3.4
150°-160°	197.1	2.4
160°-170°	115.9	1.4
170°-180°	37.7	0.5
0°-30°	1690.0	20.7
0°-40°	2714.3	33.3
0°-60°	4406.9	54.0
0°-90°	5331.5	65.3
90°-120°	1392.9	17.1
90°-150°	2480.7	30.4
90°-180°	2831.0	34.7
0°-180°	8163.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1932	1932	1932	1932	1932	
5°	1924	2266	1935	1703	1924	183
15°	1837	3113	1850	1365	1837	518
25°	1677	3305	1693	1109	1677	773
35°	1455	1954	1471	983	1455	909
45°	1160	1096	1175	879	1160	895
55°	816	717	829	766	816	734
65°	509	461	514	613	509	503
75°	250	230	248	379	250	262
85°	51	48	48	118	51	60
90°	1	16	1	16	1	5
95°	25	186	25	186	25	28
105°	89	1075	89	1075	89	95
115°	157	1032	157	1032	157	156
125°	219	823	219	823	219	195
135°	260	736	260	736	260	201
145°	300	601	300	601	300	188
155°	341	503	341	503	341	157
165°	372	439	372	439	372	105
175°	388	396	388	396	388	37
180°	389	389	389	389	389	

TEST NUMBER: P1025220

CATALOG NUMBER: S124DIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6
2.5°	1931.6	1950.8	1958.8	1965.2	1986.0	1992.4	1994.0	2003.6	2011.6	2013.2	2013.2
5°	1923.6	1954.0	1978.0	2000.4	2034.0	2048.4	2066.0	2085.2	2110.8	2126.8	2134.8
7.5°	1910.8	1955.6	1992.4	2030.8	2077.2	2106.0	2122.0	2173.2	2208.4	2237.2	2272.4
10°	1891.6	1949.2	2002.0	2058.0	2123.6	2158.8	2194.0	2256.4	2306.0	2362.0	2406.8
12.5°	1862.7	1938.0	2002.0	2080.4	2162.0	2203.6	2245.2	2354.0	2411.6	2461.3	2541.3
15°	1837.1	1912.4	2003.6	2083.6	2184.4	2246.8	2307.6	2378.0	2469.3	2576.5	2653.3
17.5°	1808.3	1902.8	1987.6	2099.6	2211.6	2270.8	2320.4	2429.3	2557.3	2662.9	2733.3
20°	1768.3	1864.3	1976.4	2094.8	2227.6	2274.0	2339.6	2485.3	2600.5	2704.5	2819.7
22.5°	1721.9	1833.9	1952.4	2066.0	2203.6	2301.2	2373.2	2501.3	2640.5	2760.5	2890.1
25°	1677.1	1798.7	1902.8	2058.0	2203.6	2269.2	2350.8	2502.9	2654.9	2800.5	2933.3
27.5°	1629.1	1742.7	1883.6	2006.8	2171.6	2243.6	2331.6	2498.1	2659.7	2805.3	2947.7
30°	1576.3	1697.9	1814.7	1960.4	2120.4	2213.2	2294.8	2475.7	2640.5	2792.5	2925.3
32.5°	1517.1	1632.3	1757.1	1894.8	2062.8	2157.2	2259.6	2445.3	2621.3	2752.5	2854.9
35°	1454.7	1571.5	1680.3	1821.1	1994.0	2088.4	2187.6	2392.4	2566.9	2674.1	2733.3
37.5°	1385.9	1496.3	1603.5	1742.7	1915.6	2016.4	2117.2	2315.6	2480.5	2570.1	2554.1
40°	1320.2	1419.5	1518.7	1649.9	1830.7	1938.0	2026.0	2226.0	2370.0	2408.4	2355.6
42.5°	1245.0	1329.8	1425.9	1560.3	1736.3	1837.1	1947.6	2130.0	2237.2	2221.2	2131.6
45°	1160.2	1235.4	1331.4	1457.9	1637.1	1741.1	1833.9	2006.8	2085.2	2045.2	1882.0
47.5°	1078.6	1152.2	1230.6	1357.1	1531.5	1619.5	1713.9	1869.1	1914.0	1829.1	1665.9
50°	990.6	1051.4	1133.0	1253.0	1416.3	1509.1	1587.5	1712.3	1728.3	1624.3	1454.7
52.5°	905.8	957.0	1035.4	1153.8	1305.8	1379.5	1456.3	1566.7	1553.9	1446.7	1283.4
55°	816.2	864.2	936.2	1045.0	1179.4	1249.8	1315.4	1413.1	1385.9	1275.4	1133.0
57.5°	740.9	774.5	845.0	945.8	1056.2	1133.0	1189.0	1265.8	1224.2	1113.8	981.0
60°	654.5	696.1	755.3	837.0	945.8	997.0	1046.6	1097.8	1069.0	963.4	845.0
62.5°	576.1	608.1	659.3	737.7	822.6	869.0	921.8	953.8	925.0	827.4	728.1
65°	508.9	534.5	574.5	638.5	720.1	758.5	788.9	819.4	795.3	704.1	632.1
67.5°	435.3	457.7	491.3	542.5	611.3	638.5	667.3	688.1	660.9	600.1	529.7
70°	369.7	385.7	417.7	456.1	504.1	529.7	553.7	574.5	550.5	499.3	446.5
72.5°	302.5	315.3	344.1	371.3	414.5	432.1	449.7	465.7	457.7	409.7	366.5
75°	249.6	254.4	273.7	296.1	323.3	342.5	355.3	364.9	358.5	320.1	292.9
77.5°	188.8	195.2	209.6	227.2	251.2	262.4	270.5	280.1	272.1	241.6	222.4
80°	137.6	139.2	147.2	163.2	179.2	180.8	188.8	201.6	196.8	176.0	161.6
82.5°	88.0	92.8	96.0	105.6	116.8	120.0	124.8	128.0	126.4	113.6	108.8
85°	51.2	51.2	54.4	60.8	64.0	68.8	70.4	72.0	75.2	67.2	62.4
87.5°	22.4	24.0	24.0	25.6	28.8	28.8	30.4	32.0	33.6	32.0	27.2
90°	0.8	2.3	4.6	5.3	6.1	6.1	6.1	10.7	10.7	12.2	13.7
92.5°	10.7	15.3	23.7	35.1	48.9	58.8	68.7	116.1	190.2	262.0	299.4
95°	25.2	27.5	35.1	45.1	63.4	79.4	95.5	161.9	287.2	469.7	622.5
97.5°	42.0	42.0	48.9	58.0	74.1	87.8	101.6	154.3	262.0	449.9	666.0
100°	58.0	58.0	63.4	72.6	87.1	99.3	111.5	156.6	242.9	398.7	614.1
102.5°	73.3	74.9	79.4	87.8	101.6	113.0	124.5	164.2	237.5	364.3	549.2
105°	89.4	91.7	95.5	104.6	118.4	129.4	140.5	177.2	240.6	347.5	501.0
107.5°	106.9	108.5	112.3	122.2	135.2	146.2	157.3	190.9	249.8	342.9	469.7
110°	124.5	126.0	129.8	139.0	152.8	163.1	173.4	207.0	260.4	344.5	455.2

TEST NUMBER: P1025220

CATALOG NUMBER: S124DIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	141.3	142.8	147.4	155.8	169.6	179.9	190.2	222.3	271.9	349.0	448.3
115°	157.3	159.6	165.0	172.6	187.1	197.4	207.7	238.3	284.1	355.2	446.8
117.5°	174.1	176.4	181.0	189.4	203.2	213.9	224.6	253.6	296.3	361.3	446.0
120°	190.9	192.5	197.8	206.2	219.2	229.9	240.6	269.6	309.3	368.1	446.0
122.5°	206.2	207.7	213.1	220.7	235.2	245.6	255.9	284.9	321.6	375.0	445.3
125°	219.2	222.3	226.8	235.2	249.8	260.5	271.1	298.6	333.8	381.9	444.5
127.5°	231.4	233.7	239.1	248.2	263.5	274.2	284.9	311.6	344.5	387.2	443.0
130°	241.4	244.4	250.5	262.0	276.5	287.6	298.6	324.6	354.4	393.3	442.2
132.5°	251.3	253.6	262.0	272.7	288.7	299.0	309.3	335.3	364.3	398.7	441.5
135°	260.4	263.5	271.1	284.1	300.2	310.1	320.0	345.2	372.7	404.0	440.7
137.5°	269.6	272.7	281.1	293.3	310.1	319.6	329.2	352.9	378.8	407.1	440.7
140°	279.5	281.8	290.2	303.2	319.3	328.5	337.6	360.5	384.9	410.9	439.9
142.5°	290.2	292.5	300.2	312.4	327.7	336.4	345.2	367.4	389.5	414.0	439.9
145°	300.2	302.5	310.1	320.8	335.3	343.7	352.1	372.0	392.6	414.7	438.4
147.5°	311.6	312.4	319.3	330.7	342.9	350.5	358.2	377.3	395.6	415.5	436.1
150°	322.3	323.1	329.2	338.4	349.8	357.0	364.3	381.1	397.9	415.5	433.8
152.5°	332.2	332.2	338.4	346.8	356.7	363.2	369.7	384.2	399.5	414.0	430.0
155°	341.4	342.2	346.8	354.4	362.8	368.6	374.3	387.2	400.2	412.4	426.2
157.5°	350.6	350.6	355.2	361.3	368.9	373.5	378.1	389.5	400.2	410.9	422.4
160°	359.0	359.0	362.0	367.4	373.5	377.7	381.9	391.1	400.2	408.6	417.8
162.5°	366.6	365.9	368.1	372.7	378.1	381.2	384.2	392.6	400.2	406.3	413.2
165°	372.0	372.0	373.5	377.3	381.1	383.4	385.7	392.6	398.7	403.3	408.6
167.5°	378.1	377.3	378.1	381.1	383.4	385.3	387.2	392.6	397.2	400.2	404.0
170°	381.9	381.1	381.9	384.2	385.7	386.8	388.0	391.8	395.6	397.2	399.5
172.5°	385.7	384.9	384.9	386.5	387.2	388.0	388.8	391.1	394.1	394.1	394.9
175°	388.0	387.2	387.2	388.0	388.8	388.8	388.8	390.3	392.6	391.8	391.8
177.5°	389.5	388.8	388.0	388.8	388.8	388.8	388.8	389.5	391.1	389.5	389.5
180°	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8

TEST NUMBER: P1025220

CATALOG NUMBER: S124DIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6
2.5°	2018.0	2046.8	2059.6	2062.8	2080.4	2069.2	2074.0	2072.4	2085.2	2086.8	2086.8
5°	2165.2	2198.8	2210.0	2226.0	2250.0	2256.4	2251.6	2261.2	2278.8	2266.0	2285.2
7.5°	2320.4	2357.2	2382.8	2418.1	2426.1	2446.9	2459.7	2470.9	2474.1	2475.7	2478.9
10°	2464.5	2510.9	2546.1	2605.3	2618.1	2629.3	2685.3	2662.9	2691.7	2682.1	2685.3
12.5°	2581.3	2672.5	2701.3	2800.5	2810.1	2848.5	2845.3	2880.5	2886.9	2899.7	2886.9
15°	2734.9	2840.5	2886.9	2942.9	2975.0	3019.8	3027.8	3075.8	3095.0	3112.6	3095.0
17.5°	2875.7	2931.7	3050.2	3095.0	3115.8	3139.8	3200.6	3218.2	3247.0	3235.8	3267.8
20°	2946.1	3026.2	3151.0	3227.8	3259.8	3282.2	3333.4	3360.6	3371.8	3371.8	3375.0
22.5°	3008.6	3123.8	3216.6	3304.6	3333.4	3349.4	3379.8	3400.6	3405.4	3408.6	3411.8
25°	3064.6	3168.6	3243.8	3293.4	3304.6	3304.6	3322.2	3309.4	3288.6	3304.6	3314.2
27.5°	3064.6	3138.2	3171.8	3189.4	3189.4	3146.2	3120.6	3067.8	3023.0	3010.2	3039.0
30°	3013.4	3047.0	3000.6	2957.4	2923.7	2894.9	2794.1	2714.1	2698.1	2686.9	2730.1
32.5°	2894.9	2851.7	2760.5	2635.7	2586.1	2520.5	2442.1	2381.2	2344.4	2331.6	2322.0
35°	2685.3	2573.3	2454.9	2286.8	2251.6	2168.4	2061.2	2016.4	1955.6	1954.0	1974.8
37.5°	2456.5	2283.6	2155.6	1995.6	1946.0	1857.9	1757.1	1710.7	1669.1	1637.1	1675.5
40°	2189.2	2038.8	1843.5	1712.3	1641.9	1595.5	1510.7	1459.5	1440.3	1424.3	1448.3
42.5°	1939.6	1774.7	1622.7	1488.3	1430.7	1377.9	1321.8	1272.2	1257.8	1256.2	1273.8
45°	1691.5	1529.9	1389.1	1273.8	1237.0	1205.0	1150.6	1136.2	1112.2	1096.2	1104.2
47.5°	1493.1	1326.6	1209.8	1121.8	1089.8	1062.6	1027.4	1003.4	982.6	976.2	985.8
50°	1297.8	1185.8	1065.8	992.2	968.2	942.6	915.4	893.0	883.4	877.0	883.4
52.5°	1141.0	1021.0	939.4	880.2	856.2	837.0	817.8	808.2	795.3	798.5	804.9
55°	1000.2	894.6	825.8	782.5	768.1	760.1	736.1	724.9	720.1	716.9	720.1
57.5°	867.4	790.5	739.3	702.5	683.3	678.5	659.3	659.3	654.5	649.7	651.3
60°	761.7	696.1	646.5	617.7	614.5	606.5	593.7	592.1	580.9	585.7	587.3
62.5°	654.5	601.7	568.1	550.5	539.3	536.1	528.1	526.5	521.7	523.3	520.1
65°	569.7	526.5	492.9	478.5	473.7	472.1	465.7	460.9	457.7	460.9	457.7
67.5°	484.9	456.1	430.5	416.1	409.7	408.1	403.3	400.1	401.7	396.9	400.1
70°	404.9	376.1	360.1	352.1	348.9	344.1	344.1	344.1	344.1	340.9	339.3
72.5°	340.9	312.1	300.9	296.1	292.9	291.3	286.5	288.1	286.5	284.9	291.3
75°	270.5	252.8	241.6	236.8	240.0	235.2	230.4	233.6	228.8	230.4	236.8
77.5°	204.8	196.8	190.4	187.2	184.0	180.8	180.8	177.6	177.6	177.6	177.6
80°	148.8	147.2	136.0	134.4	134.4	131.2	131.2	131.2	131.2	129.6	131.2
82.5°	99.2	97.6	94.4	92.8	89.6	91.2	91.2	88.0	88.0	86.4	88.0
85°	57.6	57.6	54.4	52.8	51.2	52.8	49.6	48.0	49.6	48.0	49.6
87.5°	27.2	24.0	25.6	24.0	20.8	22.4	19.2	20.8	19.2	17.6	20.8
90°	13.0	13.7	14.5	15.3	15.3	15.3	16.0	16.8	16.0	16.0	16.0
92.5°	249.0	184.1	137.5	108.5	99.0	89.4	77.9	72.6	69.5	69.5	69.5
95°	640.0	566.0	447.6	345.2	308.2	271.1	233.7	210.0	196.3	186.4	196.3
97.5°	802.7	815.0	756.1	672.1	629.4	586.6	534.6	488.8	465.9	447.6	465.9
100°	809.6	921.1	936.4	899.0	870.8	842.5	776.0	729.4	706.5	700.4	706.5
102.5°	752.3	915.8	1006.7	1029.6	1022.0	1014.3	979.9	949.4	924.9	920.4	924.9
105°	680.5	855.4	987.6	1063.2	1078.8	1094.5	1096.0	1089.9	1079.2	1074.6	1079.2
107.5°	621.7	781.3	924.2	1029.6	1061.6	1093.7	1127.3	1141.1	1147.2	1148.0	1147.2
110°	579.7	715.7	847.8	958.5	1000.6	1042.6	1096.8	1128.9	1142.6	1149.5	1142.6

TEST NUMBER: P1025220

CATALOG NUMBER: S124DIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	556.0	667.5	780.6	883.7	925.7	967.7	1031.1	1071.6	1092.2	1104.4	1092.2
115°	543.0	638.5	732.5	821.8	858.5	895.2	955.5	1001.3	1025.8	1031.9	1025.8
117.5°	536.2	621.7	701.2	773.7	805.8	837.9	891.3	931.0	957.0	960.8	957.0
120°	530.8	611.0	682.1	743.2	770.3	797.4	840.9	874.5	894.4	902.8	894.4
122.5°	524.7	601.9	669.8	724.1	747.0	769.9	805.0	832.5	848.6	857.0	848.6
125°	517.8	591.2	656.9	709.6	730.6	751.6	782.1	804.3	818.8	823.4	818.8
127.5°	508.7	578.9	642.3	695.0	714.9	734.8	765.3	785.2	797.4	802.0	797.4
130°	500.3	563.7	624.0	675.9	696.2	716.4	747.7	766.8	779.1	783.6	779.1
132.5°	492.6	547.6	603.4	653.8	674.0	694.3	724.8	747.0	758.4	763.0	758.4
135°	485.0	533.1	582.8	629.4	648.4	667.5	698.1	719.5	731.7	736.3	731.7
137.5°	478.1	519.4	562.9	603.4	621.0	638.5	667.5	689.7	699.6	705.0	699.6
140°	472.8	507.9	543.8	578.2	594.2	610.3	637.0	653.8	664.5	670.6	664.5
142.5°	468.2	497.2	527.8	556.0	569.4	582.8	605.7	621.0	630.1	633.9	630.1
145°	462.9	487.3	513.3	536.2	546.9	557.6	576.7	589.6	597.3	601.1	597.3
147.5°	458.3	478.9	500.3	519.4	528.2	536.9	551.4	562.9	569.0	570.5	569.0
150°	452.9	471.3	488.8	504.1	511.0	517.8	530.1	540.0	544.6	545.3	544.6
152.5°	446.8	462.9	477.4	491.1	496.4	501.8	511.7	519.4	521.7	522.4	521.7
155°	440.7	454.4	466.7	478.1	482.7	487.3	494.9	501.0	503.3	503.3	503.3
157.5°	434.6	445.3	456.0	465.9	469.7	473.5	479.7	484.2	485.8	485.8	485.8
160°	427.7	436.9	445.3	453.7	456.8	459.8	464.4	469.0	469.7	469.7	469.7
162.5°	421.6	428.5	435.4	441.5	444.2	446.8	449.9	454.4	455.2	454.4	455.2
165°	414.7	420.8	425.4	430.8	432.7	434.6	437.6	440.7	439.9	439.2	439.9
167.5°	408.6	413.2	417.0	421.6	422.8	423.9	425.4	427.7	427.7	427.0	427.7
170°	402.5	406.3	408.6	411.7	412.8	414.0	415.5	416.3	415.5	415.5	415.5
172.5°	397.2	400.2	401.7	403.3	404.0	404.8	405.6	406.3	405.6	404.0	405.6
175°	393.3	394.9	395.6	397.2	397.2	397.2	397.2	398.7	397.2	395.6	397.2
177.5°	390.3	391.1	391.8	391.8	392.2	392.6	391.8	392.6	391.1	389.5	391.1
180°	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8

TEST NUMBER: P1025220

CATALOG NUMBER: S124DIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6
2.5°	2083.6	2078.8	2072.4	2072.4	2064.4	2064.4	2051.6	2029.2	2010.0	2003.6	2006.8
5°	2261.2	2262.8	2253.2	2245.2	2230.8	2219.6	2198.8	2158.8	2146.0	2120.4	2102.8
7.5°	2464.5	2458.1	2440.5	2427.7	2424.5	2398.8	2354.0	2306.0	2267.6	2242.0	2205.2
10°	2693.3	2667.7	2642.1	2634.1	2614.9	2571.7	2520.5	2467.7	2414.8	2358.8	2296.4
12.5°	2885.3	2835.7	2834.1	2814.9	2778.1	2754.1	2693.3	2618.1	2526.9	2464.5	2394.0
15°	3091.8	3045.4	3007.0	2971.8	2954.2	2883.7	2832.5	2738.1	2629.3	2562.1	2514.1
17.5°	3239.0	3218.2	3152.6	3136.6	3112.6	3031.0	2949.3	2856.5	2762.1	2667.7	2538.1
20°	3357.4	3344.6	3301.4	3279.0	3240.6	3176.6	3077.4	2970.2	2861.3	2726.9	2605.3
22.5°	3408.6	3392.6	3357.4	3338.2	3314.2	3259.8	3175.0	3053.4	2910.9	2790.9	2661.3
25°	3307.8	3336.6	3327.0	3319.0	3309.4	3277.4	3213.4	3106.2	2967.0	2830.9	2669.3
27.5°	3080.6	3130.2	3178.2	3184.6	3200.6	3213.4	3187.8	3111.0	2994.2	2850.1	2672.5
30°	2774.9	2797.3	2894.9	2923.7	2946.1	3027.8	3075.8	3056.6	2967.0	2837.3	2674.1
32.5°	2382.8	2442.1	2541.3	2610.1	2670.9	2762.1	2886.9	2936.5	2904.5	2798.9	2637.3
35°	2011.6	2082.0	2197.2	2285.2	2346.0	2475.7	2622.9	2730.1	2770.1	2717.3	2573.3
37.5°	1707.5	1792.3	1894.8	1928.4	1998.8	2158.8	2362.0	2510.9	2608.5	2613.3	2501.3
40°	1478.7	1521.9	1603.5	1654.7	1723.5	1857.9	2056.4	2253.2	2400.4	2450.1	2390.8
42.5°	1285.0	1318.6	1379.5	1441.9	1504.3	1606.7	1789.1	1973.2	2171.6	2270.8	2269.2
45°	1131.4	1166.6	1208.2	1259.4	1302.6	1413.1	1557.1	1745.9	1917.2	2070.8	2109.2
47.5°	997.0	1027.4	1078.6	1101.0	1129.8	1233.8	1358.7	1534.7	1712.3	1888.4	1933.2
50°	897.8	923.4	958.6	973.0	1005.0	1081.8	1184.2	1326.6	1523.5	1685.1	1768.3
52.5°	808.2	827.4	854.6	865.8	888.2	945.8	1038.6	1150.6	1313.8	1480.3	1597.1
55°	731.3	744.1	763.3	776.1	792.1	843.4	912.2	1013.0	1153.8	1297.8	1411.5
57.5°	659.3	668.9	688.1	694.5	707.3	747.3	795.3	880.2	1009.8	1137.8	1248.2
60°	592.1	598.5	609.7	624.1	633.7	660.9	705.7	776.1	880.2	997.0	1086.6
62.5°	528.1	537.7	540.9	547.3	555.3	580.9	616.1	667.3	758.5	854.6	949.0
65°	462.5	470.5	476.9	478.5	486.5	505.7	537.7	582.5	641.7	724.9	813.0
67.5°	401.7	406.5	409.7	416.1	424.1	433.7	459.3	492.9	547.3	614.5	684.9
70°	345.7	345.7	350.5	352.1	361.7	372.9	384.1	416.1	464.1	518.5	566.5
72.5°	284.9	292.9	291.3	299.3	297.7	305.7	320.1	340.9	376.1	419.3	465.7
75°	232.0	236.8	236.8	236.8	240.0	246.4	254.4	273.7	300.9	336.1	363.3
77.5°	180.8	184.0	184.0	184.0	185.6	192.0	200.0	212.8	232.0	252.8	268.9
80°	129.6	132.8	132.8	136.0	136.0	137.6	145.6	152.0	161.6	177.6	193.6
82.5°	88.0	89.6	92.8	92.8	91.2	94.4	96.0	102.4	112.0	115.2	126.4
85°	48.0	49.6	51.2	51.2	52.8	56.0	54.4	60.8	60.8	67.2	70.4
87.5°	19.2	22.4	22.4	20.8	22.4	22.4	22.4	25.6	27.2	28.8	27.2
90°	16.8	16.0	15.3	15.3	15.3	14.5	13.7	13.0	13.7	12.2	10.7
92.5°	72.6	77.9	89.4	99.0	108.5	137.5	184.1	249.0	299.4	262.0	190.2
95°	210.0	233.7	271.1	308.2	345.2	447.6	566.0	640.0	622.5	469.7	287.2
97.5°	488.8	534.6	586.6	629.4	672.1	756.1	815.0	802.7	666.0	449.9	262.0
100°	729.4	776.0	842.5	870.8	899.0	936.4	921.1	809.6	614.1	398.7	242.9
102.5°	949.4	979.9	1014.3	1022.0	1029.6	1006.7	915.8	752.3	549.2	364.3	237.5
105°	1089.9	1096.0	1094.5	1078.8	1063.2	987.6	855.4	680.5	501.0	347.5	240.6
107.5°	1141.1	1127.3	1093.7	1061.6	1029.6	924.2	781.3	621.7	469.7	342.9	249.8
110°	1128.9	1096.8	1042.6	1000.6	958.5	847.8	715.7	579.7	455.2	344.5	260.4

TEST NUMBER: P1025220

CATALOG NUMBER: S124DIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1071.6	1031.1	967.7	925.7	883.7	780.6	667.5	556.0	448.3	349.0	271.9
115°	1001.3	955.5	895.2	858.5	821.8	732.5	638.5	543.0	446.8	355.2	284.1
117.5°	931.0	891.3	837.9	805.8	773.7	701.2	621.7	536.2	446.0	361.3	296.3
120°	874.5	840.9	797.4	770.3	743.2	682.1	611.0	530.8	446.0	368.1	309.3
122.5°	832.5	805.0	769.9	747.0	724.1	669.8	601.9	524.7	445.3	375.0	321.6
125°	804.3	782.1	751.6	730.6	709.6	656.9	591.2	517.8	444.5	381.9	333.8
127.5°	785.2	765.3	734.8	714.9	695.0	642.3	578.9	508.7	443.0	387.2	344.5
130°	766.8	747.7	716.4	696.2	675.9	624.0	563.7	500.3	442.2	393.3	354.4
132.5°	747.0	724.8	694.3	674.0	653.8	603.4	547.6	492.6	441.5	398.7	364.3
135°	719.5	698.1	667.5	648.4	629.4	582.8	533.1	485.0	440.7	404.0	372.7
137.5°	689.7	667.5	638.5	621.0	603.4	562.9	519.4	478.1	440.7	407.1	378.8
140°	653.8	637.0	610.3	594.2	578.2	543.8	507.9	472.8	439.9	410.9	384.9
142.5°	621.0	605.7	582.8	569.4	556.0	527.8	497.2	468.2	439.9	414.0	389.5
145°	589.6	576.7	557.6	546.9	536.2	513.3	487.3	462.9	438.4	414.7	392.6
147.5°	562.9	551.4	536.9	528.2	519.4	500.3	478.9	458.3	436.1	415.5	395.6
150°	540.0	530.1	517.8	511.0	504.1	488.8	471.3	452.9	433.8	415.5	397.9
152.5°	519.4	511.7	501.8	496.4	491.1	477.4	462.9	446.8	430.0	414.0	399.5
155°	501.0	494.9	487.3	482.7	478.1	466.7	454.4	440.7	426.2	412.4	400.2
157.5°	484.2	479.7	473.5	469.7	465.9	456.0	445.3	434.6	422.4	410.9	400.2
160°	469.0	464.4	459.8	456.8	453.7	445.3	436.9	427.7	417.8	408.6	400.2
162.5°	454.4	449.9	446.8	444.2	441.5	435.4	428.5	421.6	413.2	406.3	400.2
165°	440.7	437.6	434.6	432.7	430.8	425.4	420.8	414.7	408.6	403.3	398.7
167.5°	427.7	425.4	423.9	422.8	421.6	417.0	413.2	408.6	404.0	400.2	397.2
170°	416.3	415.5	414.0	412.8	411.7	408.6	406.3	402.5	399.5	397.2	395.6
172.5°	406.3	405.6	404.8	404.0	403.3	401.7	400.2	397.2	394.9	394.1	394.1
175°	398.7	397.2	397.2	397.2	397.2	395.6	394.9	393.3	391.8	391.8	392.6
177.5°	392.6	391.8	392.6	392.2	391.8	391.8	391.1	390.3	389.5	389.5	391.1
180°	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8

TEST NUMBER: P1025220

CATALOG NUMBER: S124DIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6
2.5°	1992.4	1986.0	1981.2	1981.2	1966.8	1952.4	1944.4	1941.2	1938.0	1925.2	1907.6
5°	2074.0	2053.2	2038.8	2024.4	2000.4	1974.8	1949.2	1934.8	1914.0	1885.2	1864.3
7.5°	2165.2	2115.6	2099.6	2082.0	2034.0	1990.8	1955.6	1925.2	1891.6	1854.7	1817.9
10°	2242.0	2189.2	2154.0	2123.6	2061.2	2003.6	1950.8	1906.0	1862.7	1814.7	1769.9
12.5°	2315.6	2240.4	2203.6	2158.8	2093.2	2010.0	1941.2	1885.2	1821.1	1771.5	1717.1
15°	2418.1	2291.6	2230.8	2202.0	2114.0	2016.4	1933.2	1849.9	1797.1	1721.9	1673.9
17.5°	2434.1	2331.6	2291.6	2218.0	2112.4	2002.0	1906.0	1822.7	1742.7	1675.5	1613.1
20°	2490.1	2355.6	2291.6	2245.2	2106.0	1994.0	1888.4	1781.1	1704.3	1632.3	1561.9
22.5°	2525.3	2373.2	2306.0	2232.4	2099.6	1965.2	1840.3	1747.5	1653.1	1579.5	1523.5
25°	2515.7	2363.6	2288.4	2219.6	2058.0	1923.6	1811.5	1693.1	1605.1	1525.1	1451.5
27.5°	2510.9	2339.6	2259.6	2182.8	2030.8	1890.0	1749.1	1653.1	1555.5	1462.7	1408.3
30°	2498.1	2309.2	2216.4	2133.2	1974.8	1827.5	1707.5	1595.5	1497.9	1413.1	1341.0
32.5°	2454.9	2258.0	2168.4	2078.8	1914.0	1766.7	1645.1	1541.1	1443.5	1355.5	1286.6
35°	2397.2	2197.2	2099.6	2005.2	1840.3	1691.5	1579.5	1470.7	1379.5	1294.6	1229.0
37.5°	2339.6	2126.8	2035.6	1926.8	1774.7	1619.5	1504.3	1406.7	1321.8	1233.8	1161.8
40°	2256.4	2043.6	1942.8	1849.9	1672.3	1526.7	1421.1	1333.0	1249.8	1166.6	1105.8
42.5°	2142.8	1952.4	1848.3	1745.9	1579.5	1435.5	1333.0	1254.6	1176.2	1107.4	1040.2
45°	2027.6	1841.9	1749.1	1657.9	1477.1	1341.0	1246.6	1174.6	1109.0	1033.8	979.4
47.5°	1888.4	1731.5	1638.7	1549.1	1377.9	1241.8	1155.4	1088.2	1027.4	965.0	913.8
50°	1745.9	1609.9	1525.1	1432.3	1269.0	1145.8	1061.0	1005.0	955.4	896.2	854.6
52.5°	1592.3	1473.9	1401.9	1312.2	1168.2	1054.6	968.2	912.2	870.6	827.4	790.5
55°	1429.1	1342.7	1265.8	1193.8	1057.8	955.4	878.6	829.0	800.1	760.1	728.1
57.5°	1281.8	1198.6	1152.2	1070.6	952.2	851.4	790.5	748.9	715.3	691.3	665.7
60°	1128.2	1061.0	1009.8	950.6	846.6	761.7	697.7	673.7	638.5	620.9	609.7
62.5°	981.0	933.0	885.0	840.2	747.3	667.3	619.3	588.9	568.1	550.5	540.9
65°	841.8	796.9	763.3	723.3	646.5	582.5	537.7	513.7	492.9	488.1	476.9
67.5°	705.7	686.5	649.7	617.7	552.1	502.5	468.9	438.5	427.3	422.5	412.9
70°	590.5	568.1	539.3	512.1	462.5	419.3	388.9	377.7	361.7	360.1	348.9
72.5°	486.5	459.3	438.5	417.7	380.9	342.5	326.5	310.5	302.5	296.1	291.3
75°	385.7	366.5	352.1	334.5	302.5	276.9	254.4	248.0	243.2	241.6	238.4
77.5°	288.1	275.3	268.9	251.2	228.8	206.4	196.8	187.2	187.2	184.0	185.6
80°	204.8	196.8	188.8	179.2	160.0	150.4	142.4	136.0	132.8	131.2	132.8
82.5°	129.6	124.8	123.2	116.8	104.0	99.2	92.8	88.0	88.0	88.0	88.0
85°	72.0	72.0	72.0	62.4	57.6	52.8	49.6	48.0	48.0	48.0	49.6
87.5°	30.4	30.4	25.6	25.6	24.0	20.8	19.2	19.2	20.8	20.8	22.4
90°	10.7	6.1	6.1	6.1	5.3	4.6	2.3	0.8	2.3	4.6	5.3
92.5°	116.1	68.7	58.8	48.9	35.1	23.7	15.3	10.7	15.3	23.7	35.1
95°	161.9	95.5	79.4	63.4	45.1	35.1	27.5	25.2	27.5	35.1	45.1
97.5°	154.3	101.6	87.8	74.1	58.0	48.9	42.0	42.0	42.0	48.9	58.0
100°	156.6	111.5	99.3	87.1	72.6	63.4	58.0	58.0	58.0	63.4	72.6
102.5°	164.2	124.5	113.0	101.6	87.8	79.4	74.9	73.3	74.9	79.4	87.8
105°	177.2	140.5	129.4	118.4	104.6	95.5	91.7	89.4	91.7	95.5	104.6
107.5°	190.9	157.3	146.2	135.2	122.2	112.3	108.5	106.9	108.5	112.3	122.2
110°	207.0	173.4	163.1	152.8	139.0	129.8	126.0	124.5	126.0	129.8	139.0

TEST NUMBER: P1025220

CATALOG NUMBER: S124DIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	222.3	190.2	179.9	169.6	155.8	147.4	142.8	141.3	142.8	147.4	155.8
115°	238.3	207.7	197.4	187.1	172.6	165.0	159.6	157.3	159.6	165.0	172.6
117.5°	253.6	224.6	213.9	203.2	189.4	181.0	176.4	174.1	176.4	181.0	189.4
120°	269.6	240.6	229.9	219.2	206.2	197.8	192.5	190.9	192.5	197.8	206.2
122.5°	284.9	255.9	245.6	235.2	220.7	213.1	207.7	206.2	207.7	213.1	220.7
125°	298.6	271.1	260.5	249.8	235.2	226.8	222.3	219.2	222.3	226.8	235.2
127.5°	311.6	284.9	274.2	263.5	248.2	239.1	233.7	231.4	233.7	239.1	248.2
130°	324.6	298.6	287.6	276.5	262.0	250.5	244.4	241.4	244.4	250.5	262.0
132.5°	335.3	309.3	299.0	288.7	272.7	262.0	253.6	251.3	253.6	262.0	272.7
135°	345.2	320.0	310.1	300.2	284.1	271.1	263.5	260.4	263.5	271.1	284.1
137.5°	352.9	329.2	319.6	310.1	293.3	281.1	272.7	269.6	272.7	281.1	293.3
140°	360.5	337.6	328.5	319.3	303.2	290.2	281.8	279.5	281.8	290.2	303.2
142.5°	367.4	345.2	336.4	327.7	312.4	300.2	292.5	290.2	292.5	300.2	312.4
145°	372.0	352.1	343.7	335.3	320.8	310.1	302.5	300.2	302.5	310.1	320.8
147.5°	377.3	358.2	350.5	342.9	330.7	319.3	312.4	311.6	312.4	319.3	330.7
150°	381.1	364.3	357.0	349.8	338.4	329.2	323.1	322.3	323.1	329.2	338.4
152.5°	384.2	369.7	363.2	356.7	346.8	338.4	332.2	332.2	332.2	338.4	346.8
155°	387.2	374.3	368.6	362.8	354.4	346.8	342.2	341.4	342.2	346.8	354.4
157.5°	389.5	378.1	373.5	368.9	361.3	355.2	350.6	350.6	350.6	355.2	361.3
160°	391.1	381.9	377.7	373.5	367.4	362.0	359.0	359.0	359.0	362.0	367.4
162.5°	392.6	384.2	381.2	378.1	372.7	368.1	365.9	366.6	365.9	368.1	372.7
165°	392.6	385.7	383.4	381.1	377.3	373.5	372.0	372.0	372.0	373.5	377.3
167.5°	392.6	387.2	385.3	383.4	381.1	378.1	377.3	378.1	377.3	378.1	381.1
170°	391.8	388.0	386.8	385.7	384.2	381.9	381.1	381.9	381.1	381.9	384.2
172.5°	391.1	388.8	388.0	387.2	386.5	384.9	384.9	385.7	384.9	384.9	386.5
175°	390.3	388.8	388.8	388.8	388.0	387.2	387.2	388.0	387.2	387.2	388.0
177.5°	389.5	388.8	388.8	388.8	388.8	388.0	388.8	389.5	388.8	388.0	388.8
180°	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8

TEST NUMBER: P1025220

CATALOG NUMBER: S124DIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6
2.5°	1902.8	1896.4	1899.6	1883.6	1869.1	1848.3	1830.7	1827.5	1824.3	1833.9	1827.5
5°	1848.3	1840.3	1832.3	1813.1	1784.3	1766.7	1741.1	1739.5	1729.9	1715.5	1718.7
7.5°	1789.1	1784.3	1773.1	1742.7	1717.1	1686.7	1665.9	1648.3	1640.3	1627.5	1622.7
10°	1741.1	1723.5	1713.9	1680.3	1649.9	1617.9	1590.7	1577.9	1563.5	1552.3	1544.3
12.5°	1675.5	1670.7	1643.5	1616.3	1590.7	1553.9	1533.1	1496.3	1477.1	1486.7	1483.5
15°	1632.3	1609.9	1603.5	1565.1	1521.9	1497.9	1459.5	1435.5	1427.5	1413.1	1395.5
17.5°	1574.7	1560.3	1537.9	1502.7	1453.1	1419.5	1392.3	1369.9	1360.3	1341.0	1326.6
20°	1520.3	1496.3	1478.7	1446.7	1398.7	1355.5	1321.8	1307.4	1283.4	1267.4	1259.4
22.5°	1470.7	1453.1	1427.5	1379.5	1337.8	1296.2	1256.2	1235.4	1213.0	1203.4	1190.6
25°	1409.9	1381.1	1363.5	1310.6	1265.8	1232.2	1195.4	1168.2	1155.4	1139.4	1136.2
27.5°	1350.7	1323.4	1302.6	1256.2	1201.8	1158.6	1136.2	1117.0	1094.6	1094.6	1086.6
30°	1291.4	1272.2	1240.2	1195.4	1144.2	1102.6	1077.0	1059.4	1051.4	1045.0	1043.4
32.5°	1232.2	1206.6	1187.4	1126.6	1088.2	1049.8	1030.6	1016.2	1006.6	1005.0	1006.6
35°	1171.4	1142.6	1123.4	1069.0	1030.6	995.4	987.4	974.6	969.8	968.2	976.2
37.5°	1107.4	1085.0	1061.0	1016.2	973.0	952.2	936.2	931.4	929.8	939.4	942.6
40°	1048.2	1029.0	1006.6	958.6	926.6	904.2	896.2	891.4	897.8	907.4	912.2
42.5°	992.2	965.0	947.4	904.2	875.4	862.6	853.0	853.0	859.4	870.6	878.6
45°	933.0	912.2	894.6	856.2	830.6	816.2	814.6	816.2	824.2	832.2	841.8
47.5°	875.4	854.6	835.4	803.3	780.9	772.9	771.3	772.9	785.7	796.9	808.2
50°	822.6	800.1	782.5	752.1	734.5	724.9	726.5	734.5	744.1	760.1	774.5
52.5°	760.1	744.1	728.1	700.9	684.9	678.5	683.3	689.7	707.3	718.5	736.1
55°	699.3	684.9	672.1	651.3	638.5	633.7	636.9	646.5	660.9	680.1	700.9
57.5°	643.3	627.3	614.5	600.1	585.7	587.3	588.9	601.7	619.3	636.9	660.9
60°	580.9	571.3	560.1	542.5	536.1	536.1	540.9	555.3	571.3	600.1	620.9
62.5°	524.9	512.1	504.1	492.9	483.3	484.9	496.1	508.9	528.1	552.1	579.3
65°	467.3	452.9	446.5	436.9	433.7	435.3	443.3	462.5	483.3	504.1	529.7
67.5°	403.3	398.5	392.1	382.5	385.7	387.3	395.3	411.3	433.7	454.5	483.3
70°	348.9	339.3	337.7	329.7	329.7	334.5	350.5	361.7	382.5	404.9	435.3
72.5°	291.3	283.3	283.3	276.9	281.7	286.5	294.5	310.5	329.7	352.1	377.7
75°	232.0	228.8	232.0	228.8	228.8	236.8	246.4	259.2	280.1	304.1	324.9
77.5°	179.2	179.2	177.6	182.4	182.4	187.2	200.0	212.8	228.8	248.0	270.5
80°	131.2	131.2	131.2	136.0	140.8	140.8	148.8	164.8	179.2	192.0	212.8
82.5°	89.6	89.6	89.6	92.8	99.2	99.2	108.8	118.4	134.4	145.6	155.2
85°	54.4	54.4	52.8	56.0	57.6	62.4	70.4	76.8	84.8	94.4	104.0
87.5°	24.0	24.0	25.6	27.2	28.8	32.0	35.2	38.4	46.4	49.6	54.4
90°	6.1	6.1	6.1	10.7	10.7	12.2	13.7	13.0	13.7	14.5	15.3
92.5°	48.9	58.8	68.7	116.1	190.2	262.0	299.4	249.0	184.1	137.5	108.5
95°	63.4	79.4	95.5	161.9	287.2	469.7	622.5	640.0	566.0	447.6	345.2
97.5°	74.1	87.8	101.6	154.3	262.0	449.9	666.0	802.7	815.0	756.1	672.1
100°	87.1	99.3	111.5	156.6	242.9	398.7	614.1	809.6	921.1	936.4	899.0
102.5°	101.6	113.0	124.5	164.2	237.5	364.3	549.2	752.3	915.8	1006.7	1029.6
105°	118.4	129.4	140.5	177.2	240.6	347.5	501.0	680.5	855.4	987.6	1063.2
107.5°	135.2	146.2	157.3	190.9	249.8	342.9	469.7	621.7	781.3	924.2	1029.6
110°	152.8	163.1	173.4	207.0	260.4	344.5	455.2	579.7	715.7	847.8	958.5

TEST NUMBER: P1025220

CATALOG NUMBER: S124DIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	169.6	179.9	190.2	222.3	271.9	349.0	448.3	556.0	667.5	780.6	883.7
115°	187.1	197.4	207.7	238.3	284.1	355.2	446.8	543.0	638.5	732.5	821.8
117.5°	203.2	213.9	224.6	253.6	296.3	361.3	446.0	536.2	621.7	701.2	773.7
120°	219.2	229.9	240.6	269.6	309.3	368.1	446.0	530.8	611.0	682.1	743.2
122.5°	235.2	245.6	255.9	284.9	321.6	375.0	445.3	524.7	601.9	669.8	724.1
125°	249.8	260.5	271.1	298.6	333.8	381.9	444.5	517.8	591.2	656.9	709.6
127.5°	263.5	274.2	284.9	311.6	344.5	387.2	443.0	508.7	578.9	642.3	695.0
130°	276.5	287.6	298.6	324.6	354.4	393.3	442.2	500.3	563.7	624.0	675.9
132.5°	288.7	299.0	309.3	335.3	364.3	398.7	441.5	492.6	547.6	603.4	653.8
135°	300.2	310.1	320.0	345.2	372.7	404.0	440.7	485.0	533.1	582.8	629.4
137.5°	310.1	319.6	329.2	352.9	378.8	407.1	440.7	478.1	519.4	562.9	603.4
140°	319.3	328.5	337.6	360.5	384.9	410.9	439.9	472.8	507.9	543.8	578.2
142.5°	327.7	336.4	345.2	367.4	389.5	414.0	439.9	468.2	497.2	527.8	556.0
145°	335.3	343.7	352.1	372.0	392.6	414.7	438.4	462.9	487.3	513.3	536.2
147.5°	342.9	350.5	358.2	377.3	395.6	415.5	436.1	458.3	478.9	500.3	519.4
150°	349.8	357.0	364.3	381.1	397.9	415.5	433.8	452.9	471.3	488.8	504.1
152.5°	356.7	363.2	369.7	384.2	399.5	414.0	430.0	446.8	462.9	477.4	491.1
155°	362.8	368.6	374.3	387.2	400.2	412.4	426.2	440.7	454.4	466.7	478.1
157.5°	368.9	373.5	378.1	389.5	400.2	410.9	422.4	434.6	445.3	456.0	465.9
160°	373.5	377.7	381.9	391.1	400.2	408.6	417.8	427.7	436.9	445.3	453.7
162.5°	378.1	381.2	384.2	392.6	400.2	406.3	413.2	421.6	428.5	435.4	441.5
165°	381.1	383.4	385.7	392.6	398.7	403.3	408.6	414.7	420.8	425.4	430.8
167.5°	383.4	385.3	387.2	392.6	397.2	400.2	404.0	408.6	413.2	417.0	421.6
170°	385.7	386.8	388.0	391.8	395.6	397.2	399.5	402.5	406.3	408.6	411.7
172.5°	387.2	388.0	388.8	391.1	394.1	394.1	394.9	397.2	400.2	401.7	403.3
175°	388.8	388.8	388.8	390.3	392.6	391.8	391.8	393.3	394.9	395.6	397.2
177.5°	388.8	388.8	388.8	389.5	391.1	389.5	389.5	390.3	391.1	391.8	391.8
180°	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8

TEST NUMBER: P1025220

CATALOG NUMBER: S124DIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6
2.5°	1822.7	1821.1	1813.1	1816.3	1806.7	1809.9	1814.7	1816.3	1822.7	1817.9	1816.3
5°	1710.7	1707.5	1702.7	1697.9	1696.3	1702.7	1691.5	1694.7	1697.9	1702.7	1709.1
7.5°	1619.5	1617.9	1613.1	1605.1	1601.9	1598.7	1600.3	1611.5	1609.9	1608.3	1619.5
10°	1536.3	1537.9	1528.3	1526.7	1517.1	1515.5	1517.1	1520.3	1525.1	1531.5	1533.1
12.5°	1449.9	1470.7	1453.1	1446.7	1432.3	1440.3	1443.5	1429.1	1437.1	1441.9	1465.9
15°	1395.5	1385.9	1374.7	1374.7	1368.3	1365.1	1357.1	1368.3	1374.7	1384.3	1381.1
17.5°	1320.2	1304.2	1297.8	1291.4	1293.0	1299.4	1281.8	1307.4	1307.4	1312.2	1304.2
20°	1254.6	1241.8	1233.8	1230.6	1225.8	1222.6	1221.0	1227.4	1237.0	1240.2	1248.2
22.5°	1185.8	1185.8	1173.0	1168.2	1165.0	1160.2	1168.2	1163.4	1169.8	1176.2	1189.0
25°	1128.2	1128.2	1123.4	1117.0	1112.2	1109.0	1113.8	1112.2	1117.0	1125.0	1128.2
27.5°	1081.8	1077.0	1075.4	1073.8	1072.2	1073.8	1072.2	1077.0	1081.8	1083.4	1080.2
30°	1041.8	1037.0	1038.6	1038.6	1040.2	1038.6	1037.0	1041.8	1043.4	1040.2	1041.8
32.5°	1005.0	1005.0	1008.2	1009.8	1009.8	1011.4	1013.0	1009.8	1011.4	1006.6	1008.2
35°	974.6	977.8	981.0	982.6	984.2	982.6	985.8	984.2	981.0	977.8	976.2
37.5°	944.2	947.4	953.8	955.4	960.2	961.8	958.6	958.6	957.0	950.6	947.4
40°	912.2	915.4	923.4	928.2	931.4	936.2	933.0	933.0	926.6	920.2	915.4
42.5°	881.8	888.2	896.2	901.0	907.4	907.4	907.4	904.2	896.2	889.8	885.0
45°	851.4	853.0	864.2	872.2	878.6	878.6	878.6	873.8	869.0	856.2	849.8
47.5°	817.8	822.6	835.4	843.4	849.8	851.4	851.4	846.6	837.0	825.8	817.8
50°	780.9	788.9	803.3	814.6	822.6	825.8	821.0	817.8	806.6	793.7	784.1
52.5°	745.7	755.3	772.9	782.5	793.7	795.3	793.7	788.9	776.1	758.5	750.5
55°	710.5	718.5	737.7	753.7	763.3	766.5	763.3	755.3	739.3	721.7	713.7
57.5°	672.1	683.3	704.1	720.1	731.3	732.9	729.7	721.7	708.9	686.5	675.3
60°	632.1	646.5	667.3	683.3	697.7	699.3	696.1	684.9	668.9	646.5	636.9
62.5°	592.1	603.3	627.3	644.9	656.1	664.1	657.7	646.5	630.5	608.1	593.7
65°	545.7	561.7	582.5	598.5	611.3	612.9	609.7	600.1	582.5	558.5	547.3
67.5°	500.9	512.1	532.9	553.7	558.5	563.3	558.5	548.9	534.5	513.7	497.7
70°	446.5	456.1	481.7	496.1	502.5	507.3	504.1	494.5	481.7	462.5	449.7
72.5°	392.1	400.1	424.1	435.3	448.1	446.5	444.9	438.5	420.9	408.1	400.1
75°	334.5	344.1	360.1	374.5	379.3	379.3	379.3	374.5	363.3	342.5	334.5
77.5°	281.7	286.5	299.3	307.3	312.1	313.7	312.1	304.1	297.7	283.3	278.5
80°	216.0	228.8	238.4	240.0	246.4	246.4	246.4	243.2	236.8	222.4	220.8
82.5°	163.2	166.4	176.0	180.8	184.0	182.4	182.4	176.0	174.4	166.4	163.2
85°	110.4	115.2	113.6	120.0	121.6	118.4	118.4	121.6	113.6	115.2	110.4
87.5°	60.8	60.8	64.0	62.4	68.8	68.8	65.6	67.2	64.0	62.4	60.8
90°	15.3	15.3	16.0	16.8	16.0	16.0	16.0	16.8	16.0	15.3	15.3
92.5°	99.0	89.4	77.9	72.6	69.5	69.5	69.5	72.6	77.9	89.4	99.0
95°	308.2	271.1	233.7	210.0	196.3	186.4	196.3	210.0	233.7	271.1	308.2
97.5°	629.4	586.6	534.6	488.8	465.9	447.6	465.9	488.8	534.6	586.6	629.4
100°	870.8	842.5	776.0	729.4	706.5	700.4	706.5	729.4	776.0	842.5	870.8
102.5°	1022.0	1014.3	979.9	949.4	924.9	920.4	924.9	949.4	979.9	1014.3	1022.0
105°	1078.8	1094.5	1096.0	1089.9	1079.2	1074.6	1079.2	1089.9	1096.0	1094.5	1078.8
107.5°	1061.6	1093.7	1127.3	1141.1	1147.2	1148.0	1147.2	1141.1	1127.3	1093.7	1061.6
110°	1000.6	1042.6	1096.8	1128.9	1142.6	1149.5	1142.6	1128.9	1096.8	1042.6	1000.6

TEST NUMBER: P1025220

CATALOG NUMBER: S124DIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	925.7	967.7	1031.1	1071.6	1092.2	1104.4	1092.2	1071.6	1031.1	967.7	925.7
115°	858.5	895.2	955.5	1001.3	1025.8	1031.9	1025.8	1001.3	955.5	895.2	858.5
117.5°	805.8	837.9	891.3	931.0	957.0	960.8	957.0	931.0	891.3	837.9	805.8
120°	770.3	797.4	840.9	874.5	894.4	902.8	894.4	874.5	840.9	797.4	770.3
122.5°	747.0	769.9	805.0	832.5	848.6	857.0	848.6	832.5	805.0	769.9	747.0
125°	730.6	751.6	782.1	804.3	818.8	823.4	818.8	804.3	782.1	751.6	730.6
127.5°	714.9	734.8	765.3	785.2	797.4	802.0	797.4	785.2	765.3	734.8	714.9
130°	696.2	716.4	747.7	766.8	779.1	783.6	779.1	766.8	747.7	716.4	696.2
132.5°	674.0	694.3	724.8	747.0	758.4	763.0	758.4	747.0	724.8	694.3	674.0
135°	648.4	667.5	698.1	719.5	731.7	736.3	731.7	719.5	698.1	667.5	648.4
137.5°	621.0	638.5	667.5	689.7	699.6	705.0	699.6	689.7	667.5	638.5	621.0
140°	594.2	610.3	637.0	653.8	664.5	670.6	664.5	653.8	637.0	610.3	594.2
142.5°	569.4	582.8	605.7	621.0	630.1	633.9	630.1	621.0	605.7	582.8	569.4
145°	546.9	557.6	576.7	589.6	597.3	601.1	597.3	589.6	576.7	557.6	546.9
147.5°	528.2	536.9	551.4	562.9	569.0	570.5	569.0	562.9	551.4	536.9	528.2
150°	511.0	517.8	530.1	540.0	544.6	545.3	544.6	540.0	530.1	517.8	511.0
152.5°	496.4	501.8	511.7	519.4	521.7	522.4	521.7	519.4	511.7	501.8	496.4
155°	482.7	487.3	494.9	501.0	503.3	503.3	503.3	501.0	494.9	487.3	482.7
157.5°	469.7	473.5	479.7	484.2	485.8	485.8	485.8	484.2	479.7	473.5	469.7
160°	456.8	459.8	464.4	469.0	469.7	469.7	469.7	469.0	464.4	459.8	456.8
162.5°	444.2	446.8	449.9	454.4	455.2	454.4	455.2	454.4	449.9	446.8	444.2
165°	432.7	434.6	437.6	440.7	439.9	439.2	439.9	440.7	437.6	434.6	432.7
167.5°	422.8	423.9	425.4	427.7	427.7	427.0	427.7	427.7	425.4	423.9	422.8
170°	412.8	414.0	415.5	416.3	415.5	415.5	415.5	416.3	415.5	414.0	412.8
172.5°	404.0	404.8	405.6	406.3	405.6	404.0	405.6	406.3	405.6	404.8	404.0
175°	397.2	397.2	397.2	398.7	397.2	395.6	397.2	398.7	397.2	397.2	397.2
177.5°	392.2	392.6	391.8	392.6	391.1	389.5	391.1	392.6	391.8	392.6	392.2
180°	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8

TEST NUMBER: P1025220

CATALOG NUMBER: S124DIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6	1931.6
2.5°	1816.3	1825.9	1816.3	1822.7	1825.9	1833.9	1837.1	1851.5	1856.3	1867.5	1867.5
5°	1707.5	1712.3	1713.9	1720.3	1726.7	1742.7	1753.9	1774.7	1798.7	1801.9	1816.3
7.5°	1619.5	1627.5	1640.3	1635.5	1646.7	1670.7	1685.1	1710.7	1734.7	1747.5	1765.1
10°	1541.1	1550.7	1555.5	1560.3	1581.1	1601.9	1624.3	1641.9	1673.9	1693.1	1707.5
12.5°	1477.1	1469.1	1478.7	1496.3	1520.3	1533.1	1563.5	1590.7	1614.7	1635.5	1648.3
15°	1393.9	1400.3	1409.9	1440.3	1446.7	1478.7	1489.9	1520.3	1565.1	1584.3	1600.3
17.5°	1313.8	1334.6	1353.9	1365.1	1384.3	1409.9	1441.9	1475.5	1504.3	1526.7	1545.9
20°	1249.8	1270.6	1281.8	1289.8	1309.0	1344.3	1374.7	1416.3	1453.1	1470.7	1496.3
22.5°	1198.6	1198.6	1214.6	1238.6	1249.8	1283.4	1309.0	1353.9	1393.9	1416.3	1440.3
25°	1134.6	1144.2	1157.0	1177.8	1193.8	1221.0	1257.8	1296.2	1339.4	1358.7	1389.1
27.5°	1081.8	1093.0	1110.6	1115.4	1131.4	1155.4	1193.8	1235.4	1280.2	1301.0	1326.6
30°	1041.8	1048.2	1054.6	1064.2	1078.6	1099.4	1131.4	1168.2	1222.6	1238.6	1270.6
32.5°	1006.6	1009.8	1013.0	1021.0	1029.0	1049.8	1075.4	1115.4	1160.2	1184.2	1213.0
35°	974.6	971.4	973.0	977.8	985.8	993.8	1021.0	1054.6	1096.2	1125.0	1147.4
37.5°	944.2	937.8	936.2	936.2	939.4	949.0	969.8	998.6	1043.4	1067.4	1089.8
40°	910.6	904.2	901.0	899.4	897.8	904.2	920.2	949.0	984.2	1006.6	1032.2
42.5°	878.6	872.2	864.2	862.6	859.4	862.6	873.8	901.0	931.4	953.8	974.6
45°	846.6	835.4	825.8	819.4	821.0	816.2	824.2	845.0	880.2	894.6	915.4
47.5°	811.4	798.5	785.7	779.3	772.9	776.1	779.3	796.9	827.4	841.8	862.6
50°	777.7	760.1	745.7	737.7	732.9	729.7	732.9	750.5	772.9	785.7	803.3
52.5°	739.3	721.7	707.3	694.5	688.1	683.3	684.9	700.9	721.7	734.5	752.1
55°	704.1	681.7	662.5	646.5	641.7	640.1	638.5	649.7	667.3	680.1	694.5
57.5°	664.1	641.7	620.9	601.7	592.1	590.5	590.5	593.7	616.1	625.7	633.7
60°	624.1	600.1	577.7	560.1	545.7	540.9	539.3	545.7	556.9	566.5	577.7
62.5°	579.3	555.3	528.1	512.1	497.7	484.9	489.7	491.3	507.3	512.1	521.7
65°	536.1	508.9	486.5	460.9	444.9	436.9	433.7	436.9	449.7	451.3	457.7
67.5°	486.5	460.9	433.7	416.1	401.7	387.3	384.1	384.1	390.5	395.3	403.3
70°	438.5	412.9	382.5	363.3	348.9	336.1	331.3	329.7	334.5	337.7	345.7
72.5°	382.5	356.9	334.5	313.7	296.1	286.5	281.7	278.5	283.3	286.5	288.1
75°	323.3	302.5	280.1	259.2	248.0	238.4	232.0	227.2	230.4	230.4	230.4
77.5°	267.2	246.4	228.8	214.4	200.0	188.8	184.0	179.2	180.8	180.8	184.0
80°	208.0	193.6	179.2	166.4	153.6	144.0	140.8	136.0	132.8	131.2	131.2
82.5°	153.6	142.4	129.6	118.4	112.0	102.4	99.2	92.8	92.8	91.2	91.2
85°	102.4	96.0	83.2	75.2	70.4	65.6	62.4	59.2	54.4	54.4	52.8
87.5°	54.4	51.2	48.0	38.4	38.4	33.6	32.0	30.4	25.6	27.2	27.2
90°	15.3	14.5	13.7	13.0	13.7	12.2	10.7	10.7	6.1	6.1	6.1
92.5°	108.5	137.5	184.1	249.0	299.4	262.0	190.2	116.1	68.7	58.8	48.9
95°	345.2	447.6	566.0	640.0	622.5	469.7	287.2	161.9	95.5	79.4	63.4
97.5°	672.1	756.1	815.0	802.7	666.0	449.9	262.0	154.3	101.6	87.8	74.1
100°	899.0	936.4	921.1	809.6	614.1	398.7	242.9	156.6	111.5	99.3	87.1
102.5°	1029.6	1006.7	915.8	752.3	549.2	364.3	237.5	164.2	124.5	113.0	101.6
105°	1063.2	987.6	855.4	680.5	501.0	347.5	240.6	177.2	140.5	129.4	118.4
107.5°	1029.6	924.2	781.3	621.7	469.7	342.9	249.8	190.9	157.3	146.2	135.2
110°	958.5	847.8	715.7	579.7	455.2	344.5	260.4	207.0	173.4	163.1	152.8

TEST NUMBER: P1025220

CATALOG NUMBER: S124DIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	883.7	780.6	667.5	556.0	448.3	349.0	271.9	222.3	190.2	179.9	169.6
115°	821.8	732.5	638.5	543.0	446.8	355.2	284.1	238.3	207.7	197.4	187.1
117.5°	773.7	701.2	621.7	536.2	446.0	361.3	296.3	253.6	224.6	213.9	203.2
120°	743.2	682.1	611.0	530.8	446.0	368.1	309.3	269.6	240.6	229.9	219.2
122.5°	724.1	669.8	601.9	524.7	445.3	375.0	321.6	284.9	255.9	245.6	235.2
125°	709.6	656.9	591.2	517.8	444.5	381.9	333.8	298.6	271.1	260.5	249.8
127.5°	695.0	642.3	578.9	508.7	443.0	387.2	344.5	311.6	284.9	274.2	263.5
130°	675.9	624.0	563.7	500.3	442.2	393.3	354.4	324.6	298.6	287.6	276.5
132.5°	653.8	603.4	547.6	492.6	441.5	398.7	364.3	335.3	309.3	299.0	288.7
135°	629.4	582.8	533.1	485.0	440.7	404.0	372.7	345.2	320.0	310.1	300.2
137.5°	603.4	562.9	519.4	478.1	440.7	407.1	378.8	352.9	329.2	319.6	310.1
140°	578.2	543.8	507.9	472.8	439.9	410.9	384.9	360.5	337.6	328.5	319.3
142.5°	556.0	527.8	497.2	468.2	439.9	414.0	389.5	367.4	345.2	336.4	327.7
145°	536.2	513.3	487.3	462.9	438.4	414.7	392.6	372.0	352.1	343.7	335.3
147.5°	519.4	500.3	478.9	458.3	436.1	415.5	395.6	377.3	358.2	350.5	342.9
150°	504.1	488.8	471.3	452.9	433.8	415.5	397.9	381.1	364.3	357.0	349.8
152.5°	491.1	477.4	462.9	446.8	430.0	414.0	399.5	384.2	369.7	363.2	356.7
155°	478.1	466.7	454.4	440.7	426.2	412.4	400.2	387.2	374.3	368.6	362.8
157.5°	465.9	456.0	445.3	434.6	422.4	410.9	400.2	389.5	378.1	373.5	368.9
160°	453.7	445.3	436.9	427.7	417.8	408.6	400.2	391.1	381.9	377.7	373.5
162.5°	441.5	435.4	428.5	421.6	413.2	406.3	400.2	392.6	384.2	381.2	378.1
165°	430.8	425.4	420.8	414.7	408.6	403.3	398.7	392.6	385.7	383.4	381.1
167.5°	421.6	417.0	413.2	408.6	404.0	400.2	397.2	392.6	387.2	385.3	383.4
170°	411.7	408.6	406.3	402.5	399.5	397.2	395.6	391.8	388.0	386.8	385.7
172.5°	403.3	401.7	400.2	397.2	394.9	394.1	394.1	391.1	388.8	388.0	387.2
175°	397.2	395.6	394.9	393.3	391.8	391.8	392.6	390.3	388.8	388.8	388.8
177.5°	391.8	391.8	391.1	390.3	389.5	389.5	391.1	389.5	388.8	388.8	388.8
180°	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8	388.8

TEST NUMBER: P1025220

CATALOG NUMBER: S124DIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1931.6	1931.6	1931.6	1931.6
2.5°	1878.7	1894.8	1909.2	1931.6
5°	1837.1	1859.5	1890.0	1923.6
7.5°	1789.1	1824.3	1864.3	1910.8
10°	1744.3	1784.3	1835.5	1891.6
12.5°	1697.9	1745.9	1801.9	1862.7
15°	1645.1	1693.1	1755.5	1837.1
17.5°	1597.1	1654.7	1721.9	1808.3
20°	1541.1	1595.5	1669.1	1768.3
22.5°	1491.5	1553.9	1635.5	1721.9
25°	1437.1	1491.5	1573.1	1677.1
27.5°	1382.7	1449.9	1528.3	1629.1
30°	1329.8	1385.9	1470.7	1576.3
32.5°	1272.2	1339.4	1417.9	1517.1
35°	1209.8	1273.8	1347.5	1454.7
37.5°	1153.8	1216.2	1291.4	1385.9
40°	1091.4	1157.0	1225.8	1320.2
42.5°	1030.6	1089.8	1158.6	1245.0
45°	971.4	1022.6	1085.0	1160.2
47.5°	910.6	953.8	1011.4	1078.6
50°	845.0	891.4	934.6	990.6
52.5°	784.1	824.2	859.4	905.8
55°	724.9	752.1	780.9	816.2
57.5°	662.5	683.3	704.1	740.9
60°	600.1	619.3	630.5	654.5
62.5°	539.3	547.3	561.7	576.1
65°	472.1	483.3	491.3	508.9
67.5°	411.3	416.1	424.1	435.3
70°	347.3	358.5	361.7	369.7
72.5°	292.9	297.7	300.9	302.5
75°	232.0	236.8	240.0	249.6
77.5°	182.4	180.8	187.2	188.8
80°	134.4	129.6	131.2	137.6
82.5°	88.0	89.6	88.0	88.0
85°	54.4	52.8	49.6	51.2
87.5°	24.0	24.0	22.4	22.4
90°	5.3	4.6	2.3	0.8
92.5°	35.1	23.7	15.3	10.7
95°	45.1	35.1	27.5	25.2
97.5°	58.0	48.9	42.0	42.0
100°	72.6	63.4	58.0	58.0
102.5°	87.8	79.4	74.9	73.3
105°	104.6	95.5	91.7	89.4
107.5°	122.2	112.3	108.5	106.9
110°	139.0	129.8	126.0	124.5



TEST NUMBER: P1025220

CATALOG NUMBER: S124DIP-B1195D810UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	155.8	147.4	142.8	141.3
115°	172.6	165.0	159.6	157.3
117.5°	189.4	181.0	176.4	174.1
120°	206.2	197.8	192.5	190.9
122.5°	220.7	213.1	207.7	206.2
125°	235.2	226.8	222.3	219.2
127.5°	248.2	239.1	233.7	231.4
130°	262.0	250.5	244.4	241.4
132.5°	272.7	262.0	253.6	251.3
135°	284.1	271.1	263.5	260.4
137.5°	293.3	281.1	272.7	269.6
140°	303.2	290.2	281.8	279.5
142.5°	312.4	300.2	292.5	290.2
145°	320.8	310.1	302.5	300.2
147.5°	330.7	319.3	312.4	311.6
150°	338.4	329.2	323.1	322.3
152.5°	346.8	338.4	332.2	332.2
155°	354.4	346.8	342.2	341.4
157.5°	361.3	355.2	350.6	350.6
160°	367.4	362.0	359.0	359.0
162.5°	372.7	368.1	365.9	366.6
165°	377.3	373.5	372.0	372.0
167.5°	381.1	378.1	377.3	378.1
170°	384.2	381.9	381.1	381.9
172.5°	386.5	384.9	384.9	385.7
175°	388.0	387.2	387.2	388.0
177.5°	388.8	388.0	388.8	389.5
180°	388.8	388.8	388.8	388.8

(END OF REPORT)