

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013089

Luminaire Tested: S124DIP-B575D1205UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013089
REPORT IS A COMBINATION OF REPORTS P996102 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B575D1205UB2750-4F0-XX-W2A-F_5000K
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7009.0 lumens
Efficiency: N/A
Efficacy: 118.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013089

CATALOG NUMBER: S124DIP-B575D1205UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013089

CATALOG NUMBER: S124DIP-B575D1205UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42
1	94	90	86	83	85	81	78	75	65	63	61	50	49	48	37	36	35
2	86	79	73	67	77	71	66	62	57	53	50	44	42	40	32	31	29
3	78	69	62	56	70	62	56	51	50	46	42	39	36	34	29	27	25
4	71	61	53	47	64	55	49	44	45	40	36	35	31	29	25	23	22
5	65	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19
6	60	48	41	35	54	44	37	32	36	31	27	28	24	22	21	18	16
7	56	44	36	30	50	40	33	28	32	27	24	25	22	19	19	16	15
8	52	40	32	27	46	36	29	25	29	24	21	23	20	17	17	15	13
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	14	12
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7584	7584	7584
5°	7589	7366	7375
10°	7526	7161	7111
15°	7417	6918	6813
20°	7280	6655	6506
25°	7125	6377	6174
30°	6937	6077	5811
35°	6744	5769	5459
40°	6541	5438	5085
45°	6330	5106	4735
50°	6095	4785	4348
55°	5841	4408	3963
60°	5579	3997	3563
65°	5282	3572	3111
70°	4937	3059	2627
75°	4424	2467	2104
80°	3771	1783	1480
85°	2925	992	797

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6330 cd/sqm

TEST NUMBER: P1013089

CATALOG NUMBER: S124DIP-B575D1205UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	1.3
10°-20°	247.0	3.5
20°-30°	363.4	5.2
30°-40°	422.5	6.0
40°-50°	422.5	6.0
50°-60°	369.5	5.3
60°-70°	274.3	3.9
70°-80°	155.6	2.2
80°-90°	47.6	0.7
90°-100°	49.5	0.7
100°-110°	326.3	4.7
110°-120°	623.1	8.9
120°-130°	791.0	11.3
130°-140°	846.2	12.1
140°-150°	791.3	11.3
150°-160°	638.1	9.1
160°-170°	411.5	5.9
170°-180°	141.8	2.0
0°-30°	698.1	10.0
0°-40°	1120.5	16.0
0°-60°	1912.5	27.3
0°-90°	2390.1	34.1
90°-120°	999.0	14.3
90°-150°	3427.5	48.9
90°-180°	4619.0	65.9
0°-180°	7009.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	930	930	930	930	930	
5°	929	926	918	926	925	88
15°	884	882	870	875	873	249
25°	801	796	785	786	783	369
35°	689	684	674	668	665	431
45°	563	557	546	537	535	434
55°	426	423	413	404	399	381
65°	288	285	277	270	266	285
75°	154	150	146	143	142	163
85°	40	40	39	39	38	43
90°	3	16	25	31	34	6
95°	61	23	25	31	32	76
105°	336	343	348	358	318	352
115°	627	631	630	632	632	618
125°	882	886	884	888	889	788
135°	1094	1093	1098	1100	1102	843
145°	1262	1265	1265	1266	1268	788
155°	1383	1384	1381	1386	1382	638
165°	1459	1454	1454	1462	1452	412
175°	1493	1486	1487	1497	1484	142
180°	1493	1493	1493	1493	1493	

TEST NUMBER: P1013089

CATALOG NUMBER: S124DIP-B575D1205UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	930.0	930.0	930.0	930.0	930.0
2.5°	933.0	930.7	922.5	930.0	929.2
5°	929.2	926.3	918.1	926.3	924.8
7.5°	922.5	919.6	910.6	917.3	916.6
10°	912.9	909.9	900.2	906.1	904.7
12.5°	900.2	897.2	886.8	893.5	891.2
15°	884.5	881.6	870.4	874.8	872.6
17.5°	866.6	862.9	852.5	855.5	854.0
20°	846.5	842.8	831.6	833.9	832.4
22.5°	824.9	819.7	808.5	813.0	810.0
25°	801.1	795.9	785.4	786.2	783.2
27.5°	774.2	769.0	759.3	757.9	754.1
30°	747.4	741.5	731.8	728.8	725.1
32.5°	719.1	713.9	703.5	699.7	696.0
35°	689.3	684.1	673.6	668.4	664.7
37.5°	658.0	653.5	642.3	637.1	631.9
40°	627.4	621.5	610.3	602.9	599.1
42.5°	594.7	591.7	579.0	570.1	567.8
45°	562.6	557.4	545.5	537.3	535.0
47.5°	529.1	525.4	514.2	505.2	499.3
50°	494.8	491.8	481.4	471.0	466.5
52.5°	461.3	457.5	446.4	437.4	431.5
55°	425.5	423.3	412.8	403.9	399.4
57.5°	392.0	389.7	379.3	370.4	365.9
60°	356.9	353.2	343.5	336.8	333.1
62.5°	322.7	319.7	309.3	303.3	299.6
65°	288.4	284.7	277.2	269.8	266.0
67.5°	253.4	250.4	242.9	235.5	234.7
70°	221.3	216.1	210.1	204.2	201.9
72.5°	187.0	181.8	177.4	172.9	170.6
75°	153.5	149.8	146.1	143.1	142.3
77.5°	120.7	119.2	115.5	114.8	112.5
80°	91.7	89.4	87.9	86.4	85.7
82.5°	63.3	62.6	62.6	61.9	61.1
85°	40.2	40.2	38.7	38.7	38.0
87.5°	19.4	18.6	17.9	17.9	17.9
90°	3.3	15.6	24.6	31.3	33.5
92.5°	16.7	14.5	23.4	30.1	30.1
95°	61.4	23.4	24.6	31.3	32.4
97.5°	117.2	141.8	24.6	30.1	31.3
100°	183.1	203.2	49.1	30.1	31.3
102.5°	256.8	270.2	283.6	32.4	32.4
105°	336.1	342.7	348.3	358.4	318.2
107.5°	408.6	412.0	419.8	425.4	429.8
110°	482.3	485.7	492.4	494.6	497.9

TEST NUMBER: P1013089

CATALOG NUMBER: S124DIP-B575D1205UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	553.8	560.5	562.7	561.6	566.0
115°	627.4	630.8	629.7	631.9	631.9
117.5°	693.3	697.8	701.1	700.0	700.0
120°	760.3	764.8	763.7	765.9	763.7
122.5°	822.8	825.1	827.3	828.4	826.2
125°	882.0	886.5	884.2	887.6	888.7
127.5°	938.9	940.1	945.6	944.5	943.4
130°	993.6	994.8	998.1	999.2	999.2
132.5°	1043.9	1046.1	1050.6	1051.7	1050.6
135°	1094.1	1093.0	1097.5	1099.7	1101.9
137.5°	1138.8	1138.8	1144.4	1146.6	1145.5
140°	1182.3	1184.6	1186.8	1190.1	1191.3
142.5°	1221.4	1225.9	1227.0	1229.2	1229.2
145°	1261.6	1264.9	1264.9	1266.1	1268.3
147.5°	1292.8	1299.5	1298.4	1299.5	1300.7
150°	1327.5	1331.9	1330.8	1330.8	1331.9
152.5°	1356.5	1359.8	1357.6	1359.8	1358.7
155°	1383.3	1384.4	1381.0	1385.5	1382.2
157.5°	1406.7	1406.7	1402.3	1407.8	1402.3
160°	1426.8	1423.5	1422.4	1429.1	1422.4
162.5°	1444.7	1440.2	1439.1	1445.8	1438.0
165°	1459.2	1453.6	1453.6	1462.5	1452.5
167.5°	1471.5	1465.9	1464.8	1474.8	1463.7
170°	1481.5	1474.8	1475.9	1484.9	1473.7
172.5°	1488.2	1481.5	1482.6	1491.6	1479.3
175°	1492.7	1486.0	1487.1	1497.2	1483.8
177.5°	1496.0	1488.2	1490.5	1499.4	1486.0
180°	1492.7	1492.7	1492.7	1492.7	1492.7

(END OF REPORT)