

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1025226

Luminaire Tested: S124DIP-B1195D810UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1025226
REPORT IS A COMBINATION OF REPORTS P995691 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B1195D810UB30-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7964.7 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1025226

CATALOG NUMBER: S124DIP-B1195D810UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1025226

CATALOG NUMBER: S124DIP-B1195D810UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64		
1	101	97	93	89	95	91	87	84	80	77	75	70	68	67	61	60	59	54		
2	92	84	78	73	86	79	74	69	70	66	62	62	58	56	54	51	49	45		
3	84	74	67	61	78	70	63	58	62	57	52	55	50	47	48	45	42	38		
4	77	66	58	51	72	62	55	49	55	49	45	49	44	40	43	39	36	33		
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	38	35	32	29		
6	65	53	44	38	61	50	42	37	45	38	34	40	35	31	35	31	28	25		
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	32	28	25	22		
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	29	25	22	20		
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18		
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16285	16285	16285
5°	16299	15817	15836
10°	16161	15378	15270
15°	15929	14856	14632
20°	15633	14291	13971
25°	15300	13695	13259
30°	14899	13050	12478
35°	14482	12389	11722
40°	14048	11678	10919
45°	13593	10965	10169
50°	13090	10275	9337
55°	12542	9467	8511
60°	11982	8583	7650
65°	11341	7671	6681
70°	10604	6572	5643
75°	9501	5298	4518
80°	8094	3829	3178
85°	6287	2132	1710

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13593 cd/sqm

TEST NUMBER: P1025226

CATALOG NUMBER: S124DIP-B1195D810UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.2	2.4
10°-20°	530.3	6.7
20°-30°	780.5	9.8
30°-40°	907.3	11.4
40°-50°	907.2	11.4
50°-60°	793.4	10.0
60°-70°	589.1	7.4
70°-80°	334.2	4.2
80°-90°	97.2	1.2
90°-100°	288.8	3.6
100°-110°	587.3	7.4
110°-120°	523.5	6.6
120°-130°	439.8	5.5
130°-140°	367.0	4.6
140°-150°	280.3	3.5
150°-160°	197.0	2.5
160°-170°	115.9	1.5
170°-180°	37.7	0.5
0°-30°	1499.1	18.8
0°-40°	2406.3	30.2
0°-60°	4107.0	51.6
0°-90°	5127.5	64.4
90°-120°	1399.6	17.6
90°-150°	2486.6	31.2
90°-180°	2837.0	35.6
0°-180°	7964.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1997	1997	1997	1997	1997	
5°	1996	1989	1972	1989	1986	189
15°	1900	1893	1869	1879	1874	535
25°	1720	1709	1687	1688	1682	792
35°	1480	1469	1447	1435	1427	926
45°	1208	1197	1171	1154	1149	931
55°	914	909	886	867	858	818
65°	619	611	595	579	571	613
75°	330	322	314	307	306	350
85°	86	86	83	83	82	93
90°	1	6	14	15	16	7
95°	25	79	622	308	186	28
105°	89	129	501	1079	1075	95
115°	157	197	447	858	1032	156
125°	219	260	444	731	823	195
135°	260	310	441	648	736	201
145°	300	344	438	547	601	188
155°	341	369	426	483	503	157
165°	372	383	409	433	439	105
175°	388	389	392	397	396	37
180°	389	389	389	389	389	

TEST NUMBER: P1025226

CATALOG NUMBER: S124DIP-B1195D810UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1997.1	1997.1	1997.1	1997.1	1997.1
2.5°	2003.5	1998.7	1981.1	1997.1	1995.5
5°	1995.5	1989.1	1971.5	1989.1	1985.9
7.5°	1981.1	1974.7	1955.5	1969.9	1968.3
10°	1960.3	1953.9	1933.1	1945.9	1942.7
12.5°	1933.1	1926.7	1904.3	1918.7	1913.9
15°	1899.5	1893.1	1869.1	1878.7	1873.9
17.5°	1861.1	1853.1	1830.7	1837.1	1833.9
20°	1817.9	1809.9	1785.9	1790.7	1787.5
22.5°	1771.5	1760.3	1736.3	1745.9	1739.5
25°	1720.3	1709.1	1686.7	1688.3	1681.9
27.5°	1662.7	1651.5	1630.7	1627.5	1619.5
30°	1605.1	1592.3	1571.5	1565.1	1557.1
32.5°	1544.2	1533.0	1510.6	1502.6	1494.6
35°	1480.2	1469.0	1446.6	1435.4	1427.4
37.5°	1413.0	1403.4	1379.4	1368.2	1357.0
40°	1347.4	1334.6	1310.6	1294.6	1286.6
42.5°	1277.0	1270.6	1243.4	1224.2	1219.4
45°	1208.2	1197.0	1171.4	1153.8	1149.0
47.5°	1136.2	1128.2	1104.2	1085.0	1072.2
50°	1062.6	1056.2	1033.8	1011.4	1001.8
52.5°	990.6	982.6	958.6	939.4	926.5
55°	913.7	908.9	886.5	867.3	857.7
57.5°	841.7	836.9	814.5	795.3	785.7
60°	766.5	758.5	737.7	723.3	715.3
62.5°	692.9	686.5	664.1	651.3	643.3
65°	619.3	611.3	595.3	579.3	571.3
67.5°	544.1	537.7	521.7	505.7	504.1
70°	475.3	464.1	451.3	438.5	433.7
72.5°	401.7	390.5	380.9	371.3	366.5
75°	329.7	321.7	313.7	307.2	305.6
77.5°	259.2	256.0	248.0	246.4	241.6
80°	196.8	192.0	188.8	185.6	184.0
82.5°	136.0	134.4	134.4	132.8	131.2
85°	86.4	86.4	83.2	83.2	81.6
87.5°	41.6	40.0	38.4	38.4	38.4
90°	0.8	6.1	13.7	15.3	16.0
92.5°	10.7	58.8	299.4	99.0	69.5
95°	25.2	79.4	622.5	308.2	186.4
97.5°	42.0	87.8	666.0	629.4	447.6
100°	58.0	99.3	614.1	870.8	700.4
102.5°	73.3	113.0	549.2	1022.0	920.4
105°	89.4	129.4	501.0	1078.8	1074.6
107.5°	106.9	146.2	469.7	1061.6	1148.0
110°	124.5	163.1	455.2	1000.6	1149.5

TEST NUMBER: P1025226

CATALOG NUMBER: S124DIP-B1195D810UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.3	179.9	448.3	925.7	1104.4
115°	157.3	197.4	446.8	858.5	1031.9
117.5°	174.1	213.9	446.0	805.8	960.8
120°	190.9	229.9	446.0	770.3	902.8
122.5°	206.2	245.6	445.3	747.0	857.0
125°	219.2	260.5	444.5	730.6	823.4
127.5°	231.4	274.2	443.0	714.9	802.0
130°	241.4	287.6	442.2	696.2	783.6
132.5°	251.3	299.0	441.5	674.0	763.0
135°	260.4	310.1	440.7	648.4	736.3
137.5°	269.6	319.6	440.7	621.0	705.0
140°	279.5	328.5	439.9	594.2	670.6
142.5°	290.2	336.4	439.9	569.4	633.9
145°	300.2	343.7	438.4	546.9	601.1
147.5°	311.6	350.5	436.1	528.2	570.5
150°	322.3	357.0	433.8	511.0	545.3
152.5°	332.2	363.2	430.0	496.4	522.4
155°	341.4	368.6	426.2	482.7	503.3
157.5°	350.6	373.5	422.4	469.7	485.8
160°	359.0	377.7	417.8	456.8	469.7
162.5°	366.6	381.2	413.2	444.2	454.4
165°	372.0	383.4	408.6	432.7	439.2
167.5°	378.1	385.3	404.0	422.8	427.0
170°	381.9	386.8	399.5	412.8	415.5
172.5°	385.7	388.0	394.9	404.0	404.0
175°	388.0	388.8	391.8	397.2	395.6
177.5°	389.5	388.8	389.5	392.2	389.5
180°	388.8	388.8	388.8	388.8	388.8

(END OF REPORT)