

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013100

Luminaire Tested: S124DIP-B575D365UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013100
REPORT IS A COMBINATION OF REPORTS P996160 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B575D365UB2750-4F0-XX-W2A-F_3500K
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3971.0 lumens
Efficiency: N/A
Efficacy: 119.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013100

CATALOG NUMBER: S124DIP-B575D365UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1013100

CATALOG NUMBER: S124DIP-B575D365UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	68	68	68
1	101	96	92	89	94	90	87	84	79	77	74	69	67	66	60	59	57	57	57	53
2	92	84	78	72	86	79	73	69	70	65	62	61	58	55	53	50	48	48	48	44
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	47	44	41	41	41	37
4	77	65	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35	35	35	32
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	38	34	31	31	31	28
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27	27	27	25
7	60	47	39	34	56	45	37	32	40	34	29	36	31	27	31	27	24	24	24	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	22	22	19
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20	20	20	18
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18	18	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7920	7920	7920
5°	7927	7692	7702
10°	7860	7479	7426
15°	7747	7225	7116
20°	7603	6951	6794
25°	7441	6660	6449
30°	7246	6347	6069
35°	7043	6026	5701
40°	6832	5680	5310
45°	6611	5333	4946
50°	6367	4997	4541
55°	6100	4605	4140
60°	5828	4175	3721
65°	5516	3730	3249
70°	5156	3196	2744
75°	4619	2575	2199
80°	3936	1862	1546
85°	3056	1038	832

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6611 cd/sqm

TEST NUMBER: P1013100

CATALOG NUMBER: S124DIP-B575D365UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	2.3
10°-20°	257.9	6.5
20°-30°	379.6	9.6
30°-40°	441.2	11.1
40°-50°	441.2	11.1
50°-60°	385.9	9.7
60°-70°	286.5	7.2
70°-80°	162.5	4.1
80°-90°	47.6	1.2
90°-100°	15.8	0.4
100°-110°	104.3	2.6
110°-120°	199.2	5.0
120°-130°	252.9	6.4
130°-140°	270.6	6.8
140°-150°	253.0	6.4
150°-160°	204.0	5.1
160°-170°	131.6	3.3
170°-180°	45.4	1.1
0°-30°	729.1	18.4
0°-40°	1170.3	29.5
0°-60°	1997.4	50.3
0°-90°	2494.0	62.8
90°-120°	319.4	8.0
90°-150°	1096.0	27.6
90°-180°	1477.0	37.2
0°-180°	3971.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	970	967	959	967	966	92
15°	924	921	909	914	911	260
25°	837	831	820	821	818	385
35°	720	714	704	698	694	450
45°	588	582	570	561	559	453
55°	444	442	431	422	417	398
65°	301	297	290	282	278	298
75°	160	156	152	149	149	170
85°	42	42	40	40	40	45
90°	1	5	8	10	11	4
95°	20	8	8	10	10	24
105°	108	110	111	115	102	112
115°	201	202	201	202	202	197
125°	282	284	283	284	284	252
135°	350	350	351	352	352	270
145°	403	404	404	405	406	252
155°	442	443	442	443	442	204
165°	467	465	465	468	464	132
175°	477	475	476	479	474	45
180°	477	477	477	477	477	

TEST NUMBER: P1013100

CATALOG NUMBER: S124DIP-B575D365UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	971.3	971.3	971.3	971.3	971.3
2.5°	974.4	972.1	963.5	971.3	970.5
5°	970.5	967.4	958.8	967.4	965.8
7.5°	963.5	960.4	951.1	958.1	957.3
10°	953.4	950.3	940.2	946.4	944.8
12.5°	940.2	937.0	926.1	933.2	930.8
15°	923.8	920.7	909.0	913.7	911.4
17.5°	905.1	901.2	890.3	893.5	891.9
20°	884.1	880.2	868.6	870.9	869.3
22.5°	861.6	856.1	844.4	849.1	846.0
25°	836.6	831.2	820.3	821.1	818.0
27.5°	808.6	803.2	793.1	791.5	787.6
30°	780.6	774.4	764.3	761.2	757.3
32.5°	751.0	745.6	734.7	730.8	726.9
35°	719.9	714.5	703.6	698.1	694.2
37.5°	687.2	682.5	670.9	665.4	660.0
40°	655.3	649.1	637.4	629.6	625.7
42.5°	621.1	618.0	604.7	595.4	593.0
45°	587.6	582.2	569.7	561.1	558.8
47.5°	552.6	548.7	537.0	527.7	521.4
50°	516.8	513.7	502.8	491.9	487.2
52.5°	481.8	477.9	466.2	456.8	450.6
55°	444.4	442.1	431.2	421.8	417.2
57.5°	409.4	407.0	396.1	386.8	382.1
60°	372.8	368.9	358.8	351.8	347.9
62.5°	337.0	333.9	323.0	316.8	312.9
65°	301.2	297.3	289.5	281.7	277.8
67.5°	264.6	261.5	253.7	245.9	245.2
70°	231.1	225.7	219.5	213.2	210.9
72.5°	195.3	189.9	185.2	180.6	178.2
75°	160.3	156.4	152.5	149.4	148.7
77.5°	126.1	124.5	120.6	119.9	117.5
80°	95.7	93.4	91.8	90.3	89.5
82.5°	66.2	65.4	65.4	64.6	63.8
85°	42.0	42.0	40.5	40.5	39.7
87.5°	20.2	19.5	18.7	18.7	18.7
90°	1.1	5.0	7.9	10.0	10.7
92.5°	5.4	4.6	7.5	9.6	9.6
95°	19.6	7.5	7.9	10.0	10.4
97.5°	37.5	45.3	7.9	9.6	10.0
100°	58.6	65.0	15.7	9.6	10.0
102.5°	82.1	86.4	90.7	10.4	10.4
105°	107.5	109.6	111.4	114.6	101.7
107.5°	130.7	131.7	134.2	136.0	137.4
110°	154.2	155.3	157.4	158.2	159.2



TEST NUMBER: P1013100

CATALOG NUMBER: S124DIP-B575D365UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	177.1	179.2	179.9	179.6	181.0
115°	200.6	201.7	201.4	202.1	202.1
117.5°	221.7	223.1	224.2	223.8	223.8
120°	243.1	244.6	244.2	244.9	244.2
122.5°	263.1	263.8	264.5	264.9	264.2
125°	282.0	283.5	282.8	283.8	284.2
127.5°	300.2	300.6	302.4	302.0	301.7
130°	317.7	318.1	319.2	319.5	319.5
132.5°	333.8	334.5	335.9	336.3	335.9
135°	349.9	349.5	350.9	351.7	352.4
137.5°	364.2	364.2	365.9	366.7	366.3
140°	378.1	378.8	379.5	380.6	380.9
142.5°	390.6	392.0	392.4	393.1	393.1
145°	403.4	404.5	404.5	404.9	405.6
147.5°	413.4	415.6	415.2	415.6	415.9
150°	424.5	425.9	425.6	425.6	425.9
152.5°	433.8	434.8	434.1	434.8	434.5
155°	442.3	442.7	441.6	443.1	442.0
157.5°	449.8	449.8	448.4	450.2	448.4
160°	456.3	455.2	454.8	457.0	454.8
162.5°	462.0	460.5	460.2	462.3	459.8
165°	466.6	464.8	464.8	467.7	464.5
167.5°	470.5	468.8	468.4	471.6	468.0
170°	473.8	471.6	472.0	474.8	471.3
172.5°	475.9	473.8	474.1	477.0	473.0
175°	477.3	475.2	475.5	478.8	474.5
177.5°	478.4	475.9	476.6	479.5	475.2
180°	477.3	477.3	477.3	477.3	477.3

(END OF REPORT)