

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013109

Luminaire Tested: S124DIP-B575D590UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013109
REPORT IS A COMBINATION OF REPORTS P996215 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B575D590UB2750-4F0-XX-W2A-D_3500K
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4747.0 lumens
Efficiency: N/A
Efficacy: 120.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013109

CATALOG NUMBER: S124DIP-B575D590UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1013109

CATALOG NUMBER: S124DIP-B575D590UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46		
1	96	91	87	83	88	84	80	77	70	67	65	57	55	53	45	44	43	37		
2	87	79	73	67	79	73	67	62	61	56	53	49	46	44	39	37	35	30		
3	79	69	62	55	72	64	57	52	53	48	44	43	40	37	34	32	29	25		
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	30	27	25	21		
5	66	54	46	40	60	50	43	37	42	36	32	34	30	27	27	24	22	18		
6	61	48	40	34	55	45	37	32	38	32	28	31	27	23	25	21	19	16		
7	56	44	36	30	51	40	33	28	34	28	24	28	24	20	22	19	17	14		
8	52	40	32	26	48	37	30	25	31	25	21	26	21	18	21	17	15	12		
9	48	36	28	23	44	33	27	22	28	23	19	23	19	16	19	16	13	11		
10	45	33	26	21	41	31	24	20	26	21	17	22	18	15	18	14	12	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5668	5668	5668
5°	5684	5521	5531
10°	5647	5412	5397
15°	5594	5290	5246
20°	5516	5157	5098
25°	5428	5012	4940
30°	5333	4868	4779
35°	5224	4720	4635
40°	5137	4578	4486
45°	5010	4445	4354
50°	4901	4294	4216
55°	4787	4148	4055
60°	4611	3967	3905
65°	4419	3772	3724
70°	4185	3547	3514
75°	3859	3300	3315
80°	3488	3046	3106
85°	3005	2793	2937

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5010 cd/sqm

TEST NUMBER: P1013109

CATALOG NUMBER: S124DIP-B575D590UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.9	1.4
10°-20°	188.7	4.0
20°-30°	285.3	6.0
30°-40°	345.2	7.3
40°-50°	364.9	7.7
50°-60°	343.5	7.2
60°-70°	285.0	6.0
70°-80°	200.0	4.2
80°-90°	114.3	2.4
90°-100°	92.6	2.0
100°-110°	217.5	4.6
110°-120°	353.8	7.5
120°-130°	425.6	9.0
130°-140°	443.3	9.3
140°-150°	408.6	8.6
150°-160°	328.2	6.9
160°-170°	211.6	4.5
170°-180°	72.9	1.5
0°-30°	539.9	11.4
0°-40°	885.1	18.6
0°-60°	1593.5	33.6
0°-90°	2192.9	46.2
90°-120°	664.0	14.0
90°-150°	1941.4	40.9
90°-180°	2554.0	53.8
0°-180°	4747.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	695	695	695	695	695	
5°	696	694	688	694	694	66
15°	667	668	666	673	672	188
25°	610	615	617	626	627	281
35°	534	543	551	562	564	334
45°	445	460	475	488	492	344
55°	349	365	388	404	409	311
65°	241	266	293	312	318	239
75°	134	163	195	217	224	142
85°	41	74	109	132	140	43
90°	14	52	90	116	123	10
95°	42	48	80	105	112	47
105°	180	199	230	255	241	189
115°	327	336	360	379	384	323
125°	457	458	476	493	498	408
135°	564	564	571	585	591	435
145°	650	650	650	656	660	406
155°	711	712	710	712	711	328
165°	750	748	748	752	747	212
175°	768	764	765	770	763	73
180°	768	768	768	768	768	

TEST NUMBER: P1013109

CATALOG NUMBER: S124DIP-B575D590UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	695.1	695.1	695.1	695.1	695.1
2.5°	698.2	695.9	689.7	695.1	694.4
5°	695.9	693.6	688.1	694.4	693.6
7.5°	691.2	689.7	685.0	692.0	691.2
10°	685.0	684.2	680.3	687.4	686.6
12.5°	676.5	676.5	674.1	680.3	680.3
15°	667.1	667.9	665.6	672.6	671.8
17.5°	654.7	657.0	656.2	663.2	662.4
20°	641.4	643.8	644.5	652.3	652.3
22.5°	626.6	629.7	631.3	639.1	640.6
25°	610.3	615.0	617.3	625.9	626.6
27.5°	592.4	599.4	602.5	610.3	611.1
30°	574.5	580.7	586.2	594.7	596.3
32.5°	555.0	562.8	569.0	579.1	580.7
35°	534.0	543.3	551.1	562.0	564.4
37.5°	513.0	523.9	533.2	544.1	546.5
40°	492.7	502.9	513.8	525.4	528.6
42.5°	469.4	481.1	494.3	507.5	509.9
45°	445.3	460.1	474.8	488.1	492.0
47.5°	422.7	437.5	454.6	467.8	472.5
50°	397.8	414.9	432.0	447.6	452.3
52.5°	372.9	390.0	410.2	425.8	430.5
55°	348.7	365.1	388.4	404.0	408.7
57.5°	321.5	341.7	364.3	383.0	386.9
60°	295.0	315.3	341.0	358.9	365.1
62.5°	269.3	291.9	317.6	335.5	341.7
65°	241.3	266.2	292.7	312.1	318.4
67.5°	214.8	241.3	269.3	288.8	295.0
70°	187.6	214.1	243.6	264.7	270.1
72.5°	161.1	188.4	220.3	240.5	246.8
75°	133.9	162.7	195.4	217.2	224.2
77.5°	108.2	138.6	172.8	194.6	202.4
80°	84.8	116.0	150.2	173.6	179.8
82.5°	61.5	94.2	128.4	152.6	159.6
85°	41.3	74.0	109.0	132.3	140.1
87.5°	25.7	57.6	91.9	114.4	121.4
90°	14.2	51.6	89.7	115.7	123.1
92.5°	20.3	46.4	84.5	109.7	115.9
95°	41.7	47.9	80.3	104.8	112.4
97.5°	69.6	104.8	76.4	99.6	107.2
100°	102.8	133.3	84.5	95.7	101.7
102.5°	140.7	164.6	201.1	92.2	98.4
105°	179.8	198.9	230.5	255.1	240.7
107.5°	217.1	232.1	263.4	285.7	293.5
110°	254.2	266.9	297.6	316.7	324.6

TEST NUMBER: P1013109

CATALOG NUMBER: S124DIP-B575D590UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	290.2	303.0	329.9	346.4	354.9
115°	327.4	336.1	360.4	378.7	384.2
117.5°	361.3	368.2	393.3	409.0	415.3
120°	394.9	399.5	421.5	438.3	443.3
122.5°	427.1	428.2	450.4	466.5	470.8
125°	456.7	458.2	476.5	493.1	498.3
127.5°	486.0	485.7	504.2	517.6	522.6
130°	513.3	513.2	527.3	541.9	546.6
132.5°	539.1	539.6	551.2	565.0	569.1
135°	564.3	563.7	571.4	585.1	590.8
137.5°	587.3	586.5	592.4	605.3	608.6
140°	609.6	610.0	611.9	623.8	628.2
142.5°	628.9	631.2	631.0	640.8	643.9
145°	649.6	650.5	650.5	655.8	660.1
147.5°	665.7	668.3	667.8	669.1	672.8
150°	683.5	685.0	684.4	684.4	685.0
152.5°	697.6	699.3	698.2	699.3	698.8
155°	711.4	712.0	710.2	712.5	710.8
157.5°	723.5	723.5	721.2	724.0	721.2
160°	733.8	732.1	731.5	734.9	731.5
162.5°	743.0	740.7	740.1	743.5	739.5
165°	750.4	747.6	747.6	752.2	747.0
167.5°	756.8	753.9	753.3	758.5	752.7
170°	761.9	758.5	759.0	763.6	757.9
172.5°	765.4	761.9	762.5	767.1	760.8
175°	767.7	764.2	764.8	770.0	763.1
177.5°	769.4	765.4	766.5	771.1	764.2
180°	767.7	767.7	767.7	767.7	767.7

(END OF REPORT)