

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013114

Luminaire Tested: S124DIP-B575D590UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013114
REPORT IS A COMBINATION OF REPORTS P996220 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B575D590UB2750-4F0-XX-W2A-F_3500K
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4870.0 lumens
Efficiency: N/A
Efficacy: 123.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013114

CATALOG NUMBER: S124DIP-B575D590UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1013114

CATALOG NUMBER: S124DIP-B575D590UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	57
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48	48	48	43
2	89	82	76	70	82	76	70	66	64	61	57	54	51	49	44	42	41	41	41	36
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	39	37	35	35	35	31
4	74	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	30	30	26
5	68	57	49	43	63	53	45	40	45	40	35	38	34	31	32	29	26	26	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	25	23	23	23	20
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	20	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	18	18	16
9	50	38	31	25	46	36	29	24	31	25	22	26	22	19	22	19	16	16	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	15	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7920	7920	7920
5°	7927	7692	7702
10°	7860	7479	7426
15°	7747	7225	7116
20°	7603	6951	6794
25°	7441	6660	6449
30°	7246	6347	6069
35°	7043	6026	5701
40°	6832	5680	5310
45°	6611	5333	4946
50°	6367	4997	4541
55°	6100	4605	4140
60°	5828	4175	3721
65°	5516	3730	3249
70°	5156	3196	2744
75°	4619	2575	2199
80°	3936	1862	1546
85°	3056	1038	832

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6611 cd/sqm

TEST NUMBER: P1013114

CATALOG NUMBER: S124DIP-B575D590UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.5	1.9
10°-20°	257.9	5.3
20°-30°	379.6	7.8
30°-40°	441.2	9.1
40°-50°	441.2	9.1
50°-60°	385.9	7.9
60°-70°	286.5	5.9
70°-80°	162.5	3.3
80°-90°	48.1	1.0
90°-100°	25.5	0.5
100°-110°	167.8	3.4
110°-120°	320.5	6.6
120°-130°	406.8	8.4
130°-140°	435.2	8.9
140°-150°	406.9	8.4
150°-160°	328.2	6.7
160°-170°	211.6	4.3
170°-180°	72.9	1.5
0°-30°	729.1	15.0
0°-40°	1170.3	24.0
0°-60°	1997.4	41.0
0°-90°	2494.6	51.2
90°-120°	513.8	10.5
90°-150°	1762.7	36.2
90°-180°	2375.0	48.8
0°-180°	4870.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	971	971	971	971	971	
5°	970	967	959	967	966	92
15°	924	921	909	914	911	260
25°	837	831	820	821	818	385
35°	720	714	704	698	694	450
45°	588	582	570	561	559	453
55°	444	442	431	422	417	398
65°	301	297	290	282	278	298
75°	160	156	152	149	149	170
85°	42	42	40	40	40	45
90°	2	8	13	16	17	4
95°	32	12	13	16	17	39
105°	173	176	179	184	164	181
115°	323	324	324	325	325	318
125°	454	456	455	456	457	405
135°	563	562	564	566	567	434
145°	649	650	650	651	652	405
155°	711	712	710	712	711	328
165°	750	748	748	752	747	212
175°	768	764	765	770	763	73
180°	768	768	768	768	768	

TEST NUMBER: P1013114

CATALOG NUMBER: S124DIP-B575D590UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	971.3	971.3	971.3	971.3	971.3
2.5°	974.4	972.1	963.5	971.3	970.5
5°	970.5	967.4	958.8	967.4	965.8
7.5°	963.5	960.4	951.1	958.1	957.3
10°	953.4	950.3	940.2	946.4	944.8
12.5°	940.2	937.0	926.1	933.2	930.8
15°	923.8	920.7	909.0	913.7	911.4
17.5°	905.1	901.2	890.3	893.5	891.9
20°	884.1	880.2	868.6	870.9	869.3
22.5°	861.6	856.1	844.4	849.1	846.0
25°	836.6	831.2	820.3	821.1	818.0
27.5°	808.6	803.2	793.1	791.5	787.6
30°	780.6	774.4	764.3	761.2	757.3
32.5°	751.0	745.6	734.7	730.8	726.9
35°	719.9	714.5	703.6	698.1	694.2
37.5°	687.2	682.5	670.9	665.4	660.0
40°	655.3	649.1	637.4	629.6	625.7
42.5°	621.1	618.0	604.7	595.4	593.0
45°	587.6	582.2	569.7	561.1	558.8
47.5°	552.6	548.7	537.0	527.7	521.4
50°	516.8	513.7	502.8	491.9	487.2
52.5°	481.8	477.9	466.2	456.8	450.6
55°	444.4	442.1	431.2	421.8	417.2
57.5°	409.4	407.0	396.1	386.8	382.1
60°	372.8	368.9	358.8	351.8	347.9
62.5°	337.0	333.9	323.0	316.8	312.9
65°	301.2	297.3	289.5	281.7	277.8
67.5°	264.6	261.5	253.7	245.9	245.2
70°	231.1	225.7	219.5	213.2	210.9
72.5°	195.3	189.9	185.2	180.6	178.2
75°	160.3	156.4	152.5	149.4	148.7
77.5°	126.1	124.5	120.6	119.9	117.5
80°	95.7	93.4	91.8	90.3	89.5
82.5°	66.2	65.4	65.4	64.6	63.8
85°	42.0	42.0	40.5	40.5	39.7
87.5°	20.2	19.5	18.7	18.7	18.7
90°	1.7	8.0	12.6	16.1	17.2
92.5°	8.6	7.5	12.1	15.5	15.5
95°	31.6	12.1	12.6	16.1	16.7
97.5°	60.3	72.9	12.6	15.5	16.1
100°	94.2	104.5	25.3	15.5	16.1
102.5°	132.1	138.9	145.8	16.7	16.7
105°	172.8	176.3	179.1	184.3	163.6
107.5°	210.1	211.9	215.9	218.8	221.1
110°	248.0	249.8	253.2	254.4	256.1

TEST NUMBER: P1013114

CATALOG NUMBER: S124DIP-B575D590UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	284.8	288.2	289.4	288.8	291.1
115°	322.7	324.4	323.8	325.0	325.0
117.5°	356.6	358.9	360.6	360.0	360.0
120°	391.0	393.3	392.7	393.9	392.7
122.5°	423.2	424.3	425.5	426.0	424.9
125°	453.6	455.9	454.7	456.5	457.0
127.5°	482.9	483.4	486.3	485.7	485.2
130°	511.0	511.6	513.3	513.9	513.9
132.5°	536.8	538.0	540.3	540.9	540.3
135°	562.7	562.1	564.4	565.6	566.7
137.5°	585.7	585.7	588.5	589.7	589.1
140°	608.0	609.2	610.3	612.1	612.6
142.5°	628.1	630.4	631.0	632.2	632.2
145°	648.8	650.5	650.5	651.1	652.3
147.5°	664.9	668.3	667.8	668.3	668.9
150°	682.7	685.0	684.4	684.4	685.0
152.5°	697.6	699.3	698.2	699.3	698.8
155°	711.4	712.0	710.2	712.5	710.8
157.5°	723.5	723.5	721.2	724.0	721.2
160°	733.8	732.1	731.5	734.9	731.5
162.5°	743.0	740.7	740.1	743.5	739.5
165°	750.4	747.6	747.6	752.2	747.0
167.5°	756.8	753.9	753.3	758.5	752.7
170°	761.9	758.5	759.0	763.6	757.9
172.5°	765.4	761.9	762.5	767.1	760.8
175°	767.7	764.2	764.8	770.0	763.1
177.5°	769.4	765.4	766.5	771.1	764.2
180°	767.7	767.7	767.7	767.7	767.7

(END OF REPORT)