

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013140

Luminaire Tested: S124DIP-B795D1035UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013140
REPORT IS A COMBINATION OF REPORTS P996336 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B795D1035UB2750-4F0-XX-W2A-D_4000K
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7305.0 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013140

CATALOG NUMBER: S124DIP-B795D1035UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013140

CATALOG NUMBER: S124DIP-B795D1035UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41	41	41
1	95	90	86	82	86	82	79	76	67	65	63	54	52	50	41	40	39	33	33	33
2	86	78	72	67	78	71	66	61	59	55	51	47	44	41	36	34	32	27	27	27
3	78	69	61	55	71	63	56	51	51	46	42	41	37	34	31	29	27	22	22	22
4	71	60	52	46	65	55	48	43	45	40	36	36	32	29	28	25	23	19	19	19
5	65	54	45	39	59	49	42	36	40	35	31	32	28	25	25	22	20	16	16	16
6	60	48	40	34	54	44	37	31	36	31	27	29	25	22	22	20	17	14	14	14
7	56	43	35	30	50	40	32	27	33	27	23	26	22	19	20	17	15	12	12	12
8	51	39	31	26	47	36	29	24	30	24	21	24	20	17	19	16	14	11	11	11
9	48	36	28	23	43	33	26	21	27	22	18	22	18	15	17	14	12	10	10	10
10	45	33	25	20	41	30	23	19	25	20	16	20	16	14	16	13	11	9	9	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7742	7742	7742
5°	7763	7541	7554
10°	7713	7392	7371
15°	7641	7225	7164
20°	7534	7044	6964
25°	7413	6845	6747
30°	7283	6648	6527
35°	7136	6446	6330
40°	7017	6253	6127
45°	6842	6071	5947
50°	6693	5865	5757
55°	6538	5665	5539
60°	6300	5418	5333
65°	6036	5152	5085
70°	5716	4846	4799
75°	5271	4507	4527
80°	4767	4162	4242
85°	4097	3813	4012

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6842 cd/sqm

TEST NUMBER: P1013140

CATALOG NUMBER: S124DIP-B795D1035UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.0	1.2
10°-20°	257.7	3.5
20°-30°	389.7	5.3
30°-40°	471.5	6.5
40°-50°	498.4	6.8
50°-60°	469.1	6.4
60°-70°	389.3	5.3
70°-80°	273.2	3.7
80°-90°	156.7	2.1
90°-100°	135.3	1.9
100°-110°	355.1	4.9
110°-120°	594.0	8.1
120°-130°	721.9	9.9
130°-140°	755.9	10.3
140°-150°	698.6	9.6
150°-160°	561.6	7.7
160°-170°	362.2	5.0
170°-180°	124.8	1.7
0°-30°	737.4	10.1
0°-40°	1208.9	16.5
0°-60°	2176.5	29.8
0°-90°	2995.6	41.0
90°-120°	1084.4	14.8
90°-150°	3260.8	44.6
90°-180°	4309.0	59.0
0°-180°	7305.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	949	949	949	949	949	
5°	950	947	940	948	947	90
15°	911	912	909	919	918	257
25°	834	840	843	855	856	384
35°	729	742	753	768	771	457
45°	608	628	648	667	672	470
55°	476	499	530	552	558	424
65°	330	364	400	426	435	327
75°	183	222	267	297	306	194
85°	56	101	149	181	191	59
90°	20	73	127	164	174	14
95°	68	70	114	149	159	78
105°	305	332	377	412	385	320
115°	559	571	604	630	637	550
125°	781	783	808	831	838	697
135°	965	964	976	994	1003	744
145°	1112	1113	1113	1121	1127	695
155°	1218	1218	1216	1219	1216	561
165°	1284	1279	1279	1287	1278	363
175°	1314	1308	1309	1318	1306	125
180°	1314	1314	1314	1314	1314	

TEST NUMBER: P1013140

CATALOG NUMBER: S124DIP-B795D1035UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	949.4	949.4	949.4	949.4	949.4
2.5°	953.7	950.5	942.0	949.4	948.4
5°	950.5	947.3	939.9	948.4	947.3
7.5°	944.1	942.0	935.6	945.2	944.1
10°	935.6	934.5	929.2	938.8	937.7
12.5°	923.9	923.9	920.7	929.2	929.2
15°	911.2	912.2	909.0	918.6	917.5
17.5°	894.1	897.3	896.3	905.8	904.8
20°	876.1	879.3	880.3	891.0	891.0
22.5°	855.9	860.1	862.2	872.9	875.0
25°	833.5	839.9	843.1	854.8	855.9
27.5°	809.1	818.7	822.9	833.5	834.6
30°	784.6	793.1	800.6	812.3	814.4
32.5°	758.1	768.7	777.2	791.0	793.1
35°	729.4	742.1	752.7	767.6	770.8
37.5°	700.6	715.5	728.3	743.2	746.4
40°	673.0	686.8	701.7	717.7	721.9
42.5°	641.1	657.1	675.1	693.2	696.4
45°	608.1	628.3	648.5	666.6	671.9
47.5°	577.3	597.5	620.9	639.0	645.4
50°	543.3	566.7	590.1	611.3	617.7
52.5°	509.3	532.7	560.3	581.6	587.9
55°	476.3	498.6	530.5	551.8	558.2
57.5°	439.1	466.7	497.6	523.1	528.4
60°	403.0	430.6	465.7	490.1	498.6
62.5°	367.9	398.7	433.8	458.2	466.7
65°	329.6	363.6	399.8	426.3	434.8
67.5°	293.4	329.6	367.9	394.4	403.0
70°	256.2	292.4	332.8	361.5	368.9
72.5°	220.1	257.3	300.9	328.5	337.0
75°	182.9	222.2	266.9	296.6	306.2
77.5°	147.8	189.2	236.0	265.8	276.4
80°	115.9	158.4	205.2	237.1	245.6
82.5°	84.0	128.6	175.4	208.4	218.0
85°	56.3	101.0	148.8	180.7	191.4
87.5°	35.1	78.7	125.5	156.3	165.9
90°	19.9	73.3	126.9	163.6	174.1
92.5°	30.6	66.0	119.5	155.1	163.7
95°	67.8	69.5	114.1	148.7	159.3
97.5°	116.0	168.4	108.8	141.3	151.9
100°	172.9	218.1	124.0	136.0	144.5
102.5°	237.7	272.9	325.1	131.6	140.1
105°	305.4	332.5	376.8	412.2	385.3
107.5°	369.2	390.2	434.4	465.8	477.2
110°	433.0	450.8	493.9	520.4	531.9

TEST NUMBER: P1013140

CATALOG NUMBER: S124DIP-B795D1035UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	494.8	513.5	550.5	573.0	585.4
115°	558.6	571.1	604.2	629.6	637.0
117.5°	616.6	626.9	661.8	683.1	691.6
120°	674.5	681.6	711.4	734.7	741.2
122.5°	729.5	731.5	762.1	784.4	789.8
125°	780.6	783.4	808.0	831.2	838.5
127.5°	830.7	830.6	856.8	874.9	881.3
130°	877.7	877.6	897.6	917.8	924.2
132.5°	922.0	922.8	939.6	958.6	964.0
135°	965.1	964.1	975.5	994.5	1002.9
137.5°	1004.4	1003.4	1012.5	1030.5	1034.8
140°	1042.7	1043.7	1046.6	1063.4	1069.8
142.5°	1076.1	1080.0	1079.9	1093.6	1097.8
145°	1111.5	1113.3	1113.3	1120.7	1126.9
147.5°	1139.0	1143.8	1142.8	1144.9	1150.1
150°	1169.4	1172.3	1171.3	1171.3	1172.3
152.5°	1193.9	1196.8	1194.9	1196.8	1195.9
155°	1217.5	1218.5	1215.5	1219.4	1216.5
157.5°	1238.1	1238.1	1234.2	1239.1	1234.2
160°	1255.8	1252.9	1251.9	1257.8	1251.9
162.5°	1271.5	1267.6	1266.6	1272.5	1265.6
165°	1284.3	1279.4	1279.4	1287.2	1278.4
167.5°	1295.1	1290.2	1289.2	1298.1	1288.2
170°	1303.9	1298.1	1299.0	1306.9	1297.1
172.5°	1309.8	1303.9	1304.9	1312.8	1302.0
175°	1313.8	1307.9	1308.9	1317.7	1305.9
177.5°	1316.7	1309.8	1311.8	1319.7	1307.9
180°	1313.8	1313.8	1313.8	1313.8	1313.8

(END OF REPORT)