

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013146

Luminaire Tested: S124DIP-B795D1035UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013146
REPORT IS A COMBINATION OF REPORTS P996342 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B795D1035UB2750-4F0-XX-W2A-F_5000K
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7227.0 lumens
Efficiency: N/A
Efficacy: 112.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013146

CATALOG NUMBER: S124DIP-B795D1035UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013146

CATALOG NUMBER: S124DIP-B795D1035UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52			46
1	97	92	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44			38
2	88	81	75	69	81	74	69	64	62	58	55	51	48	46	40	39	37			32
3	80	71	64	58	73	65	59	54	55	50	46	45	42	39	36	33	31			27
4	73	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27			23
5	67	56	48	42	62	52	44	39	43	38	34	36	32	29	29	26	24			20
6	62	50	42	36	57	46	39	34	39	34	29	32	28	25	26	23	21			18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18			16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17			14
9	50	37	30	25	45	35	28	23	30	24	21	25	21	18	20	17	15			13
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14			12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10462	10462	10462
5°	10470	10161	10174
10°	10382	9879	9810
15°	10233	9543	9399
20°	10043	9181	8975
25°	9829	8797	8518
30°	9571	8383	8016
35°	9303	7958	7531
40°	9025	7503	7014
45°	8733	7044	6532
50°	8409	6600	5998
55°	8058	6082	5467
60°	7697	5514	4915
65°	7285	4927	4292
70°	6811	4222	3625
75°	6104	3403	2904
80°	5199	2460	2042
85°	4039	1371	1098

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8733 cd/sqm

TEST NUMBER: P1013146

CATALOG NUMBER: S124DIP-B795D1035UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.9	1.7
10°-20°	340.7	4.7
20°-30°	501.4	6.9
30°-40°	582.8	8.1
40°-50°	582.8	8.1
50°-60°	509.7	7.1
60°-70°	378.4	5.2
70°-80°	214.7	3.0
80°-90°	64.1	0.9
90°-100°	42.2	0.6
100°-110°	277.7	3.8
110°-120°	530.3	7.3
120°-130°	673.3	9.3
130°-140°	720.3	10.0
140°-150°	673.5	9.3
150°-160°	543.1	7.5
160°-170°	350.3	4.8
170°-180°	120.7	1.7
0°-30°	963.0	13.3
0°-40°	1545.9	21.4
0°-60°	2638.4	36.5
0°-90°	3295.6	45.6
90°-120°	850.3	11.8
90°-150°	2917.3	40.4
90°-180°	3931.0	54.4
0°-180°	7227.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1283	1283	1283	1283	1283	
5°	1282	1278	1266	1278	1276	122
15°	1220	1216	1201	1207	1204	344
25°	1105	1098	1084	1085	1080	509
35°	951	944	929	922	917	595
45°	776	769	752	741	738	598
55°	587	584	570	557	551	526
65°	398	393	382	372	367	394
75°	212	207	202	197	196	225
85°	56	56	54	54	52	60
90°	3	13	21	27	28	6
95°	52	20	21	27	28	64
105°	286	292	296	305	271	299
115°	534	537	536	538	538	526
125°	751	754	753	756	756	670
135°	931	930	934	936	938	718
145°	1074	1077	1077	1078	1080	671
155°	1177	1178	1176	1179	1176	543
165°	1242	1237	1237	1245	1236	351
175°	1270	1265	1266	1274	1263	121
180°	1270	1270	1270	1270	1270	

TEST NUMBER: P1013146

CATALOG NUMBER: S124DIP-B795D1035UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1283.0	1283.0	1283.0	1283.0	1283.0
2.5°	1287.1	1284.0	1272.7	1283.0	1281.9
5°	1281.9	1277.8	1266.5	1277.8	1275.8
7.5°	1272.7	1268.6	1256.2	1265.5	1264.5
10°	1259.3	1255.2	1241.9	1250.1	1248.0
12.5°	1241.9	1237.7	1223.3	1232.6	1229.5
15°	1220.3	1216.2	1200.7	1206.9	1203.8
17.5°	1195.6	1190.5	1176.1	1180.2	1178.1
20°	1167.8	1162.7	1147.3	1150.4	1148.3
22.5°	1138.0	1130.8	1115.4	1121.6	1117.5
25°	1105.1	1097.9	1083.5	1084.6	1080.5
27.5°	1068.1	1060.9	1047.6	1045.5	1040.4
30°	1031.1	1022.9	1009.5	1005.4	1000.3
32.5°	992.0	984.8	970.5	965.3	960.2
35°	950.9	943.7	929.3	922.1	917.0
37.5°	907.7	901.6	886.2	879.0	871.8
40°	865.6	857.4	842.0	831.7	826.5
42.5°	820.4	816.3	798.8	786.4	783.4
45°	776.2	769.0	752.5	741.2	738.1
47.5°	729.9	724.8	709.3	697.0	688.8
50°	682.6	678.5	664.1	649.7	643.5
52.5°	636.3	631.2	615.8	603.4	595.2
55°	587.0	583.9	569.5	557.2	551.0
57.5°	540.7	537.7	523.3	510.9	504.8
60°	492.4	487.3	473.9	464.7	459.5
62.5°	445.1	441.0	426.6	418.4	413.3
65°	397.8	392.7	382.4	372.1	367.0
67.5°	349.5	345.4	335.1	324.9	323.8
70°	305.3	298.1	289.9	281.7	278.6
72.5°	258.0	250.8	244.7	238.5	235.4
75°	211.8	206.6	201.5	197.4	196.4
77.5°	166.5	164.5	159.3	158.3	155.2
80°	126.4	123.4	121.3	119.3	118.2
82.5°	87.4	86.4	86.4	85.3	84.3
85°	55.5	55.5	53.5	53.5	52.4
87.5°	26.7	25.7	24.7	24.7	24.7
90°	2.9	13.3	20.9	26.6	28.5
92.5°	14.3	12.4	20.0	25.7	25.7
95°	52.3	20.0	20.9	26.6	27.6
97.5°	99.8	120.7	20.9	25.7	26.6
100°	155.8	172.9	41.8	25.7	26.6
102.5°	218.6	230.0	241.4	27.6	27.6
105°	286.0	291.7	296.5	305.0	270.8
107.5°	347.8	350.6	357.3	362.0	365.9
110°	410.5	413.4	419.1	421.0	423.8

TEST NUMBER: P1013146

CATALOG NUMBER: S124DIP-B795D1035UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	471.3	477.0	478.9	478.0	481.8
115°	534.0	536.9	535.9	537.8	537.8
117.5°	590.1	593.9	596.8	595.8	595.8
120°	647.1	650.9	650.0	651.9	650.0
122.5°	700.3	702.2	704.1	705.1	703.2
125°	750.7	754.5	752.6	755.5	756.4
127.5°	799.2	800.1	804.9	803.9	803.0
130°	845.7	846.7	849.5	850.5	850.5
132.5°	888.5	890.4	894.2	895.1	894.2
135°	931.3	930.3	934.1	936.0	937.9
137.5°	969.3	969.3	974.0	975.9	975.0
140°	1006.3	1008.2	1010.1	1013.0	1013.9
142.5°	1039.6	1043.4	1044.3	1046.2	1046.2
145°	1073.8	1076.6	1076.6	1077.6	1079.5
147.5°	1100.4	1106.1	1105.2	1106.1	1107.1
150°	1129.9	1133.7	1132.7	1132.7	1133.7
152.5°	1154.6	1157.4	1155.5	1157.4	1156.5
155°	1177.4	1178.3	1175.5	1179.3	1176.4
157.5°	1197.3	1197.3	1193.5	1198.3	1193.5
160°	1214.4	1211.6	1210.6	1216.3	1210.6
162.5°	1229.6	1225.8	1224.9	1230.6	1223.9
165°	1242.0	1237.2	1237.2	1244.8	1236.3
167.5°	1252.4	1247.7	1246.7	1255.3	1245.8
170°	1261.0	1255.3	1256.2	1263.8	1254.3
172.5°	1266.7	1261.0	1261.9	1269.6	1259.1
175°	1270.5	1264.8	1265.7	1274.3	1262.9
177.5°	1273.4	1266.7	1268.6	1276.2	1264.8
180°	1270.5	1270.5	1270.5	1270.5	1270.5

(END OF REPORT)