

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1025388

Luminaire Tested: S124DIP-B350D365UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1025388
REPORT IS A COMBINATION OF REPORTS P995898 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B350D365UB50-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2689.5 lumens
Efficiency: N/A
Efficacy: 120.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1025388

CATALOG NUMBER: S124DIP-B350D365UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1025388

CATALOG NUMBER: S124DIP-B350D365UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85		71	71	71		59
1	98	94	90	87	91	87	84	81	74	72	70		63	61	59		52
2	90	82	76	71	83	76	71	66	65	61	58		55	52	49		46
3	82	72	65	59	75	67	61	55	57	53	48		49	45	42		40
4	75	64	56	50	69	59	52	47	51	46	41		43	39	36		36
5	69	57	49	43	63	53	46	40	46	40	36		39	35	31		33
6	63	51	43	37	58	48	40	35	41	35	31		35	31	27		30
7	58	46	38	33	54	43	36	31	37	32	27		32	27	24		27
8	54	42	34	29	50	39	32	27	34	28	24		29	25	22		25
9	51	38	31	26	47	36	29	24	31	26	22		27	23	19		23
10	47	35	28	23	44	33	26	22	29	23	20		25	21	18		21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4509	4509	4509
5°	4512	4379	4384
10°	4474	4257	4227
15°	4409	4112	4050
20°	4327	3956	3867
25°	4235	3791	3671
30°	4124	3612	3454
35°	4009	3430	3245
40°	3889	3233	3023
45°	3763	3036	2815
50°	3623	2844	2585
55°	3472	2621	2356
60°	3317	2376	2118
65°	3139	2124	1849
70°	2936	1819	1563
75°	2631	1466	1251
80°	2242	1061	879
85°	1739	589	474

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3763 cd/sqm

TEST NUMBER: P1025388

CATALOG NUMBER: S124DIP-B350D365UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.1	1.9
10°-20°	146.8	5.5
20°-30°	216.1	8.0
30°-40°	251.2	9.3
40°-50°	251.1	9.3
50°-60°	219.6	8.2
60°-70°	163.1	6.1
70°-80°	92.5	3.4
80°-90°	27.2	1.0
90°-100°	129.3	4.8
100°-110°	262.9	9.8
110°-120°	234.3	8.7
120°-130°	196.8	7.3
130°-140°	164.2	6.1
140°-150°	125.4	4.7
150°-160°	88.2	3.3
160°-170°	51.9	1.9
170°-180°	16.9	0.6
0°-30°	415.0	15.4
0°-40°	666.1	24.8
0°-60°	1136.9	42.3
0°-90°	1419.7	52.8
90°-120°	626.5	23.3
90°-150°	1113.0	41.4
90°-180°	1270.0	47.2
0°-180°	2689.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	553	553	553	553	553	
5°	552	551	546	551	550	52
15°	526	524	517	520	519	148
25°	476	473	467	467	466	219
35°	410	407	400	397	395	256
45°	334	331	324	319	318	258
55°	253	252	245	240	237	227
65°	171	169	165	160	158	170
75°	91	89	87	85	85	97
85°	24	24	23	23	23	26
90°	0	3	6	7	7	2
95°	11	36	279	138	83	12
105°	40	58	224	483	481	43
115°	70	88	200	384	462	70
125°	98	117	199	327	368	87
135°	117	139	197	290	330	90
145°	134	154	196	245	269	84
155°	153	165	191	216	225	70
165°	166	172	183	194	197	47
175°	174	174	175	178	177	16
180°	174	174	174	174	174	

TEST NUMBER: P1025388

CATALOG NUMBER: S124DIP-B350D365UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	552.9	552.9	552.9	552.9	552.9
2.5°	554.6	553.3	548.4	552.9	552.4
5°	552.4	550.6	545.8	550.6	549.8
7.5°	548.4	546.6	541.3	545.3	544.9
10°	542.7	540.9	535.1	538.7	537.8
12.5°	535.1	533.4	527.2	531.1	529.8
15°	525.8	524.1	517.4	520.1	518.7
17.5°	515.2	513.0	506.8	508.6	507.7
20°	503.2	501.0	494.4	495.7	494.8
22.5°	490.4	487.3	480.6	483.3	481.5
25°	476.2	473.1	466.9	467.4	465.6
27.5°	460.3	457.2	451.4	450.5	448.3
30°	444.3	440.8	435.0	433.2	431.0
32.5°	427.5	424.4	418.2	416.0	413.8
35°	409.8	406.7	400.5	397.4	395.1
37.5°	391.2	388.5	381.9	378.8	375.7
40°	373.0	369.5	362.8	358.4	356.2
42.5°	353.5	351.7	344.2	338.9	337.6
45°	334.5	331.4	324.3	319.4	318.1
47.5°	314.5	312.3	305.7	300.3	296.8
50°	294.1	292.4	286.2	280.0	277.3
52.5°	274.2	272.0	265.4	260.0	256.5
55°	252.9	251.6	245.4	240.1	237.4
57.5°	233.0	231.7	225.5	220.2	217.5
60°	212.2	210.0	204.2	200.2	198.0
62.5°	191.8	190.0	183.8	180.3	178.1
65°	171.4	169.2	164.8	160.4	158.1
67.5°	150.6	148.8	144.4	140.0	139.5
70°	131.6	128.5	124.9	121.4	120.1
72.5°	111.2	108.1	105.4	102.8	101.4
75°	91.3	89.0	86.8	85.1	84.6
77.5°	71.8	70.9	68.7	68.2	66.9
80°	54.5	53.2	52.3	51.4	50.9
82.5°	37.7	37.2	37.2	36.8	36.3
85°	23.9	23.9	23.0	23.0	22.6
87.5°	11.5	11.1	10.6	10.6	10.6
90°	0.3	2.7	6.2	6.8	7.2
92.5°	4.8	26.4	134.0	44.2	31.1
95°	11.3	35.6	278.6	138.0	83.4
97.5°	18.8	39.4	298.1	281.6	200.3
100°	26.0	44.4	274.9	389.8	313.5
102.5°	32.8	50.6	245.8	457.4	411.9
105°	40.0	58.0	224.3	482.9	481.0
107.5°	47.9	65.4	210.2	475.2	513.8
110°	55.7	73.0	203.7	447.8	514.5



TEST NUMBER: P1025388

CATALOG NUMBER: S124DIP-B350D365UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	63.2	80.5	200.7	414.3	494.3
115°	70.4	88.4	200.0	384.2	461.8
117.5°	77.9	95.7	199.6	360.6	430.1
120°	85.5	102.9	199.6	344.8	404.1
122.5°	92.3	109.9	199.3	334.4	383.6
125°	98.1	116.6	199.0	327.0	368.5
127.5°	103.6	122.7	198.3	320.0	358.9
130°	108.0	128.8	197.9	311.6	350.7
132.5°	112.5	133.8	197.6	301.6	341.5
135°	116.6	138.8	197.3	290.2	329.5
137.5°	120.7	143.0	197.3	278.0	315.5
140°	125.1	147.0	196.9	266.0	300.1
142.5°	129.9	150.6	196.9	254.8	283.7
145°	134.3	153.8	196.2	244.8	269.0
147.5°	139.5	156.9	195.2	236.4	255.4
150°	144.3	159.8	194.2	228.7	244.1
152.5°	148.7	162.6	192.5	222.2	233.8
155°	152.8	165.0	190.8	216.0	225.3
157.5°	156.9	167.1	189.0	210.2	217.4
160°	160.7	169.0	187.0	204.4	210.2
162.5°	164.1	170.6	184.9	198.8	203.4
165°	166.5	171.6	182.9	193.6	196.6
167.5°	169.2	172.4	180.8	189.2	191.1
170°	170.9	173.1	178.8	184.8	186.0
172.5°	172.6	173.6	176.7	180.8	180.8
175°	173.7	174.0	175.4	177.8	177.1
177.5°	174.3	174.0	174.3	175.6	174.3
180°	174.0	174.0	174.0	174.0	174.0

(END OF REPORT)