

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013181

Luminaire Tested: S124DIP-B795D590UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013181
REPORT IS A COMBINATION OF REPORTS P996515 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B795D590UB2750-4F0-XX-W2A-D_3500K
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5647.0 lumens
Efficiency: N/A
Efficacy: 110.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013181

CATALOG NUMBER: S124DIP-B795D590UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1013181

CATALOG NUMBER: S124DIP-B795D590UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	98	93	88	84	90	86	82	79	73	70	68	62	60	58	51	49	48
2	88	80	74	68	81	74	69	64	63	59	55	53	50	47	44	42	40
3	80	70	62	56	74	65	58	53	56	50	46	47	43	39	39	36	33
4	73	62	54	47	67	57	50	44	49	43	39	41	37	33	34	31	28
5	67	55	46	40	62	51	44	38	44	38	33	37	32	29	31	27	24
6	62	49	41	35	57	46	38	33	39	33	29	33	29	25	28	24	21
7	57	44	36	30	53	41	34	29	36	30	25	30	26	22	25	22	19
8	53	40	32	27	49	38	30	25	32	27	22	28	23	20	23	20	17
9	49	37	29	24	46	34	27	22	30	24	20	25	21	18	21	18	15
10	46	34	26	21	43	31	25	20	27	22	18	24	19	16	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7821	7821	7821
5°	7843	7617	7631
10°	7791	7467	7446
15°	7718	7299	7237
20°	7611	7116	7034
25°	7489	6915	6816
30°	7357	6715	6593
35°	7208	6512	6395
40°	7089	6317	6190
45°	6911	6133	6008
50°	6761	5924	5816
55°	6605	5723	5595
60°	6364	5473	5387
65°	6097	5203	5138
70°	5774	4896	4849
75°	5323	4553	4573
80°	4816	4204	4286
85°	4141	3854	4052

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6911 cd/sqm

TEST NUMBER: P1013181

CATALOG NUMBER: S124DIP-B795D590UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.9	1.6
10°-20°	260.4	4.6
20°-30°	393.7	7.0
30°-40°	476.3	8.4
40°-50°	503.5	8.9
50°-60°	473.9	8.4
60°-70°	393.2	7.0
70°-80°	276.0	4.9
80°-90°	157.2	2.8
90°-100°	118.1	2.1
100°-110°	236.4	4.2
110°-120°	366.5	6.5
120°-130°	432.7	7.7
130°-140°	446.4	7.9
140°-150°	409.2	7.2
150°-160°	328.2	5.8
160°-170°	211.6	3.7
170°-180°	72.9	1.3
0°-30°	744.9	13.2
0°-40°	1221.2	21.6
0°-60°	2198.6	38.9
0°-90°	3025.0	53.6
90°-120°	721.0	12.8
90°-150°	2009.3	35.6
90°-180°	2622.0	46.4
0°-180°	5647.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	959	959	959	959	959	
5°	960	957	949	958	957	91
15°	920	922	918	928	927	259
25°	842	848	852	864	865	388
35°	737	750	760	776	779	461
45°	614	635	655	673	679	475
55°	481	504	536	557	564	429
65°	333	367	404	431	439	330
75°	185	224	270	300	309	196
85°	57	102	150	183	193	59
90°	19	68	119	154	163	13
95°	46	62	106	138	149	50
105°	182	207	250	282	270	192
115°	329	340	374	399	407	324
125°	458	459	485	507	514	409
135°	565	564	574	592	600	436
145°	650	650	650	658	663	406
155°	711	712	710	712	711	328
165°	750	748	748	752	747	212
175°	768	764	765	770	763	73
180°	768	768	768	768	768	

TEST NUMBER: P1013181

CATALOG NUMBER: S124DIP-B795D590UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	959.1	959.1	959.1	959.1	959.1
2.5°	963.4	960.2	951.6	959.1	958.0
5°	960.2	957.0	949.4	958.0	957.0
7.5°	953.7	951.6	945.1	954.8	953.7
10°	945.1	944.1	938.7	948.4	947.3
12.5°	933.3	933.3	930.1	938.7	938.7
15°	920.4	921.5	918.3	928.0	926.9
17.5°	903.3	906.5	905.4	915.1	914.0
20°	885.0	888.2	889.3	900.0	900.0
22.5°	864.6	868.9	871.0	881.8	883.9
25°	842.0	848.5	851.7	863.5	864.6
27.5°	817.3	827.0	831.3	842.0	843.1
30°	792.6	801.2	808.7	820.6	822.7
32.5°	765.8	776.5	785.1	799.1	801.2
35°	736.8	749.7	760.4	775.5	778.7
37.5°	707.8	722.8	735.7	750.7	754.0
40°	679.9	693.8	708.9	725.0	729.3
42.5°	647.6	663.8	682.0	700.3	703.5
45°	614.3	634.8	655.2	673.4	678.8
47.5°	583.2	603.6	627.2	645.5	651.9
50°	548.8	572.5	596.1	617.6	624.0
52.5°	514.5	538.1	566.0	587.5	593.9
55°	481.2	503.7	535.9	557.4	563.9
57.5°	443.6	471.5	502.6	528.4	533.8
60°	407.1	435.0	470.4	495.1	503.7
62.5°	371.6	402.8	438.2	462.9	471.5
65°	332.9	367.3	403.8	430.7	439.3
67.5°	296.4	332.9	371.6	398.5	407.1
70°	258.8	295.4	336.2	365.2	372.7
72.5°	222.3	259.9	304.0	331.9	340.5
75°	184.7	224.5	269.6	299.7	309.3
77.5°	149.3	191.2	238.4	268.5	279.2
80°	117.1	160.0	207.3	239.5	248.1
82.5°	84.8	130.0	177.2	210.5	220.2
85°	56.9	102.0	150.4	182.6	193.3
87.5°	35.4	79.5	126.7	157.9	167.5
90°	18.9	68.1	118.9	153.6	163.3
92.5°	24.7	61.2	112.0	145.5	154.1
95°	45.6	61.5	106.0	138.5	148.8
97.5°	73.2	116.9	100.7	131.5	141.8
100°	106.0	144.2	106.9	126.1	134.2
102.5°	143.9	174.3	222.1	120.9	129.5
105°	182.5	207.4	250.0	282.0	269.9
107.5°	219.8	239.8	281.4	311.2	321.0
110°	256.6	273.4	314.4	340.3	350.6

TEST NUMBER: P1013181

CATALOG NUMBER: S124DIP-B795D590UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	292.3	308.6	345.2	368.3	379.2
115°	329.1	340.5	374.3	399.1	406.6
117.5°	363.0	371.8	405.7	427.7	436.3
120°	396.4	401.9	432.4	455.1	462.5
122.5°	428.6	429.7	459.9	481.8	488.3
125°	457.9	459.1	484.8	507.0	513.9
127.5°	487.2	486.6	511.0	529.7	536.8
130°	514.2	513.7	532.6	552.6	559.0
132.5°	540.0	540.1	555.3	574.2	580.0
135°	564.8	564.2	574.1	592.5	600.0
137.5°	587.8	586.8	593.9	611.2	616.0
140°	610.1	610.3	612.4	628.2	634.1
142.5°	629.2	631.5	631.0	644.0	648.3
145°	649.9	650.5	650.5	657.5	663.0
147.5°	666.0	668.3	667.8	669.4	674.3
150°	683.8	685.0	684.4	684.4	685.0
152.5°	697.6	699.3	698.2	699.3	698.8
155°	711.4	712.0	710.2	712.5	710.8
157.5°	723.5	723.5	721.2	724.0	721.2
160°	733.8	732.1	731.5	734.9	731.5
162.5°	743.0	740.7	740.1	743.5	739.5
165°	750.4	747.6	747.6	752.2	747.0
167.5°	756.8	753.9	753.3	758.5	752.7
170°	761.9	758.5	759.0	763.6	757.9
172.5°	765.4	761.9	762.5	767.1	760.8
175°	767.7	764.2	764.8	770.0	763.1
177.5°	769.4	765.4	766.5	771.1	764.2
180°	767.7	767.7	767.7	767.7	767.7

(END OF REPORT)