

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1025667

Luminaire Tested: S124DIP-B575D810UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1025667
REPORT IS A COMBINATION OF REPORTS P996267 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B575D810UB27-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5274.7 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1025667

CATALOG NUMBER: S124DIP-B575D810UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1025667

CATALOG NUMBER: S124DIP-B575D810UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	47	47	47
1	97	93	89	85	89	85	82	79	71	69	67	59	57	55	47	46	45	39	39	39
2	88	81	75	70	81	75	69	65	63	59	55	51	49	46	41	39	38	33	33	33
3	81	71	64	58	74	66	59	54	55	50	46	45	42	39	37	34	32	28	28	28
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24	24	24
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	29	26	24	21	21	21
6	62	50	42	36	57	47	39	34	39	34	30	33	29	25	27	24	21	18	18	18
7	58	45	37	32	53	42	35	30	36	30	26	30	26	22	24	21	19	16	16	16
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	22	19	17	14	14	14
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13	13	13
10	46	34	27	22	43	32	26	21	27	22	19	23	19	16	19	16	14	12	12	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7819	7819	7819
5°	7826	7594	7603
10°	7759	7383	7331
15°	7648	7133	7025
20°	7506	6861	6708
25°	7345	6575	6366
30°	7153	6265	5990
35°	6953	5948	5628
40°	6745	5607	5242
45°	6527	5265	4882
50°	6284	4933	4482
55°	6022	4545	4086
60°	5753	4121	3673
65°	5445	3683	3208
70°	5091	3156	2709
75°	4562	2543	2169
80°	3887	1839	1527
85°	3020	1025	822

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6527 cd/sqm

TEST NUMBER: P1025667

CATALOG NUMBER: S124DIP-B575D810UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.4	1.7
10°-20°	254.6	4.8
20°-30°	374.7	7.1
30°-40°	435.6	8.3
40°-50°	435.5	8.3
50°-60°	380.9	7.2
60°-70°	282.8	5.4
70°-80°	160.5	3.0
80°-90°	47.4	0.9
90°-100°	286.2	5.4
100°-110°	582.2	11.0
110°-120°	518.9	9.8
120°-130°	435.9	8.3
130°-140°	363.7	6.9
140°-150°	277.8	5.3
150°-160°	195.3	3.7
160°-170°	114.8	2.2
170°-180°	37.3	0.7
0°-30°	719.7	13.6
0°-40°	1155.3	21.9
0°-60°	1971.8	37.4
0°-90°	2462.5	46.7
90°-120°	1387.3	26.3
90°-150°	2464.7	46.7
90°-180°	2812.0	53.3
0°-180°	5274.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	959	959	959	959	959	
5°	958	955	946	955	953	91
15°	912	909	897	902	900	257
25°	826	820	810	810	808	380
35°	711	705	694	689	685	444
45°	580	575	562	554	552	447
55°	439	436	426	416	412	393
65°	297	294	286	278	274	294
75°	158	154	151	148	147	168
85°	42	42	40	40	39	45
90°	1	6	14	15	16	4
95°	25	79	617	305	185	27
105°	89	128	497	1069	1065	94
115°	156	196	443	851	1023	155
125°	217	258	441	724	816	194
135°	258	307	437	643	730	200
145°	298	341	434	542	596	187
155°	338	365	422	478	499	156
165°	369	380	405	429	435	104
175°	385	385	388	394	392	37
180°	385	385	385	385	385	

TEST NUMBER: P1025667

CATALOG NUMBER: S124DIP-B575D810UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	958.8	958.8	958.8	958.8	958.8
2.5°	961.9	959.6	951.1	958.8	958.1
5°	958.1	955.0	946.5	955.0	953.4
7.5°	951.1	948.1	938.8	945.8	945.0
10°	941.2	938.1	928.1	934.2	932.7
12.5°	928.1	925.0	914.3	921.2	918.9
15°	912.0	908.9	897.4	902.0	899.7
17.5°	893.5	889.7	878.9	882.0	880.5
20°	872.8	868.9	857.4	859.7	858.2
22.5°	850.5	845.1	833.6	838.2	835.1
25°	825.9	820.5	809.8	810.5	807.5
27.5°	798.2	792.9	782.9	781.3	777.5
30°	770.6	764.4	754.5	751.4	747.5
32.5°	741.4	736.0	725.3	721.4	717.6
35°	710.7	705.3	694.5	689.2	685.3
37.5°	678.4	673.8	662.3	656.9	651.5
40°	646.9	640.8	629.2	621.5	617.7
42.5°	613.1	610.0	597.0	587.7	585.4
45°	580.1	574.7	562.4	553.9	551.6
47.5°	545.5	541.6	530.1	520.9	514.8
50°	510.1	507.1	496.3	485.6	480.9
52.5°	475.6	471.7	460.2	451.0	444.8
55°	438.7	436.4	425.6	416.4	411.8
57.5°	404.1	401.8	391.1	381.8	377.2
60°	368.0	364.2	354.2	347.3	343.4
62.5°	332.7	329.6	318.8	312.7	308.9
65°	297.3	293.5	285.8	278.1	274.3
67.5°	261.2	258.1	250.5	242.8	242.0
70°	228.2	222.8	216.7	210.5	208.2
72.5°	192.8	187.5	182.9	178.2	175.9
75°	158.3	154.4	150.6	147.5	146.7
77.5°	124.5	122.9	119.1	118.3	116.0
80°	94.5	92.2	90.7	89.1	88.4
82.5°	65.3	64.5	64.5	63.8	63.0
85°	41.5	41.5	40.0	40.0	39.2
87.5°	20.0	19.2	18.4	18.4	18.4
90°	0.8	6.1	13.6	15.1	15.9
92.5°	10.6	58.3	296.8	98.0	68.9
95°	25.0	78.7	617.0	305.4	184.7
97.5°	41.6	87.1	660.1	623.8	443.6
100°	57.5	98.4	608.7	863.0	694.2
102.5°	72.7	112.0	544.3	1013.0	912.2
105°	88.6	128.3	496.6	1069.3	1065.2
107.5°	106.0	145.0	465.6	1052.3	1137.8
110°	123.4	161.6	451.2	991.8	1139.3

TEST NUMBER: P1025667

CATALOG NUMBER: S124DIP-B575D810UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	140.1	178.3	444.4	917.6	1094.7
115°	156.0	195.7	442.9	851.0	1022.8
117.5°	172.6	212.0	442.1	798.7	952.4
120°	189.3	227.9	442.1	763.5	894.8
122.5°	204.4	243.4	441.4	740.4	849.4
125°	217.3	258.2	440.6	724.1	816.1
127.5°	229.4	271.8	439.1	708.6	794.9
130°	239.2	285.0	438.3	690.0	776.7
132.5°	249.1	296.4	437.6	668.1	756.3
135°	258.2	307.4	436.8	642.8	729.8
137.5°	267.2	316.8	436.8	615.5	698.7
140°	277.1	325.5	436.1	589.0	664.7
142.5°	287.7	333.5	436.1	564.4	628.3
145°	297.5	340.6	434.5	542.0	595.8
147.5°	308.9	347.5	432.3	523.5	565.5
150°	319.5	353.9	430.0	506.4	540.5
152.5°	329.3	360.0	426.2	492.1	517.8
155°	338.4	365.3	422.4	478.4	498.9
157.5°	347.5	370.2	418.6	465.6	481.5
160°	355.8	374.4	414.1	452.7	465.6
162.5°	363.4	377.8	409.6	440.2	450.4
165°	368.7	380.0	405.0	428.9	435.3
167.5°	374.7	381.9	400.5	419.0	423.2
170°	378.5	383.5	395.9	409.2	411.8
172.5°	382.3	384.6	391.4	400.4	400.5
175°	384.6	385.3	388.4	393.7	392.1
177.5°	386.1	385.3	386.1	388.8	386.1
180°	385.3	385.3	385.3	385.3	385.3

(END OF REPORT)