

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013279

Luminaire Tested: S124RDIP-B1195D365UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013279
REPORT IS A COMBINATION OF REPORTS P999113 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D365UB2750-4F0-XX-W2A-F_4000K
Description: Define 4 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6266.0 lumens
Efficiency: N/A
Efficacy: 88.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013279

CATALOG NUMBER: S124RDIP-B1195D365UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013279

CATALOG NUMBER: S124RDIP-B1195D365UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	81	81	81
1	104	100	96	92	99	95	92	89	87	84	82	79	77	75	72	70	69
2	95	88	82	76	91	84	78	74	77	72	68	70	67	63	64	61	59
3	87	78	70	64	83	74	67	62	68	63	58	62	58	54	57	53	50
4	80	69	61	55	76	66	59	53	61	55	50	56	51	47	51	47	44
5	74	62	53	47	70	59	52	46	55	48	43	50	45	41	46	42	38
6	68	56	47	41	65	54	46	40	50	43	38	46	40	36	42	38	34
7	63	51	42	37	60	49	41	36	45	39	34	42	36	32	39	34	30
8	59	46	38	33	56	45	37	32	41	35	30	38	33	29	36	31	27
9	55	42	35	29	52	41	34	29	38	32	27	35	30	26	33	28	25
10	52	39	32	27	49	38	31	26	35	29	25	33	28	24	31	26	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16947	16947	16947
5°	16949	16444	16445
10°	16805	15925	15736
15°	16574	15279	14898
20°	16271	14542	13943
25°	15893	13747	13009
30°	15524	12937	11962
35°	15117	12115	10938
40°	14633	11230	9886
45°	14180	10353	8844
50°	13663	9394	7786
55°	13106	8412	6695
60°	12487	7368	5616
65°	11891	6172	4579
70°	11041	4913	3498
75°	9951	3573	2447
80°	8312	2194	1758
85°	6251	1263	966

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14180 cd/sqm

TEST NUMBER: P1013279

CATALOG NUMBER: S124RDIP-B1195D365UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.4	3.1
10°-20°	544.9	8.7
20°-30°	786.7	12.6
30°-40°	891.6	14.2
40°-50°	860.8	13.7
50°-60°	715.7	11.4
60°-70°	494.0	7.9
70°-80°	249.6	4.0
80°-90°	64.4	1.0
90°-100°	15.7	0.3
100°-110°	103.4	1.6
110°-120°	197.4	3.1
120°-130°	250.5	4.0
130°-140°	268.0	4.3
140°-150°	250.6	4.0
150°-160°	202.1	3.2
160°-170°	130.3	2.1
170°-180°	44.9	0.7
0°-30°	1527.0	24.4
0°-40°	2418.5	38.6
0°-60°	3995.0	63.8
0°-90°	4803.0	76.7
90°-120°	316.4	5.0
90°-150°	1085.6	17.3
90°-180°	1463.0	23.3
0°-180°	6266.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2078	2078	2078	2078	2078	
5°	2075	2069	2050	2066	2062	197
15°	1976	1962	1922	1919	1908	557
25°	1787	1758	1693	1666	1650	823
35°	1545	1494	1415	1361	1332	966
45°	1260	1201	1106	1028	999	972
55°	955	891	788	705	675	854
65°	649	581	479	411	392	641
75°	345	286	212	175	166	364
85°	86	54	49	46	46	94
90°	1	5	8	10	11	6
95°	19	7	8	10	10	24
105°	106	109	110	114	101	111
115°	199	200	199	200	200	196
125°	279	281	280	281	282	249
135°	347	346	348	348	349	267
145°	400	401	401	401	402	250
155°	438	438	437	439	438	202
165°	462	460	460	463	460	131
175°	473	471	471	474	470	45
180°	473	473	473	473	473	

TEST NUMBER: P1013279

CATALOG NUMBER: S124RDIP-B1195D365UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2078.2	2078.2	2078.2	2078.2	2078.2
2.5°	2084.6	2078.2	2060.7	2078.2	2076.7
5°	2075.1	2068.7	2049.6	2065.5	2062.3
7.5°	2060.7	2054.4	2030.5	2041.6	2036.9
10°	2038.5	2030.5	2001.9	2008.2	2001.9
12.5°	2009.8	2000.3	1965.3	1968.4	1958.9
15°	1976.4	1962.1	1922.3	1919.1	1908.0
17.5°	1938.2	1917.5	1871.4	1863.4	1847.5
20°	1892.1	1871.4	1817.3	1804.5	1783.9
22.5°	1841.1	1817.3	1758.4	1737.7	1721.8
25°	1787.0	1758.4	1693.1	1666.1	1650.2
27.5°	1731.3	1696.3	1627.9	1596.1	1573.8
30°	1672.5	1632.7	1557.9	1518.1	1492.6
32.5°	1610.4	1564.3	1486.3	1438.5	1414.7
35°	1545.2	1494.2	1414.7	1360.6	1331.9
37.5°	1476.7	1424.2	1336.7	1277.8	1249.2
40°	1403.5	1351.0	1260.3	1193.5	1164.8
42.5°	1333.5	1277.8	1182.3	1113.9	1083.7
45°	1260.3	1201.4	1106.0	1028.0	999.3
47.5°	1185.5	1125.1	1026.4	945.2	913.4
50°	1109.1	1047.1	945.2	865.7	835.4
52.5°	1031.2	970.7	865.7	784.5	752.7
55°	954.8	891.1	787.7	704.9	674.7
57.5°	880.0	813.2	711.3	627.0	604.7
60°	798.8	735.2	633.3	550.6	525.1
62.5°	725.6	658.8	553.8	479.0	459.9
65°	649.3	580.8	479.0	410.6	391.5
67.5°	569.7	504.4	409.0	348.5	326.2
70°	494.9	428.1	337.4	284.8	268.9
72.5°	415.3	356.5	272.1	229.1	214.8
75°	345.3	286.4	211.6	175.0	165.5
77.5°	272.1	221.2	157.5	132.1	128.9
80°	202.1	155.9	108.2	103.4	101.8
82.5°	141.6	100.3	78.0	74.8	73.2
85°	85.9	54.1	49.3	46.1	46.1
87.5°	36.6	23.9	22.3	20.7	22.3
90°	1.1	5.0	7.8	9.9	10.6
92.5°	5.3	4.6	7.4	9.5	9.5
95°	19.4	7.4	7.8	9.9	10.3
97.5°	37.1	44.9	7.8	9.5	9.9
100°	58.0	64.4	15.6	9.5	9.9
102.5°	81.3	85.6	89.8	10.3	10.3
105°	106.4	108.6	110.3	113.5	100.8
107.5°	129.4	130.5	133.0	134.7	136.1
110°	152.8	153.8	156.0	156.7	157.7



TEST NUMBER: P1013279

CATALOG NUMBER: S124RDIP-B1195D365UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	175.4	177.5	178.2	177.9	179.3
115°	198.7	199.8	199.4	200.2	200.2
117.5°	219.6	221.0	222.1	221.7	221.7
120°	240.8	242.2	241.9	242.6	241.9
122.5°	260.6	261.3	262.0	262.4	261.7
125°	279.4	280.8	280.1	281.1	281.5
127.5°	297.4	297.8	299.5	299.2	298.8
130°	314.7	315.1	316.1	316.5	316.5
132.5°	330.6	331.4	332.8	333.1	332.8
135°	346.6	346.2	347.6	348.3	349.0
137.5°	360.7	360.7	362.5	363.2	362.8
140°	374.5	375.2	375.9	377.0	377.3
142.5°	386.9	388.3	388.6	389.3	389.3
145°	399.6	400.7	400.7	401.0	401.7
147.5°	409.5	411.6	411.3	411.6	412.0
150°	420.5	421.9	421.5	421.5	421.9
152.5°	429.7	430.7	430.0	430.7	430.4
155°	438.1	438.5	437.4	438.9	437.8
157.5°	445.6	445.6	444.2	445.9	444.2
160°	451.9	450.9	450.5	452.6	450.5
162.5°	457.6	456.2	455.8	458.0	455.5
165°	462.2	460.4	460.4	463.3	460.1
167.5°	466.1	464.3	464.0	467.1	463.6
170°	469.3	467.1	467.5	470.3	466.8
172.5°	471.4	469.3	469.6	472.5	468.6
175°	472.8	470.7	471.0	474.2	470.0
177.5°	473.9	471.4	472.1	474.9	470.7
180°	472.8	472.8	472.8	472.8	472.8

(END OF REPORT)