

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013295

Luminaire Tested: S124RDIP-B1195D810UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013295
REPORT IS A COMBINATION OF REPORTS P999190 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D810UB2750-4F0-XX-W2A-F_2700K
Description: Define 4 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7922.0 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013295

CATALOG NUMBER: S124RDIP-B1195D810UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1013295

CATALOG NUMBER: S124RDIP-B1195D810UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66
1	100	96	92	89	94	90	87	84	79	76	74	68	67	65	59	57	56
2	92	84	78	73	86	79	74	69	69	65	62	60	57	55	52	50	48
3	84	74	67	61	78	70	64	58	61	56	52	54	50	47	46	44	41
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	38	36
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31
6	65	53	45	39	61	50	43	38	45	39	34	39	34	31	34	31	28
7	61	48	40	35	57	46	38	33	41	35	30	36	31	27	31	28	25
8	56	44	36	31	53	42	34	30	37	31	27	33	28	25	29	25	22
9	52	40	33	28	49	38	31	26	34	28	24	30	26	22	27	23	20
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16898	16898	16898
5°	16899	16395	16397
10°	16756	15878	15689
15°	16525	15234	14854
20°	16223	14500	13902
25°	15847	13707	12972
30°	15479	12899	11927
35°	15073	12079	10906
40°	14590	11197	9857
45°	14138	10322	8818
50°	13624	9367	7764
55°	13068	8387	6675
60°	12451	7347	5600
65°	11856	6154	4565
70°	11010	4899	3488
75°	9922	3563	2440
80°	8287	2188	1753
85°	6236	1261	964

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14138 cd/sqm

TEST NUMBER: P1013295

CATALOG NUMBER: S124RDIP-B1195D810UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.9	2.5
10°-20°	543.3	6.9
20°-30°	784.4	9.9
30°-40°	889.0	11.2
40°-50°	858.3	10.8
50°-60°	713.6	9.0
60°-70°	492.5	6.2
70°-80°	248.9	3.1
80°-90°	65.3	0.8
90°-100°	33.6	0.4
100°-110°	221.3	2.8
110°-120°	422.5	5.3
120°-130°	536.4	6.8
130°-140°	573.8	7.2
140°-150°	536.5	6.8
150°-160°	432.7	5.5
160°-170°	279.0	3.5
170°-180°	96.2	1.2
0°-30°	1522.5	19.2
0°-40°	2411.5	30.4
0°-60°	3983.4	50.3
0°-90°	4790.1	60.5
90°-120°	677.4	8.6
90°-150°	2324.0	29.3
90°-180°	3132.0	39.5
0°-180°	7922.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2072	2072	2072	2072	2072	
5°	2069	2063	2044	2060	2056	196
15°	1971	1956	1917	1914	1902	555
25°	1782	1753	1688	1661	1645	821
35°	1541	1490	1410	1357	1328	963
45°	1257	1198	1103	1025	996	969
55°	952	888	785	703	673	852
65°	647	579	478	409	390	639
75°	344	286	211	174	165	363
85°	86	54	49	46	46	94
90°	2	11	17	21	23	7
95°	42	16	17	21	22	51
105°	228	232	236	243	216	238
115°	425	428	427	428	428	419
125°	598	601	600	602	603	534
135°	742	741	744	746	747	572
145°	855	858	858	858	860	535
155°	938	939	936	940	937	432
165°	989	986	986	992	985	280
175°	1012	1008	1008	1015	1006	96
180°	1012	1012	1012	1012	1012	

TEST NUMBER: P1013295

CATALOG NUMBER: S124RDIP-B1195D810UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2072.2	2072.2	2072.2	2072.2	2072.2
2.5°	2078.5	2072.2	2054.7	2072.2	2070.6
5°	2069.0	2062.7	2043.6	2059.5	2056.3
7.5°	2054.7	2048.4	2024.6	2035.7	2030.9
10°	2032.5	2024.6	1996.0	2002.4	1996.0
12.5°	2004.0	1994.4	1959.5	1962.7	1953.2
15°	1970.6	1956.4	1916.7	1913.5	1902.4
17.5°	1932.6	1911.9	1865.9	1858.0	1842.1
20°	1886.5	1865.9	1812.0	1799.3	1778.7
22.5°	1835.8	1812.0	1753.3	1732.6	1716.8
25°	1781.8	1753.3	1688.2	1661.2	1645.4
27.5°	1726.3	1691.4	1623.2	1591.4	1569.2
30°	1667.6	1627.9	1553.3	1513.7	1488.3
32.5°	1605.7	1559.7	1481.9	1434.3	1410.5
35°	1540.7	1489.9	1410.5	1356.6	1328.0
37.5°	1472.4	1420.1	1332.8	1274.1	1245.5
40°	1399.4	1347.1	1256.6	1190.0	1161.4
42.5°	1329.6	1274.1	1178.9	1110.7	1080.5
45°	1256.6	1197.9	1102.7	1025.0	996.4
47.5°	1182.1	1121.8	1023.4	942.5	910.7
50°	1105.9	1044.0	942.5	863.1	833.0
52.5°	1028.2	967.9	863.1	782.2	750.5
55°	952.0	888.5	785.4	702.9	672.7
57.5°	877.4	810.8	709.2	625.1	602.9
60°	796.5	733.0	631.5	549.0	523.6
62.5°	723.5	656.9	552.2	477.6	458.5
65°	647.4	579.1	477.6	409.4	390.3
67.5°	568.0	503.0	407.8	347.5	325.3
70°	493.5	426.8	336.4	284.0	268.1
72.5°	414.1	355.4	271.3	228.5	214.2
75°	344.3	285.6	211.0	174.5	165.0
77.5°	271.3	220.5	157.1	131.7	128.5
80°	201.5	155.5	107.9	103.1	101.5
82.5°	141.2	100.0	77.7	74.6	73.0
85°	85.7	53.9	49.2	46.0	46.0
87.5°	36.5	23.8	22.2	20.6	22.2
90°	2.3	10.6	16.7	21.2	22.7
92.5°	11.4	9.8	15.9	20.4	20.4
95°	41.6	15.9	16.7	21.2	22.0
97.5°	79.5	96.1	16.7	20.4	21.2
100°	124.2	137.8	33.3	20.4	21.2
102.5°	174.1	183.2	192.3	22.0	22.0
105°	227.9	232.4	236.2	243.0	215.8
107.5°	277.1	279.3	284.6	288.4	291.5
110°	327.0	329.3	333.8	335.4	337.6



TEST NUMBER: P1013295

CATALOG NUMBER: S124RDIP-B1195D810UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.5	380.0	381.5	380.8	383.8
115°	425.4	427.7	427.0	428.5	428.5
117.5°	470.1	473.1	475.4	474.7	474.7
120°	515.5	518.6	517.8	519.3	517.8
122.5°	557.9	559.4	561.0	561.7	560.2
125°	598.0	601.1	599.6	601.8	602.6
127.5°	636.7	637.4	641.2	640.4	639.7
130°	673.7	674.5	676.8	677.5	677.5
132.5°	707.8	709.3	712.4	713.1	712.4
135°	741.9	741.1	744.2	745.7	747.2
137.5°	772.2	772.2	775.9	777.5	776.7
140°	801.7	803.2	804.7	807.0	807.7
142.5°	828.2	831.2	832.0	833.5	833.5
145°	855.4	857.7	857.7	858.5	860.0
147.5°	876.6	881.2	880.4	881.2	881.9
150°	900.1	903.1	902.4	902.4	903.1
152.5°	919.8	922.1	920.5	922.1	921.3
155°	937.9	938.7	936.4	939.5	937.2
157.5°	953.8	953.8	950.8	954.6	950.8
160°	967.5	965.2	964.4	969.0	964.4
162.5°	979.6	976.6	975.8	980.3	975.0
165°	989.4	985.6	985.6	991.7	984.9
167.5°	997.8	994.0	993.2	1000.0	992.5
170°	1004.6	1000.0	1000.8	1006.8	999.3
172.5°	1009.1	1004.6	1005.3	1011.4	1003.1
175°	1012.1	1007.6	1008.4	1015.2	1006.1
177.5°	1014.4	1009.1	1010.6	1016.7	1007.6
180°	1012.1	1012.1	1012.1	1012.1	1012.1

(END OF REPORT)