

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1025931

Luminaire Tested: S124RDIP-B1020D1035UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P1025931  
REPORT IS A COMBINATION OF REPORTS P998821 AND P1007351  
Test Lab: INNOVATION CENTER  
Issue Date: 5/7/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S124RDIP-B1020D1035UB27-4F0-XX-W2A-A4  
Description: Define 4 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}  
{m-EER=0.52}  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7908.0 lumens  
Efficiency: N/A  
Efficacy: 105.0 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38  
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')  
CIE Type: General Diffuse

Input Watts (W): 75.3  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1025931

CATALOG NUMBER: S124RDIP-B1020D1035UB27-4F0-XX-W2A-A4

### Luminous Intensity Polar Plot



TEST NUMBER: P1025931

CATALOG NUMBER: S124RDIP-B1020D1035UB27-4F0-XX-W2A-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20 |    |    |    | 20 |    |    |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     | 50 |    |    |    | 30 |    |    |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |    |
| 0   | 108 | 108 | 108 | 108 | 100 | 100 | 100 | 100 | 86 | 86 | 86 | 72 | 72 | 72 | 60 | 60 | 60 |
| 1   | 99  | 95  | 91  | 88  | 92  | 88  | 85  | 82  | 76 | 74 | 71 | 64 | 63 | 61 | 54 | 53 | 52 |
| 2   | 91  | 84  | 78  | 73  | 84  | 78  | 73  | 68  | 67 | 63 | 60 | 57 | 54 | 52 | 48 | 46 | 44 |
| 3   | 83  | 74  | 67  | 61  | 77  | 69  | 63  | 58  | 60 | 55 | 51 | 51 | 47 | 44 | 43 | 40 | 38 |
| 4   | 76  | 66  | 58  | 52  | 71  | 61  | 55  | 49  | 53 | 48 | 44 | 46 | 42 | 38 | 39 | 36 | 33 |
| 5   | 70  | 59  | 51  | 45  | 65  | 55  | 48  | 43  | 48 | 42 | 38 | 41 | 37 | 34 | 35 | 32 | 29 |
| 6   | 65  | 53  | 45  | 39  | 60  | 50  | 42  | 37  | 43 | 38 | 33 | 37 | 33 | 30 | 32 | 29 | 26 |
| 7   | 60  | 48  | 40  | 35  | 56  | 45  | 38  | 33  | 39 | 34 | 30 | 34 | 30 | 26 | 29 | 26 | 23 |
| 8   | 56  | 44  | 36  | 31  | 52  | 41  | 34  | 29  | 36 | 30 | 26 | 31 | 27 | 24 | 27 | 23 | 21 |
| 9   | 52  | 40  | 32  | 27  | 48  | 37  | 31  | 26  | 33 | 28 | 24 | 29 | 24 | 21 | 25 | 21 | 19 |
| 10  | 49  | 37  | 29  | 25  | 45  | 34  | 28  | 24  | 30 | 25 | 21 | 27 | 22 | 19 | 23 | 20 | 17 |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°    | 90°   | 180°  | 270°  |
|-----|-------|-------|-------|-------|
| 0°  | 13787 | 13787 | 13787 | 13787 |
| 5°  | 13787 | 15579 | 13809 | 11907 |
| 10° | 13714 | 17959 | 13702 | 10355 |
| 15° | 13550 | 20212 | 13550 | 8670  |
| 20° | 13380 | 21914 | 13310 | 7634  |
| 25° | 13171 | 22008 | 13110 | 6896  |
| 30° | 12949 | 18714 | 12848 | 6387  |
| 35° | 12636 | 14120 | 12476 | 6008  |
| 40° | 12287 | 10233 | 12045 | 5712  |
| 45° | 11711 | 7778  | 11420 | 5450  |
| 50° | 11027 | 6286  | 10725 | 5066  |
| 55° | 10285 | 5204  | 9949  | 4555  |
| 60° | 9542  | 4400  | 9115  | 3788  |
| 65° | 8607  | 3585  | 8333  | 3011  |
| 70° | 7750  | 2906  | 7387  | 2446  |
| 75° | 6792  | 2095  | 6320  | 1793  |
| 80° | 5602  | 1389  | 5100  | 1318  |
| 85° | 4068  | 715   | 3369  | 715   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 17260 cd/sqm

TEST NUMBER: P1025931

CATALOG NUMBER: S124RDIP-B1020D1035UB27-4F0-XX-W2A-A4

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 163.7  | 2.1       |
| 10°-20°   | 494.4  | 6.3       |
| 20°-30°   | 774.4  | 9.8       |
| 30°-40°   | 860.0  | 10.9      |
| 40°-50°   | 762.1  | 9.6       |
| 50°-60°   | 593.9  | 7.5       |
| 60°-70°   | 388.5  | 4.9       |
| 70°-80°   | 190.6  | 2.4       |
| 80°-90°   | 48.4   | 0.6       |
| 90°-100°  | 361.4  | 4.6       |
| 100°-110° | 754.6  | 9.5       |
| 110°-120° | 670.7  | 8.5       |
| 120°-130° | 564.6  | 7.1       |
| 130°-140° | 471.1  | 6.0       |
| 140°-150° | 359.7  | 4.5       |
| 150°-160° | 252.9  | 3.2       |
| 160°-170° | 148.7  | 1.9       |
| 170°-180° | 48.4   | 0.6       |
| 0°-30°    | 1432.6 | 18.1      |
| 0°-40°    | 2292.5 | 29.0      |
| 0°-60°    | 3648.5 | 46.1      |
| 0°-90°    | 4276.0 | 54.1      |
| 90°-120°  | 1786.7 | 22.6      |
| 90°-150°  | 3182.1 | 40.2      |
| 90°-180°  | 3632.0 | 45.9      |
| 0°-180°   | 7908.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°   | 90°  | 180° | 270° | 360° | Flux |
|------|------|------|------|------|------|------|
| 0°   | 1691 | 1691 | 1691 | 1691 | 1691 |      |
| 5°   | 1688 | 1954 | 1691 | 1493 | 1688 | 160  |
| 15°  | 1616 | 2589 | 1616 | 1110 | 1616 | 456  |
| 25°  | 1481 | 2792 | 1474 | 875  | 1481 | 683  |
| 35°  | 1292 | 1719 | 1275 | 732  | 1292 | 807  |
| 45°  | 1041 | 879  | 1015 | 616  | 1041 | 803  |
| 55°  | 749  | 524  | 725  | 459  | 749  | 670  |
| 65°  | 470  | 306  | 455  | 258  | 470  | 469  |
| 75°  | 236  | 142  | 219  | 121  | 236  | 250  |
| 85°  | 56   | 34   | 46   | 34   | 56   | 63   |
| 90°  | 1    | 21   | 1    | 21   | 1    | 6    |
| 95°  | 32   | 239  | 32   | 239  | 32   | 35   |
| 105° | 115  | 1378 | 115  | 1378 | 115  | 122  |
| 115° | 202  | 1324 | 202  | 1324 | 202  | 200  |
| 125° | 281  | 1056 | 281  | 1056 | 281  | 251  |
| 135° | 334  | 944  | 334  | 944  | 334  | 258  |
| 145° | 385  | 771  | 385  | 771  | 385  | 242  |
| 155° | 438  | 646  | 438  | 646  | 438  | 202  |
| 165° | 477  | 563  | 477  | 563  | 477  | 135  |
| 175° | 498  | 508  | 498  | 508  | 498  | 47   |
| 180° | 499  | 499  | 499  | 499  | 499  |      |

TEST NUMBER: P1025931

CATALOG NUMBER: S124RDIP-B1020D1035UB27-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 5°     | 10°    | 15°    | 20°    | 22.5°  | 25°    | 30°    | 35°    | 40°    | 45°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 |
| 2.5°   | 1693.5 | 1708.5 | 1716.6 | 1723.4 | 1737.1 | 1742.5 | 1753.4 | 1756.1 | 1767.0 | 1765.7 | 1761.6 |
| 5°     | 1688.0 | 1713.9 | 1733.0 | 1753.4 | 1777.9 | 1791.6 | 1806.5 | 1828.3 | 1839.2 | 1854.2 | 1863.8 |
| 7.5°   | 1678.5 | 1713.9 | 1745.2 | 1776.6 | 1816.1 | 1837.9 | 1857.0 | 1891.0 | 1919.6 | 1944.2 | 1971.4 |
| 10°    | 1663.5 | 1708.5 | 1754.8 | 1797.0 | 1851.5 | 1877.4 | 1906.0 | 1956.4 | 1995.9 | 2030.0 | 2073.6 |
| 12.5°  | 1640.3 | 1703.0 | 1754.8 | 1812.0 | 1881.5 | 1916.9 | 1955.0 | 2015.0 | 2061.3 | 2117.2 | 2171.7 |
| 15°    | 1615.8 | 1685.3 | 1753.4 | 1828.3 | 1907.4 | 1948.2 | 1986.4 | 2066.8 | 2137.6 | 2201.6 | 2261.6 |
| 17.5°  | 1588.6 | 1664.9 | 1739.8 | 1822.9 | 1918.3 | 1968.7 | 2013.6 | 2110.4 | 2188.0 | 2271.1 | 2331.1 |
| 20°    | 1555.9 | 1639.0 | 1724.8 | 1817.4 | 1925.1 | 1980.9 | 2031.3 | 2141.7 | 2227.5 | 2317.4 | 2392.4 |
| 22.5°  | 1520.4 | 1610.4 | 1704.4 | 1805.2 | 1916.9 | 1978.2 | 2036.8 | 2155.3 | 2254.8 | 2337.9 | 2438.7 |
| 25°    | 1480.9 | 1576.3 | 1673.0 | 1779.3 | 1904.6 | 1971.4 | 2031.3 | 2148.5 | 2254.8 | 2363.8 | 2461.9 |
| 27.5°  | 1440.1 | 1538.2 | 1639.0 | 1750.7 | 1878.8 | 1944.2 | 2012.3 | 2125.3 | 2249.3 | 2367.9 | 2467.3 |
| 30°    | 1395.1 | 1490.5 | 1596.7 | 1703.0 | 1839.2 | 1904.6 | 1974.1 | 2096.7 | 2231.6 | 2350.1 | 2457.8 |
| 32.5°  | 1346.1 | 1444.1 | 1545.0 | 1655.3 | 1788.8 | 1859.7 | 1923.7 | 2062.7 | 2200.3 | 2317.4 | 2418.3 |
| 35°    | 1291.6 | 1384.2 | 1479.6 | 1592.6 | 1724.8 | 1788.8 | 1865.1 | 2009.5 | 2148.5 | 2272.5 | 2337.9 |
| 37.5°  | 1233.0 | 1321.5 | 1410.1 | 1521.8 | 1648.5 | 1726.2 | 1801.1 | 1946.9 | 2094.0 | 2177.1 | 2211.2 |
| 40°    | 1178.5 | 1256.1 | 1333.8 | 1441.4 | 1569.5 | 1649.9 | 1726.2 | 1877.4 | 2006.8 | 2070.9 | 2045.0 |
| 42.5°  | 1109.0 | 1189.4 | 1258.9 | 1358.3 | 1487.7 | 1562.7 | 1640.3 | 1797.0 | 1901.9 | 1927.8 | 1863.8 |
| 45°    | 1040.9 | 1107.6 | 1174.4 | 1271.1 | 1407.4 | 1471.4 | 1554.5 | 1700.3 | 1787.5 | 1764.3 | 1670.3 |
| 47.5°  | 974.1  | 1028.6 | 1091.3 | 1185.3 | 1307.9 | 1384.2 | 1461.9 | 1588.6 | 1649.9 | 1617.2 | 1486.4 |
| 50°    | 895.1  | 949.6  | 1015.0 | 1096.7 | 1215.3 | 1288.8 | 1350.1 | 1467.3 | 1513.6 | 1433.2 | 1275.2 |
| 52.5°  | 820.2  | 867.9  | 923.7  | 1000.0 | 1113.1 | 1179.8 | 1246.6 | 1347.4 | 1362.4 | 1269.8 | 1103.5 |
| 55°    | 749.3  | 787.5  | 846.1  | 907.4  | 1010.9 | 1081.7 | 1128.1 | 1213.9 | 1209.8 | 1094.0 | 951.0  |
| 57.5°  | 675.8  | 711.2  | 750.7  | 814.7  | 912.8  | 965.9  | 1016.4 | 1091.3 | 1051.8 | 953.7  | 812.0  |
| 60°    | 610.4  | 630.8  | 670.3  | 731.6  | 814.7  | 861.0  | 900.5  | 941.4  | 907.4  | 801.1  | 692.1  |
| 62.5°  | 538.1  | 561.3  | 589.9  | 639.0  | 712.5  | 756.1  | 784.7  | 802.5  | 767.0  | 685.3  | 585.8  |
| 65°    | 470.0  | 490.5  | 520.4  | 564.0  | 619.9  | 652.6  | 667.6  | 679.8  | 660.8  | 568.1  | 489.1  |
| 67.5°  | 408.7  | 422.3  | 449.6  | 478.2  | 538.1  | 546.3  | 566.8  | 572.2  | 534.1  | 463.2  | 400.5  |
| 70°    | 347.4  | 361.0  | 373.3  | 407.4  | 434.6  | 449.6  | 453.7  | 453.7  | 415.5  | 369.2  | 317.4  |
| 72.5°  | 290.2  | 298.4  | 310.6  | 333.8  | 348.8  | 359.7  | 365.1  | 358.3  | 322.9  | 284.7  | 246.6  |
| 75°    | 235.7  | 239.8  | 250.7  | 265.7  | 277.9  | 273.8  | 272.5  | 264.3  | 238.4  | 211.2  | 189.4  |
| 77.5°  | 181.2  | 183.9  | 196.2  | 200.3  | 200.3  | 204.4  | 198.9  | 190.7  | 168.9  | 148.5  | 139.0  |
| 80°    | 136.2  | 140.3  | 141.7  | 144.4  | 141.7  | 141.7  | 137.6  | 124.0  | 113.1  | 103.5  | 96.7   |
| 82.5°  | 94.0   | 96.7   | 98.1   | 94.0   | 96.7   | 92.6   | 85.8   | 76.3   | 69.5   | 68.1   | 65.4   |
| 85°    | 55.9   | 57.2   | 55.9   | 55.9   | 51.8   | 50.4   | 45.0   | 43.6   | 40.9   | 40.9   | 39.5   |
| 87.5°  | 27.2   | 25.9   | 23.2   | 20.4   | 20.4   | 19.1   | 20.4   | 17.7   | 20.4   | 19.1   | 17.7   |
| 90°    | 1.0    | 2.9    | 5.9    | 6.9    | 7.8    | 7.8    | 7.8    | 13.7   | 13.7   | 15.7   | 17.6   |
| 92.5°  | 13.7   | 19.6   | 30.4   | 45.1   | 62.7   | 75.4   | 88.2   | 148.9  | 244.0  | 336.0  | 384.1  |
| 95°    | 32.3   | 35.3   | 45.1   | 57.8   | 81.3   | 101.9  | 122.5  | 207.7  | 368.4  | 602.5  | 798.5  |
| 97.5°  | 53.9   | 53.9   | 62.7   | 74.5   | 95.0   | 112.6  | 130.3  | 197.9  | 336.0  | 577.1  | 854.3  |
| 100°   | 74.5   | 74.5   | 81.3   | 93.1   | 111.7  | 127.4  | 143.0  | 200.8  | 311.6  | 511.4  | 787.7  |
| 102.5° | 94.1   | 96.0   | 101.9  | 112.7  | 130.3  | 145.0  | 159.7  | 210.6  | 304.7  | 467.3  | 704.4  |
| 105°   | 114.6  | 117.6  | 122.5  | 134.2  | 151.9  | 166.1  | 180.3  | 227.3  | 308.6  | 445.8  | 642.7  |
| 107.5° | 137.2  | 139.1  | 144.0  | 156.8  | 173.4  | 187.6  | 201.8  | 244.9  | 320.4  | 439.9  | 602.5  |
| 110°   | 159.7  | 161.7  | 166.6  | 178.3  | 195.9  | 209.2  | 222.4  | 265.5  | 334.1  | 441.9  | 583.9  |

TEST NUMBER: P1025931

CATALOG NUMBER: S124RDIP-B1020D1035UB27-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 0°    | 5°    | 10°   | 15°   | 20°   | 22.5° | 25°   | 30°   | 35°   | 40°   | 45°   |
|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 112.5° | 181.3 | 183.2 | 189.1 | 199.9 | 217.5 | 230.8 | 244.0 | 285.1 | 348.8 | 447.7 | 575.1 |
| 115°   | 201.8 | 204.8 | 211.6 | 221.4 | 240.0 | 253.2 | 266.5 | 305.7 | 364.5 | 455.6 | 573.1 |
| 117.5° | 223.4 | 226.3 | 232.2 | 243.0 | 260.6 | 274.3 | 288.0 | 325.3 | 380.1 | 463.4 | 572.2 |
| 120°   | 244.9 | 246.9 | 253.8 | 264.5 | 281.2 | 294.9 | 308.6 | 345.8 | 396.8 | 472.2 | 572.2 |
| 122.5° | 264.5 | 266.5 | 273.3 | 283.1 | 301.8 | 315.0 | 328.2 | 365.4 | 412.5 | 481.0 | 571.2 |
| 125°   | 281.2 | 285.1 | 291.0 | 301.8 | 320.4 | 334.1 | 347.8 | 383.1 | 428.1 | 489.9 | 570.2 |
| 127.5° | 296.9 | 299.8 | 306.7 | 318.4 | 338.0 | 351.7 | 365.4 | 399.7 | 441.9 | 496.7 | 568.2 |
| 130°   | 309.6 | 313.5 | 321.4 | 336.0 | 354.7 | 368.9 | 383.1 | 416.4 | 454.6 | 504.6 | 567.3 |
| 132.5° | 322.3 | 325.3 | 336.0 | 349.8 | 370.3 | 383.6 | 396.8 | 430.1 | 467.3 | 511.4 | 566.3 |
| 135°   | 334.1 | 338.0 | 347.8 | 364.5 | 385.0 | 397.8 | 410.5 | 442.8 | 478.1 | 518.3 | 565.3 |
| 137.5° | 345.8 | 349.8 | 360.5 | 376.2 | 397.8 | 410.0 | 422.3 | 452.6 | 485.9 | 522.2 | 565.3 |
| 140°   | 358.6 | 361.5 | 372.3 | 389.0 | 409.5 | 421.2 | 433.0 | 462.4 | 493.8 | 527.1 | 564.3 |
| 142.5° | 372.3 | 375.2 | 385.0 | 400.7 | 420.3 | 431.6 | 442.8 | 471.3 | 499.7 | 531.0 | 564.3 |
| 145°   | 385.0 | 388.0 | 397.8 | 411.5 | 430.1 | 440.9 | 451.7 | 477.1 | 503.6 | 532.0 | 562.4 |
| 147.5° | 399.7 | 400.7 | 409.5 | 424.2 | 439.9 | 449.7 | 459.5 | 484.0 | 507.5 | 533.0 | 559.4 |
| 150°   | 413.4 | 414.4 | 422.3 | 434.0 | 448.7 | 458.0 | 467.3 | 488.9 | 510.4 | 533.0 | 556.5 |
| 152.5° | 426.2 | 426.2 | 434.0 | 444.8 | 457.5 | 465.8 | 474.2 | 492.8 | 512.4 | 531.0 | 551.6 |
| 155°   | 437.9 | 438.9 | 444.8 | 454.6 | 465.4 | 472.8 | 480.1 | 496.7 | 513.4 | 529.1 | 546.7 |
| 157.5° | 449.7 | 449.7 | 455.6 | 463.4 | 473.2 | 479.1 | 485.0 | 499.7 | 513.4 | 527.1 | 541.8 |
| 160°   | 460.5 | 460.5 | 464.4 | 471.3 | 479.1 | 484.5 | 489.9 | 501.6 | 513.4 | 524.2 | 535.9 |
| 162.5° | 470.3 | 469.3 | 472.2 | 478.1 | 485.0 | 488.9 | 492.8 | 503.6 | 513.4 | 521.2 | 530.0 |
| 165°   | 477.1 | 477.1 | 479.1 | 484.0 | 488.9 | 491.8 | 494.8 | 503.6 | 511.4 | 517.3 | 524.2 |
| 167.5° | 485.0 | 484.0 | 485.0 | 488.9 | 491.8 | 494.2 | 496.7 | 503.6 | 509.5 | 513.4 | 518.3 |
| 170°   | 489.9 | 488.9 | 489.9 | 492.8 | 494.8 | 496.2 | 497.7 | 502.6 | 507.5 | 509.5 | 512.4 |
| 172.5° | 494.8 | 493.8 | 493.8 | 495.7 | 496.7 | 497.7 | 498.7 | 501.6 | 505.5 | 505.5 | 506.5 |
| 175°   | 497.7 | 496.7 | 496.7 | 497.7 | 498.7 | 498.7 | 498.7 | 500.6 | 503.6 | 502.6 | 502.6 |
| 177.5° | 499.7 | 498.7 | 497.7 | 498.7 | 498.7 | 498.7 | 498.7 | 499.7 | 501.6 | 499.7 | 499.7 |
| 180°   | 498.7 | 498.7 | 498.7 | 498.7 | 498.7 | 498.7 | 498.7 | 498.7 | 498.7 | 498.7 | 498.7 |

TEST NUMBER: P1025931

CATALOG NUMBER: S124RDIP-B1020D1035UB27-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 50°    | 55°    | 60°    | 65°    | 67.5°  | 70°    | 75°    | 80°    | 85°    | 90°    | 95°    |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 |
| 2.5°   | 1772.5 | 1787.5 | 1788.8 | 1802.5 | 1798.4 | 1791.6 | 1803.8 | 1795.6 | 1812.0 | 1806.5 | 1813.4 |
| 5°     | 1876.0 | 1896.5 | 1914.2 | 1925.1 | 1944.2 | 1940.1 | 1960.5 | 1953.7 | 1968.7 | 1953.7 | 1972.8 |
| 7.5°   | 1997.3 | 2031.3 | 2049.1 | 2077.7 | 2085.8 | 2087.2 | 2111.7 | 2117.2 | 2126.7 | 2117.2 | 2128.1 |
| 10°    | 2115.8 | 2156.7 | 2197.6 | 2220.7 | 2235.7 | 2256.1 | 2277.9 | 2287.5 | 2294.3 | 2284.8 | 2291.6 |
| 12.5°  | 2223.4 | 2287.5 | 2332.4 | 2378.8 | 2389.7 | 2407.4 | 2430.5 | 2427.8 | 2455.1 | 2449.6 | 2461.9 |
| 15°    | 2322.9 | 2393.7 | 2448.2 | 2485.0 | 2515.0 | 2530.0 | 2573.6 | 2576.3 | 2574.9 | 2588.6 | 2580.4 |
| 17.5°  | 2411.5 | 2471.4 | 2549.1 | 2596.7 | 2633.5 | 2633.5 | 2658.0 | 2708.5 | 2704.4 | 2703.0 | 2711.2 |
| 20°    | 2483.7 | 2551.8 | 2624.0 | 2704.4 | 2734.3 | 2739.8 | 2773.9 | 2799.7 | 2803.8 | 2803.8 | 2803.8 |
| 22.5°  | 2538.2 | 2618.5 | 2696.2 | 2753.4 | 2776.6 | 2795.7 | 2825.6 | 2842.0 | 2847.4 | 2844.7 | 2847.4 |
| 25°    | 2565.4 | 2641.7 | 2720.7 | 2772.5 | 2786.1 | 2797.0 | 2799.7 | 2809.3 | 2807.9 | 2791.6 | 2801.1 |
| 27.5°  | 2570.9 | 2644.4 | 2696.2 | 2709.8 | 2703.0 | 2696.2 | 2652.6 | 2656.7 | 2644.4 | 2619.9 | 2629.4 |
| 30°    | 2546.3 | 2585.8 | 2584.5 | 2542.2 | 2530.0 | 2501.4 | 2461.9 | 2403.3 | 2355.6 | 2335.2 | 2342.0 |
| 32.5°  | 2457.8 | 2457.8 | 2408.7 | 2313.4 | 2271.1 | 2219.4 | 2148.5 | 2095.4 | 2032.7 | 2019.1 | 2045.0 |
| 35°    | 2335.2 | 2265.7 | 2175.8 | 2050.4 | 1986.4 | 1948.2 | 1825.6 | 1787.5 | 1734.3 | 1719.4 | 1731.6 |
| 37.5°  | 2144.4 | 2028.6 | 1897.8 | 1780.7 | 1726.2 | 1658.0 | 1550.4 | 1495.9 | 1457.8 | 1431.9 | 1444.1 |
| 40°    | 1930.5 | 1790.2 | 1654.0 | 1509.5 | 1449.6 | 1393.7 | 1313.4 | 1264.3 | 1203.0 | 1205.7 | 1209.8 |
| 42.5°  | 1726.2 | 1561.3 | 1408.7 | 1275.2 | 1218.0 | 1171.7 | 1115.8 | 1055.9 | 1034.1 | 1027.3 | 1020.4 |
| 45°    | 1509.5 | 1333.8 | 1190.7 | 1091.3 | 1039.5 | 995.9  | 944.1  | 910.1  | 884.2  | 878.8  | 885.6  |
| 47.5°  | 1305.2 | 1156.7 | 1020.4 | 927.8  | 885.6  | 863.8  | 822.9  | 791.6  | 775.2  | 761.6  | 769.8  |
| 50°    | 1119.9 | 980.9  | 871.9  | 794.3  | 764.3  | 749.3  | 711.2  | 694.8  | 678.5  | 674.4  | 673.0  |
| 52.5°  | 967.3  | 848.8  | 754.8  | 692.1  | 668.9  | 660.8  | 632.2  | 609.0  | 595.4  | 599.5  | 602.2  |
| 55°    | 828.3  | 727.5  | 654.0  | 603.5  | 584.5  | 574.9  | 554.5  | 538.1  | 528.6  | 524.5  | 527.3  |
| 57.5°  | 705.7  | 618.5  | 565.4  | 524.5  | 509.5  | 505.5  | 483.7  | 478.2  | 471.4  | 467.3  | 467.3  |
| 60°    | 594.0  | 532.7  | 483.7  | 460.5  | 444.1  | 440.1  | 423.7  | 416.9  | 415.5  | 411.4  | 408.7  |
| 62.5°  | 500.0  | 449.6  | 415.5  | 391.0  | 384.2  | 382.8  | 371.9  | 363.8  | 359.7  | 356.9  | 356.9  |
| 65°    | 418.3  | 381.5  | 352.9  | 335.2  | 329.7  | 327.0  | 314.7  | 312.0  | 309.3  | 306.5  | 305.2  |
| 67.5°  | 348.8  | 316.1  | 295.6  | 283.4  | 276.6  | 277.9  | 271.1  | 265.7  | 265.7  | 264.3  | 262.9  |
| 70°    | 282.0  | 261.6  | 243.9  | 237.1  | 234.3  | 231.6  | 228.9  | 224.8  | 223.4  | 223.4  | 223.4  |
| 72.5°  | 222.1  | 208.4  | 198.9  | 194.8  | 192.1  | 189.4  | 186.6  | 186.6  | 186.6  | 185.3  | 185.3  |
| 75°    | 170.3  | 164.9  | 158.0  | 154.0  | 154.0  | 156.7  | 152.6  | 148.5  | 144.4  | 141.7  | 143.1  |
| 77.5°  | 128.1  | 125.3  | 121.3  | 114.4  | 115.8  | 113.1  | 113.1  | 110.4  | 111.7  | 111.7  | 109.0  |
| 80°    | 94.0   | 89.9   | 88.6   | 84.5   | 85.8   | 84.5   | 83.1   | 83.1   | 80.4   | 80.4   | 80.4   |
| 82.5°  | 65.4   | 61.3   | 61.3   | 59.9   | 58.6   | 58.6   | 57.2   | 57.2   | 58.6   | 55.9   | 55.9   |
| 85°    | 39.5   | 38.1   | 38.1   | 35.4   | 35.4   | 35.4   | 35.4   | 36.8   | 35.4   | 34.1   | 34.1   |
| 87.5°  | 17.7   | 19.1   | 17.7   | 16.3   | 16.3   | 16.3   | 15.0   | 15.0   | 13.6   | 15.0   | 15.0   |
| 90°    | 16.7   | 17.6   | 18.6   | 19.6   | 19.6   | 19.6   | 20.6   | 21.6   | 20.6   | 20.6   | 20.6   |
| 92.5°  | 319.4  | 236.1  | 176.4  | 139.1  | 126.8  | 114.6  | 99.9   | 93.1   | 89.2   | 89.2   | 89.2   |
| 95°    | 821.0  | 726.0  | 574.1  | 442.8  | 395.3  | 347.8  | 299.8  | 269.4  | 251.8  | 239.1  | 251.8  |
| 97.5°  | 1029.7 | 1045.4 | 969.9  | 862.2  | 807.3  | 752.4  | 685.8  | 627.0  | 597.6  | 574.1  | 597.6  |
| 100°   | 1038.5 | 1181.6 | 1201.2 | 1153.1 | 1116.8 | 1080.6 | 995.4  | 935.6  | 906.3  | 898.4  | 906.3  |
| 102.5° | 965.0  | 1174.7 | 1291.3 | 1320.7 | 1310.9 | 1301.1 | 1257.0 | 1217.8 | 1186.5 | 1180.6 | 1186.5 |
| 105°   | 872.9  | 1097.3 | 1266.8 | 1363.8 | 1383.9 | 1404.0 | 1405.9 | 1398.1 | 1384.4 | 1378.5 | 1384.4 |
| 107.5° | 797.5  | 1002.3 | 1185.5 | 1320.7 | 1361.8 | 1403.0 | 1446.1 | 1463.7 | 1471.6 | 1472.5 | 1471.6 |
| 110°   | 743.6  | 918.0  | 1087.5 | 1229.6 | 1283.4 | 1337.3 | 1406.9 | 1448.0 | 1465.7 | 1474.5 | 1465.7 |

TEST NUMBER: P1025931

CATALOG NUMBER: S124RDIP-B1020D1035UB27-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 50°   | 55°   | 60°    | 65°    | 67.5°  | 70°    | 75°    | 80°    | 85°    | 90°    | 95°    |
|--------|-------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 112.5° | 713.2 | 856.3 | 1001.3 | 1133.5 | 1187.4 | 1241.3 | 1322.6 | 1374.6 | 1401.0 | 1416.7 | 1401.0 |
| 115°   | 696.6 | 819.1 | 939.6  | 1054.2 | 1101.2 | 1148.2 | 1225.6 | 1284.4 | 1315.8 | 1323.6 | 1315.8 |
| 117.5° | 687.8 | 797.5 | 899.4  | 992.5  | 1033.6 | 1074.8 | 1143.3 | 1194.3 | 1227.6 | 1232.5 | 1227.6 |
| 120°   | 680.9 | 783.8 | 874.9  | 953.3  | 988.0  | 1022.8 | 1078.7 | 1121.8 | 1147.3 | 1158.0 | 1147.3 |
| 122.5° | 673.1 | 772.0 | 859.2  | 928.8  | 958.2  | 987.6  | 1032.6 | 1067.9 | 1088.5 | 1099.3 | 1088.5 |
| 125°   | 664.3 | 758.3 | 842.6  | 910.2  | 937.2  | 964.1  | 1003.2 | 1031.7 | 1050.3 | 1056.2 | 1050.3 |
| 127.5° | 652.5 | 742.6 | 824.0  | 891.6  | 917.0  | 942.5  | 981.7  | 1007.2 | 1022.8 | 1028.7 | 1022.8 |
| 130°   | 641.7 | 723.0 | 800.4  | 867.1  | 893.0  | 919.0  | 959.2  | 983.7  | 999.3  | 1005.2 | 999.3  |
| 132.5° | 631.9 | 702.5 | 774.0  | 838.7  | 864.6  | 890.6  | 929.8  | 958.2  | 972.9  | 978.8  | 972.9  |
| 135°   | 622.1 | 683.9 | 747.5  | 807.3  | 831.8  | 856.3  | 895.5  | 922.9  | 938.6  | 944.5  | 938.6  |
| 137.5° | 613.3 | 666.2 | 722.1  | 774.0  | 796.6  | 819.1  | 856.3  | 884.7  | 897.4  | 904.3  | 897.4  |
| 140°   | 606.5 | 651.5 | 697.6  | 741.7  | 762.2  | 782.8  | 817.1  | 838.7  | 852.4  | 860.2  | 852.4  |
| 142.5° | 600.6 | 637.8 | 677.0  | 713.2  | 730.4  | 747.5  | 776.9  | 796.5  | 808.3  | 813.2  | 808.3  |
| 145°   | 593.7 | 625.1 | 658.4  | 687.8  | 701.5  | 715.2  | 739.7  | 756.4  | 766.2  | 771.0  | 766.2  |
| 147.5° | 587.8 | 614.3 | 641.7  | 666.2  | 677.5  | 688.8  | 707.4  | 722.1  | 729.9  | 731.9  | 729.9  |
| 150°   | 581.0 | 604.5 | 627.0  | 646.6  | 655.4  | 664.3  | 679.9  | 692.7  | 698.5  | 699.5  | 698.5  |
| 152.5° | 573.1 | 593.7 | 612.3  | 630.0  | 636.8  | 643.7  | 656.4  | 666.2  | 669.2  | 670.1  | 669.2  |
| 155°   | 565.3 | 582.9 | 598.6  | 613.3  | 619.2  | 625.1  | 634.9  | 642.7  | 645.6  | 645.6  | 645.6  |
| 157.5° | 557.5 | 571.2 | 584.9  | 597.6  | 602.5  | 607.4  | 615.3  | 621.1  | 623.1  | 623.1  | 623.1  |
| 160°   | 548.6 | 560.4 | 571.2  | 582.0  | 585.9  | 589.8  | 595.7  | 601.6  | 602.5  | 602.5  | 602.5  |
| 162.5° | 540.8 | 549.6 | 558.4  | 566.3  | 569.7  | 573.1  | 577.1  | 582.9  | 583.9  | 582.9  | 583.9  |
| 165°   | 532.0 | 539.8 | 545.7  | 552.6  | 555.0  | 557.5  | 561.4  | 565.3  | 564.3  | 563.3  | 564.3  |
| 167.5° | 524.2 | 530.0 | 534.9  | 540.8  | 542.3  | 543.8  | 545.7  | 548.6  | 548.6  | 547.7  | 548.6  |
| 170°   | 516.3 | 521.2 | 524.2  | 528.1  | 529.6  | 531.0  | 533.0  | 534.0  | 533.0  | 533.0  | 533.0  |
| 172.5° | 509.5 | 513.4 | 515.3  | 517.3  | 518.3  | 519.3  | 520.2  | 521.2  | 520.2  | 518.3  | 520.2  |
| 175°   | 504.6 | 506.5 | 507.5  | 509.5  | 509.5  | 509.5  | 509.5  | 511.4  | 509.5  | 507.5  | 509.5  |
| 177.5° | 500.6 | 501.6 | 502.6  | 502.6  | 503.1  | 503.6  | 502.6  | 503.6  | 501.6  | 499.7  | 501.6  |
| 180°   | 498.7 | 498.7 | 498.7  | 498.7  | 498.7  | 498.7  | 498.7  | 498.7  | 498.7  | 498.7  | 498.7  |

TEST NUMBER: P1025931

CATALOG NUMBER: S124RDIP-B1020D1035UB27-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 100°   | 105°   | 110°   | 112.5° | 115°   | 120°   | 125°   | 130°   | 135°   | 140°   | 145°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 |
| 2.5°   | 1817.4 | 1807.9 | 1806.5 | 1806.5 | 1791.6 | 1799.7 | 1783.4 | 1765.7 | 1757.5 | 1757.5 | 1742.5 |
| 5°     | 1968.7 | 1959.1 | 1949.6 | 1934.6 | 1934.6 | 1926.4 | 1900.6 | 1874.7 | 1855.6 | 1839.2 | 1821.5 |
| 7.5°   | 2124.0 | 2114.5 | 2087.2 | 2072.2 | 2080.4 | 2064.0 | 2030.0 | 1986.4 | 1953.7 | 1927.8 | 1891.0 |
| 10°    | 2292.9 | 2267.0 | 2253.4 | 2245.2 | 2216.6 | 2198.9 | 2159.4 | 2095.4 | 2054.5 | 2020.4 | 1972.8 |
| 12.5°  | 2430.5 | 2438.7 | 2386.9 | 2391.0 | 2362.4 | 2337.9 | 2276.6 | 2215.3 | 2154.0 | 2106.3 | 2035.4 |
| 15°    | 2579.0 | 2554.5 | 2523.2 | 2498.6 | 2489.1 | 2459.1 | 2407.4 | 2325.6 | 2258.9 | 2183.9 | 2103.6 |
| 17.5°  | 2696.2 | 2677.1 | 2647.2 | 2624.0 | 2603.6 | 2531.3 | 2487.7 | 2415.5 | 2324.3 | 2250.7 | 2152.6 |
| 20°    | 2795.7 | 2777.9 | 2735.7 | 2720.7 | 2683.9 | 2632.2 | 2569.5 | 2457.8 | 2376.0 | 2295.7 | 2200.3 |
| 22.5°  | 2837.9 | 2820.2 | 2783.4 | 2764.3 | 2741.2 | 2690.7 | 2630.8 | 2524.5 | 2423.7 | 2322.9 | 2222.1 |
| 25°    | 2802.5 | 2802.5 | 2784.8 | 2777.9 | 2757.5 | 2712.5 | 2651.2 | 2561.3 | 2453.7 | 2344.7 | 2224.8 |
| 27.5°  | 2630.8 | 2664.9 | 2677.1 | 2683.9 | 2683.9 | 2685.3 | 2643.1 | 2555.9 | 2451.0 | 2344.7 | 2219.4 |
| 30°    | 2382.8 | 2440.1 | 2490.5 | 2505.5 | 2531.3 | 2560.0 | 2577.7 | 2535.4 | 2441.4 | 2329.7 | 2204.4 |
| 32.5°  | 2070.9 | 2144.4 | 2238.4 | 2261.6 | 2297.0 | 2382.8 | 2430.5 | 2448.2 | 2396.5 | 2298.4 | 2164.9 |
| 35°    | 1760.2 | 1852.9 | 1910.1 | 1980.9 | 2013.6 | 2140.3 | 2246.6 | 2310.6 | 2298.4 | 2239.8 | 2118.5 |
| 37.5°  | 1489.1 | 1542.2 | 1611.7 | 1686.7 | 1752.1 | 1873.3 | 2005.5 | 2129.4 | 2179.8 | 2151.2 | 2060.0 |
| 40°    | 1228.9 | 1291.6 | 1374.7 | 1436.0 | 1480.9 | 1602.2 | 1765.7 | 1900.6 | 2010.9 | 2028.6 | 1972.8 |
| 42.5°  | 1045.0 | 1107.6 | 1158.0 | 1224.8 | 1260.2 | 1377.4 | 1521.8 | 1690.7 | 1821.5 | 1891.0 | 1866.5 |
| 45°    | 903.3  | 941.4  | 982.3  | 1020.4 | 1064.0 | 1167.6 | 1301.1 | 1486.4 | 1633.5 | 1731.6 | 1741.2 |
| 47.5°  | 779.3  | 813.4  | 848.8  | 884.2  | 908.7  | 989.1  | 1111.7 | 1262.9 | 1423.7 | 1558.6 | 1611.7 |
| 50°    | 692.1  | 708.4  | 734.3  | 754.8  | 783.4  | 852.9  | 951.0  | 1081.7 | 1252.0 | 1397.8 | 1467.3 |
| 52.5°  | 606.3  | 626.7  | 647.1  | 664.9  | 683.9  | 733.0  | 822.9  | 936.0  | 1083.1 | 1233.0 | 1318.8 |
| 55°    | 534.1  | 550.4  | 569.5  | 581.7  | 592.6  | 636.2  | 704.4  | 791.6  | 918.3  | 1060.0 | 1166.2 |
| 57.5°  | 475.5  | 482.3  | 498.6  | 505.5  | 517.7  | 553.1  | 602.2  | 679.8  | 782.0  | 919.6  | 1006.8 |
| 60°    | 411.4  | 425.1  | 437.3  | 442.8  | 452.3  | 476.8  | 510.9  | 583.1  | 671.7  | 772.5  | 871.9  |
| 62.5°  | 359.7  | 365.1  | 374.7  | 381.5  | 388.3  | 414.2  | 442.8  | 497.3  | 564.0  | 648.5  | 739.8  |
| 65°    | 312.0  | 314.7  | 320.2  | 329.7  | 333.8  | 352.9  | 369.2  | 408.7  | 471.4  | 535.4  | 626.7  |
| 67.5°  | 262.9  | 265.7  | 272.5  | 277.9  | 282.0  | 294.3  | 312.0  | 340.6  | 374.7  | 445.5  | 495.9  |
| 70°    | 224.8  | 224.8  | 228.9  | 231.6  | 235.7  | 241.1  | 250.7  | 272.5  | 303.8  | 348.8  | 395.1  |
| 72.5°  | 188.0  | 188.0  | 188.0  | 192.1  | 192.1  | 196.2  | 201.6  | 216.6  | 238.4  | 273.8  | 303.8  |
| 75°    | 145.8  | 147.1  | 149.9  | 149.9  | 151.2  | 156.7  | 160.8  | 164.9  | 175.8  | 198.9  | 226.2  |
| 77.5°  | 110.4  | 113.1  | 114.4  | 111.7  | 114.4  | 114.4  | 119.9  | 125.3  | 130.8  | 137.6  | 158.0  |
| 80°    | 81.7   | 83.1   | 80.4   | 81.7   | 81.7   | 84.5   | 87.2   | 85.8   | 88.6   | 96.7   | 102.2  |
| 82.5°  | 54.5   | 55.9   | 55.9   | 55.9   | 55.9   | 59.9   | 59.9   | 58.6   | 59.9   | 61.3   | 62.7   |
| 85°    | 34.1   | 32.7   | 32.7   | 34.1   | 32.7   | 32.7   | 34.1   | 35.4   | 34.1   | 35.4   | 36.8   |
| 87.5°  | 15.0   | 15.0   | 15.0   | 15.0   | 13.6   | 13.6   | 15.0   | 13.6   | 15.0   | 13.6   | 12.3   |
| 90°    | 21.6   | 20.6   | 19.6   | 19.6   | 19.6   | 18.6   | 17.6   | 16.7   | 17.6   | 15.7   | 13.7   |
| 92.5°  | 93.1   | 99.9   | 114.6  | 126.8  | 139.1  | 176.4  | 236.1  | 319.4  | 384.1  | 336.0  | 244.0  |
| 95°    | 269.4  | 299.8  | 347.8  | 395.3  | 442.8  | 574.1  | 726.0  | 821.0  | 798.5  | 602.5  | 368.4  |
| 97.5°  | 627.0  | 685.8  | 752.4  | 807.3  | 862.2  | 969.9  | 1045.4 | 1029.7 | 854.3  | 577.1  | 336.0  |
| 100°   | 935.6  | 995.4  | 1080.6 | 1116.8 | 1153.1 | 1201.2 | 1181.6 | 1038.5 | 787.7  | 511.4  | 311.6  |
| 102.5° | 1217.8 | 1257.0 | 1301.1 | 1310.9 | 1320.7 | 1291.3 | 1174.7 | 965.0  | 704.4  | 467.3  | 304.7  |
| 105°   | 1398.1 | 1405.9 | 1404.0 | 1383.9 | 1363.8 | 1266.8 | 1097.3 | 872.9  | 642.7  | 445.8  | 308.6  |
| 107.5° | 1463.7 | 1446.1 | 1403.0 | 1361.8 | 1320.7 | 1185.5 | 1002.3 | 797.5  | 602.5  | 439.9  | 320.4  |
| 110°   | 1448.0 | 1406.9 | 1337.3 | 1283.4 | 1229.6 | 1087.5 | 918.0  | 743.6  | 583.9  | 441.9  | 334.1  |

TEST NUMBER: P1025931

CATALOG NUMBER: S124RDIP-B1020D1035UB27-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 100°   | 105°   | 110°   | 112.5° | 115°   | 120°   | 125°  | 130°  | 135°  | 140°  | 145°  |
|--------|--------|--------|--------|--------|--------|--------|-------|-------|-------|-------|-------|
| 112.5° | 1374.6 | 1322.6 | 1241.3 | 1187.4 | 1133.5 | 1001.3 | 856.3 | 713.2 | 575.1 | 447.7 | 348.8 |
| 115°   | 1284.4 | 1225.6 | 1148.2 | 1101.2 | 1054.2 | 939.6  | 819.1 | 696.6 | 573.1 | 455.6 | 364.5 |
| 117.5° | 1194.3 | 1143.3 | 1074.8 | 1033.6 | 992.5  | 899.4  | 797.5 | 687.8 | 572.2 | 463.4 | 380.1 |
| 120°   | 1121.8 | 1078.7 | 1022.8 | 988.0  | 953.3  | 874.9  | 783.8 | 680.9 | 572.2 | 472.2 | 396.8 |
| 122.5° | 1067.9 | 1032.6 | 987.6  | 958.2  | 928.8  | 859.2  | 772.0 | 673.1 | 571.2 | 481.0 | 412.5 |
| 125°   | 1031.7 | 1003.2 | 964.1  | 937.2  | 910.2  | 842.6  | 758.3 | 664.3 | 570.2 | 489.9 | 428.1 |
| 127.5° | 1007.2 | 981.7  | 942.5  | 917.0  | 891.6  | 824.0  | 742.6 | 652.5 | 568.2 | 496.7 | 441.9 |
| 130°   | 983.7  | 959.2  | 919.0  | 893.0  | 867.1  | 800.4  | 723.0 | 641.7 | 567.3 | 504.6 | 454.6 |
| 132.5° | 958.2  | 929.8  | 890.6  | 864.6  | 838.7  | 774.0  | 702.5 | 631.9 | 566.3 | 511.4 | 467.3 |
| 135°   | 922.9  | 895.5  | 856.3  | 831.8  | 807.3  | 747.5  | 683.9 | 622.1 | 565.3 | 518.3 | 478.1 |
| 137.5° | 884.7  | 856.3  | 819.1  | 796.6  | 774.0  | 722.1  | 666.2 | 613.3 | 565.3 | 522.2 | 485.9 |
| 140°   | 838.7  | 817.1  | 782.8  | 762.2  | 741.7  | 697.6  | 651.5 | 606.5 | 564.3 | 527.1 | 493.8 |
| 142.5° | 796.5  | 776.9  | 747.5  | 730.4  | 713.2  | 677.0  | 637.8 | 600.6 | 564.3 | 531.0 | 499.7 |
| 145°   | 756.4  | 739.7  | 715.2  | 701.5  | 687.8  | 658.4  | 625.1 | 593.7 | 562.4 | 532.0 | 503.6 |
| 147.5° | 722.1  | 707.4  | 688.8  | 677.5  | 666.2  | 641.7  | 614.3 | 587.8 | 559.4 | 533.0 | 507.5 |
| 150°   | 692.7  | 679.9  | 664.3  | 655.4  | 646.6  | 627.0  | 604.5 | 581.0 | 556.5 | 533.0 | 510.4 |
| 152.5° | 666.2  | 656.4  | 643.7  | 636.8  | 630.0  | 612.3  | 593.7 | 573.1 | 551.6 | 531.0 | 512.4 |
| 155°   | 642.7  | 634.9  | 625.1  | 619.2  | 613.3  | 598.6  | 582.9 | 565.3 | 546.7 | 529.1 | 513.4 |
| 157.5° | 621.1  | 615.3  | 607.4  | 602.5  | 597.6  | 584.9  | 571.2 | 557.5 | 541.8 | 527.1 | 513.4 |
| 160°   | 601.6  | 595.7  | 589.8  | 585.9  | 582.0  | 571.2  | 560.4 | 548.6 | 535.9 | 524.2 | 513.4 |
| 162.5° | 582.9  | 577.1  | 573.1  | 569.7  | 566.3  | 558.4  | 549.6 | 540.8 | 530.0 | 521.2 | 513.4 |
| 165°   | 565.3  | 561.4  | 557.5  | 555.0  | 552.6  | 545.7  | 539.8 | 532.0 | 524.2 | 517.3 | 511.4 |
| 167.5° | 548.6  | 545.7  | 543.8  | 542.3  | 540.8  | 534.9  | 530.0 | 524.2 | 518.3 | 513.4 | 509.5 |
| 170°   | 534.0  | 533.0  | 531.0  | 529.6  | 528.1  | 524.2  | 521.2 | 516.3 | 512.4 | 509.5 | 507.5 |
| 172.5° | 521.2  | 520.2  | 519.3  | 518.3  | 517.3  | 515.3  | 513.4 | 509.5 | 506.5 | 505.5 | 505.5 |
| 175°   | 511.4  | 509.5  | 509.5  | 509.5  | 509.5  | 507.5  | 506.5 | 504.6 | 502.6 | 502.6 | 503.6 |
| 177.5° | 503.6  | 502.6  | 503.6  | 503.1  | 502.6  | 502.6  | 501.6 | 500.6 | 499.7 | 499.7 | 501.6 |
| 180°   | 498.7  | 498.7  | 498.7  | 498.7  | 498.7  | 498.7  | 498.7 | 498.7 | 498.7 | 498.7 | 498.7 |

TEST NUMBER: P1025931

CATALOG NUMBER: S124RDIP-B1020D1035UB27-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 150°   | 155°   | 157.5° | 160°   | 165°   | 170°   | 175°   | 180°   | 185°   | 190°   | 195°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 |
| 2.5°   | 1734.3 | 1727.5 | 1723.4 | 1722.1 | 1709.8 | 1703.0 | 1698.9 | 1696.2 | 1692.1 | 1681.2 | 1671.7 |
| 5°     | 1799.7 | 1780.7 | 1771.1 | 1760.2 | 1741.2 | 1719.4 | 1701.6 | 1690.7 | 1677.1 | 1655.3 | 1634.9 |
| 7.5°   | 1861.0 | 1832.4 | 1813.4 | 1798.4 | 1765.7 | 1730.3 | 1701.6 | 1678.5 | 1652.6 | 1622.6 | 1594.0 |
| 10°    | 1925.1 | 1878.8 | 1854.2 | 1831.1 | 1783.4 | 1737.1 | 1696.2 | 1662.1 | 1625.3 | 1585.8 | 1554.5 |
| 12.5°  | 1975.5 | 1914.2 | 1886.9 | 1854.2 | 1795.6 | 1741.2 | 1689.4 | 1643.1 | 1595.4 | 1553.1 | 1508.2 |
| 15°    | 2034.1 | 1957.8 | 1926.4 | 1884.2 | 1803.8 | 1733.0 | 1666.2 | 1615.8 | 1566.8 | 1504.1 | 1456.4 |
| 17.5°  | 2068.1 | 1979.6 | 1934.6 | 1897.8 | 1810.6 | 1724.8 | 1647.1 | 1584.5 | 1527.3 | 1464.6 | 1414.2 |
| 20°    | 2102.2 | 2001.4 | 1951.0 | 1899.2 | 1795.6 | 1704.4 | 1622.6 | 1547.7 | 1487.7 | 1419.6 | 1367.9 |
| 22.5°  | 2113.1 | 1995.9 | 1942.8 | 1895.1 | 1786.1 | 1683.9 | 1589.9 | 1513.6 | 1444.1 | 1376.0 | 1317.4 |
| 25°    | 2113.1 | 1994.6 | 1931.9 | 1870.6 | 1756.1 | 1651.2 | 1557.2 | 1474.1 | 1396.5 | 1328.3 | 1269.8 |
| 27.5°  | 2091.3 | 1967.3 | 1901.9 | 1846.1 | 1727.5 | 1614.4 | 1517.7 | 1426.4 | 1351.5 | 1283.4 | 1216.6 |
| 30°    | 2064.0 | 1927.8 | 1862.4 | 1795.6 | 1681.2 | 1573.6 | 1468.7 | 1384.2 | 1305.2 | 1227.5 | 1167.6 |
| 32.5°  | 2030.0 | 1885.6 | 1813.4 | 1745.2 | 1624.0 | 1512.3 | 1415.5 | 1332.4 | 1257.5 | 1177.1 | 1110.4 |
| 35°    | 1980.9 | 1822.9 | 1742.5 | 1682.6 | 1565.4 | 1449.6 | 1357.0 | 1275.2 | 1203.0 | 1119.9 | 1047.7 |
| 37.5°  | 1918.3 | 1765.7 | 1683.9 | 1610.4 | 1489.1 | 1382.8 | 1295.6 | 1216.6 | 1145.8 | 1069.5 | 989.1  |
| 40°    | 1844.7 | 1685.3 | 1614.4 | 1536.8 | 1408.7 | 1307.9 | 1226.2 | 1155.3 | 1084.5 | 1012.3 | 934.6  |
| 42.5°  | 1761.6 | 1603.5 | 1524.5 | 1449.6 | 1327.0 | 1227.5 | 1151.2 | 1087.2 | 1021.8 | 955.0  | 871.9  |
| 45°    | 1662.1 | 1513.6 | 1437.3 | 1366.5 | 1248.0 | 1145.8 | 1076.3 | 1015.0 | 959.1  | 891.0  | 817.4  |
| 47.5°  | 1550.4 | 1421.0 | 1343.3 | 1267.0 | 1151.2 | 1062.7 | 994.6  | 942.8  | 895.1  | 827.0  | 760.2  |
| 50°    | 1441.4 | 1313.4 | 1250.7 | 1173.0 | 1066.8 | 983.7  | 914.2  | 870.6  | 833.8  | 767.0  | 707.1  |
| 52.5°  | 1303.8 | 1207.1 | 1147.1 | 1080.4 | 978.2  | 893.7  | 839.2  | 801.1  | 757.5  | 705.7  | 652.6  |
| 55°    | 1182.6 | 1092.6 | 1045.0 | 982.3  | 881.5  | 806.5  | 760.2  | 724.8  | 690.7  | 644.4  | 602.2  |
| 57.5°  | 1045.0 | 989.1  | 941.4  | 886.9  | 787.5  | 723.4  | 682.6  | 652.6  | 621.3  | 583.1  | 549.0  |
| 60°    | 900.5  | 874.7  | 828.3  | 784.7  | 700.3  | 644.4  | 610.4  | 583.1  | 553.1  | 521.8  | 493.2  |
| 62.5°  | 772.5  | 757.5  | 730.2  | 696.2  | 617.2  | 569.5  | 535.4  | 515.0  | 493.2  | 464.6  | 437.3  |
| 65°    | 651.2  | 644.4  | 618.5  | 594.0  | 539.5  | 497.3  | 467.3  | 455.0  | 430.5  | 408.7  | 384.2  |
| 67.5°  | 543.6  | 535.4  | 520.4  | 509.5  | 463.2  | 423.7  | 408.7  | 392.4  | 371.9  | 355.6  | 335.2  |
| 70°    | 434.6  | 433.2  | 423.7  | 410.1  | 385.6  | 356.9  | 342.0  | 331.1  | 310.6  | 298.4  | 283.4  |
| 72.5°  | 337.9  | 344.7  | 336.5  | 331.1  | 314.7  | 294.3  | 280.7  | 273.8  | 257.5  | 248.0  | 237.1  |
| 75°    | 252.0  | 257.5  | 261.6  | 252.0  | 248.0  | 238.4  | 226.2  | 219.3  | 211.2  | 197.5  | 193.5  |
| 77.5°  | 171.7  | 183.9  | 183.9  | 186.6  | 188.0  | 182.6  | 173.0  | 167.6  | 158.0  | 155.3  | 149.9  |
| 80°    | 113.1  | 124.0  | 125.3  | 128.1  | 132.2  | 132.2  | 125.3  | 124.0  | 114.4  | 113.1  | 109.0  |
| 82.5°  | 65.4   | 74.9   | 80.4   | 84.5   | 83.1   | 88.6   | 83.1   | 81.7   | 76.3   | 76.3   | 73.6   |
| 85°    | 35.4   | 36.8   | 39.5   | 42.2   | 45.0   | 47.7   | 47.7   | 46.3   | 45.0   | 43.6   | 40.9   |
| 87.5°  | 13.6   | 13.6   | 15.0   | 13.6   | 15.0   | 17.7   | 19.1   | 19.1   | 17.7   | 16.3   | 13.6   |
| 90°    | 13.7   | 7.8    | 7.8    | 7.8    | 6.9    | 5.9    | 2.9    | 1.0    | 2.9    | 5.9    | 6.9    |
| 92.5°  | 148.9  | 88.2   | 75.4   | 62.7   | 45.1   | 30.4   | 19.6   | 13.7   | 19.6   | 30.4   | 45.1   |
| 95°    | 207.7  | 122.5  | 101.9  | 81.3   | 57.8   | 45.1   | 35.3   | 32.3   | 35.3   | 45.1   | 57.8   |
| 97.5°  | 197.9  | 130.3  | 112.6  | 95.0   | 74.5   | 62.7   | 53.9   | 53.9   | 53.9   | 62.7   | 74.5   |
| 100°   | 200.8  | 143.0  | 127.4  | 111.7  | 93.1   | 81.3   | 74.5   | 74.5   | 74.5   | 81.3   | 93.1   |
| 102.5° | 210.6  | 159.7  | 145.0  | 130.3  | 112.7  | 101.9  | 96.0   | 94.1   | 96.0   | 101.9  | 112.7  |
| 105°   | 227.3  | 180.3  | 166.1  | 151.9  | 134.2  | 122.5  | 117.6  | 114.6  | 117.6  | 122.5  | 134.2  |
| 107.5° | 244.9  | 201.8  | 187.6  | 173.4  | 156.8  | 144.0  | 139.1  | 137.2  | 139.1  | 144.0  | 156.8  |
| 110°   | 265.5  | 222.4  | 209.2  | 195.9  | 178.3  | 166.6  | 161.7  | 159.7  | 161.7  | 166.6  | 178.3  |

TEST NUMBER: P1025931

CATALOG NUMBER: S124RDIP-B1020D1035UB27-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 150°  | 155°  | 157.5° | 160°  | 165°  | 170°  | 175°  | 180°  | 185°  | 190°  | 195°  |
|--------|-------|-------|--------|-------|-------|-------|-------|-------|-------|-------|-------|
| 112.5° | 285.1 | 244.0 | 230.8  | 217.5 | 199.9 | 189.1 | 183.2 | 181.3 | 183.2 | 189.1 | 199.9 |
| 115°   | 305.7 | 266.5 | 253.2  | 240.0 | 221.4 | 211.6 | 204.8 | 201.8 | 204.8 | 211.6 | 221.4 |
| 117.5° | 325.3 | 288.0 | 274.3  | 260.6 | 243.0 | 232.2 | 226.3 | 223.4 | 226.3 | 232.2 | 243.0 |
| 120°   | 345.8 | 308.6 | 294.9  | 281.2 | 264.5 | 253.8 | 246.9 | 244.9 | 246.9 | 253.8 | 264.5 |
| 122.5° | 365.4 | 328.2 | 315.0  | 301.8 | 283.1 | 273.3 | 266.5 | 264.5 | 266.5 | 273.3 | 283.1 |
| 125°   | 383.1 | 347.8 | 334.1  | 320.4 | 301.8 | 291.0 | 285.1 | 281.2 | 285.1 | 291.0 | 301.8 |
| 127.5° | 399.7 | 365.4 | 351.7  | 338.0 | 318.4 | 306.7 | 299.8 | 296.9 | 299.8 | 306.7 | 318.4 |
| 130°   | 416.4 | 383.1 | 368.9  | 354.7 | 336.0 | 321.4 | 313.5 | 309.6 | 313.5 | 321.4 | 336.0 |
| 132.5° | 430.1 | 396.8 | 383.6  | 370.3 | 349.8 | 336.0 | 325.3 | 322.3 | 325.3 | 336.0 | 349.8 |
| 135°   | 442.8 | 410.5 | 397.8  | 385.0 | 364.5 | 347.8 | 338.0 | 334.1 | 338.0 | 347.8 | 364.5 |
| 137.5° | 452.6 | 422.3 | 410.0  | 397.8 | 376.2 | 360.5 | 349.8 | 345.8 | 349.8 | 360.5 | 376.2 |
| 140°   | 462.4 | 433.0 | 421.2  | 409.5 | 389.0 | 372.3 | 361.5 | 358.6 | 361.5 | 372.3 | 389.0 |
| 142.5° | 471.3 | 442.8 | 431.6  | 420.3 | 400.7 | 385.0 | 375.2 | 372.3 | 375.2 | 385.0 | 400.7 |
| 145°   | 477.1 | 451.7 | 440.9  | 430.1 | 411.5 | 397.8 | 388.0 | 385.0 | 388.0 | 397.8 | 411.5 |
| 147.5° | 484.0 | 459.5 | 449.7  | 439.9 | 424.2 | 409.5 | 400.7 | 399.7 | 400.7 | 409.5 | 424.2 |
| 150°   | 488.9 | 467.3 | 458.0  | 448.7 | 434.0 | 422.3 | 414.4 | 413.4 | 414.4 | 422.3 | 434.0 |
| 152.5° | 492.8 | 474.2 | 465.8  | 457.5 | 444.8 | 434.0 | 426.2 | 426.2 | 426.2 | 434.0 | 444.8 |
| 155°   | 496.7 | 480.1 | 472.8  | 465.4 | 454.6 | 444.8 | 438.9 | 437.9 | 438.9 | 444.8 | 454.6 |
| 157.5° | 499.7 | 485.0 | 479.1  | 473.2 | 463.4 | 455.6 | 449.7 | 449.7 | 449.7 | 455.6 | 463.4 |
| 160°   | 501.6 | 489.9 | 484.5  | 479.1 | 471.3 | 464.4 | 460.5 | 460.5 | 460.5 | 464.4 | 471.3 |
| 162.5° | 503.6 | 492.8 | 488.9  | 485.0 | 478.1 | 472.2 | 469.3 | 470.3 | 469.3 | 472.2 | 478.1 |
| 165°   | 503.6 | 494.8 | 491.8  | 488.9 | 484.0 | 479.1 | 477.1 | 477.1 | 477.1 | 479.1 | 484.0 |
| 167.5° | 503.6 | 496.7 | 494.2  | 491.8 | 488.9 | 485.0 | 484.0 | 485.0 | 484.0 | 485.0 | 488.9 |
| 170°   | 502.6 | 497.7 | 496.2  | 494.8 | 492.8 | 489.9 | 488.9 | 489.9 | 488.9 | 489.9 | 492.8 |
| 172.5° | 501.6 | 498.7 | 497.7  | 496.7 | 495.7 | 493.8 | 493.8 | 494.8 | 493.8 | 493.8 | 495.7 |
| 175°   | 500.6 | 498.7 | 498.7  | 498.7 | 497.7 | 496.7 | 496.7 | 497.7 | 496.7 | 496.7 | 497.7 |
| 177.5° | 499.7 | 498.7 | 498.7  | 498.7 | 498.7 | 497.7 | 498.7 | 499.7 | 498.7 | 497.7 | 498.7 |
| 180°   | 498.7 | 498.7 | 498.7  | 498.7 | 498.7 | 498.7 | 498.7 | 498.7 | 498.7 | 498.7 | 498.7 |

TEST NUMBER: P1025931

CATALOG NUMBER: S124RDIP-B1020D1035UB27-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 200°   | 202.5° | 205°   | 210°   | 215°   | 220°   | 225°   | 230°   | 235°   | 240°   | 245°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 |
| 2.5°   | 1663.5 | 1660.8 | 1658.0 | 1647.1 | 1637.6 | 1621.3 | 1607.6 | 1602.2 | 1600.8 | 1602.2 | 1598.1 |
| 5°     | 1615.8 | 1614.4 | 1604.9 | 1585.8 | 1568.1 | 1549.1 | 1535.4 | 1521.8 | 1513.6 | 1513.6 | 1504.1 |
| 7.5°   | 1570.9 | 1561.3 | 1553.1 | 1528.6 | 1508.2 | 1482.3 | 1461.9 | 1449.6 | 1442.8 | 1427.8 | 1427.8 |
| 10°    | 1523.2 | 1509.5 | 1498.6 | 1475.5 | 1445.5 | 1419.6 | 1393.7 | 1378.8 | 1366.5 | 1355.6 | 1351.5 |
| 12.5°  | 1475.5 | 1464.6 | 1444.1 | 1419.6 | 1389.7 | 1357.0 | 1329.7 | 1318.8 | 1290.2 | 1267.0 | 1268.4 |
| 15°    | 1430.5 | 1406.0 | 1396.5 | 1361.0 | 1325.6 | 1294.3 | 1254.8 | 1223.4 | 1200.3 | 1185.3 | 1166.2 |
| 17.5°  | 1380.1 | 1355.6 | 1337.9 | 1307.9 | 1261.6 | 1212.5 | 1174.4 | 1132.2 | 1109.0 | 1083.1 | 1070.8 |
| 20°    | 1324.3 | 1303.8 | 1290.2 | 1242.5 | 1186.7 | 1128.1 | 1085.8 | 1060.0 | 1034.1 | 1015.0 | 1004.1 |
| 22.5°  | 1276.6 | 1250.7 | 1234.3 | 1170.3 | 1109.0 | 1050.4 | 1017.7 | 995.9  | 974.1  | 957.8  | 952.3  |
| 25°    | 1215.3 | 1200.3 | 1160.8 | 1104.9 | 1030.0 | 990.5  | 961.9  | 933.2  | 921.0  | 910.1  | 897.8  |
| 27.5°  | 1164.9 | 1128.1 | 1100.8 | 1027.3 | 980.9  | 936.0  | 907.4  | 885.6  | 870.6  | 859.7  | 850.1  |
| 30°    | 1102.2 | 1068.1 | 1030.0 | 968.7  | 926.4  | 884.2  | 858.3  | 840.6  | 824.3  | 817.4  | 809.3  |
| 32.5°  | 1036.8 | 1005.5 | 968.7  | 919.6  | 867.9  | 835.2  | 814.7  | 795.6  | 784.7  | 777.9  | 768.4  |
| 35°    | 978.2  | 938.7  | 914.2  | 867.9  | 825.6  | 788.8  | 769.8  | 753.4  | 741.1  | 738.4  | 737.1  |
| 37.5°  | 915.5  | 885.6  | 862.4  | 814.7  | 779.3  | 748.0  | 730.2  | 712.5  | 705.7  | 704.4  | 698.9  |
| 40°    | 861.0  | 835.2  | 813.4  | 768.4  | 730.2  | 701.6  | 688.0  | 677.1  | 670.3  | 670.3  | 668.9  |
| 42.5°  | 813.4  | 786.1  | 764.3  | 723.4  | 689.4  | 663.5  | 648.5  | 637.6  | 634.9  | 636.2  | 634.9  |
| 45°    | 760.2  | 737.1  | 715.3  | 673.0  | 644.4  | 625.3  | 609.0  | 603.5  | 599.5  | 600.8  | 602.2  |
| 47.5°  | 709.8  | 690.7  | 668.9  | 634.9  | 602.2  | 581.7  | 572.2  | 566.8  | 566.8  | 566.8  | 569.5  |
| 50°    | 664.9  | 643.1  | 624.0  | 588.6  | 558.6  | 542.2  | 534.1  | 527.3  | 528.6  | 530.0  | 531.3  |
| 52.5°  | 611.7  | 592.6  | 579.0  | 543.6  | 521.8  | 501.4  | 491.8  | 493.2  | 491.8  | 491.8  | 494.6  |
| 55°    | 565.4  | 546.3  | 532.7  | 500.0  | 478.2  | 464.6  | 456.4  | 452.3  | 453.7  | 451.0  | 456.4  |
| 57.5°  | 513.6  | 497.3  | 487.7  | 456.4  | 437.3  | 425.1  | 418.3  | 411.4  | 414.2  | 412.8  | 411.4  |
| 60°    | 468.7  | 449.6  | 434.6  | 412.8  | 396.5  | 381.5  | 377.4  | 370.6  | 373.3  | 370.6  | 369.2  |
| 62.5°  | 416.9  | 401.9  | 391.0  | 369.2  | 355.6  | 343.3  | 333.8  | 329.7  | 328.3  | 324.3  | 320.2  |
| 65°    | 365.1  | 356.9  | 346.1  | 324.3  | 310.6  | 301.1  | 295.6  | 291.6  | 290.2  | 279.3  | 267.0  |
| 67.5°  | 317.4  | 312.0  | 301.1  | 284.7  | 272.5  | 262.9  | 254.8  | 248.0  | 239.8  | 231.6  | 224.8  |
| 70°    | 272.5  | 264.3  | 257.5  | 242.5  | 231.6  | 222.1  | 213.9  | 205.7  | 201.6  | 193.5  | 190.7  |
| 72.5°  | 228.9  | 220.7  | 213.9  | 200.3  | 190.7  | 181.2  | 178.5  | 168.9  | 164.9  | 163.5  | 163.5  |
| 75°    | 183.9  | 177.1  | 173.0  | 160.8  | 152.6  | 145.8  | 141.7  | 139.0  | 136.2  | 133.5  | 129.4  |
| 77.5°  | 140.3  | 136.2  | 133.5  | 125.3  | 118.5  | 114.4  | 113.1  | 103.5  | 100.8  | 98.1   | 95.4   |
| 80°    | 102.2  | 100.8  | 98.1   | 91.3   | 88.6   | 79.0   | 79.0   | 76.3   | 74.9   | 74.9   | 74.9   |
| 82.5°  | 69.5   | 66.8   | 65.4   | 58.6   | 57.2   | 55.9   | 54.5   | 53.1   | 54.5   | 53.1   | 54.5   |
| 85°    | 36.8   | 35.4   | 34.1   | 34.1   | 34.1   | 34.1   | 34.1   | 34.1   | 34.1   | 32.7   | 34.1   |
| 87.5°  | 13.6   | 13.6   | 13.6   | 13.6   | 12.3   | 13.6   | 13.6   | 12.3   | 13.6   | 13.6   | 13.6   |
| 90°    | 7.8    | 7.8    | 7.8    | 13.7   | 13.7   | 15.7   | 17.6   | 16.7   | 17.6   | 18.6   | 19.6   |
| 92.5°  | 62.7   | 75.4   | 88.2   | 148.9  | 244.0  | 336.0  | 384.1  | 319.4  | 236.1  | 176.4  | 139.1  |
| 95°    | 81.3   | 101.9  | 122.5  | 207.7  | 368.4  | 602.5  | 798.5  | 821.0  | 726.0  | 574.1  | 442.8  |
| 97.5°  | 95.0   | 112.6  | 130.3  | 197.9  | 336.0  | 577.1  | 854.3  | 1029.7 | 1045.4 | 969.9  | 862.2  |
| 100°   | 111.7  | 127.4  | 143.0  | 200.8  | 311.6  | 511.4  | 787.7  | 1038.5 | 1181.6 | 1201.2 | 1153.1 |
| 102.5° | 130.3  | 145.0  | 159.7  | 210.6  | 304.7  | 467.3  | 704.4  | 965.0  | 1174.7 | 1291.3 | 1320.7 |
| 105°   | 151.9  | 166.1  | 180.3  | 227.3  | 308.6  | 445.8  | 642.7  | 872.9  | 1097.3 | 1266.8 | 1363.8 |
| 107.5° | 173.4  | 187.6  | 201.8  | 244.9  | 320.4  | 439.9  | 602.5  | 797.5  | 1002.3 | 1185.5 | 1320.7 |
| 110°   | 195.9  | 209.2  | 222.4  | 265.5  | 334.1  | 441.9  | 583.9  | 743.6  | 918.0  | 1087.5 | 1229.6 |

TEST NUMBER: P1025931

CATALOG NUMBER: S124RDIP-B1020D1035UB27-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 200°  | 202.5° | 205°  | 210°  | 215°  | 220°  | 225°  | 230°  | 235°  | 240°   | 245°   |
|--------|-------|--------|-------|-------|-------|-------|-------|-------|-------|--------|--------|
| 112.5° | 217.5 | 230.8  | 244.0 | 285.1 | 348.8 | 447.7 | 575.1 | 713.2 | 856.3 | 1001.3 | 1133.5 |
| 115°   | 240.0 | 253.2  | 266.5 | 305.7 | 364.5 | 455.6 | 573.1 | 696.6 | 819.1 | 939.6  | 1054.2 |
| 117.5° | 260.6 | 274.3  | 288.0 | 325.3 | 380.1 | 463.4 | 572.2 | 687.8 | 797.5 | 899.4  | 992.5  |
| 120°   | 281.2 | 294.9  | 308.6 | 345.8 | 396.8 | 472.2 | 572.2 | 680.9 | 783.8 | 874.9  | 953.3  |
| 122.5° | 301.8 | 315.0  | 328.2 | 365.4 | 412.5 | 481.0 | 571.2 | 673.1 | 772.0 | 859.2  | 928.8  |
| 125°   | 320.4 | 334.1  | 347.8 | 383.1 | 428.1 | 489.9 | 570.2 | 664.3 | 758.3 | 842.6  | 910.2  |
| 127.5° | 338.0 | 351.7  | 365.4 | 399.7 | 441.9 | 496.7 | 568.2 | 652.5 | 742.6 | 824.0  | 891.6  |
| 130°   | 354.7 | 368.9  | 383.1 | 416.4 | 454.6 | 504.6 | 567.3 | 641.7 | 723.0 | 800.4  | 867.1  |
| 132.5° | 370.3 | 383.6  | 396.8 | 430.1 | 467.3 | 511.4 | 566.3 | 631.9 | 702.5 | 774.0  | 838.7  |
| 135°   | 385.0 | 397.8  | 410.5 | 442.8 | 478.1 | 518.3 | 565.3 | 622.1 | 683.9 | 747.5  | 807.3  |
| 137.5° | 397.8 | 410.0  | 422.3 | 452.6 | 485.9 | 522.2 | 565.3 | 613.3 | 666.2 | 722.1  | 774.0  |
| 140°   | 409.5 | 421.2  | 433.0 | 462.4 | 493.8 | 527.1 | 564.3 | 606.5 | 651.5 | 697.6  | 741.7  |
| 142.5° | 420.3 | 431.6  | 442.8 | 471.3 | 499.7 | 531.0 | 564.3 | 600.6 | 637.8 | 677.0  | 713.2  |
| 145°   | 430.1 | 440.9  | 451.7 | 477.1 | 503.6 | 532.0 | 562.4 | 593.7 | 625.1 | 658.4  | 687.8  |
| 147.5° | 439.9 | 449.7  | 459.5 | 484.0 | 507.5 | 533.0 | 559.4 | 587.8 | 614.3 | 641.7  | 666.2  |
| 150°   | 448.7 | 458.0  | 467.3 | 488.9 | 510.4 | 533.0 | 556.5 | 581.0 | 604.5 | 627.0  | 646.6  |
| 152.5° | 457.5 | 465.8  | 474.2 | 492.8 | 512.4 | 531.0 | 551.6 | 573.1 | 593.7 | 612.3  | 630.0  |
| 155°   | 465.4 | 472.8  | 480.1 | 496.7 | 513.4 | 529.1 | 546.7 | 565.3 | 582.9 | 598.6  | 613.3  |
| 157.5° | 473.2 | 479.1  | 485.0 | 499.7 | 513.4 | 527.1 | 541.8 | 557.5 | 571.2 | 584.9  | 597.6  |
| 160°   | 479.1 | 484.5  | 489.9 | 501.6 | 513.4 | 524.2 | 535.9 | 548.6 | 560.4 | 571.2  | 582.0  |
| 162.5° | 485.0 | 488.9  | 492.8 | 503.6 | 513.4 | 521.2 | 530.0 | 540.8 | 549.6 | 558.4  | 566.3  |
| 165°   | 488.9 | 491.8  | 494.8 | 503.6 | 511.4 | 517.3 | 524.2 | 532.0 | 539.8 | 545.7  | 552.6  |
| 167.5° | 491.8 | 494.2  | 496.7 | 503.6 | 509.5 | 513.4 | 518.3 | 524.2 | 530.0 | 534.9  | 540.8  |
| 170°   | 494.8 | 496.2  | 497.7 | 502.6 | 507.5 | 509.5 | 512.4 | 516.3 | 521.2 | 524.2  | 528.1  |
| 172.5° | 496.7 | 497.7  | 498.7 | 501.6 | 505.5 | 505.5 | 506.5 | 509.5 | 513.4 | 515.3  | 517.3  |
| 175°   | 498.7 | 498.7  | 498.7 | 500.6 | 503.6 | 502.6 | 502.6 | 504.6 | 506.5 | 507.5  | 509.5  |
| 177.5° | 498.7 | 498.7  | 498.7 | 499.7 | 501.6 | 499.7 | 499.7 | 500.6 | 501.6 | 502.6  | 502.6  |
| 180°   | 498.7 | 498.7  | 498.7 | 498.7 | 498.7 | 498.7 | 498.7 | 498.7 | 498.7 | 498.7  | 498.7  |

TEST NUMBER: P1025931

CATALOG NUMBER: S124RDIP-B1020D1035UB27-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250°   | 255°   | 260°   | 265°   | 270°   | 275°   | 280°   | 285°   | 290°   | 292.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 |
| 2.5°   | 1598.1 | 1603.5 | 1596.7 | 1600.8 | 1591.3 | 1589.9 | 1591.3 | 1591.3 | 1592.6 | 1594.0 | 1595.4 |
| 5°     | 1508.2 | 1506.8 | 1498.6 | 1493.2 | 1489.1 | 1493.2 | 1495.9 | 1498.6 | 1495.9 | 1498.6 | 1500.0 |
| 7.5°   | 1423.7 | 1419.6 | 1415.5 | 1406.0 | 1408.7 | 1406.0 | 1414.2 | 1410.1 | 1410.1 | 1416.9 | 1422.3 |
| 10°    | 1348.8 | 1340.6 | 1337.9 | 1327.0 | 1318.8 | 1317.4 | 1327.0 | 1331.1 | 1335.2 | 1337.9 | 1348.8 |
| 12.5°  | 1252.0 | 1239.8 | 1230.3 | 1234.3 | 1211.2 | 1220.7 | 1223.4 | 1218.0 | 1234.3 | 1253.4 | 1242.5 |
| 15°    | 1148.5 | 1149.9 | 1130.8 | 1124.0 | 1104.9 | 1110.4 | 1111.7 | 1125.3 | 1139.0 | 1137.6 | 1154.0 |
| 17.5°  | 1072.2 | 1064.0 | 1047.7 | 1046.3 | 1038.2 | 1042.2 | 1040.9 | 1051.8 | 1047.7 | 1054.5 | 1068.1 |
| 20°    | 1001.4 | 995.9  | 982.3  | 976.8  | 979.6  | 976.8  | 978.2  | 979.6  | 983.7  | 998.6  | 995.9  |
| 22.5°  | 945.5  | 938.7  | 938.7  | 931.9  | 923.7  | 921.0  | 927.8  | 931.9  | 937.3  | 940.1  | 946.9  |
| 25°    | 896.5  | 891.0  | 884.2  | 880.1  | 873.3  | 874.7  | 878.8  | 884.2  | 888.3  | 893.7  | 899.2  |
| 27.5°  | 846.1  | 846.1  | 839.2  | 837.9  | 835.2  | 833.8  | 839.2  | 842.0  | 842.0  | 846.1  | 851.5  |
| 30°    | 806.5  | 806.5  | 799.7  | 798.4  | 797.0  | 797.0  | 801.1  | 802.5  | 803.8  | 807.9  | 810.6  |
| 32.5°  | 768.4  | 767.0  | 764.3  | 765.7  | 764.3  | 765.7  | 765.7  | 767.0  | 769.8  | 771.1  | 776.6  |
| 35°    | 733.0  | 734.3  | 731.6  | 731.6  | 730.2  | 731.6  | 734.3  | 735.7  | 737.1  | 739.8  | 739.8  |
| 37.5°  | 698.9  | 701.6  | 700.3  | 704.4  | 704.4  | 704.4  | 704.4  | 707.1  | 707.1  | 707.1  | 705.7  |
| 40°    | 668.9  | 668.9  | 667.6  | 670.3  | 673.0  | 673.0  | 674.4  | 674.4  | 675.8  | 675.8  | 674.4  |
| 42.5°  | 634.9  | 637.6  | 641.7  | 643.1  | 645.8  | 644.4  | 648.5  | 647.1  | 648.5  | 645.8  | 643.1  |
| 45°    | 603.5  | 603.5  | 609.0  | 614.4  | 615.8  | 615.8  | 615.8  | 618.5  | 615.8  | 611.7  | 610.4  |
| 47.5°  | 569.5  | 572.2  | 574.9  | 581.7  | 583.1  | 583.1  | 583.1  | 583.1  | 580.4  | 580.4  | 580.4  |
| 50°    | 535.4  | 536.8  | 538.1  | 540.9  | 545.0  | 543.6  | 543.6  | 543.6  | 549.0  | 543.6  | 545.0  |
| 52.5°  | 494.6  | 495.9  | 497.3  | 502.7  | 501.4  | 501.4  | 502.7  | 502.7  | 506.8  | 505.5  | 502.7  |
| 55°    | 453.7  | 453.7  | 456.4  | 456.4  | 456.4  | 459.1  | 460.5  | 463.2  | 461.9  | 463.2  | 464.6  |
| 57.5°  | 412.8  | 410.1  | 408.7  | 408.7  | 412.8  | 411.4  | 412.8  | 412.8  | 418.3  | 421.0  | 422.3  |
| 60°    | 365.1  | 365.1  | 363.8  | 355.6  | 355.6  | 354.2  | 358.3  | 361.0  | 363.8  | 376.0  | 374.7  |
| 62.5°  | 316.1  | 310.6  | 305.2  | 306.5  | 298.4  | 302.5  | 299.7  | 302.5  | 310.6  | 320.2  | 321.5  |
| 65°    | 267.0  | 262.9  | 257.5  | 256.1  | 253.4  | 257.5  | 256.1  | 257.5  | 261.6  | 267.0  | 273.8  |
| 67.5°  | 223.4  | 222.1  | 219.3  | 218.0  | 218.0  | 218.0  | 220.7  | 220.7  | 222.1  | 226.2  | 230.2  |
| 70°    | 190.7  | 189.4  | 190.7  | 188.0  | 189.4  | 188.0  | 189.4  | 190.7  | 192.1  | 193.5  | 197.5  |
| 72.5°  | 160.8  | 160.8  | 160.8  | 158.0  | 160.8  | 159.4  | 159.4  | 160.8  | 162.1  | 163.5  | 166.2  |
| 75°    | 128.1  | 125.3  | 122.6  | 119.9  | 118.5  | 121.3  | 122.6  | 121.3  | 125.3  | 130.8  | 130.8  |
| 77.5°  | 96.7   | 95.4   | 95.4   | 95.4   | 96.7   | 95.4   | 98.1   | 96.7   | 98.1   | 98.1   | 100.8  |
| 80°    | 74.9   | 73.6   | 74.9   | 74.9   | 73.6   | 76.3   | 74.9   | 74.9   | 76.3   | 77.7   | 76.3   |
| 82.5°  | 54.5   | 55.9   | 54.5   | 54.5   | 54.5   | 57.2   | 54.5   | 54.5   | 54.5   | 55.9   | 55.9   |
| 85°    | 34.1   | 34.1   | 34.1   | 34.1   | 35.4   | 34.1   | 35.4   | 34.1   | 36.8   | 35.4   | 35.4   |
| 87.5°  | 12.3   | 13.6   | 15.0   | 15.0   | 15.0   | 15.0   | 13.6   | 15.0   | 16.3   | 15.0   | 16.3   |
| 90°    | 19.6   | 19.6   | 20.6   | 21.6   | 20.6   | 20.6   | 20.6   | 21.6   | 20.6   | 19.6   | 19.6   |
| 92.5°  | 126.8  | 114.6  | 99.9   | 93.1   | 89.2   | 89.2   | 89.2   | 93.1   | 99.9   | 114.6  | 126.8  |
| 95°    | 395.3  | 347.8  | 299.8  | 269.4  | 251.8  | 239.1  | 251.8  | 269.4  | 299.8  | 347.8  | 395.3  |
| 97.5°  | 807.3  | 752.4  | 685.8  | 627.0  | 597.6  | 574.1  | 597.6  | 627.0  | 685.8  | 752.4  | 807.3  |
| 100°   | 1116.8 | 1080.6 | 995.4  | 935.6  | 906.3  | 898.4  | 906.3  | 935.6  | 995.4  | 1080.6 | 1116.8 |
| 102.5° | 1310.9 | 1301.1 | 1257.0 | 1217.8 | 1186.5 | 1180.6 | 1186.5 | 1217.8 | 1257.0 | 1301.1 | 1310.9 |
| 105°   | 1383.9 | 1404.0 | 1405.9 | 1398.1 | 1384.4 | 1378.5 | 1384.4 | 1398.1 | 1405.9 | 1404.0 | 1383.9 |
| 107.5° | 1361.8 | 1403.0 | 1446.1 | 1463.7 | 1471.6 | 1472.5 | 1471.6 | 1463.7 | 1446.1 | 1403.0 | 1361.8 |
| 110°   | 1283.4 | 1337.3 | 1406.9 | 1448.0 | 1465.7 | 1474.5 | 1465.7 | 1448.0 | 1406.9 | 1337.3 | 1283.4 |

TEST NUMBER: P1025931

CATALOG NUMBER: S124RDIP-B1020D1035UB27-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 247.5° | 250°   | 255°   | 260°   | 265°   | 270°   | 275°   | 280°   | 285°   | 290°   | 292.5° |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 112.5° | 1187.4 | 1241.3 | 1322.6 | 1374.6 | 1401.0 | 1416.7 | 1401.0 | 1374.6 | 1322.6 | 1241.3 | 1187.4 |
| 115°   | 1101.2 | 1148.2 | 1225.6 | 1284.4 | 1315.8 | 1323.6 | 1315.8 | 1284.4 | 1225.6 | 1148.2 | 1101.2 |
| 117.5° | 1033.6 | 1074.8 | 1143.3 | 1194.3 | 1227.6 | 1232.5 | 1227.6 | 1194.3 | 1143.3 | 1074.8 | 1033.6 |
| 120°   | 988.0  | 1022.8 | 1078.7 | 1121.8 | 1147.3 | 1158.0 | 1147.3 | 1121.8 | 1078.7 | 1022.8 | 988.0  |
| 122.5° | 958.2  | 987.6  | 1032.6 | 1067.9 | 1088.5 | 1099.3 | 1088.5 | 1067.9 | 1032.6 | 987.6  | 958.2  |
| 125°   | 937.2  | 964.1  | 1003.2 | 1031.7 | 1050.3 | 1056.2 | 1050.3 | 1031.7 | 1003.2 | 964.1  | 937.2  |
| 127.5° | 917.0  | 942.5  | 981.7  | 1007.2 | 1022.8 | 1028.7 | 1022.8 | 1007.2 | 981.7  | 942.5  | 917.0  |
| 130°   | 893.0  | 919.0  | 959.2  | 983.7  | 999.3  | 1005.2 | 999.3  | 983.7  | 959.2  | 919.0  | 893.0  |
| 132.5° | 864.6  | 890.6  | 929.8  | 958.2  | 972.9  | 978.8  | 972.9  | 958.2  | 929.8  | 890.6  | 864.6  |
| 135°   | 831.8  | 856.3  | 895.5  | 922.9  | 938.6  | 944.5  | 938.6  | 922.9  | 895.5  | 856.3  | 831.8  |
| 137.5° | 796.6  | 819.1  | 856.3  | 884.7  | 897.4  | 904.3  | 897.4  | 884.7  | 856.3  | 819.1  | 796.6  |
| 140°   | 762.2  | 782.8  | 817.1  | 838.7  | 852.4  | 860.2  | 852.4  | 838.7  | 817.1  | 782.8  | 762.2  |
| 142.5° | 730.4  | 747.5  | 776.9  | 796.5  | 808.3  | 813.2  | 808.3  | 796.5  | 776.9  | 747.5  | 730.4  |
| 145°   | 701.5  | 715.2  | 739.7  | 756.4  | 766.2  | 771.0  | 766.2  | 756.4  | 739.7  | 715.2  | 701.5  |
| 147.5° | 677.5  | 688.8  | 707.4  | 722.1  | 729.9  | 731.9  | 729.9  | 722.1  | 707.4  | 688.8  | 677.5  |
| 150°   | 655.4  | 664.3  | 679.9  | 692.7  | 698.5  | 699.5  | 698.5  | 692.7  | 679.9  | 664.3  | 655.4  |
| 152.5° | 636.8  | 643.7  | 656.4  | 666.2  | 669.2  | 670.1  | 669.2  | 666.2  | 656.4  | 643.7  | 636.8  |
| 155°   | 619.2  | 625.1  | 634.9  | 642.7  | 645.6  | 645.6  | 645.6  | 642.7  | 634.9  | 625.1  | 619.2  |
| 157.5° | 602.5  | 607.4  | 615.3  | 621.1  | 623.1  | 623.1  | 623.1  | 621.1  | 615.3  | 607.4  | 602.5  |
| 160°   | 585.9  | 589.8  | 595.7  | 601.6  | 602.5  | 602.5  | 602.5  | 601.6  | 595.7  | 589.8  | 585.9  |
| 162.5° | 569.7  | 573.1  | 577.1  | 582.9  | 583.9  | 582.9  | 583.9  | 582.9  | 577.1  | 573.1  | 569.7  |
| 165°   | 555.0  | 557.5  | 561.4  | 565.3  | 564.3  | 563.3  | 564.3  | 565.3  | 561.4  | 557.5  | 555.0  |
| 167.5° | 542.3  | 543.8  | 545.7  | 548.6  | 548.6  | 547.7  | 548.6  | 548.6  | 545.7  | 543.8  | 542.3  |
| 170°   | 529.6  | 531.0  | 533.0  | 534.0  | 533.0  | 533.0  | 533.0  | 534.0  | 533.0  | 531.0  | 529.6  |
| 172.5° | 518.3  | 519.3  | 520.2  | 521.2  | 520.2  | 518.3  | 520.2  | 521.2  | 520.2  | 519.3  | 518.3  |
| 175°   | 509.5  | 509.5  | 509.5  | 511.4  | 509.5  | 507.5  | 509.5  | 511.4  | 509.5  | 509.5  | 509.5  |
| 177.5° | 503.1  | 503.6  | 502.6  | 503.6  | 501.6  | 499.7  | 501.6  | 503.6  | 502.6  | 503.6  | 503.1  |
| 180°   | 498.7  | 498.7  | 498.7  | 498.7  | 498.7  | 498.7  | 498.7  | 498.7  | 498.7  | 498.7  | 498.7  |

TEST NUMBER: P1025931

CATALOG NUMBER: S124RDIP-B1020D1035UB27-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 295°   | 300°   | 305°   | 310°   | 315°   | 320°   | 325°   | 330°   | 335°   | 337.5° | 340°   |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°     | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 | 1690.7 |
| 2.5°   | 1600.8 | 1607.6 | 1604.9 | 1595.4 | 1599.5 | 1607.6 | 1615.8 | 1626.7 | 1633.5 | 1639.0 | 1641.7 |
| 5°     | 1506.8 | 1519.1 | 1516.4 | 1516.4 | 1521.8 | 1535.4 | 1549.1 | 1572.2 | 1580.4 | 1589.9 | 1603.5 |
| 7.5°   | 1423.7 | 1433.2 | 1441.4 | 1444.1 | 1452.3 | 1470.0 | 1487.7 | 1513.6 | 1534.1 | 1545.0 | 1553.1 |
| 10°    | 1350.1 | 1357.0 | 1369.2 | 1376.0 | 1384.2 | 1406.0 | 1431.9 | 1459.1 | 1479.6 | 1498.6 | 1509.5 |
| 12.5°  | 1256.1 | 1283.4 | 1299.7 | 1310.6 | 1321.5 | 1354.2 | 1374.7 | 1404.6 | 1429.2 | 1446.9 | 1463.2 |
| 15°    | 1151.2 | 1183.9 | 1193.5 | 1235.7 | 1262.9 | 1288.8 | 1320.2 | 1355.6 | 1378.8 | 1399.2 | 1421.0 |
| 17.5°  | 1062.7 | 1085.8 | 1096.7 | 1141.7 | 1164.9 | 1205.7 | 1250.7 | 1295.6 | 1331.1 | 1346.1 | 1367.9 |
| 20°    | 1006.8 | 1019.1 | 1040.9 | 1055.9 | 1080.4 | 1128.1 | 1177.1 | 1231.6 | 1284.7 | 1299.7 | 1321.5 |
| 22.5°  | 949.6  | 965.9  | 980.9  | 1001.4 | 1020.4 | 1053.1 | 1102.2 | 1162.1 | 1219.4 | 1246.6 | 1272.5 |
| 25°    | 897.8  | 914.2  | 923.7  | 945.5  | 963.2  | 995.9  | 1030.0 | 1091.3 | 1159.4 | 1182.6 | 1223.4 |
| 27.5°  | 857.0  | 866.5  | 882.8  | 892.4  | 912.8  | 942.8  | 974.1  | 1020.4 | 1087.2 | 1126.7 | 1166.2 |
| 30°    | 816.1  | 822.9  | 836.5  | 850.1  | 865.1  | 885.6  | 921.0  | 965.9  | 1027.3 | 1061.3 | 1100.8 |
| 32.5°  | 775.2  | 786.1  | 794.3  | 803.8  | 820.2  | 844.7  | 869.2  | 912.8  | 961.9  | 1000.0 | 1039.5 |
| 35°    | 741.1  | 745.2  | 756.1  | 767.0  | 777.9  | 799.7  | 825.6  | 867.9  | 911.4  | 941.4  | 976.8  |
| 37.5°  | 704.4  | 711.2  | 719.3  | 723.4  | 741.1  | 754.8  | 782.0  | 814.7  | 866.5  | 885.6  | 921.0  |
| 40°    | 675.8  | 674.4  | 682.6  | 689.4  | 697.6  | 719.3  | 735.7  | 771.1  | 812.0  | 842.0  | 863.8  |
| 42.5°  | 640.3  | 640.3  | 643.1  | 651.2  | 662.1  | 675.8  | 694.8  | 724.8  | 767.0  | 788.8  | 814.7  |
| 45°    | 611.7  | 607.6  | 609.0  | 614.4  | 621.3  | 634.9  | 654.0  | 679.8  | 722.1  | 739.8  | 767.0  |
| 47.5°  | 577.7  | 573.6  | 573.6  | 579.0  | 584.5  | 594.0  | 609.0  | 639.0  | 673.0  | 696.2  | 716.6  |
| 50°    | 539.5  | 540.9  | 539.5  | 543.6  | 546.3  | 555.9  | 572.2  | 596.7  | 628.1  | 647.1  | 670.3  |
| 52.5°  | 504.1  | 501.4  | 500.0  | 502.7  | 508.2  | 515.0  | 532.7  | 554.5  | 584.5  | 603.5  | 624.0  |
| 55°    | 460.5  | 463.2  | 463.2  | 463.2  | 471.4  | 474.1  | 487.7  | 509.5  | 539.5  | 554.5  | 573.6  |
| 57.5°  | 421.0  | 419.6  | 422.3  | 421.0  | 427.8  | 437.3  | 448.2  | 464.6  | 494.6  | 509.5  | 527.3  |
| 60°    | 377.4  | 378.7  | 380.1  | 380.1  | 385.6  | 395.1  | 407.4  | 422.3  | 446.9  | 461.9  | 478.2  |
| 62.5°  | 324.3  | 331.1  | 337.9  | 340.6  | 348.8  | 355.6  | 363.8  | 380.1  | 401.9  | 412.8  | 427.8  |
| 65°    | 273.8  | 283.4  | 292.9  | 299.7  | 305.2  | 312.0  | 322.9  | 337.9  | 355.6  | 366.5  | 381.5  |
| 67.5°  | 230.2  | 237.1  | 249.3  | 256.1  | 267.0  | 275.2  | 282.0  | 294.3  | 316.1  | 320.2  | 332.4  |
| 70°    | 198.9  | 201.6  | 207.1  | 212.5  | 224.8  | 231.6  | 239.8  | 252.0  | 268.4  | 277.9  | 284.7  |
| 72.5°  | 167.6  | 168.9  | 171.7  | 177.1  | 182.6  | 190.7  | 200.3  | 211.2  | 226.2  | 230.2  | 239.8  |
| 75°    | 133.5  | 141.7  | 141.7  | 145.8  | 149.9  | 154.0  | 162.1  | 173.0  | 182.6  | 189.4  | 194.8  |
| 77.5°  | 99.5   | 103.5  | 106.3  | 113.1  | 118.5  | 122.6  | 128.1  | 136.2  | 141.7  | 147.1  | 151.2  |
| 80°    | 77.7   | 79.0   | 80.4   | 80.4   | 83.1   | 88.6   | 94.0   | 99.5   | 106.3  | 109.0  | 113.1  |
| 82.5°  | 57.2   | 57.2   | 57.2   | 59.9   | 61.3   | 62.7   | 62.7   | 65.4   | 72.2   | 74.9   | 79.0   |
| 85°    | 36.8   | 36.8   | 36.8   | 36.8   | 38.1   | 39.5   | 40.9   | 42.2   | 42.2   | 42.2   | 45.0   |
| 87.5°  | 15.0   | 17.7   | 16.3   | 17.7   | 17.7   | 17.7   | 17.7   | 19.1   | 19.1   | 20.4   | 20.4   |
| 90°    | 19.6   | 18.6   | 17.6   | 16.7   | 17.6   | 15.7   | 13.7   | 13.7   | 7.8    | 7.8    | 7.8    |
| 92.5°  | 139.1  | 176.4  | 236.1  | 319.4  | 384.1  | 336.0  | 244.0  | 148.9  | 88.2   | 75.4   | 62.7   |
| 95°    | 442.8  | 574.1  | 726.0  | 821.0  | 798.5  | 602.5  | 368.4  | 207.7  | 122.5  | 101.9  | 81.3   |
| 97.5°  | 862.2  | 969.9  | 1045.4 | 1029.7 | 854.3  | 577.1  | 336.0  | 197.9  | 130.3  | 112.6  | 95.0   |
| 100°   | 1153.1 | 1201.2 | 1181.6 | 1038.5 | 787.7  | 511.4  | 311.6  | 200.8  | 143.0  | 127.4  | 111.7  |
| 102.5° | 1320.7 | 1291.3 | 1174.7 | 965.0  | 704.4  | 467.3  | 304.7  | 210.6  | 159.7  | 145.0  | 130.3  |
| 105°   | 1363.8 | 1266.8 | 1097.3 | 872.9  | 642.7  | 445.8  | 308.6  | 227.3  | 180.3  | 166.1  | 151.9  |
| 107.5° | 1320.7 | 1185.5 | 1002.3 | 797.5  | 602.5  | 439.9  | 320.4  | 244.9  | 201.8  | 187.6  | 173.4  |
| 110°   | 1229.6 | 1087.5 | 918.0  | 743.6  | 583.9  | 441.9  | 334.1  | 265.5  | 222.4  | 209.2  | 195.9  |

TEST NUMBER: P1025931

CATALOG NUMBER: S124RDIP-B1020D1035UB27-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 295°   | 300°   | 305°  | 310°  | 315°  | 320°  | 325°  | 330°  | 335°  | 337.5° | 340°  |
|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|--------|-------|
| 112.5° | 1133.5 | 1001.3 | 856.3 | 713.2 | 575.1 | 447.7 | 348.8 | 285.1 | 244.0 | 230.8  | 217.5 |
| 115°   | 1054.2 | 939.6  | 819.1 | 696.6 | 573.1 | 455.6 | 364.5 | 305.7 | 266.5 | 253.2  | 240.0 |
| 117.5° | 992.5  | 899.4  | 797.5 | 687.8 | 572.2 | 463.4 | 380.1 | 325.3 | 288.0 | 274.3  | 260.6 |
| 120°   | 953.3  | 874.9  | 783.8 | 680.9 | 572.2 | 472.2 | 396.8 | 345.8 | 308.6 | 294.9  | 281.2 |
| 122.5° | 928.8  | 859.2  | 772.0 | 673.1 | 571.2 | 481.0 | 412.5 | 365.4 | 328.2 | 315.0  | 301.8 |
| 125°   | 910.2  | 842.6  | 758.3 | 664.3 | 570.2 | 489.9 | 428.1 | 383.1 | 347.8 | 334.1  | 320.4 |
| 127.5° | 891.6  | 824.0  | 742.6 | 652.5 | 568.2 | 496.7 | 441.9 | 399.7 | 365.4 | 351.7  | 338.0 |
| 130°   | 867.1  | 800.4  | 723.0 | 641.7 | 567.3 | 504.6 | 454.6 | 416.4 | 383.1 | 368.9  | 354.7 |
| 132.5° | 838.7  | 774.0  | 702.5 | 631.9 | 566.3 | 511.4 | 467.3 | 430.1 | 396.8 | 383.6  | 370.3 |
| 135°   | 807.3  | 747.5  | 683.9 | 622.1 | 565.3 | 518.3 | 478.1 | 442.8 | 410.5 | 397.8  | 385.0 |
| 137.5° | 774.0  | 722.1  | 666.2 | 613.3 | 565.3 | 522.2 | 485.9 | 452.6 | 422.3 | 410.0  | 397.8 |
| 140°   | 741.7  | 697.6  | 651.5 | 606.5 | 564.3 | 527.1 | 493.8 | 462.4 | 433.0 | 421.2  | 409.5 |
| 142.5° | 713.2  | 677.0  | 637.8 | 600.6 | 564.3 | 531.0 | 499.7 | 471.3 | 442.8 | 431.6  | 420.3 |
| 145°   | 687.8  | 658.4  | 625.1 | 593.7 | 562.4 | 532.0 | 503.6 | 477.1 | 451.7 | 440.9  | 430.1 |
| 147.5° | 666.2  | 641.7  | 614.3 | 587.8 | 559.4 | 533.0 | 507.5 | 484.0 | 459.5 | 449.7  | 439.9 |
| 150°   | 646.6  | 627.0  | 604.5 | 581.0 | 556.5 | 533.0 | 510.4 | 488.9 | 467.3 | 458.0  | 448.7 |
| 152.5° | 630.0  | 612.3  | 593.7 | 573.1 | 551.6 | 531.0 | 512.4 | 492.8 | 474.2 | 465.8  | 457.5 |
| 155°   | 613.3  | 598.6  | 582.9 | 565.3 | 546.7 | 529.1 | 513.4 | 496.7 | 480.1 | 472.8  | 465.4 |
| 157.5° | 597.6  | 584.9  | 571.2 | 557.5 | 541.8 | 527.1 | 513.4 | 499.7 | 485.0 | 479.1  | 473.2 |
| 160°   | 582.0  | 571.2  | 560.4 | 548.6 | 535.9 | 524.2 | 513.4 | 501.6 | 489.9 | 484.5  | 479.1 |
| 162.5° | 566.3  | 558.4  | 549.6 | 540.8 | 530.0 | 521.2 | 513.4 | 503.6 | 492.8 | 488.9  | 485.0 |
| 165°   | 552.6  | 545.7  | 539.8 | 532.0 | 524.2 | 517.3 | 511.4 | 503.6 | 494.8 | 491.8  | 488.9 |
| 167.5° | 540.8  | 534.9  | 530.0 | 524.2 | 518.3 | 513.4 | 509.5 | 503.6 | 496.7 | 494.2  | 491.8 |
| 170°   | 528.1  | 524.2  | 521.2 | 516.3 | 512.4 | 509.5 | 507.5 | 502.6 | 497.7 | 496.2  | 494.8 |
| 172.5° | 517.3  | 515.3  | 513.4 | 509.5 | 506.5 | 505.5 | 505.5 | 501.6 | 498.7 | 497.7  | 496.7 |
| 175°   | 509.5  | 507.5  | 506.5 | 504.6 | 502.6 | 502.6 | 503.6 | 500.6 | 498.7 | 498.7  | 498.7 |
| 177.5° | 502.6  | 502.6  | 501.6 | 500.6 | 499.7 | 499.7 | 501.6 | 499.7 | 498.7 | 498.7  | 498.7 |
| 180°   | 498.7  | 498.7  | 498.7 | 498.7 | 498.7 | 498.7 | 498.7 | 498.7 | 498.7 | 498.7  | 498.7 |

TEST NUMBER: P1025931

CATALOG NUMBER: S124RDIP-B1020D1035UB27-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 345°   | 350°   | 355°   | 360°   |
|--------|--------|--------|--------|--------|
| 0°     | 1690.7 | 1690.7 | 1690.7 | 1690.7 |
| 2.5°   | 1652.6 | 1660.8 | 1674.4 | 1693.5 |
| 5°     | 1614.4 | 1637.6 | 1659.4 | 1688.0 |
| 7.5°   | 1580.4 | 1607.6 | 1637.6 | 1678.5 |
| 10°    | 1540.9 | 1574.9 | 1613.1 | 1663.5 |
| 12.5°  | 1494.6 | 1542.2 | 1585.8 | 1640.3 |
| 15°    | 1460.5 | 1495.9 | 1551.8 | 1615.8 |
| 17.5°  | 1412.8 | 1460.5 | 1516.4 | 1588.6 |
| 20°    | 1367.9 | 1418.3 | 1480.9 | 1555.9 |
| 22.5°  | 1320.2 | 1377.4 | 1440.1 | 1520.4 |
| 25°    | 1271.1 | 1332.4 | 1395.1 | 1480.9 |
| 27.5°  | 1226.2 | 1282.0 | 1352.9 | 1440.1 |
| 30°    | 1171.7 | 1235.7 | 1303.8 | 1395.1 |
| 32.5°  | 1118.5 | 1185.3 | 1254.8 | 1346.1 |
| 35°    | 1061.3 | 1128.1 | 1204.4 | 1291.6 |
| 37.5°  | 1005.5 | 1079.0 | 1148.5 | 1233.0 |
| 40°    | 944.1  | 1020.4 | 1092.6 | 1178.5 |
| 42.5°  | 884.2  | 963.2  | 1035.4 | 1109.0 |
| 45°    | 828.3  | 906.0  | 971.4  | 1040.9 |
| 47.5°  | 775.2  | 844.7  | 911.4  | 974.1  |
| 50°    | 723.4  | 782.0  | 843.3  | 895.1  |
| 52.5°  | 668.9  | 724.8  | 773.8  | 820.2  |
| 55°    | 619.9  | 663.5  | 707.1  | 749.3  |
| 57.5°  | 561.3  | 604.9  | 643.1  | 675.8  |
| 60°    | 512.3  | 539.5  | 576.3  | 610.4  |
| 62.5°  | 456.4  | 487.7  | 516.4  | 538.1  |
| 65°    | 401.9  | 429.2  | 451.0  | 470.0  |
| 67.5°  | 355.6  | 371.9  | 388.3  | 408.7  |
| 70°    | 299.7  | 313.4  | 332.4  | 347.4  |
| 72.5°  | 252.0  | 262.9  | 272.5  | 290.2  |
| 75°    | 204.4  | 213.9  | 219.3  | 235.7  |
| 77.5°  | 158.0  | 167.6  | 171.7  | 181.2  |
| 80°    | 121.3  | 122.6  | 128.1  | 136.2  |
| 82.5°  | 83.1   | 85.8   | 87.2   | 94.0   |
| 85°    | 47.7   | 54.5   | 53.1   | 55.9   |
| 87.5°  | 20.4   | 21.8   | 24.5   | 27.2   |
| 90°    | 6.9    | 5.9    | 2.9    | 1.0    |
| 92.5°  | 45.1   | 30.4   | 19.6   | 13.7   |
| 95°    | 57.8   | 45.1   | 35.3   | 32.3   |
| 97.5°  | 74.5   | 62.7   | 53.9   | 53.9   |
| 100°   | 93.1   | 81.3   | 74.5   | 74.5   |
| 102.5° | 112.7  | 101.9  | 96.0   | 94.1   |
| 105°   | 134.2  | 122.5  | 117.6  | 114.6  |
| 107.5° | 156.8  | 144.0  | 139.1  | 137.2  |
| 110°   | 178.3  | 166.6  | 161.7  | 159.7  |



TEST NUMBER: P1025931

CATALOG NUMBER: S124RDIP-B1020D1035UB27-4F0-XX-W2A-A4

**CANDELA DISTRIBUTION (continued):**

|        | 345°  | 350°  | 355°  | 360°  |
|--------|-------|-------|-------|-------|
| 112.5° | 199.9 | 189.1 | 183.2 | 181.3 |
| 115°   | 221.4 | 211.6 | 204.8 | 201.8 |
| 117.5° | 243.0 | 232.2 | 226.3 | 223.4 |
| 120°   | 264.5 | 253.8 | 246.9 | 244.9 |
| 122.5° | 283.1 | 273.3 | 266.5 | 264.5 |
| 125°   | 301.8 | 291.0 | 285.1 | 281.2 |
| 127.5° | 318.4 | 306.7 | 299.8 | 296.9 |
| 130°   | 336.0 | 321.4 | 313.5 | 309.6 |
| 132.5° | 349.8 | 336.0 | 325.3 | 322.3 |
| 135°   | 364.5 | 347.8 | 338.0 | 334.1 |
| 137.5° | 376.2 | 360.5 | 349.8 | 345.8 |
| 140°   | 389.0 | 372.3 | 361.5 | 358.6 |
| 142.5° | 400.7 | 385.0 | 375.2 | 372.3 |
| 145°   | 411.5 | 397.8 | 388.0 | 385.0 |
| 147.5° | 424.2 | 409.5 | 400.7 | 399.7 |
| 150°   | 434.0 | 422.3 | 414.4 | 413.4 |
| 152.5° | 444.8 | 434.0 | 426.2 | 426.2 |
| 155°   | 454.6 | 444.8 | 438.9 | 437.9 |
| 157.5° | 463.4 | 455.6 | 449.7 | 449.7 |
| 160°   | 471.3 | 464.4 | 460.5 | 460.5 |
| 162.5° | 478.1 | 472.2 | 469.3 | 470.3 |
| 165°   | 484.0 | 479.1 | 477.1 | 477.1 |
| 167.5° | 488.9 | 485.0 | 484.0 | 485.0 |
| 170°   | 492.8 | 489.9 | 488.9 | 489.9 |
| 172.5° | 495.7 | 493.8 | 493.8 | 494.8 |
| 175°   | 497.7 | 496.7 | 496.7 | 497.7 |
| 177.5° | 498.7 | 497.7 | 498.7 | 499.7 |
| 180°   | 498.7 | 498.7 | 498.7 | 498.7 |

(END OF REPORT)