

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013305

Luminaire Tested: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013305
REPORT IS A COMBINATION OF REPORTS P999230 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_2700K
Description: Define 4 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5434.0 lumens
Efficiency: N/A
Efficacy: 130.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013305

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1013305

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34				25
1	92	88	85	81	82	79	76	73	61	59	57	45	44	42	30	29	29				22
2	84	77	71	67	75	69	64	60	54	50	48	39	37	36	26	25	24				18
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	23	22	21				16
4	70	60	53	47	62	54	47	43	42	38	34	31	28	26	21	19	18				14
5	64	53	46	40	57	48	41	36	38	33	29	28	25	22	19	17	16				12
6	59	48	40	35	53	43	36	31	34	29	25	25	22	20	17	15	14				10
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12				9
8	51	39	32	26	45	35	29	24	28	23	20	21	18	15	14	12	11				8
9	47	35	28	23	42	32	26	21	25	21	18	19	16	14	13	11	10				8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9				7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4863	4863	4863
5°	4864	4719	4719
10°	4823	4570	4516
15°	4757	4384	4275
20°	4670	4173	4001
25°	4561	3945	3733
30°	4454	3713	3432
35°	4338	3477	3139
40°	4200	3223	2837
45°	4069	2971	2538
50°	3921	2695	2234
55°	3761	2414	1921
60°	3583	2114	1612
65°	3412	1772	1313
70°	3168	1410	1004
75°	2856	1025	702
80°	2385	631	504
85°	1797	364	277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4069 cd/sqm

TEST NUMBER: P1013305

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.1	1.0
10°-20°	156.4	2.9
20°-30°	225.7	4.2
30°-40°	255.9	4.7
40°-50°	247.0	4.5
50°-60°	205.4	3.8
60°-70°	141.8	2.6
70°-80°	71.6	1.3
80°-90°	20.9	0.4
90°-100°	43.5	0.8
100°-110°	286.4	5.3
110°-120°	546.8	10.1
120°-130°	694.2	12.8
130°-140°	742.6	13.7
140°-150°	694.4	12.8
150°-160°	560.0	10.3
160°-170°	361.1	6.6
170°-180°	124.5	2.3
0°-30°	438.2	8.1
0°-40°	694.0	12.8
0°-60°	1146.4	21.1
0°-90°	1380.7	25.4
90°-120°	876.6	16.1
90°-150°	3007.8	55.4
90°-180°	4053.0	74.6
0°-180°	5434.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	596	596	596	596	596	
5°	596	594	588	593	592	57
15°	567	563	552	551	548	160
25°	513	505	486	478	474	236
35°	443	429	406	390	382	277
45°	362	345	317	295	287	279
55°	274	256	226	202	194	245
65°	186	167	138	118	112	184
75°	99	82	61	50	48	105
85°	25	16	14	13	13	27
90°	3	14	22	27	29	4
95°	54	21	22	27	28	66
105°	295	301	306	314	279	309
115°	551	554	553	554	554	542
125°	774	778	776	779	780	691
135°	960	959	963	965	967	740
145°	1107	1110	1110	1111	1113	692
155°	1214	1215	1212	1216	1213	560
165°	1280	1276	1276	1283	1275	362
175°	1310	1304	1305	1314	1302	125
180°	1310	1310	1310	1310	1310	

TEST NUMBER: P1013305

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	596.4	596.4	596.4	596.4	596.4
2.5°	598.2	596.4	591.4	596.4	595.9
5°	595.5	593.6	588.2	592.7	591.8
7.5°	591.4	589.5	582.7	585.9	584.5
10°	585.0	582.7	574.5	576.3	574.5
12.5°	576.7	574.0	564.0	564.9	562.1
15°	567.2	563.0	551.6	550.7	547.5
17.5°	556.2	550.3	537.0	534.7	530.2
20°	543.0	537.0	521.5	517.8	511.9
22.5°	528.3	521.5	504.6	498.7	494.1
25°	512.8	504.6	485.9	478.1	473.5
27.5°	496.8	486.8	467.1	458.0	451.6
30°	479.9	468.5	447.1	435.6	428.3
32.5°	462.1	448.9	426.5	412.8	406.0
35°	443.4	428.8	406.0	390.4	382.2
37.5°	423.8	408.7	383.6	366.7	358.5
40°	402.8	387.7	361.7	342.5	334.3
42.5°	382.7	366.7	339.3	319.7	311.0
45°	361.7	344.8	317.4	295.0	286.8
47.5°	340.2	322.8	294.5	271.2	262.1
50°	318.3	300.5	271.2	248.4	239.7
52.5°	295.9	278.6	248.4	225.1	216.0
55°	274.0	255.7	226.0	202.3	193.6
57.5°	252.5	233.3	204.1	179.9	173.5
60°	229.2	211.0	181.7	158.0	150.7
62.5°	208.2	189.1	158.9	137.5	132.0
65°	186.3	166.7	137.5	117.8	112.3
67.5°	163.5	144.8	117.4	100.0	93.6
70°	142.0	122.8	96.8	81.7	77.2
72.5°	119.2	102.3	78.1	65.8	61.6
75°	99.1	82.2	60.7	50.2	47.5
77.5°	78.1	63.5	45.2	37.9	37.0
80°	58.0	44.8	31.1	29.7	29.2
82.5°	40.6	28.8	22.4	21.5	21.0
85°	24.7	15.5	14.2	13.2	13.2
87.5°	10.5	6.8	6.4	5.9	6.4
90°	2.9	13.7	21.6	27.4	29.4
92.5°	14.7	12.7	20.6	26.5	26.5
95°	53.9	20.6	21.6	27.4	28.4
97.5°	102.9	124.4	21.6	26.5	27.4
100°	160.7	178.3	43.1	26.5	27.4
102.5°	225.3	237.1	248.9	28.4	28.4
105°	294.9	300.8	305.7	314.5	279.2
107.5°	358.6	361.5	368.4	373.3	377.2
110°	423.2	426.2	432.1	434.0	437.0

TEST NUMBER: P1013305

CATALOG NUMBER: S124RDIP-B350D1035UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	485.9	491.8	493.8	492.8	496.7
115°	550.6	553.5	552.6	554.5	554.5
117.5°	608.4	612.3	615.3	614.3	614.3
120°	667.2	671.1	670.1	672.1	670.1
122.5°	722.1	724.0	726.0	727.0	725.0
125°	774.0	777.9	775.9	778.9	779.9
127.5°	824.0	824.9	829.8	828.9	827.9
130°	872.0	872.9	875.9	876.9	876.9
132.5°	916.0	918.0	921.9	922.9	921.9
135°	960.1	959.2	963.1	965.0	967.0
137.5°	999.3	999.3	1004.2	1006.2	1005.2
140°	1037.5	1039.5	1041.5	1044.4	1045.4
142.5°	1071.8	1075.7	1076.7	1078.7	1078.7
145°	1107.1	1110.0	1110.0	1111.0	1113.0
147.5°	1134.5	1140.4	1139.4	1140.4	1141.4
150°	1164.9	1168.8	1167.8	1167.8	1168.8
152.5°	1190.4	1193.3	1191.4	1193.3	1192.3
155°	1213.9	1214.9	1211.9	1215.8	1212.9
157.5°	1234.5	1234.5	1230.5	1235.4	1230.5
160°	1252.1	1249.2	1248.2	1254.1	1248.2
162.5°	1267.8	1263.9	1262.9	1268.8	1261.9
165°	1280.5	1275.6	1275.6	1283.4	1274.6
167.5°	1291.3	1286.4	1285.4	1294.2	1284.4
170°	1300.1	1294.2	1295.2	1303.0	1293.2
172.5°	1306.0	1300.1	1301.1	1308.9	1298.1
175°	1309.9	1304.0	1305.0	1313.8	1302.1
177.5°	1312.8	1306.0	1307.9	1315.8	1304.0
180°	1309.9	1309.9	1309.9	1309.9	1309.9

(END OF REPORT)