

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013318

Luminaire Tested: S124RDIP-B350D1205UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013318
REPORT IS A COMBINATION OF REPORTS P999273 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B350D1205UB2750-4F0-XX-W2A-F_4000K
Description: Define 4 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6163.0 lumens
Efficiency: N/A
Efficacy: 128.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013318

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013318

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31			22
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	27	27	26			19
2	84	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22			16
3	76	67	60	55	67	60	54	50	46	42	39	33	31	29	22	20	19			14
4	70	60	52	46	62	53	47	42	41	37	33	30	27	25	19	18	16			12
5	64	53	45	40	56	47	41	36	37	32	29	27	24	21	17	16	14			10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13			9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	13	11			8
8	50	38	31	26	44	35	28	24	27	22	19	20	17	15	13	11	10			7
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9			7
10	43	32	25	21	38	29	23	19	23	18	15	17	14	12	11	9	8			6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4880	4880	4880
5°	4881	4736	4737
10°	4840	4586	4531
15°	4773	4400	4291
20°	4686	4188	4016
25°	4578	3959	3747
30°	4471	3726	3445
35°	4354	3489	3150
40°	4214	3235	2847
45°	4084	2981	2547
50°	3935	2705	2242
55°	3775	2423	1928
60°	3597	2122	1617
65°	3425	1777	1318
70°	3179	1415	1008
75°	2867	1030	705
80°	2394	633	506
85°	1797	364	279

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4084 cd/sqm

TEST NUMBER: P1013318

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.3	0.9
10°-20°	156.9	2.5
20°-30°	226.6	3.7
30°-40°	256.8	4.2
40°-50°	247.9	4.0
50°-60°	206.1	3.3
60°-70°	142.3	2.3
70°-80°	71.9	1.2
80°-90°	21.4	0.3
90°-100°	51.2	0.8
100°-110°	337.5	5.5
110°-120°	644.4	10.5
120°-130°	818.1	13.3
130°-140°	875.1	14.2
140°-150°	818.3	13.3
150°-160°	659.9	10.7
160°-170°	425.6	6.9
170°-180°	146.7	2.4
0°-30°	439.8	7.1
0°-40°	696.6	11.3
0°-60°	1150.6	18.7
0°-90°	1386.2	22.5
90°-120°	1033.1	16.8
90°-150°	3544.6	57.5
90°-180°	4777.0	77.5
0°-180°	6163.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	598	598	598	598	598	
5°	598	596	590	595	594	57
15°	569	565	554	553	550	160
25°	515	506	488	480	475	237
35°	445	430	407	392	384	278
45°	363	346	318	296	288	280
55°	275	257	227	203	194	246
65°	187	167	138	118	113	185
75°	100	82	61	50	48	105
85°	25	16	14	13	13	27
90°	4	16	25	32	35	5
95°	64	24	25	32	34	78
105°	348	354	360	371	329	364
115°	649	652	651	654	654	639
125°	912	917	914	918	919	815
135°	1132	1130	1135	1137	1140	872
145°	1305	1308	1308	1309	1312	815
155°	1431	1432	1428	1433	1429	660
165°	1509	1503	1503	1512	1502	426
175°	1544	1537	1538	1548	1534	147
180°	1544	1544	1544	1544	1544	

TEST NUMBER: P1013318

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	598.5	598.5	598.5	598.5	598.5
2.5°	600.4	598.5	593.5	598.5	598.1
5°	597.6	595.8	590.3	594.9	594.0
7.5°	593.5	591.7	584.8	588.0	586.6
10°	587.1	584.8	576.5	578.4	576.5
12.5°	578.8	576.1	566.0	566.9	564.2
15°	569.2	565.1	553.6	552.7	549.5
17.5°	558.2	552.3	539.0	536.7	532.1
20°	544.9	539.0	523.4	519.7	513.8
22.5°	530.3	523.4	506.4	500.5	495.9
25°	514.7	506.4	487.6	479.8	475.3
27.5°	498.6	488.6	468.8	459.7	453.3
30°	481.7	470.2	448.7	437.2	429.9
32.5°	463.8	450.5	428.1	414.3	407.4
35°	445.0	430.3	407.4	391.8	383.6
37.5°	425.3	410.2	385.0	368.0	359.8
40°	404.2	389.1	363.0	343.7	335.5
42.5°	384.1	368.0	340.5	320.8	312.1
45°	363.0	346.0	318.5	296.1	287.8
47.5°	341.4	324.0	295.6	272.2	263.1
50°	319.4	301.6	272.2	249.3	240.6
52.5°	297.0	279.6	249.3	225.9	216.8
55°	275.0	256.6	226.9	203.0	194.3
57.5°	253.4	234.2	204.9	180.6	174.2
60°	230.1	211.7	182.4	158.6	151.2
62.5°	209.0	189.7	159.5	137.9	132.4
65°	187.0	167.3	137.9	118.2	112.7
67.5°	164.1	145.3	117.8	100.4	94.0
70°	142.5	123.3	97.2	82.0	77.5
72.5°	119.6	102.7	78.4	66.0	61.9
75°	99.5	82.5	61.0	50.4	47.7
77.5°	78.4	63.7	45.4	38.0	37.1
80°	58.2	44.9	31.2	29.8	29.3
82.5°	40.8	28.9	22.5	21.5	21.1
85°	24.7	15.6	14.2	13.3	13.3
87.5°	10.5	6.9	6.4	6.0	6.4
90°	3.5	16.2	25.4	32.3	34.6
92.5°	17.3	15.0	24.2	31.2	31.2
95°	63.5	24.2	25.4	32.3	33.5
97.5°	121.2	146.6	25.4	31.2	32.3
100°	189.4	210.1	50.8	31.2	32.3
102.5°	265.6	279.4	293.3	33.5	33.5
105°	347.5	354.5	360.2	370.6	329.1
107.5°	422.6	426.1	434.1	439.9	444.5
110°	498.8	502.3	509.2	511.5	515.0

TEST NUMBER: P1013318

CATALOG NUMBER: S124RDIP-B350D1205UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	572.7	579.6	581.9	580.8	585.4
115°	648.9	652.4	651.2	653.5	653.5
117.5°	717.0	721.6	725.1	723.9	723.9
120°	786.3	790.9	789.8	792.1	789.8
122.5°	851.0	853.3	855.6	856.7	854.4
125°	912.1	916.8	914.5	917.9	919.1
127.5°	971.0	972.2	978.0	976.8	975.6
130°	1027.6	1028.8	1032.2	1033.4	1033.4
132.5°	1079.6	1081.9	1086.5	1087.6	1086.5
135°	1131.5	1130.4	1135.0	1137.3	1139.6
137.5°	1177.7	1177.7	1183.5	1185.8	1184.6
140°	1222.7	1225.0	1227.4	1230.8	1232.0
142.5°	1263.1	1267.8	1268.9	1271.2	1271.2
145°	1304.7	1308.2	1308.2	1309.3	1311.6
147.5°	1337.0	1344.0	1342.8	1344.0	1345.1
150°	1372.8	1377.5	1376.3	1376.3	1377.5
152.5°	1402.9	1406.3	1404.0	1406.3	1405.2
155°	1430.6	1431.7	1428.3	1432.9	1429.4
157.5°	1454.8	1454.8	1450.2	1456.0	1450.2
160°	1475.6	1472.1	1471.0	1477.9	1471.0
162.5°	1494.1	1489.5	1488.3	1495.2	1487.1
165°	1509.1	1503.3	1503.3	1512.5	1502.2
167.5°	1521.8	1516.0	1514.9	1525.2	1513.7
170°	1532.2	1525.2	1526.4	1535.6	1524.1
172.5°	1539.1	1532.2	1533.3	1542.6	1529.9
175°	1543.7	1536.8	1537.9	1548.3	1534.5
177.5°	1547.2	1539.1	1541.4	1550.6	1536.8
180°	1543.7	1543.7	1543.7	1543.7	1543.7

(END OF REPORT)